SARA-N2 series

Power-optimized NB-IoT (LTE Cat NB1) modules

The world's first NB-IoT modules

- Ultra low power consumption delivering 10+ years battery life
- Excellent extended range in buildings, underground (MCL 164 dB)
- Extended temperature range of -40 °C to +85 °C and ISO/TS16949 manufacturing
- Easy migration between u-blox 2G, 3G, and 4G modules
- Very small SARA LGA form factor for easy manufacturing



Standard







Product description

The SARA-N2 series NB-IoT modules feature extremely low power consumption in both idle and connected modes of cellular operation. They are available in a small LGA form factor and have been designed explicitly with the needs of batterypowered applications that need to communicate for long periods of time in challenging radio propagation conditions.

The modules support a comprehensive set of communication protocols with minimal signaling overhead to preserve power consumption. The feature set makes these modules ideally suited for applications where longevity of operation and reachability in poor propagation conditions are missioncritical. Smart water metering, smart gas metering, smart sensors for remote monitoring and nomadic asset tracking are perfect examples of applications where these modules could be used.

The SARA-N2 series modules target high volume, cost sensitive applications, and provide "bit pipe" communication functionalities while minimizing the customer's total cost of ownership. The modules offer easy migration from u-blox GSM (SARA-G3 series), UMTS (SARA-U2 series), and

LTE Cat 1 (LARA-R2 series) modules.

The temperature range of -40 °C to +85 °C guarantees operation in harsh environments and in very compact designs.

The modules are for global use and are certified and approved by the main regulatory bodies.

The modules are manufactured in ISO/TS 16949 certified sites, with the highest production standards and the highest quality and reliability. Each module is fully tested and inspected during production.

	SARA-N200	SARA-N201	SARA-N210	SARA-N211 [₽]	SARA-N280
	SA	SA	SA	SA	SA
Grade					
Automotive			•		
Professional Standard	•	•	•	•	•
Regions					
	EMEA/ APAC	APAC	EMEA	EMEA	S. America/ APAC
Access Technology					
LTE bands	8	5	20	8, 20	28
Data rate	NB	NB	NB	NB	NB
Interfaces					
UART	2	2	2	2	2
GPIO	2	2	2	2	2
Audio					
Digital audio					
Features					
Embedded UDP	•	•	•	•	•
Power Save Mode Rel.12	•	•	•	•	•
eDRX	•	•	•	•	•
Deep sleep mode	•	•	•	•	•
CoAP	•	•	•	•	•
FW update via serial	•	•	•	•	•
FOTA	•	•	•	•	•

A = ATEX variant available

NB = Cat NB1 (27.2 kb/s DL, 62.5 kb/s UL)

∢



SARA-N2 series



Features	
NB-loT	Cat NB1, single-tone uplink (up to 27.2 kb/s DL, 62.5 kb/s UL) 3GPP Release 13 FDD bands: – SARA-N200: band 8 – SARA-N201: band 5 – SARA-N210: band 20 – SARA-N211: bands 8, 20 – SARA-N280: band 28
Data Transfer	Non-IP based Small Data over NAS (SDoNAS) IP based SDoNAS
Network	Paging Idle and Connected DRX Deep sleep mode Power saving mode

Software features

Protocols	IPv4
	Embedded UDP/IP
	Generic Constrained Application Protocol (CoAP)
Firmware upgrade	Via UART and Over the Air

Electrical data

Power supply	3.6 V nominal, range	2.75 V to 4.2 V
Power consumption	Deep-sleep mode:	< 3 µA
	Active mode:	< 6 mA
	Rx mode:	< 46 mA
	Tx mode:	< 220 mA

Interfaces

Serial	2 UART (data and debug interfaces)
GPIO	Up to 2 GPIOs, configurable
(U)SIM	Supports 1.8 V

Package

96 pin LGA: 16.0 x 26.0 x 2.4 mm, < 3 g	

Environmental data, quality & reliability

Operating temperature	–40 °C to +85 °C	
RoHS compliant	(lead-free)	
Qualification acc	cording to ISO 16750	
Manufactured ir	ISO/TS 16949 certified production sites	

Certifications and approvals

SARA-N200	CE / RED, CCC, NCC, SRRC, NBTC, IMDA, Deutsche Telekom, China Unicom (CUCC)
SARA-N201	CCC, SRRC, China Telecom (CTCC)
SARA-N210	CE / RED, Deutsche Telekom
SARA-N211	CE / RED, NCC, ATEX, GCF, Deutsche Telekom
SARA-N280	NCC, Anatel, RCM

Support products

Evaluation kit for SARA-N200
Evaluation kit for SARA-N201
Evaluation kit for SARA-N210
Evaluation kit for SARA-N211
Evaluation kit for SARA-N280

Product variants

SARA-N200	NB-loT module for Europe / APAC; Cat NB1; band 8	
SARA-N201	NB-loT module for APAC; Cat NB1; band 5	
SARA-N210	NB-loT module for Europe; Cat NB1; band 20	
SARA-N211	NB-loT module for Europe; Cat NB1; bands 8, 20	
SARA-N280	NB-loT module for S. America / APAC; Cat NB1; band 28	

Further information

For contact information, see www.u-blox.com/contact-us.

For more product details and ordering information, see the product data sheet. $% \left({{{\left({{{{\bf{n}}}} \right)}_{i}}_{i}}} \right)$

Legal Notice:

u-blox reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. Reproduction, use, modification or disclosure to third parties of this document or any part thereof without the express permission of u-blox is strictly prohibited.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit www.u-blox.com. Copyright © 2018, u-blox AG