

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C4	REVISED ECR-23-169773	21AUG2023	M.G	D.Z

- 1.APPLICABLE CONTACT P/N
REC CONTACT:177915-(20-16AWG)
177914-(26-22AWG)
- 2.MATING CONN.P/N
CAP HSG:177912-(PANEL MOUNT)
TAB CONTACT:177917-(20-16AWG)
177916-(26-22AWG)
- 3.APPLICABLE PLATE P/N:177921
- 4.INSTRUCTION SHEET:411-5638

5.PART 6-177904-1 COMPLY WITH GLOW WIRE
REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL
SUPPORTING A CURRENT-CARRYING CONNECTION
DETAILED IN IEC 60335-1, SECTION 30(GWT)

6.PART 177904-7 COMPLY WITH HOT WIRE
REQUIREMENT, PA66,UL 94V-0,HOT WIRE IGNITION
(HWI)VERSION ARE MOLDED IN A RESIN THAT
COMPLIES WIHT TE HOT WIRE IGNITION TEST
109-32026 AND ARE RECOMMENDED FOR USE WITH
HWI HOUSING THAT ALSO COMPLY






7.TOLERANCE REQUEST

<10 ±0.2

10-30 ±0.25

>30 ±0.3

8 SEE TABLE 1



8 TABLE 1

TRADE MARK	MANUFACTURING PLACE
—AMP OR AMP	JAPAN
—+AMP OR AMP	CHINA
AMP OR AMP	KOREA

LOCK TYPE III	NATURAL	10	5-177904-1
LOCK TYPE I	NATURAL	10	177904-7
LOCK TYPE I	NATURAL	10	6-177904-1
	BLUE	10	177904-6
	YELLOW	10	177904-4
	NATURAL	10	177904-1
LOCK TYPE	HOUSING COLOR	POS.	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. YAMASAKI 22.NOV'95	 TE Connectivity			
DIMENSIONS: mm		CHK M. SHINDO 22.NOV'95				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD H. TAGUCHI 22.NOV'95	NAME AMP PDL CONN. 3.96MM PITCH PLUG HOUSING 10 POS (DBL ROW) -			
		PRODUCT SPEC 108-5410				
		APPLICATION SPEC 114-5175	SIZE A2	CAGE CODE -	DRAWING NO C=177904	RESTRICTED TO -
		MATERIAL 6/6 NYLON (UL94V-0)	FINISH -	WEIGHT -	CUSTOMER DRAWING	
			SCALE 3:1	SHEET 1 OF 1	REV C4	