



# **Product Specification**

### **Ningbo East Electronics Limited**

NO. 88 East Jinhui Road, Yinzhou Ningbo 315100, P.R. China http://www.east-mingtao.com

Product Name:	Self-Driven Piezo Transducer
Part Number:	TFM-36
Version:	1.02
Date:	2019-8-20
Note:	


### East is an ISO 9001, IATF16949 and ISO 14001Certified Company

### **Revision History**

Rev.	Description	Author/Date	Checked By	Approver
1.02	Quality management system revised	汤礼东 2019-8-20	吕文斌	王建成
1.01	Quality Certificate Symbol revised	刘宁 2015-2-12	汤礼东	王建成
1.0	Released	汤礼东 2011-7-30	张春雷	王建成

#### 1. Part Number TFM-36

### 2. Dimension Drawing (Unit: mm)




### 3. Specification

No.	Item	Specification
3-1	Min. Sound Pressure Level	106dB/12V <sub>DC</sub> /10cm
3-2	Rate Voltage	12V <sub>DC</sub>
3-3	Operating Voltage	3~18V <sub>DC</sub>
3-4	Max. Consumption	15mA/12V <sub>DC</sub>
3-5	Oscillating Frequency	3.2± 0.3kHz
3-6	Tone Nature	Continuous
3-7	Operating Temperature	-20~+60°C
3-8	Storage Temperature	-20~+70°C
3-9	Case Material /Color	ABS(PA-757)/Black
3-10	Weight	8.4g
3-11	Pin Strength	More Then 10N

#### NOTES:

Test should be made under the conditions of room temperature  $(20\pm10^{\circ}\text{C})$ , normal humidity  $(60\pm20\%)$  and normal atmospheric pressure. In this case, however, that the judgment is questionable, the test conditions are to be changed to room temperature  $20\pm2^{\circ}\text{C}$ , relative humidity  $60\sim70\%$  and normal atmospheric pressure

# **4.**Typical Frequency Response Curve



**Note:** Distance 10 cm


## 5. Reliability Test

No.	Item	Method of Test	Tolerance after Testing	
5-1	Operating Temperature	-20~60°C	Sound pressure level	
5-2	Storage in high temperature	Storage in +70°C test box 96 hours then exposed to the room temperature for 2 hours	initial value ±10dB  Max. consumption value ±20%  Capacitance value ±20%	
5-3	Storage in low temperature	Storage in -20°C test box 96 hours then exposed to the room temperature for 2 hours		
5-4	Life test in the room temperature	Operate the product continuously 5 seconds on 5 seconds off 300 hours at rated voltage		
5-5	Temperature / humidity cycle test	Storage in +40°C, 93±3%RH test box 96 hours then exposed to the room temperature for 2 hours		
5-6	Temperature (high and low) cycle test	Conduct the test for 5 cycles without applying power then expose to the room temperature for 2 hours.(See Figure 5-6)		
5-7	Vibration test	Conduct the test for the directions of X Y and Z for 0.5 hour each (total 1.5 hours). To-and Fri sweep time(from 10 to 55Hz and then 55 to 10) under single amplitude of 0.75mm is 3 minute, then expose to the room temperature for 2 hours		
	East Electronics Limited	minute, then expose to the room temperature for 2 hours		


5-8	Drop test	Drop a product naturally from the height of 700mm onto the surface of 100mm thick wooden board. Two directions: upper and side of the product are to be applied for this drop test once respectively		
5-9	Soldering heat resistance test	Dip the connecting pins in soldering at 260±5°C for 10±1 seconds		
5-10	Test of soldering	Dip the connecting pins in soldering at 230±5°C for 3±0.5 seconds	Solder shall be attached around over 95% of the dipped portion	

**NOTE**: The pins are allowed to deform after drop test.

Figure 5-6




### **6. Electrical Testing Method**



S.P.L.M	Sound Pressure Level Meter	
T.S	Testing Sample	
F.C	Frequency Counter	
T.C	Test Circuit	
P.S	Power Supply	
A.V.M	AC Voltage Meter	
A.A.M	AC Ampere Meter	

### TC:



### 7. Packing Information

Packing: 672pcs per export carton Carton Size: 47× 30.5× 35 cm

G. Weight: 8.7 kgs N. Weight: 5.7 kgs