



Connectors > Terminal Blocks & Strips > Barrier Strips



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **14.5 mm [.571 in]**

Number of Rows: **1**

Operating Voltage: **600 V**

Features

Product Type Features

Block Style	None
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Levels	1
Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Quick Connect Tab Plating Material	Tin
Primary Product Color	Natural
Product Orientation	Right Angle



Contact Features

Contact Base Material	Brass
Contact Current Rating (Max)	65 A

Mechanical Attachment

Screw Plating Material	Zinc Chromate
Screw Material	Steel
Mounting Options	4.3mm Diameter Mounting Holes
Thread Size	M3.5
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Polyamide 6
Centerline (Pitch)	14.5 mm[.571 in]

Dimensions

Product Length	25.7 mm
Wire Size	2 – 14 mm²

Usage Conditions

Operating Temperature Range	-35 – 100 °C[-31 – 212 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	120
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)
SVHC > Threshold:
Pb (3% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1776312-2
TSB200002=EUROPA TM-BLK,14.5MM




TE Part # 1776315-2
TSB200002KDS=EUROPA BL,14.5MM

Customers Also Bought



TE Part #1-163084-0
SPEC. PLATED



TE Part #1734829-5
1.25 WTB HDR DIP, 5 POS




TE Part #2560-201-2031L
CONT PIN



TE Part #8-1879028-8
RN 0805 432K 0.1% 10PPM 1K RL





TE Part #5205980-5
SCREW RETAINER KIT,BULK PACK



TE Part #2-2176337-5
CRGCQ 0402 1K0 1%



TE Part #6-2176337-1
CRGCQ 0402 1M0 1%



TE Part #2129320-3
Mini Displayport Reverse Offset



TE Part #CSJ-SGFB-200-MHF4
SMA to MHF4 200mm 0.81 OD

Documents

Product Drawings

TSB200002DS=EUROPA T-BL,14.5MM

English

CAD Files

Customer View Model

ENG_CVM_1776313-2_O1.3d_igs.zip

English

Customer View Model

ENG_CVM_1776313-2_O1.3d_stp.zip

English

Customer View Model

ENG_CVM_1776313-2_O1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_1776313-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1776313-2_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1776313-2_O.2d_dxf.zip

English

3D PDF

3D

1776313-2

Barrier Strips, Wire-to-Wire, 2 Position, 14.5 mm [.571 in] Centerline, 1 Row,
Operating Voltage 600 V, 14 – 6 AWG Wire Size, 2 – 14 mm² Wire Size



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROPA TERMINAL BLOCKS

English