



Small Signal Schottky Diodes

**DESIGN SUPPORT TOOLS** click logo to get started**MECHANICAL DATA****Case:** SOD-323**Weight:** approx. 4.3 mg**Packaging codes/options:**

18/10K per 13" reel (8 mm tape), 10K/box

08/3K per 7" reel (8 mm tape), 15K/box

FEATURES

- For general purpose applications
- The SD101 series is a metal-on-silicon Schottky barrier device which is protected by a PN junction guarding
- The low forward voltage drop and fast switching make it ideal for protection of MOS devices, steering, biasing and coupling diodes for fast switching and low logic level applications
- AEC-Q101 qualified available
- Base P/N-E3 - RoHS-compliant, commercial grade
- Base P/N-HE3 - RoHS-compliant, AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

**RoHS**
COMPLIANT**PARTS TABLE**

PART	ORDERING CODE	CIRCUIT CONFIGURATION	TYPE MARKING	REMARKS
SD101AWS	SD101AWS-E3-08 or SD101AWS-E3-18	Single	SA	Tape and reel
	SD101AWS-HE3-08 or SD101AWS-HE3-18			
SD101BWS	SD101BWS-E3-08 or SD101BWS-E3-18	Single	SB	
	SD101BWS-HE3-08 or SD101BWS-HE3-18			
SD101CWS	SD101CWS-E3-08 or SD101CWS-E3-18	Single	SC	
	SD101CWS-HE3-08 or SD101CWS-HE3-18			

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT
Repetitive peak reverse voltage		SD101AWS	V_{RRM}	60	V
		SD101BWS	V_{RRM}	50	V
		SD101CWS	V_{RRM}	40	V
Power dissipation (infinite heatsink) ⁽¹⁾			P_{tot}	150	mW
Forward continuous current			I_F	30	mA
Maximum single cycle surge	10 μs square wave		I_{FSM}	2	A

Note⁽¹⁾ Valid provided that electrodes are kept at ambient temperature**THERMAL CHARACTERISTICS** ($T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Thermal resistance junction to ambient air ⁽¹⁾		R_{thJA}	650	K/W
Junction temperature ⁽¹⁾		T_j	125	$^{\circ}\text{C}$
Operating temperature range		T_{op}	-55 to +125	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-65 to +150	$^{\circ}\text{C}$

Note⁽¹⁾ Valid provided that electrodes are kept at ambient temperature



ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Reverse breakdown voltage	$I_R = 10\text{ }\mu\text{A}$	SD101AWS	$V_{(BR)}$	60			V
		SD101BWS	$V_{(BR)}$	50			V
		SD101CWS	$V_{(BR)}$	40			V
Leakage current	$V_R = 50\text{ V}$	SD101AWS	I_R			200	nA
	$V_R = 40\text{ V}$	SD101BWS	I_R			200	nA
	$V_R = 30\text{ V}$	SD101CWS	I_R			200	nA
Forward voltage drop	$I_F = 1\text{ mA}$	SD101AWS	V_F			410	mV
		SD101BWS	V_F			400	mV
		SD101CWS	V_F			390	mV
	$I_F = 15\text{ mA}$	SD101AWS	V_F			1000	mV
		SD101BWS	V_F			950	mV
		SD101CWS	V_F			900	mV
Junction capacitance	$V_R = 0\text{ V}, f = 1\text{ MHz}$	SD101AWS	C_D			2.0	ns
		SD101BWS	C_D			2.1	ns
		SD101CWS	C_D			2.2	ns
Reverse recovery time	$I_F = I_R = 5\text{ mA}$, recover to $0.1\text{ }I_R$		t_{rr}			1	ns

TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 1 - Typical Variation of Forward Current vs. Forward Voltage




Fig. 3 - Typical Variation of Reverse Current at Various Temperatures




Fig. 2 - Typical Forward Conduction Curve






Fig. 4 - Typical Capacitance Curve as a Function of Reverse Voltage



PACKAGE DIMENSIONS in millimeters (inches): SOD-323



Footprint recommendation:



Document no.: S8-V-3910.02-001 (4)
Created - Date: 24.August.2004
Rev. 6 - Date: 23.Sept.2016
17443



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.