



Sensors > Temperature Sensors > NTC Thermistors Sensors & Probes > NTC Thermistors



Discrete NTC Sensor Type: **NTC Thermistor**

Wire Connection: **Open End**

Discrete NTC Wire Length: **56 mm**

Resistance (at 25°C): **10 kΩ**

Tolerance Resistance: **± .88 %**

Features

Product Type Features

Discrete NTC Sensor Type	NTC Thermistor
Tolerance β-Value	±.5 %

Body Features

Wire Connection	Open End
-----------------	----------

Dimensions

Discrete NTC Wire Length	56 mm
--------------------------	-------

Usage Conditions

Resistance (at 25°C)	10 kΩ
Tolerance Resistance	± .88 %
Discrete NTC Ambient Temperature Range	-40 – 125 °C
Temperature Accuracy	± .2 from 0 – 70 °C

Operation/Application

Wire/Cladding Connection	30 AWG Silver Plated Copper, Black PVDF Insulated .019" OD
--------------------------	--

Packaging Features

Discrete NTC Package	Miniature Epoxy Discrete
----------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-NTC0065
Thermistor Probe — Micro BetaCHIP (MCD)

TE Part # GA100K6MBD1
MBD9-MBD

TE Part # GA10K3MRBD1
MBD9-MRBD

Customers Also Bought

TE Part #T4162123005-001
RPC-M12-5MS-0.5SH-M12-5FS-PUR

TE Part #61116-7
CMNL PIN 24-18 AUNIBR

TE Part #1423673-1
W51-A121B1-5=CKTBKR,THERM, ROCK

TE Part #2000973-1
Connector Kit, Rcpt, Backplane, MT, V66.1



TE Part #3979470001
RPS-8-4/2.0-9



TE Part #1-1617128-2
JMSCD-26XM = M39016/16-036M



TE Part #F60401-000
B-155-06-35-22-5



TE Part #2-2176238-0
CPF A 0805 120R 0.1% 25PPM 5K RL



TE Part #1-2176455-3
CPF 0402 5R62 0.1% 25ppm 1K RL



TE Part #2294585-1
CONN KIT, PLUG,MODULE, V66.1,
ROUND SP

Documents

Datasheets & Catalog Pages

MBD_10K3MBD1

English