

[Connectors](#) > [Connector Accessories](#) > [Connector Backshells](#)Connector Backshell Product Type: **Backshell**Primary Product Material: **66Nylon**Operating Temperature Range: **-40 – 130 °C**

Features

Product Type Features

Connector Backshell Product Type	Backshell
----------------------------------	-----------

Body Features

Cable Exit Angle	90°
------------------	-----

Primary Product Color	Black
-----------------------	-------

Primary Product Material	66Nylon
--------------------------	---------

Usage Conditions

Operating Temperature (Max)	130 °C
-----------------------------	--------

Operating Temperature Range	-40 – 130 °C
-----------------------------	--------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)
--	---

Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1703768-1
14POS,AMP MCP1.5K,SOCK HSG,
ASSY,10POS



TE Part # 1703768-3
14POS,AMP MCP1.5K,SOCK HSG,
ASSY



TE Part # 1-1703963-1
16POS,AMP MCP1.5K,REC HSG,ASSY,
SEALED




TE Part # 1703768-2
14POS,AMP MCP1.5K,SOCK HSG,
ASSY,12POS




TE Part # 1703768-4
14POS,AMP MCP1.5K,SOCK HSG,ASS

Customers Also Bought




TE Part #964408-1
08P.JR-TIMER HSG.



TE Part #368539-1
070 MLC PLUG HSG 6P(D.B)



TE Part #2-1355123-7
MQS BU-GEH 60P



TE Part #2141892-2
JPT A REC 2.8 Contact SRC Sn



TE Part #0989076025
RBK-ILS-125-NR2-0-35MM



TE Part #1-1703963-1
16POS,AMP MCP1.5K,REC HSG,ASSY,
SEALED



TE Part #2098866-1
PLUG ASSY, 96P GPECIII KEY H L



TE Part #2363714-2
REC CONN CVR ASSY,2POS,DT,
180DEG



TE Part #8-1452423-7
96 POS. PCM CPNNECTOR



TE Part #C616253001
55E0219-0.75-9(B01)

Documents

Product Drawings

ADAPTER 90?FOR 10-14POS. SOCKET

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1718284-2_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1718284-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1718284-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Instruction Sheets

Instruction Sheet (non U.S.)

German