

EMIPAK 1B PressFit Power Module 600 V Double PFC MOSFET, 25 A



EMIPAK 1B
(package example)



RoHS
COMPLIANT

FEATURES

- E series Power MOSFET
- MOAT and SiC diode technology
- Exposed Al_2O_3 substrate with low thermal resistance
- Low input capacitance
- Low switching and conduction losses
- Ultra low gate charge Q_g
- Low internal inductances
- Qualified using AQG324 guideline as reference
- PressFit pins locking technology
PATENT(S): www.vishay.com/patents
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

DESCRIPTION

The EMIPAK 1B package is easy to use thanks to the PressFit pins. The exposed substrate provides improved thermal performance.

The optimized layout also helps to minimize stray parameters, allowing for better EMI performance.

PRIMARY CHARACTERISTICS	
Q1 - Q4 MOSFET	
V_{DSS}	600 V
$R_{DS(on)}$ typical at $I_C = 25$ A	59 m Ω
I_D at $T_{SINK} = 37$ °C	25 A
Da1 - Da2 DIODE	
V_{RRM}	1200 V
V_{FM} typical at 20 A	1.29 V
I_F at $T_{SINK} = 83$ °C	20 A
D1 - D4 SILICON CARBIDE CLAMP DIODE	
V_{RRM}	600 V
V_{FM} typical at 10 A	1.72 V
I_F at $T_{SINK} = 62$ °C	10 A
Package	EMIPAK 1B
Circuit configuration	Double interleaved bridgless PFC (4 x channels) with individual return diodes
Type	Modules - MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_J = 25$ °C unless otherwise noted)				
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Operating junction temperature	T_J		150	°C
Storage temperature range	T_{Stg}		-40 to +150	
RMS isolation voltage	V_{ISOL}	$T_J = 25$ °C, all terminals shorted, $f = 50$ Hz, $t = 1$ s	3500	V
Q1 - Q4 MOSFET				
Drain to source voltage	V_{DSS}		600	V
Gate to source voltage	V_{GS}		± 20	
Pulsed drain current	I_{DM}	$V_{GS} = 10$ V	85	A
Continuous drain current	I_D	$T_{SINK} = 25$ °C	26	A
		$T_{SINK} = 80$ °C	20	
Power dissipation	P_D	$T_{SINK} = 25$ °C	104	W
		$T_{SINK} = 80$ °C	58	
Single pulse avalanche energy	E_{AS}	$L = 10$ mH, $I_{AS} = 19$ A, $T_J = 25$ °C	1800	mJ
Pulsed source current (body diode)	I_{SM}		85	A

PATENT(S): www.vishay.com/patents

This Vishay product is protected by one or more United States and international patents.

**ABSOLUTE MAXIMUM RATINGS** ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DA1 - DA2 DIODE				
Cathode to anode voltage	V_{RRM}		1200	V
Single pulse forward current	I_{FSM}		230	A
Diode continuous forward current	I_F	$T_{SINK} = 25\text{ }^{\circ}\text{C}$	29	A
		$T_{SINK} = 80\text{ }^{\circ}\text{C}$	21	
Power dissipation	P_D	$T_{SINK} = 25\text{ }^{\circ}\text{C}$	70	W
		$T_{SINK} = 80\text{ }^{\circ}\text{C}$	39	
D1 - D4 SILICON CARBIDE CLAMP DIODE				
Cathode to anode voltage	V_{RRM}		600	V
Single pulse forward current	I_{FSM}	10 ms sine or 6 ms rectangular pulse, $T_J = 25\text{ }^{\circ}\text{C}$	80	A
Diode continuous forward current	I_F	$T_{SINK} = 25\text{ }^{\circ}\text{C}$	12	A
		$T_{SINK} = 80\text{ }^{\circ}\text{C}$	9	
Power dissipation	P_D	$T_{SINK} = 25\text{ }^{\circ}\text{C}$	38	W
		$T_{SINK} = 80\text{ }^{\circ}\text{C}$	21	

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Q1 - Q4 MOSFET						
Drain to source breakdown voltage	BV _{DSS}	V _{GS} = 0 V, I _D = 500 μA	600	-	-	mΩ
Drain to source on resistance	R _{DS(on)}	V _{GS} = 10 V, I _D = 25 A	-	59	71	
		V _{GS} = 10 V, I _D = 25 A, T _J = 150 °C	-	140	-	
Gate threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	1.8	2.6	4.4	V
Temperature coefficient of threshold voltage	ΔV _{GS(th)} /ΔT _J	V _{DS} = V _{GS} , I _D = 250 μA (25 °C to 125 °C)	-	-9.7	-	mV/°C
Forward transconductance	g _{fs}	V _{DS} = 20 V, I _D = 25 A	-	29	-	S
Transfer characteristics	V _{GS}	V _{DS} = 20 V, I _D = 25 A	-	5.1	-	V
Zero gate voltage drain current	I _{DSS}	V _{GS} = 0 V, V _{DS} = 600 V	-	0.3	5	μA
		V _{GS} = 0 V, V _{DS} = 600 V, T _J = 150 °C	-	19	-	
Gate to source leakage current	I _{GSS}	V _{GS} = ± 20 V, V _{DS} = 0 V	-	-	± 150	nA
Q1 - Q4 BODY DIODE						
Source-to-drain voltage drop	V _{SD}	I _{SD} = 25 A, V _{GS} = 0 V	-	0.9	1.32	V
Da1 - Da2 DIODE						
Forward voltage drop	V _{FM}	I _F = 20 A	-	1.29	1.90	V
		I _F = 20 A, T _J = 150 °C	-	1.26	-	
Breakdown voltage	V _{BR}	I _R = 500 μA	1200	-	-	V
Reverse leakage current	I _{RM}	V _R = 1200 V	-	1.0	100	μA
		V _R = 1200 V, T _J = 150 °C	-	900	-	
D1 - D4 SILICON CARBIDE CLAMP DIODE						
Forward voltage drop	V _{FM}	I _F = 10 A	-	1.72	1.98	V
		I _F = 10 A, T _J = 150 °C	-	2.21	-	
Breakdown voltage	V _{BR}	I _R = 500 μA	600	-	-	V
Reverse leakage current	I _{RM}	V _R = 600 V	-	0.2	100	μA
		V _R = 600 V, T _J = 150 °C	-	1.4	-	



SWITCHING CHARACTERISTICS (T _J = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Q1 - Q4 MOSFET WITH D1 - D4 CLAMP DIODE						
Total gate charge (turn-on)	Q _g	I _D = 24 A	-	147	-	nC
Gate to source charge (turn-on)	Q _{gs}	V _{DS} = 480 V	-	36	-	
Gate to drain charge (turn-on)	Q _{gd}	V _{GS} = 10 V	-	60	-	
Turn-on delay time	t _{d(on)}	I _D = 25 A V _{DD} = 300 V V _{GS} = 10 V R _g = 4.7 Ω, L = 500 μH	-	82	-	ns
Rise time	t _r		-	23	-	
Turn-off delay time	t _{d(off)}		-	109	-	
Fall time	t _f		-	9	-	
Turn-on delay time	t _{d(on)}	I _D = 25 A V _{DD} = 300 V V _{GS} = 10 V R _g = 4.7 Ω, L = 500 μH, T _J = 125 °C	-	83	-	ns
Rise time	t _r		-	26	-	
Turn-off delay time	t _{d(off)}		-	111	-	
Fall time	t _f		-	22	-	
Input capacitance	C _{iss}	V _{GS} = 0 V V _{DS} = 100 V f = 1 MHz	-	4810	-	pF
Output capacitance	C _{oss}		-	230	-	
Reverse transfer capacitance	C _{rss}		-	5	-	
Reverse bias safe operating area	RBSOA	T _J = 150 °C, I _D = 50 A, V _{DD} = 400 V, V _P = 600 V, R _g = 4.7 Ω, V _{GS} = +10 /0 V				
Q1 - Q4 BODY DIODE						
Diode reverse recovery time	t _{rr}	V _R = 30 V, T _J = 25 °C I _S = 30 A dI/dt = 100 A/μs	-	500	-	ns
Diode reverse recovery current	I _{rr}		-	41	-	A
Diode reverse recovery charge	Q _{rr}		-	10.5	-	μC
D1 - D4 SILICON CARBIDE CLAMP DIODE						
Total capacitive charge	Q _C	V _R = 600 V I _F = 10 A dI/dt = 500 A/μs	-	30	-	nC

INTERNAL NTC - THERMISTOR SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUE	UNITS
Resistance	R_{25}	$T_C = 25\text{ }^{\circ}\text{C}$	5000	Ω
	R_{100}	$T_C = 100\text{ }^{\circ}\text{C}$	$493 \pm 5\%$	
B-value	$B_{25/50}$	$R_2 = R_{25} \exp. [B_{25/50}(1/T_2 - 1/(298.15\text{ K}))]$	$3375 \pm 5\%$	K
Maximum operating temperature			220	$^{\circ}\text{C}$
Dissipation constant			2	$\text{mW}/^{\circ}\text{C}$
Thermal time constant			8	s

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNITS
Q1 - Q4 MOSFET - Junction to sink thermal resistance (per switch) ⁽¹⁾	R_{thJS}	-	1.00	-	$^{\circ}\text{C}/\text{W}$
Da1 - Da2 DIODE - Junction to sink thermal resistance (per diode) ⁽¹⁾		-	1.48	-	
D1 - D4 SILICON CARBIDE DIODE - Junction to sink thermal resistance (per diode) ⁽¹⁾		-	2.76	-	
Case to sink thermal resistance (per module) ⁽¹⁾		-	0.1	-	
Mounting torque (M4)		2	-	3	Nm
Weight		-	28	-	g

Note

⁽¹⁾ Mounting surface flat, smooth, and greased, $\lambda_{grease} = 0.67\text{ W/mK}$




Fig. 1 - Maximum Continuous Drain Current vs. Sink Temperature




Fig. 4 - Typical Drain-to-Source On-Resistance vs. Temperature




Fig. 2 - Typical Drain to Source Current Output Characteristics at $T_J = 25\text{ °C}$




Fig. 5 - Typical Transfer Characteristics




Fig. 3 - Typical Drain to Source Current Output Characteristics at $T_J = 125\text{ °C}$




Fig. 6 - Typical Gate Threshold Voltage Characteristics




Fig. 7 - Typical Drain-State Resistance vs. Gate-to-Source Voltage




Fig. 10 - Typical Turn-off Switching Time vs. I_D
 $V_{DD} = 300\text{ V}$, $R_g = 4.7\Omega$, $V_{GS} = \pm 10\text{ V}$, $L = 500\text{ }\mu\text{H}$


Fig. 8 - Typical Body Diode Source-to-Drain Current Characteristics




Fig. 11 - Typical Turn-on Switching Time vs. I_D
 $V_{DD} = 300\text{ V}$, $R_g = 4.7\Omega$, $V_{GS} = \pm 10\text{ V}$, $L = 500\text{ }\mu\text{H}$


Fig. 9 - Typical Zero Gate Voltage Drain Current




Fig. 12 - Power Dissipation Curve




Fig. 13 - Safe Operating Area




Fig. 16 - Maximum Da1-Da2 Diode Continuous Forward Current vs. Sink Temperature




Fig. 14 - Reverse BIAS SOA




Fig. 17 - Typical Da1-Da2 Diode Reverse Leakage Current




Fig. 15 - Typical Da1-Da2 Diode Forward Characteristics




Fig. 18 - Typical D1-D4 Clamp Diode Forward Characteristics




Fig. 19 - Maximum D1-D4 Clamp Diode Continuous Forward Current vs. Sink Temperature




Fig. 20 - Typical D1-D4 Clamp Diode Reverse Leakage Current




Fig. 21 - Maximum Thermal Impedance Z_{thJS} Characteristics - (Q1-Q4 MOSFET)




Fig. 22 - Maximum Thermal Impedance Z_{thJS} Characteristics - (Da1-Da2 Diode)




Fig. 23 - Maximum Thermal Impedance Z_{thJS} Characteristics - (D1-D4 Clamp Diode)


ORDERING INFORMATION TABLE

Device code


VS-	EN	Z	025	C	60	N
------------	-----------	----------	------------	----------	-----------	----------

1 2 3 4 5 6 7

- 1** - Vishay Semiconductors product
- 2** - Package indicator (EN = EMIPAK 1B)
- 3** - Circuit configuration (Z = Double interleaved bridgless PFC (4 x channels) with individual return diodes)
- 4** - Current rating (025 = 25 A)
- 5** - Switch die technology (C = PowerMOS)
- 6** - Voltage rating (60 = 600 V)
- 7** - Diode die technology

CIRCUIT CONFIGURATION		
CIRCUIT	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Double interleaved bridgless PFC (4 x channels) with individual return diodes	Z	


PACKAGE



LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95558
Application Note	www.vishay.com/doc?95580

EMIPAK-1B PressFit

DIMENSIONS in millimeters





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.