

201088-1

✓ ACTIVE

AMP


TE Internal #: 201088-1

Rectangular Connector Hardware, Jackscrew Kit, Turnable, Female

Jackscrew, 42 / 104 / 50 Position, -55 – 150 °C [-67 – 302 °F]

[View on TE.com >](#)

Connectors &gt; Rectangular Connectors &gt; Rectangular Connector Accessories &gt; Rectangular Connector Hardware

Connector Hardware Type: **Jackscrew Kit**Jackscrew Type: **Turnable**Jackscrew Style: **Female**Number of Positions: **6, 12, 14, 15, 16, 20, 26, 28, 34, 41, 42, 50, 75, 104**Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**

## Features

### Configuration Features

Number of Positions	6, 12, 14, 15, 16, 20, 26, 28, 34, 41, 42, 50, 75, 104
---------------------	--

### Body Features

Thread Lead Type	Single
Primary Product Material	Stainless Steel, Zinc Alloy

### Mechanical Attachment

Primary Product Plating Finish	Clear Chromate
Strain Relief	Without
Mounting Hardware	Jackscrew Pin and Jackscrew Tip Female
Thread Size	6-32 [M3.5 x .6]
Connector Hardware Type	Jackscrew Kit
Jackscrew Type	Turnable
Jackscrew Style	Female

### Dimensions

Product Width	7.92 mm [.312 in]
---------------	-------------------

Product Length	43 mm[1.693 in]
----------------	-----------------

Product Height	7.92 mm[.312 in]
----------------	------------------

### Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

### Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Bag
------------------	-----

### Other

Connector Accessory Comment	Two required., Use turnable jackscrews on mating housings when mating to grounding block.
-----------------------------	---

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 201087-1  
SERIES "M" JACKSCREW - MALE AS

## Customers Also Bought



TE Part #796291-1  
SEALED CPC,SER1,23-24,FR RCPT



TE Part #207052-3  
CPC Sealing Kits/Accessories



TE Part #8-31895-1  
PIDG R 22-16COMM 22-18MIL 5/16



TE Part #205690-2  
SOC. BLOCK 28 POS. SPL.



TE Part #350690-1  
UMNL PIN 24-18 PTPBR L/P



TE Part #643030-1  
05P UMNL STR/REL



TE Part #350781-1  
06P UMNL CAP HSG



TE Part #111451-3  
LATCH,UNIV I/O



TE Part #111547-3  
016 UNIV I/O STRAIN RELIEF

## Documents

### Product Drawings

[SERIES "M" JACKSCREW-ASSY. FEMA](#)

English

### CAD Files

[Customer View Model](#)

[ENG\\_CVM\\_201088-1\\_K.3d\\_igs.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_201088-1\\_K.3d\\_stp.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_201088-1\\_K.2d\\_dxf.zip](#)

English

[3D PDF](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201088-1\\_E.3d\\_igs.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201088-1\\_E.3d\\_stp.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201088-1\\_E.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[M\\_SERIES\\_PIN\\_AND\\_SOCKET\\_CONNECTORS](#)

English