



Terminals & Splices > Spade Terminals > AMPOWER Terminal, 2 Stud Holes



Spade Terminal Type: Rectangular Tongue Terminal

Wire Size: 450000 – 550000 CMA

Stud Size: 3/8

Stud Diameter: 9.91 mm [.39 in]

[All AMPOWER Terminal, 2 Stud Holes \(25\)](#)

Features

Product Type Features

Terminal Features	Inspection Slot
Stud Size	3/8
Sealable	No

Configuration Features

Number of Holes	2
-----------------	---

Body Features

Product Weight	220.151 g
----------------	-----------

Contact Features

Spade Terminal Type	Rectangular Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	450000 – 550000 CMA
Stud Diameter	9.91 mm[.39 in]



Tongue Thickness	5.08 mm[.2 in]
Product Length	102.9 mm[4.051 in]
Barrel Inside Diameter	24.92 mm[.981 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Other

Terminals & Splices Comment	Electrodeposited Tin Plate per MIL-T-10727.
-----------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46755-2
HYP8 AMPPOWER 500MCM DIE SET

Also in the Series | AMPPOWER



Busbar Connectors(13)




Knife Disconnects(14)




PCB Headers & Receptacles(2)



Power Cable Assemblies(7)




Power Contacts(1)



Quick Disconnects(1)



Rectangular Power Connectors(6)



Spade Terminals(139)



Splices(39)



Customers Also Bought



TE Part #206137-1
23-7 RECEPT STD SEX



TE Part #2-36158-1
PIDG 16-14 R 6; TAPE



TE Part #326005
AMPPOWER Lug Crimp Terminal, 1 Stud Hole




TE Part #35184
TERMINAL,SOLIS R 2 3/8



TE Part #121727-000
HT-SCE-1K-3/8-2.0-9




TE Part #321878
TERMINAL,SOLIS R 4/0 3/8



TE Part #324487
SPARE WIRE CAP,YEL .150-.210 INS.



TE Part #CR0178-000
CWT-7-W116-9



TE Part #1-1618060-0
1100-42X=RELAY, OVERCURRENT

Documents

Product Drawings

TERMINAL,AMPOWER 500MCM 3/8

English

CAD Files

Customer View Model

ENG_CVM_CVM_326808_Z.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_326808_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_326808_Z.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
AMPOWER Terminals and Splices Flyer
English

Product Environmental Compliance
Product Compliance
English
Product Compliance
English

Agency Approvals
UL Report
English