

1-208979-4**✓ ACTIVE****AMP**


TE Internal #: 1-208979-4

Panel & PCB Outlets, Wire & Cable, 15 A, White, 14 AWG / 12

AWG Wire Size, Nylon, Height 1.06 in [26.9 mm], Width 1.06 in [26.9 mm]

[View on TE.com >](#)

Connectors > Power Connectors > Panel & PCB Outlets

Connector System: **Cable-to-Panel**Number of Positions: **3**Centerline (Pitch): **12.7 mm [.5 in]**Connector & Contact Terminates To: **Wire & Cable**Contact Current Rating (Max): **15 A**

Features

Product Type Features

| | |
|-----------------------------------|----------------|
| Connector System | Cable-to-Panel |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 3 |
|---------------------|---|

Body Features

| | |
|----------------|-------|
| Cover Material | Nylon |
| Cover Color | Black |

Contact Features

| | |
|------------------------------|-------|
| Contact Base Material | Brass |
| Contact Current Rating (Max) | 15 A |

Termination Features

| | |
|------------------------------------|------------|
| Termination Method to Wire & Cable | FASTON Tab |
|------------------------------------|------------|

Mechanical Attachment

| | |
|-------------------------|-------------|
| Connector Mounting Type | Panel Mount |
|-------------------------|-------------|

Housing Features

| | |
|--------------------|-----------------|
| Centerline (Pitch) | 12.7 mm [.5 in] |
| Housing Color | White |

Housing Material

Nylon

Dimensions

Wire Size

12 AWG, 14 AWG

Product Height

26.9 mm[1.06 in]

Product Width

26.9 mm[1.06 in]

Product Depth

30.3 mm[1.19 in]

Usage Conditions

Operating Temperature Range

-40 – 110 °C[-40 – 230 °F]

Operation/Application

Circuit Application

Power

Other

Power Connectors Comment

Unassembled receptacle kit with cover.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUL 2021
(219)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 62531-1
205 FASTON TAB 18-14 AWG TPBR



TE Part # 796285-1
HOUSING,CONV OUTLET,DUMMY

Customers Also Bought



TE Part #HD16-6-96S
PLG, 6P, GRY, N, THRD, 16



TE Part #HDP24-24-31SE
DEUTSCH HDP20 Housings



TE Part #DT06-4S-P012
PLG, 4P, BLK, N, SEAL RET



TE Part #DRC24-BT
BOOT, 24P, 16SZ, PLG/REC, ST, BLK



TE Part #HD34-24-16PN-059
REC,16P,AL,N, CBL CLMP BT, DRAIN, 12,P,MC



TE Part #DRC12-24PB
REC, 24P, BLK, N, FLANGE, B



TE Part #1060-20-0222
PIN, SF, SIZE 20, 16-22, NI/NI



TE Part #1060-16-0144-PS
PIN, SF, SIZE 16, 14-18, AU/SN, 100 PC



TE Part #1062-12-0222-PS
SOC, SF, SIZE 12, 10, NI/NI, 100 PC

Documents

Product Drawings

[CONV OUTLET ASSY \(PUTTY WHITE\)](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_1-208979-4_AF.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-208979-4_AF.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-208979-4_AF.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC08_AC_INPUTS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English