



HVA 280

TE Internal #: 5-2103177-1

Housing for Female Terminals, Wire-to-Device / Wire-to-Board, 2 Position, .409 in [10.4 mm] Centerline, Sealable, Orange, Signal, HVA 280

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Board, Wire-to-Device**

Number of Positions: **2**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **10.4 mm [.409 in]**

Sealable: **Yes**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Board, Wire-to-Device
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	600 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V, 240 V, 500 V, 550 V, 600 V

Body Features

Cable Exit Angle	180°
------------------	------



Primary Product Color	Orange
Connector & Keying Code	A

Contact Features

Contact Size	2.8mm
Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	10.4 mm[.409 in]

Dimensions

Connector Height	26.4 mm[1.03 in]
Product Width	32.9 mm[1.29 in]
Product Length	51.25 mm[2.01 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP6K9K
Agency/Standard	USCAR-2

Packaging Features

Packaging Quantity	1
Packaging Method	Package



Other

Serviceable	No
Connector Position Assurance Capable	Yes

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <div>TE Part # 2103124-1 HVA280 2P HEADER ASSY, KEY A</div>	 <div>TE Part # 2103181-2 CABLE SEAL RTNR, SIZE B, HVA280-2PI XE</div>	 <div>TE Part # 1587826-2 CABLE SEAL, SIZE B, HVA280-2PI</div>	 <div>TE Part # 1587828-3 INNER FERRULE, SIZE C, HVA280-2PI</div>
---	---	---	--



TE Part # 1587829-2
OUTER FERRULE, SIZE B, HVA280-2PI

TE Part # 2103181-1
CABLE SEAL RTNR, SIZE A, HVA280-2PI XE

TE Part # 2103181-3
CABLE SEAL RTNR, SIZE C, HVA280-2PI XE

TE Part # 1587828-2
INNER FERRULE, SIZE B, HVA280-2PI

TE Part # 1587829-3
OUTER FERRULE, SIZE C, HVA280-2PI

TE Part # 2103414-1
SHIPPING CAP TYPE 1, PLUG, HVA280

TE Part # 1587826-1
CABLE SEAL, SIZE A, HVA280-2PI

TE Part # YHVA280-2PHX-HDR-A
HVA280 2P (2103124-1) HEADER, KEY A

Also in the Series | **HVA 280**

Automotive Connector Caps & Covers
(5)

Automotive Connector EMC Shielding
(15)

Automotive Housings(78)

Connector Seals & Cavity Plugs(8)

Electric, Hybrid & Fuel Cell Cable
Assemblies(6)

High Voltage Wire Processing
Equipment(7)

Other Automotive Connector
Accessories(37)

PCB Headers & Receptacles(37)

Customers Also Bought

TE Part #HDP26-24-23PE
PLG, 23P, BLK, E, 16, P

TE Part #1318386-2
TH/.025 CONNECTOR SYSTEM,
HOUSING

TE Part #1587828-3
INNER FERRULE, SIZE C, HVA280-2PI

TE Part #2-1419158-5
GET MALE TERM, B, SN, REREEL



Documents

Product Drawings

PLUG ASSY, KEY A, FA, HVA280-2PHI XE

English

PLUG ASSY, KEY A, FA, HVA280-2PHI XE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English