



MTA 156

TE Internal #: 640643-6
PCB Connector Covers, 6 Position, .156 in [3.96 mm] Centerline,
Polyester, Standard Product Profile, Dust Cap, -55 – 105 °C [-67 –
221 °F], MTA 156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Connector Accessories > PCB Protection & Strain Relief > PCB Connector Covers



Number of Positions: 6
Centerline (Pitch): 3.96 mm [.156 in]
Primary Product Material: Polyester
Product Profile: Standard
Connector Cover Type: Dust Cap

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Dust Cap

Configuration Features

Number of Positions	6
---------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	Polyester

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Feed Thru
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

--	--



UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156	 TE Part # 640251-6 06P SL156 HSG W/O LCK RAMP	 TE Part # 3-641437-6 06P MTA156 PSTD CONN ASSY RED	 TE Part # 640389-6 06P MTA156 HDR ASSY SQ R/A F/L
---	---	---	--



 TE Part # 3-641119-6 06P MTA156 HDR ASSY FL/ST LF	 TE Part # 3-640428-6 06P MTA156 CONN ASSY 22AWG RED	 TE Part # 3-643817-6 06P MTA156 CONN ASSY 18AWG ORA	 TE Part # 640387-6 06P MTA156 HDR ASSY SQ R/A
 TE Part # 3-643819-6 06P MTA156 CONN ASSY 22AWG RED	 TE Part # 3-640599-6 06P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-640427-6 06P MTA156 CONN ASSY 20AWG YEL	 TE Part # 644752-6 06P MTA156 HDR ASSY SQ STR F/L
 TE Part # 640384-6 06P MTA156 HDR ASSY STR RND SN	 TE Part # 640388-6 06P MTA156 HDR ASSY RN STR F/L	 TE Part # 3-644465-6 06P MTA156 CONN ASSY 18AWG ORA	 TE Part # 644408-1 06P MTA156 HDR ASSY,R/A,W/O#4
 TE Part # 640385-6 06P MTA156 HDR ASSY SQ R/A	 TE Part # 640383-6 06P MTA156 HDR ASSY STR SQ SN	 TE Part # 644408-2 06P MTA156 HDR ASSY,R/A,W/O#5	 TE Part # 3-641208-6 06P MTA156 HDR ASSY FL ST LF

Also in the Series | MTA 156

 Insertion & Extraction Tools(1)	 PCB Connector Covers(88)	 PCB Connector Keying(2)	 PCB Connector Mounting(1)
--	--	--	--



PCB Headers & Receptacles(314)



Power Contacts(2)



Rectangular Power Connectors(698)




Standard Rectangular Connectors(337)



Wire-to-Board Connector Contacts(2)

Customers Also Bought



TE Part #776428-2
AS 16, 2P CAP ASSY, KEY 2




TE Part #6609032-5
3VR1=F7198 S0




TE Part #6609036-9
10VSK1=F7242 S0



TE Part #1825261-2
MSS2200G04=DPDT SL SW VERT AU



TE Part #1-1658526-6
609-2641LF FEM SOCKT,LEAD FREE



TE Part #2-1658526-4
609-5041LF FEM SOCKT,LEAD FREE



TE Part #1-6609028-8
10VK6=F7356 S0



TE Part #1-206763-1
METRIMATE PIN HEADER ASSY,24P



TE Part #2-34112-2
SOLIS R 22-16COMM 22-18MIL 10



TE Part #3-640600-5
05P MTA156 CONN ASSY 20AWG LF

Documents



Product Drawings

06P MTA156 COVER F/T

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_640643-6_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_640643-6_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_640643-6_N.3d_stp.zip

English

Customer View Model

ENG_CVM_640643-6_R.3d_igs.zip

English

Customer View Model

ENG_CVM_640643-6_R.3d_stp.zip

English

Customer View Model

ENG_CVM_640643-6_R.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

