




SL-156

TE Internal #: 1-2132189-1

TE Internal Description: 11P SL156 HSG W/LCK RMP, TABS & RTNR

Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156

[View on TE.com >](#)



All Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156 (107)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

SL-156

Insertion & Extraction Tools(1)

PCB Connector Keying(2)

PCB Latches, Locks & Retainers(1)

Rectangular Connector Housings(11)

Rectangular Connector Keying Plugs(1)

Wire-to-Board Connector Assemblies & Housings(140)

Wire-to-Board Connector Contacts(23)

Customers Also Bought

TE Part #1586076-1
02P UMNL PIN HDR W/O DRNS V2

TE Part #643464-2
07P MTA156 HDR ASSY STR W/O#2

TE Part #643495-1
05P MTA156 HDR ASSY W/O#4

TE Part #4-644615-1
11P MTA156 POL HDR ASSY LF

TE Part #1586176-1
12P UMNL PIN HDR 94VO NDH

TE Part #1744427-5
EP Header Asy,Shrouded,5 Pos, GW

TE Part #1744439-4
EP2.5 Shrd HDR ASSY 4P VERT, GW

TE Part #1744439-6
EP2.5 Shrd HDR ASSY 6P VERT, GW

TE Part #8-1415034-1
MT78760



Documents

Product Drawings

11P SL156 HSG W/LCK RMP, TABS & RTNR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2132189-1_C_c-1-2132189-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2132189-1_C_c-1-2132189-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2132189-1_C_c-1-2132189-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-7_SL-156_CONNECTOR_TPA_DEVICE

English

Product Specifications

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English