




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM GG SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**
Input Voltage Selection: **None**
Filter Switch Type: **No Switch**
Filter Shield Type: **Shielded**
Product Orientation: **Right Angle**

All CORCOM GG SERIES MULTI-FUNCTION INLET FI (36)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	No Switch
Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Fuse Options	Dual
--------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Leakage Current (Max) (250VAC, 50Hz)	420 μ A



Current Rating	6 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Shielded
Product Orientation	Right Angle

Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-C8114-G34

CORCOM GG SERIES MULTI-FUNCTION INLET FI



TE Part # 1609116-6

10EHGS1-2=F8242

Also in the Series | Corcom GG



Multi-Function Inlet Filters(36)

Customers Also Bought



TE Part #1-6609037-6

30EMC6=F8131



TE Part #1-1462038-6

IM06NS=IM RELAY 140mW 12V



TE Part #6609116-5

10EHG8-2=F8245




TE Part #T4111401021-000

M12,MALE,STRAIGHT,B CODE,2P, PG7,GOLD



TE Part #5207719-3

KIT SCREWLOCK FEMALE CLEAR ZIN




TE Part #7-534998-0

40 MODIV VRT DR CE 100/125



TE Part #170020-1

SHUR PLUG 20-14 MM2 TPBR



TE Part #9-2176412-1

5W XSM M/OX 5% 30K



TE Part #NB17632001

TAT-125-1-1/2-0-STK



Documents

Product Drawings

6EGG8-2 S0=F7386B

English

CAD Files

Customer View Model

ENG_CVM_2-6609115-9_B.3d_igs.zip

English

Customer View Model

ENG_CVM_2-6609115-9_B.3d_stp.zip

English

Customer View Model

ENG_CVM_2-6609115-9_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-6609115-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-6609115-9_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-6609115-9_C.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_CORCOM_PRODUCT_GUIDE_GG_HG

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

Product Environmental Compliance

TE Material Declaration

English