



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Connector Hardware Type: Jackscrew Kit

Jackscrew Type: Turnable

Jackscrew Style: Male

Number of Positions: 6, 12, 14, 15, 16, 20, 26, 28, 34, 41, 42, 50, 75, 104

Operating Temperature Range: -55 – 150 °C [-67 – 302 °F]

Features

Configuration Features

Number of Positions	6, 12, 14, 15, 16, 20, 26, 28, 34, 41, 42, 50, 75, 104
---------------------	--

Body Features

Thread Lead Type	Double
Primary Product Material	Stainless Steel, Zinc Alloy

Mechanical Attachment

Primary Product Plating Finish	Non-Hexavalent Chromate
Strain Relief	Without
Mounting Hardware	Jackscrew Pin and Jackscrew Tip Male
Thread Size	6-32 [M3.5 x .6]
Connector Hardware Type	Jackscrew Kit
Jackscrew Type	Turnable
Jackscrew Style	Male

Dimensions

Product Width	7.92 mm[.312 in]
---------------	------------------



Product Length	43.26 mm[2.138 in]
Product Height	7.92 mm[.312 in]

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Connector Accessory Comment	Two required., Use turnable jackscrews on mating housings when mating to grounding block.
-----------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(7)




Rack & Panel Connectors(1)



Rectangular Connector Hardware(51)



Rectangular Power Connectors(66)



Standard Edge Connectors(2)

Customers Also Bought



TE Part #53410-1
TERMINAL,PIDG PVF2 R 22-16 1/4



TE Part #2-327950-1
PIDG RECT 22-16COMM 22-18MIL 5



TE Part #YDTS20T17-06PNV001
RECP ASSY



TE Part #YDTS24T21-11PAV001
RECP ASSY



TE Part #1053372-1
2062 8001 90,OSM JACK, OPL



TE Part #1757829-3
AMPLIMITE,PLUG ASY,POSTD,109,ZN, 3



TE Part #2000713-8
RA Keyed Guide Mod, Vita 46, Machined



TE Part #YDIV40E21-11PNC009
RECP ASSY



TE Part #3-1618400-8
DS11-1005T=SOLID STATE RELAY

TE Part #YCTJ720K01BC017000
MODULE ASSY



Documents

CAD Files

Customer View Model
[ENG_CVM_CVM_200871-1_Y.2d_dxf.zip](#)
English

3D PDF

3D
Customer View Model
[ENG_CVM_CVM_200871-1_Y.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_CVM_200871-1_Y.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)
English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)
English
[AMP Jack Screw Selection Chart for Series "M", COAXICON and Miniature](#)
English

[Instruction Sheet \(U.S.\)](#)
English
[AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS](#)
English

[Instruction Sheet \(U.S.\)](#)
English
[75 and 104 Position Series "M" Connectors and Accessories](#)
English

[Instruction Sheet \(U.S.\)](#)
English
[21 & 26 POSITION SERIES "M" CONNECTORS AND ACCESSORIES](#)
English