

Europa

TE Internal #: 1-1776294-2

Barrier Strips, Wire-to-Wire, 12 Position, 8 mm [.315 in] Centerline, 1

Row, Operating Voltage 250 V, 24 – 12 AWG Wire Size, .2 – 3 mm²

Wire Size

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > Barrier Strips

Connector System: **Wire-to-Wire**Number of Positions: **12**Centerline (Pitch): **8 mm [.315 in]**Number of Rows: **1**Operating Voltage: **250 V****Features****Product Type Features**

Block Style	None
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Levels	1
Number of Positions	12
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Body Features

Quick Connect Tab Plating Material	Tin
Primary Product Color	Natural
Product Orientation	Right Angle

Contact Features

Contact Base Material	Brass
Contact Current Rating (Max)	30 A

Mechanical Attachment

Screw Plating Material	Zinc Chromate
------------------------	---------------

Screw Material	Steel
Mounting Options	2.8mm Diameter Mounting Holes
Thread Size	M3
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Polyamide 6
Centerline (Pitch)	8 mm [.315 in]

Dimensions

Wire Size	.2 – 3 mm ²
-----------	------------------------

Usage Conditions

Operating Temperature Range	-35 – 100 °C [-31 – 212 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	50
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (.23% in Component Part)
Halogen Content	Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1776293-2
TSB23012DS-EUROPA TERM BLK,
8MM



TE Part # 1-1776295-2
TSB23012DSHT-EUROPA TM BLK,
8MM

Customers Also Bought



TE Part #1658640-2
RECP. ASSEMBLY SIZE 5



TE Part #HDP24-24-23SN
REC, 23P, BLK, N, 16, S



TE Part #91503-1
CCII AMPLIMITE 20 DF PIN SKT 28-20
ASSY



TE Part #3-1393310-8
VCFM-1002=SOCKET,VCFM,5,PC,PLA-
ASSY



TE Part #2-324165-1
TERMINAL,PG SPD FLG 16-14 6



TE Part #1776293-4
TSB23004DS-EUROPA TERM BLK,
8MM



TE Part #NB11644001
ATUM-6/2-0-SP



TE Part #02172013-000
RVIT-Z HONEYWELL 150 DEG



Documents

Product Drawings

[TSB23012=EUROPA TERM BLK,8MM](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1776294-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1776294-2_O.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1776294-2_O.3d_jgs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROPA TERMINAL BLOCKS](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English