




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > IEC Filtered Inlets, Corcom EEJ Series



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **220 μ A**

Leakage Current (Max) (250VAC, 50Hz): **380 μ A**

Current Rating: **6 A**

[All IEC Filtered Inlets, Corcom EEJ Series \(32\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-20

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 μ A
Leakage Current (Max) (250VAC, 50Hz)	380 μ A
Current Rating	6 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------



Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-EE11
IEC Filtered Inlets, Corcom EEA Series

Also in the Series | Corcom EEJ



Multi-Function Inlet Filters(32)

Customers Also Bought



TE Part #5-6609107-4
PS0SXDS3A=C1111



TE Part #2013595-1
INDUSTRIAL MINI I/O PLUG KIT D1



TE Part #1757824-2
AMPLIMITE,ASY,RCPT,STD,90,ZN,2



TE Part #5-1478762-2
Metal backshell 15 way Top Entry-KIT



TE Part #1-1478762-5
METAL BACKSHELL 15 WAY TOP E



TE Part #5-1478762-1
Metal backshell 9 way Top Entry-KIT




TE Part #5-1478762-3
Metal backshell 25 way Top Ent



TE Part #102387-4
20 MODIV HSG COMP DR .100 POL



TE Part #5205817-1
KIT SCREWLOCK FEMALE



TE Part #1776296-3
TSB5000331DS=EUROPA T-BLK,10MM

Documents

Product Drawings

6EEJ8=F8015

English

CAD Files

Customer View Model

ENG_CVM_3-6609006-4_0.3d_igs.zip

English

Customer View Model

[ENG_CVM_3-6609006-4_0.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-6609006-4_0.2d_dxf.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_CVM_3-6609006-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-6609006-4_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-6609006-4_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English