



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **4**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Housing Material	Nylon
------------------	-------

Dimensions

	.08 – .12 in
--	--------------

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







Also in the Series

FASTON 110





Also in the Series

FASTON 187



Customers Also Bought



 TE Part #520963-2 ULTRA-POD 250 ASSY REC 18-14 AWG TPBR	 TE Part #521367-1 ULTRA POD: Straight, Receptacle Assembly, Unplated, .250 inch	 TE Part #63482-1 RING 18-14 AWG TPSTL	 TE Part #63306-2 250 FASTON REC 18-14 AWG TPBR
 TE Part #521411-1 ULTRA-POD 250 ASY REC 22-18 AWG BR	 TE Part #42660-1 250 FASTON REC 18-14 AWG BR	 TE Part #61795-3 RING 18-14 AWG TPBR	 TE Part #42800-1 187 FASTON REC 20-16 AWG BR
 TE Part #179464-1 POWER DBL LOCK CAP HSG F/H 3P			

Documents

Product Drawings
187 FAST&110 PL HSG.,REC.,4 POS,BLACK
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1969725-1_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1969725-1_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1969725-1_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Environmental Compliance



TE Material Declaration

English

MD_1969725-1_10032016328_dmtec

English

MD_1969725-1_10032016328_dmtec

English