



SL-156

TE Internal #: 1-640251-5
Housing, Receptacle, Wire-to-Board, 15 Position, .156 in [3.96 mm]
Centerline, Crimp, 1 Row, Natural, Wire & Cable, Power & Signal,
SL-156

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >
Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **15**
Centerline (Pitch): **3.96 mm [.156 in]**

[All Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156 \(27\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

--	--



Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Retention Within Housing	Without
Contact Layout	Inline
Contact Type	Socket
Contact Current Rating (Max)	6.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Left End Open
Housing Material	Nylon - GF
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

	2.34 in
Connector Height	6.35 mm
Wire Size	.0509 – .823 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Agency/Standard	CSA, UL
UL Flammability Rating	UL 94V-0

Packaging Features

--	--



Packaging Quantity	1
Packaging Method	Package

Other

Discrete Wire Connector Comment	Unit Accepts 1.14[.045] Square or Round Post, Accepts Keying Plug 640254-1and 640255-1
---------------------------------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>









EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1-640388-5 15P MTA156 HDR ASSY RN STR F/L	 TE Part # 1-640445-5 15P MTA156 HDR ASSY FL/STR SNL	 TE Part # 1-640383-5 15P MTA156 HDR ASSY STR SQ SN	 TE Part # 1-643067-5 15P MTA156 MOLDED COVER
 TE Part # 1-640384-5 15P MTA156 HDR ASSY STR RND SN	 TE Part # 1-640387-5 15P MTA156 HDR ASSY SQ R/A	 TE Part # CAT-103156-WBHSN Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156	 TE Part # 1-644752-5 15P MTA156 HDR ASSY SQ STR F/L
 TE Part # 1-640385-5 15P MTA156 HDR ASSY SQ R/A	 TE Part # 1-643071-5 15P 156 CL MTA FD/TH COVER	 TE Part # 1-640389-5 15P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 1-640551-5 15P MTA156 COVER
 TE Part # 1-770996-5 15P SL 156 HSG W/TABS W/O LR	 TE Part # 1-640643-5 15P MTA156 COVER F/T	 TE Part # 1-641119-5 15P MTA156 HDR ASSY FL/ST 15AU	 TE Part # 1-644751-5 15P MTA156 HDR ASSY R/A
 TE Part # 1-644753-5 15P MTA156 HDR ASSY RN STR F/L	 TE Part # 1-770996-2 12P SL 156 HSG W/TABS W/O LR	 TE Part # 4-641119-5 15P MTA156 HDR ASSY FL/ST LF	 TE Part # 4-641120-5 15P MTA156 HDR ASSY FL/ST LF

Also in the Series | [SL-156](#)



Insertion & Extraction Tools(1)



PCB Connector Keying(2)



PCB Latches, Locks & Retainers(1)



Rectangular Connector Housings(11)



Rectangular Connector Keying Plugs(1)



Wire-to-Board Connector Assemblies & Housings(140)



Wire-to-Board Connector Contacts(23)


Customers Also Bought



TE Part #2-748003-0
09 PLUG SP/FMS BRDLK



TE Part #640250-7
07P SL156 HSG W/LCK RAMP NATL




TE Part #1-5102155-0
AMP-LATCH UNIVERSAL HEADERS




TE Part #1-747150-6
09 RCPT SP/FMS SCRLK



TE Part #350585-4
06P UMNL PIN HDR ASSY V2 LF




TE Part #640254-1
KEYING PLUG .045 SQ PST CONN



TE Part #350417-1
.093 COMM P&S SOK 18-24 PTPBR



TE Part #770095-1
09P .093 COMM P&S PLUG



TE Part #640500-2
06P MR HDR ASSY V0

Documents



Product Drawings

15P SL156 HSG W/O LCK RAMP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-640251-5_AL_c-1-640251-5-al.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-640251-5_AL_c-1-640251-5-al.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-640251-5_AL_c-1-640251-5-al.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English