



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	7.95 mm[.312 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	500
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 63239-1 POSITIVE LOCK 250 REC 12-10 AWG TPBR	 TE Part # 170335-1 PL 250 RECEPTACLE 15-10 AWG PTPBR	 TE Part # 170329-1 250 PL MKII REC. 15-10AWG PTBR	 TE Part # 170327-1 250 PL MKII REC. 22-18AWG PTBR
 TE Part # 170328-1 250 PL MKII REC. 18-14AWG PTBR	 TE Part # 170333-1 PL 250 RECEPTACLE 22-18 AWG PTPBR	 TE Part # 926522-2 PL 250 REC HSG 2P NYLON NAT	 TE Part # 170334-1 205 PL MII,REC.,18-14,PTBR
 TE Part # 1-926522-2 PL 250 REC HSG 2P NYLON NAT	 TE Part # 100100-1 2 POS POSITIVE LOCK (PL) HOUSING	 TE Part # 2238155-1 POS LOCK 250 Rec, MKII, 18-14 TPBR	 TE Part # 2238156-1 POS LOCK 250 Rec, MKII, 22-18 TPBR

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(193)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(4)
--	---	--	--



[Quick Disconnects\(186\)](#)

Customers Also Bought




TE Part #917699-1
[2.5 SIGNAL DBL LOCK D.L.P 3P](#)




TE Part #917684-1
[2.5 SIGNAL DBL LOCK REC CONT M](#)



TE Part #1-6609036-3
[20VSK6=F7586 S0](#)



TE Part #170328-1
[250 PL MKII REC. 18-14AWG PTBR](#)




TE Part #284391-4
[TERMI-BLOK PCB SIDE ENTRY STAC](#)




TE Part #2232563-1
[GHC 9.0MM 3POS TPA](#)



TE Part #179464-1
[POWER DBL LOCK CAP HSG F/H 3P](#)



TE Part #177627-1
[PL .250 \(6.3 MM\) HOUSING RECEPTACLE](#)



TE Part #172210-6
[POSITIVE LOCK 250 HOUSING RECEPTACLE](#)



TE Part #917687-9
[2.5 SIGNAL D/LOCK PLUG HSG 3P](#)

Documents

Product Drawings

[POSITIVE LOCK .250 HOUSING RECEPTACLE](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_178833-1_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_178833-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_178833-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English