

**2212243-1**

✓ ACTIVE


## FORGE

TE Internal #: 2212243-1

Rectangular Power Connectors, Connector Assembly, Plug, Wire-to-Panel, 4 Position, 250 mm [9.84 in] Centerline, Wire & Cable, UL 94V-0

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Panel**

Number of Positions: **4**

Centerline (Pitch): **250 mm [9.84 in]**

## Features

### Product Type Features

Compatible With Discrete Wire Type	Stranded
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	4
Number of Rows	2

### Body Features

Cable Exit Angle	180°
Connector Profile	Standard

### Contact Features

Contact Retention Within Housing	With
----------------------------------	------

Contact Type

Pin

**Termination Features**

Termination Method to Wire &amp; Cable

Crimp

**Mechanical Attachment**

Mating Alignment Type

Blindmate

Mating Alignment

With

Panel Mount Feature

With

Panel Mount Feature Type

Screw Mount

Connector Mounting Type

Panel Mount

**Housing Features**

Centerline (Pitch)

250 mm[9.84 in]

Housing Color

Black

Housing Material

Polyester GF

**Dimensions**

Panel Thickness (Recommended)

1.5 – 1.78 mm[.59 – .7 in]

Connector Height

42 mm[1.654 in]

Product Width

32.2 mm[1.268 in]

Product Length

60 mm[2.362 in]

Row-to-Row Spacing

21 mm[.827 in]

**Usage Conditions**

Operating Temperature Range

-40 – 105 °C[-40 – 221 °F]

**Operation/Application**

Shielded

No

Circuit Application

Power

**Identification Marking**

Circuit Identification Feature

Without

**Industry Standards**

UL Rating

Certified

Approved Standards

UL 1977

UL Flammability Rating

UL 94V-0

Glow Wire Rating

Standard Part - Not Glow Wire

## Packaging Features

Packaging Method	Box
------------------	-----

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Customers Also Bought



## Documents

### Product Drawings

[FORGE, ASSY PIN, 0#0-4#4-0#8-0#12-0#22](#)

English

### CAD Files

[3D PDF](#)

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2212243-1\\_2.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2212243-1\\_2.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2212243-1\\_2.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

[1-1773875-1\\_FORGE\\_DRAWER\\_CONNECTORS\\_CN](#)

[3-1773463-3\\_FORGE\\_DRAWER\\_CONNECTORS](#)

English

---

[Product Specifications](#)

[Application Specification](#)

English

[Application Specification](#)

English