



TE Internal #: 2103177-2
Housing for Female Terminals, 2 Position, .41 in [10.4 mm]
Centerline, Sealable, Orange, Wire & Cable, Cable Mount (Free-Hanging)
[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 2
Connector & Housing Type: **Housing for Female Terminals**
Centerline (Pitch): 10.4 mm [.41 in]
Sealable: **Yes**
Mating Tab Width: 2.8 mm [.11 in]

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Orange
Connector & Keying Code	B

Contact Features

Contact Size	2.8mm
--------------	-------



Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Contact Current Rating (Max)	40 A

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 66 GF
Centerline (Pitch)	10.4 mm[.41 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Packaging Features

Packaging Quantity	50
Packaging Method	Package

Other

Connector Position Assurance Capable	Yes
--------------------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2103247-2
SPLIT HEADER ASSY, Ag, KEY B, HVA280



TE Part # CAT-LMPH9507
Low & Medium Power Header

Customers Also Bought



TE Part #2112323-1
SINGLE WIRE SEAL,MT 2,VT



TE Part #1418408-1
AMP MCP 1.5K, CONTACT



TE Part #D20444-000
FL2500-NO.1-I8-0-STK



TE Part #1-1414995-0
V23230D2001B200



TE Part #5474213003
FLHTC0311-1.00-2



TE Part #1742513003
FLHTC0311-1.00-0



TE Part #5773073002
FLHTC0311-1.00-4



TE Part #2-1924067-0
2POS, MCON 1.2 CB REC 2p TL SEALED



TE Part #4-1415419-2
[0419 11 1301 00](#)



TE Part #2503573002
[FLHTC0311-0.75-5](#)

Documents

Product Drawings

[PLUG ASSY, KEY B, TA,CPA, HVA280-2PHI XE](#)

English

[PLUG ASSY, KEY B, TA,CPA, HVA280-2PHI XE](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2103177-2_B_c-2103177-2-b.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2103177-2_B_c-2103177-2-b.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2103177-2_B_c-2103177-2-b.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English