



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Contact Current Rating (Max): 66 A

Circuit Application: Power

Shell Base Material: Brass

Circular Connector Shell Size: 40

Features

Product Type Features

|            |       |
|------------|-------|
| Sealable   | No    |
| Shell Type | Metal |

Body Features

|                     |       |
|---------------------|-------|
| Shell Base Material | Brass |
|---------------------|-------|

Contact Features

|                                 |      |
|---------------------------------|------|
| Contact Current Rating (Max)    | 66 A |
| Circular Connector Contact Type | Pin  |

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Housing Features

|                               |    |
|-------------------------------|----|
| Circular Connector Shell Size | 40 |
| Alignment Keyed               | 0° |

Operation/Application

|                   |            |
|-------------------|------------|
| Durability Rating | 500 Cycles |
|-------------------|------------|



Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                          |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                     |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JAN 2023 (233)<br>SVHC > Threshold:<br>Pb (1.6% in Component)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                      |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                                                                                                                                                                                                                                                                                                             |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                      |                                                                         |                                                               |
|------------------------------------------------------|-------------------------------------------------------------------------|---------------------------------------------------------------|
| <br>TE Part # C0-0008-000-000<br>CRIMPING TOOL LARGE | <br>TE Part # C0-0247-000-000<br>POSITIONING INSERT FOR 3.6 MM CONTACTS | <br>TE Part # C0-0313-000-000<br>CRIMPING DEVICE HC20 IN CASE |
|------------------------------------------------------|-------------------------------------------------------------------------|---------------------------------------------------------------|

Customers Also Bought





TE Part #61-0004-011-000  
CONTACT PIN 1 MM



TE Part #61-0193-011-000  
CONTACT PIN 2 MM



TE Part #ASA014F11610235000  
623 PLUG



TE Part #BGC110N00001200000  
923 RECEPTACLE, ANGLED,  
ROTATABLE



TE Part #BGC110N00001216000  
923 RECEPTACLE, ANGLED,  
ROTATABLE



TE Part #CGA258N00000056000  
940 RECEPTACLE ANGLED,  
ROTATABLE,SP-READY



TE Part #CGE270N00000020000  
940 RECEPTACLE ANGLED,  
ROTATABLE,SPEEDTEC



TE Part #CGE270N00000051000  
940 RECEPTACLE ANGLED,  
ROTATABLE,SP-READY

TE Part #CGE271M07000091000  
940 RECEPTACLE ANGLED,  
ROTATABLE,SP-READY

TE Part #HEC402N00000300000  
723 HTEC RECEPTACLE, SPEEDTEC

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_61-0195-011-000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_61-0195-011-000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_61-0195-011-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Contact pin 3.6 mm 61-0195-011-000

English