

## ATGBICS 100G QSFP28 Loopback Cisco Compatible Transceiver 100G QSFP28 Loopback Testing Module

**Brand :** ATGBICS

**Product code:** 100G QSFP28  
LOOPBACK-C



**Product name :** 100G QSFP28 Loopback Cisco Compatible Transceiver 100G QSFP28 Loopback Testing Module


100G QSFP28 Loopback Cisco Compatible Transceiver 100G QSFP28 Loopback Testing Module

ATGBICS 100G QSFP28 Loopback Cisco Compatible Transceiver 100G QSFP28 Loopback Testing Module:

ATGBICS 100G QSFP28 Loopback QSFP28 Loopback Testing Module is used for testing QSFP28 transceiver ports in board level test. By substituting for a full-featured QSFP28 transceiver, the electrical loopback provides a cost effective low loss method for QSFP28 port testing. our product is packaged in a standard MSA housing compatible with all QSFP28 ports. Transmit data from the host is electrically routed (internal to the loopback module) to the receive data outputs and back to the host. We proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



<b>Performance</b>		<b>Operational conditions</b>	
SFP transceiver type *	Fiber optic	Storage temperature (T-T)	-40 - 85 °C
Maximum data transfer rate *	10000 Mbit/s	Operating relative humidity (H-H)	0 - 95%
Interface type *	QSFP	Storage relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	<b>Weight &amp; dimensions</b>	
Product colour	Silver	Width	13.5 mm
Housing material	Metal	Depth	72.4 mm
Country of origin	United Kingdom	Height	18.4 mm
Brand compatibility	Cisco	Weight	42 g
Certification	CE, FCC, RoHS	<b>Packaging data</b>	
		Number of products included	1 pc(s)
		Package type	Box
<b>Operational conditions</b>		<b>Technical details</b>	
Minimum operating temperature	-20 °C	Sustainability compliance	✓
Maximum operating temperature	85 °C	Sustainability certificates	RoHS
Operating temperature (T-T)	-20 - 80 °C	Doesn't contain	Lead



5056468717092

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.