



Positive Lock | Positive Lock 187

TE Internal #: 521198-1

Crimp Terminal Housings, Receptacle, Receptacle, 3 Position, Straight, UL 94V-2, Natural, Nylon, Contact Mating Retention, Positive Lock 187

[View on TE.com >](#)

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **3**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6.07 mm, 7.82 mm[.239 in][.308 in]

Dimensions

Product Length	9.53 mm[.375 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	500
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1217114-2
187 PL MKIII REC. 18-14AWG TPBR

TE Part # 1217113-2
187 PL MKIII REC. 22-18AWG TPBR

TE Part # 1217097-2
PL 187 TERMINAL REC 22-18 AWG TPBR

TE Part # 1217096-1
REC 187 POS LOC 18-14 014 BR

TE Part # 1217114-1
REC 187 POS-LOC MKIII BR 18-14

Also in the Series | Positive Lock 187

Crimp Terminal Housings(86)

Insertion & Extraction Tools(2)

Insulation Boots & Sleeves(7)

Quick Disconnects(57)

Customers Also Bought




TE Part #8-1971775-3
PTL 2X3 CAP PANEL MT HIGH TEMP
KEY D NAT



TE Part #8-1971776-3
PTL 2X3 PLUG HSG HIGH TEMP KEY
D NAT



TE Part #EG8142-000
RNF-100-3/32-WH-85MM



TE Part #1-1969605-8
18P PM PLUG VAL-U-LOK PM GW




TE Part #1969655-1
250 FASTON HSG.,REC.,1 POS,
NATURAL



TE Part #2-2150198-2
OCEAN_2.0_Applicator-E-210F250O



TE Part #2151025-2
OCEAN_2.0_APPLICATOR-S-090F200F



TE Part #2178930-3
3P STD TIMER GEH V0 GWT



TE Part #453838-1
CRIMPER, WIRE-VAR WIDTH-F



TE Part #CV7318-000
VERSAFIT-1/4-4-1IN

Documents

Product Drawings

HSG.REC.POS-LOK.187 NAT.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_521198-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_521198-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_521198-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Positive Lock Receptacles

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_521198-1_060720181011_dmtec

English

MD_521198-1_060720181011_dmtec

English