



Terminals & Splices > Spade Terminals > AMPOWER Lug Crimp Terminal, 1 Stud Hole



Spade Terminal Type: Rectangular Tongue Terminal

Wire Size: 325000 – 375000 CMA

Stud Size: 1/2, M12

Stud Diameter: 14.27 mm [.562 in]

Tongue Thickness: 4.32 mm [.17 in]

[All AMPOWER Lug Crimp Terminal, 1 Stud Hole \(52\)](#)

Features

Product Type Features

Stud Size	1/2, M12
Sealable	No

Configuration Features

Number of Holes	2
-----------------	---

Body Features

Product Weight	120.96 g
----------------	----------

Contact Features

Military Part Class	Class II
Spade Terminal Type	Rectangular Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

--	--



Wire Size	325000 – 375000 CMA
Stud Diameter	14.27 mm[.562 in]
Tongue Thickness	4.32 mm[.17 in]
Product Length	101.85 mm[4.01 in]
Barrel Inside Diameter	21.06 mm[.829 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Other

Terminals & Splices Comment	Electrodeposited Tin Plate per MIL-T-10727.
-----------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 46753-2
HYP8 AMPPOWER 350MCM DIE SET

TE Part # 69653
HYP8 AMPPOWER 350MCM 69082 DIE SET

Also in the Series | AMPPOWER

Busbar Connectors(13)

Knife Disconnects(14)

PCB Headers & Receptacles(2)

Power Cable Assemblies(7)

Power Contacts(1)

Quick Disconnects(1)

Rectangular Power Connectors(6)

Spade Terminals(139)



Customers Also Bought

TE Part #211839-1
CPC RCPT SZ 23-24 W/THRD INSRT

TE Part #4785230001
TMS-SCE-1/4-2.0-S1-4

TE Part #696058-1
AMPOWER BUTT SPLICE 500 HD

TE Part #696683-1
AMPOWER,500MCM,2-1/2,1.25 CNTR

TE Part #237025
FEED WHEEL SUB-ASS'Y

TE Part #314253-1
SPRING

TE Part #69903
DIE DG 69875 22-16

TE Part #91269-1
TOOL, LATCH REMOVAL AL

Documents

Product Drawings
TERMINAL,AMPOWER 350MCM
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_325926-1_L.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_325926-1_L.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_325926-1_L.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
AMPPOWER Terminals and Splices Flyer

English

Product Specifications
Application Specification

English

Instruction Sheets
Instruction Sheet (U.S.)

English

Agency Approvals
UL Report

English