

2098891-2

✓ ACTIVE

AMP | LEAVYSEAL

TE Internal #: 2098891-2

Other Automotive Connector Accessories, Flange Assembly, PBT

GF, Black, -40 – 140 °C [-40 – 284 °F], LEAVYSEAL

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories >

LEAVYSEAL Mounting Accessories



Automotive Connector Accessory Type: **Flange Assembly**

Primary Product Material: **PBT GF**

Primary Product Color: **Black**

Number of Positions: **39, 62**

Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

[All LEAVYSEAL Mounting Accessories \(8\)](#)

Features

Product Type Features

Automotive Connector Accessory Type

Flange Assembly

Configuration Features

Number of Positions

39, 62

Body Features

Primary Product Material

PBT GF

Primary Product Color

Black

Usage Conditions

Operating Temperature Range

-40 – 140 °C [-40 – 284 °F]

Industry Standards

UL Flammability Rating

UL 94HB

Packaging Features

Packaging Quantity

1

Packaging Method

Package

Other

Serviceable

Yes

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | LEAVYSEAL




Automotive Connector Caps & Covers (17)



Automotive Housings(79)



Insertion & Extraction Tools(5)




Other Automotive Connector Accessories(15)



PCB Headers & Receptacles(16)

Customers Also Bought

TE Part #DTM04-4P-E003
DEUTSCH DTM HousingsTE Part #DT06-2S-CE05
PLG, 2P, BLK, E, SEAL RET, CAPTE Part #1060-16-0622
DEUTSCH Size 16 Crimp ContactsTE Part #1-1823449-1
22POS, MIXED,TAB HSG,ASSYTE Part #WM-3P
WEDGE LOCK, 3P, REC, ORG, DTMTE Part #1813123-2
ASSY FOR SUPPORT PLATE AND
SEALINGTE Part #0411-240-2005
EXT TOOL, SIZE 20, 16-22 AWG, N,
REDTE Part #0411-204-1605
EXT TOOL, SIZE 16, 16-18 AWG, N,
DRK BLU

Documents

Product Drawings

4 bay mounting frame assembly

English

CAD Files

3D PDF

3D

Customer View Model[ENG_CVM_CVM_2098891-2_A.2d_dxf.zip](#)

English

Customer View Model[ENG_CVM_CVM_2098891-2_A.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_2098891-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Product Specifications**[Application Specification](#)

German