



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Seal Protector**

Primary Product Color: **Natural**

Features

Product Type Features

Connector Seal & Plug Type	Seal Protector
----------------------------	----------------

Body Features

Primary Product Color	Natural
-----------------------	---------

Packaging Features

Packaging Quantity	1
Packaging Method	Loose Piece

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998Y
One-Piece Connector, Sealed, CPC Series 1




TE Part # 208337-1
SEAL PROTECTOR PIN

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Power Connectors(458)



Connector Backshells(56)




Connector Seals & Cavity Plugs(36)



Connector Strain Relief(6)



Insertion & Extraction Tools(1)




Power Contacts(6)



Sealing Sleeves(2)


Customers Also Bought




TE Part #213920-1
CPC SEAL KIT,UNASSM,SZ 17-16




TE Part #1445534-3
PLUG,8-3,LARGE INS,STD KEY




TE Part #1586039-6
6P VAL-U-LOK VRT HDR W/P V2



TE Part #1586039-4
4P VAL-U-LOK VRT HDR W/P V2



TE Part #1586039-2
2P VAL-U-LOK VRT HDR W/P V2



TE Part #63757-1
250 FASTON REC 16-12 AWG BR



TE Part #9-103329-0
40 MODII HDR SRRA B/A .100 CL LF



TE Part #HD36-18-21SN-059
PLG,21P,AL,N, CBL CLMP BT, DRAIN, 20,S,MC



TE Part #DTM1312PA12PBR008
HDR, 24P, BLK, RA EEC, NI/CU, AB



TE Part #DTM13-12PA-R008
HDR, 12P, BLK, RA EEC, NI/CU, A

Documents

Product Drawings
SEAL PROTECTOR SOCKET

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_208338-1_G.2d_dxf.zip



English

Customer View Model
[ENG_CVM_CVM_208338-1_G.3d_igs.zip](#)

English

Customer View Model
[ENG_CVM_CVM_208338-1_G.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model
[ENG_CVM_208338-1_B.2d_dxf.zip](#)

English

Customer View Model
[ENG_CVM_208338-1_B.3d_igs.zip](#)

English

Customer View Model
[ENG_CVM_208338-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
[Product Specification](#)

English

Instruction Sheets
[Instruction Sheet \(U.S.\)](#)

English