

APPLICABLE STANDARD		SPECIFICATIONS																																										
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)		STORAGE TEMPERATURE RANGE	-10°C TO +60°C																																							
	VOLTAGE	30V AC		APPLICABLE CONNECTOR	DF37*-*DS-0.4V (**)																																							
	CURRENT	0.3A																																										
CONSTRUCTION																																												
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.																																								
MARKING		CONFIRMED VISUALLY.		X X																																								
ELECTRIC CHARACTERISTICS																																												
CONTACT RESISTANCE	20mV AC OR LESS 1khz,1m A .		100mΩ MAX.		X -																																							
INSULATION RESISTANCE	100V DC.		50MΩ MIN.		X -																																							
VOLTAGE PROOF	100V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		X -																																							
MECHANICAL CHARACTERISTICS																																												
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.			<table border="1"> <thead> <tr> <th>PIN COUNT</th> <th>INSERTION FORCE [N MAX]</th> <th>WITHDRAWAL FORCE [N MIN]</th> </tr> </thead> <tbody> <tr><td>10</td><td>15.4</td><td>2.6</td></tr> <tr><td>16</td><td>20.7</td><td>3.6</td></tr> <tr><td>20</td><td>24.3</td><td>4.4</td></tr> <tr><td>24</td><td>27.8</td><td>5.1</td></tr> <tr><td>30</td><td>33.1</td><td>6.2</td></tr> <tr><td>34</td><td>40.8</td><td>6.9</td></tr> <tr><td>40</td><td>41.9</td><td>8</td></tr> <tr><td>44</td><td>45.4</td><td>8.7</td></tr> <tr><td>50</td><td>50.7</td><td>9.8</td></tr> <tr><td>60</td><td>59.5</td><td>11.7</td></tr> <tr><td>70</td><td>68.4</td><td>13.5</td></tr> <tr><td>74</td><td>71.9</td><td>14.2</td></tr> </tbody> </table>	PIN COUNT	INSERTION FORCE [N MAX]	WITHDRAWAL FORCE [N MIN]	10	15.4	2.6	16	20.7	3.6	20	24.3	4.4	24	27.8	5.1	30	33.1	6.2	34	40.8	6.9	40	41.9	8	44	45.4	8.7	50	50.7	9.8	60	59.5	11.7	70	68.4	13.5	74	71.9	14.2	X -
PIN COUNT	INSERTION FORCE [N MAX]	WITHDRAWAL FORCE [N MIN]																																										
10	15.4	2.6																																										
16	20.7	3.6																																										
20	24.3	4.4																																										
24	27.8	5.1																																										
30	33.1	6.2																																										
34	40.8	6.9																																										
40	41.9	8																																										
44	45.4	8.7																																										
50	50.7	9.8																																										
60	59.5	11.7																																										
70	68.4	13.5																																										
74	71.9	14.2																																										
MECHANICAL OPERATION	10TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.																																									
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min, SINGLE AMPLITUDE 0.75 mm, 10CYCLES, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.																																									
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.																																									
ENVIRONMENTAL CHARACTERISTICS																																												
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85 °C TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN 2 ~3 MIN)		① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -																																							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 100mΩ MAX. ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -																																							
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25°C, 75%. (REFER TO JIS C 60068)		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -																																							
SALT MIST		EXPOSED IN 5% SALT MIST FOR 48h.		① CONTACT RESISTANCE: 100mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -																																							
COUNT		DESCRIPTION OF REVISIONS		DESIGNED	CHECKED																																							
1		DIS-H-00003087		YT. TAKAGI	TS. MIYAZAKI																																							
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT Unless otherwise specified, refer to JIS C 5402 and IEC 60512				APPROVED	MO. NAKAMURA																																							
				CHECKED	KH. IKEDA																																							
				DESIGNED	KY. MIDORIKAWA																																							
				DRAWN	KY. MIDORIKAWA																																							
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.																																								
				ELC4-314974-01																																								
HRS	SPECIFICATION SHEET			PART NO.	DF37C-*DP-0.4V (51)																																							
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL684																																							
					△ 1/1																																							