



REVISIONS					
REV	DATE	BY	CHK	APPV	DESCRIPTION
G1	16JUN2023	RK	MF		REVISED PER ECN-23-194767



RECOMMENDED PC BOARD MOUNTING DIMENSIONS FOR .063 [1.60] THICK PC BOARD AND .012 [.305] STENCIL THICK.

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3** MATERIAL: HOUSING - LCP, COLOR: BLACK. POSTS - COPPER ALLOY.
- 4** 0.000127 [0.000005] GOLD IN CONTACT AREA, 0.00254-0.00508 [0.000100-0.000200] MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [0.000050] NICKEL.
- 5** THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 6** 0.000127 [0.000005] GOLD IN CONTACT AREA, 0.00254-0.00508 [0.000100-0.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [0.000050] NICKEL.
- 7** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER
6	101.19 [3.984]	99.06 [3.900]	39	40	9-146279-0
6	98.65 [3.884]	96.52 [3.800]	38	39	8-146279-9
6	96.11 [3.784]	93.98 [3.700]	37	38	8-146279-8
6	93.57 [3.684]	91.44 [3.600]	36	37	8-146279-7
6	91.03 [3.584]	88.90 [3.500]	35	36	8-146279-6
6	88.49 [3.484]	86.36 [3.400]	34	35	8-146279-5
6	85.95 [3.384]	83.82 [3.300]	33	34	8-146279-4
6	83.41 [3.284]	81.28 [3.200]	32	33	8-146279-3
6	80.87 [3.184]	78.74 [3.100]	31	32	8-146279-2
6	78.33 [3.084]	76.20 [3.000]	30	31	8-146279-1
6	75.79 [2.984]	73.66 [2.900]	29	30	8-146279-0
6	73.25 [2.884]	71.12 [2.800]	28	29	7-146279-9
6	70.71 [2.784]	68.58 [2.700]	27	28	7-146279-8
6	68.17 [2.684]	66.04 [2.600]	26	27	7-146279-7
6	65.63 [2.584]	63.5 [2.500]	25	26	7-146279-6
6	63.09 [2.484]	60.96 [2.400]	24	25	7-146279-5
6	60.55 [2.384]	58.42 [2.300]	23	24	7-146279-4
6	58.01 [2.284]	55.88 [2.200]	22	23	7-146279-3
6	55.47 [2.184]	53.34 [2.100]	21	22	7-146279-2
6	52.93 [2.084]	50.80 [2.000]	20	21	7-146279-1
6	50.39 [1.984]	48.26 [1.900]	19	20	7-146279-0
6	47.85 [1.884]	45.72 [1.800]	18	19	6-146279-9
6	45.31 [1.784]	43.18 [1.700]	17	18	6-146279-8
6	42.77 [1.684]	40.64 [1.600]	16	17	6-146279-7
6	40.23 [1.584]	38.10 [1.500]	15	16	6-146279-6
6	37.69 [1.484]	35.56 [1.400]	14	15	6-146279-5
6	35.15 [1.384]	33.02 [1.300]	13	14	6-146279-4
6	32.61 [1.284]	30.48 [1.200]	12	13	6-146279-3
6	30.07 [1.184]	27.94 [1.100]	11	12	6-146279-2
6	27.53 [1.084]	25.40 [1.000]	10	11	6-146279-1
6	24.99 [0.984]	22.86 [0.900]	9	10	6-146279-0
6	22.45 [0.884]	20.32 [0.800]	8	9	5-146279-9
6	19.91 [0.784]	17.78 [0.700]	7	8	5-146279-8
6	17.37 [0.684]	15.24 [0.600]	6	7	5-146279-7
6	14.83 [0.584]	12.70 [0.500]	5	6	5-146279-6
6	12.29 [0.484]	10.16 [0.400]	4	5	5-146279-5
6	9.75 [0.384]	7.62 [0.300]	3	4	5-146279-4
6	7.21 [0.284]	5.08 [0.200]	2	3	5-146279-3
6	4.67 [0.184]	2.54 [0.100]	1	2	5-146279-2
6	2.13 [0.084]	-	0	1	5-146279-1

PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER
4	101.19 [3.984]	99.06 [3.900]	39	40	4-146279-0
4	98.65 [3.884]	96.52 [3.800]	38	39	3-146279-9
4	96.11 [3.784]	93.98 [3.700]	37	38	3-146279-8
4	93.57 [3.684]	91.44 [3.600]	36	37	3-146279-7
4	91.03 [3.584]	88.90 [3.500]	35	36	3-146279-6
4	88.49 [3.484]	86.36 [3.400]	34	35	3-146279-5
4	85.95 [3.384]	83.82 [3.300]	33	34	3-146279-4
4	83.41 [3.284]	81.28 [3.200]	32	33	3-146279-3
4	80.87 [3.184]	78.74 [3.100]	31	32	3-146279-2
4	78.33 [3.084]	76.20 [3.000]	30	31	3-146279-1
4	75.79 [2.984]	73.66 [2.900]	29	30	3-146279-0
4	73.25 [2.884]	71.12 [2.800]	28	29	2-146279-9
4	70.71 [2.784]	68.58 [2.700]	27	28	2-146279-8
4	68.17 [2.684]	66.04 [2.600]	26	27	2-146279-7
4	65.63 [2.584]	63.5 [2.500]	25	26	2-146279-6
4	63.09 [2.484]	60.96 [2.400]	24	25	2-146279-5
4	60.55 [2.384]	58.42 [2.300]	23	24	2-146279-4
4	58.01 [2.284]	55.88 [2.200]	22	23	2-146279-3
4	55.47 [2.184]	53.34 [2.100]	21	22	2-146279-2
4	52.93 [2.084]	50.80 [2.000]	20	21	2-146279-1
4	50.39 [1.984]	48.26 [1.900]	19	20	2-146279-0
4	47.85 [1.884]	45.72 [1.800]	18	19	1-146279-9
4	45.31 [1.784]	43.18 [1.700]	17	18	1-146279-8
4	42.77 [1.684]	40.64 [1.600]	16	17	1-146279-7
4	40.23 [1.584]	38.10 [1.500]	15	16	1-146279-6
4	37.69 [1.484]	35.56 [1.400]	14	15	1-146279-5
4	35.15 [1.384]	33.02 [1.300]	13	14	1-146279-4
4	32.61 [1.284]	30.48 [1.200]	12	13	1-146279-3
4	30.07 [1.184]	27.94 [1.100]	11	12	1-146279-2
4	27.53 [1.084]	25.40 [1.000]	10	11	1-146279-1
4	24.99 [0.984]	22.86 [0.900]	9	10	1-146279-0
4	22.45 [0.884]	20.32 [0.800]	8	9	1-146279-9
4	19.91 [0.784]	17.78 [0.700]	7	8	1-146279-8
4	17.37 [0.684]	15.24 [0.600]	6	7	1-146279-7
4	14.83 [0.584]	12.70 [0.500]	5	6	1-146279-6
4	12.29 [0.484]	10.16 [0.400]	4	5	1-146279-5
4	9.75 [0.384]	7.62 [0.300]	3	4	1-146279-4
4	7.21 [0.284]	5.08 [0.200]	2	3	1-146279-3
4	4.67 [0.184]	2.54 [0.100]	1	2	1-146279-2
4	2.13 [0.084]	-	0	1	1-146279-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	±	-
1. PLC	±	0.127 [0.005]
2. PLC	±	0.254 [0.010]
3. PLC	±	0.508 [0.020]
4. PLC	±	1.27 [0.050]
ANGLES	±	0.127 [0.005]

MATERIAL: **3** FINISH: SEE TABLE

WEIGHT: 0.000000

CUSTOMER DRAWING

DIN: T. HOFFMAN 6/12/95

CHK: G. DUBNICZKI 3/18/96

APPV: G. DUBNICZKI 3/18/96

NAME: G. DUBNICZKI

APPLICATION SPEC

SIZE: A1

SCALE: 4:1

SHEET: 1 of 1

REV: G1

TE Connectivity

HEADER ASSY, MOD II, B/A, SINGLE ROW, HIGH TEMP, VERT W/.025 SQ POSTS, .100 C