Product data sheet Characteristics

RPM1SOC24D

Plug in relay, Zelio Relay, SPDT, power, socket, 24 VDC coil



Main

Range of Product	Harmony Relay
Series name	Power
Product or Component Type	Plug-in relay
Device short name	RPM
Contacts type and composition	1 C/O
[Uc] control circuit voltage	24 V DC
[Ithe] conventional enclosed thermal current	15 A -40131 °F (-4055 °C)
Status LED	With
Control Type	Lockable test button
Utilisation coefficient	20 %

Complementary

Complementary	
Shape of pin	Flat
[Ui] rated insulation voltage	250 V IEC
	300 V CSA
	300 V UL
[Uimp] rated impulse withstand voltage	4 kV 1.2/50 μs
Contacts material	AgNi
[le] rated operational current	15 A 277 V AC) UL
	15 A 28 V DC) UL
	15 A 250 V AC) NO IEC
	15 A 28 V DC) NO IEC 7.5 A 250 V AC) NC IEC
	7.5 A 28 V DC) NC IEC
Maximum switching voltage	250 V IEC
Resistive load current	15 A 250 V AC
	15 A 28 V DC
Maximum switching capacity	3750 VA
	420 W
Minimum switching capacity	170 mW 10 mA, 17 V
Operating rate	<= 1200 cycles/hour under load
	<= 18000 cycles/hour no-load
Mechanical durability	10000000 cycles
Electrical durability	100000 cycles resistive
Average coil consumption	1.1 W
Drop-out voltage threshold	>= 0.1 Uc DC
Operate time	20 ms at nominal voltage
Release time	20 ms at nominal voltage
Average coil resistance	450 Ohm at 68 °F (20 °C) +/- 10 %
Rated operational voltage limits	19.226.4 V DC
Protection category	RTI
Operating position	Any position
Pollution degree	3
Safety reliability data	B10d = 100000
Net Weight	0.06 lb(US) (0.026 kg)
Device presentation	Complete product

Environment

Dielectric strength	1500 V AC between contacts with micro disconnection 2000 V AC between coil and contact with reinforced	
Standards	UL 508 CSA C22.2 No 14 EN/IEC 61810-1	
Product Certifications	EAC UL CSA	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Ambient air temperature for operation	-40131 °F (-4055 °C)	
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating	
Degree of protection (Housing only)	IP40 conforming to EN/IEC 60529	
Shock resistance	15 gnin operation 30 gnnot operating	

Ordering and shipping details

Category	22750-INDUSTRIAL POINT OF PURCHASE
Discount Schedule	IPOP
GTIN	785901659433
Nbr. of units in pkg.	1
Package weight(Lbs)	2.00 lb(US) (0.907 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	19.05 in (48.387 cm)
Package 1 width	7.50 in (19.05 cm)
Package 1 Length	48.39 in (122.903 cm)

Offer Sustainability

Office Oddital lability	
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	€Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.