

MLX90411-L

SINGLE-COIL FAN DRIVER

LOW NOISE FAN DRIVER FOR AUTOMOTIVE APPLICATIONS

MLX90411-L _

The **L-grade version** of the MLX90411 operates over a supply voltage range from 3.2 V to 32 V, and is robust up to 40 V. With an operating temperature up to 150°C, it is a perfect fit for any automotive fan, blower or pump application on a 5 V regulated supply, or directly on the 12 V boardnet, or even the 24 V boardnet for trucks. With current limit options **from 330 mA up to 800 mA**, the MLX90411 can drive automotive applications **from 0.1 W up to 7 W** in a safe and cost effective way, without risk for overheating the device or the motor coil. The closed-loop speed control limits the speed variation to less than +/-5% regardless of the load condition, battery voltage variation, or fan production tolerances over the full temperature range. Together with the adaptive low noise commutation it enables industry standard efficiency and acoustic performance. Multiple commutation options are available, including a sinewave option offering unprecedented low levels of vibration.



KEY FEATURES

- All-in-one fan driver, including high-sensitivity Hall-effect sensor
- 🕑 Up to 800 mA motor current
- Adaptive commutuation for best in class efficiency over the full speed range for any fan design
- Ocommutation options
 - Maximum torque
 - Very low acoustic noise
- 🞯 PWM control input
 - Open loop
 - Closed loop speed control (+/-5%)
- Operating supply range from 3.2 V to 32 V
- Operating junction temperature from -40 to 150°C

- Orotections and diagnostics
 - Locked Rotor Protection (LRP) (Programmable
 - Temperature Shutdown (TSD)
 - Over Voltage protection (OVP) (Programmable)
 - Short circuit protection (OCP)
 - Current limit (CL)
 - FG/RD open drain diagnostics output (Programmable)
- ⊘ Certifications MLX90411-L
 - AEC-Q100-Rev-H qualified packages
 - Automotive PPAP (PSW)
- Ø I2C programming
 - Fast prototyping
 - End-of-line programming
- 🞯 Package
 - Straight-lead SOT package (ZE)
 - Tiny UTDFN 2.5 x 2.0 x 0.4 mm (LD)



APPLICATION VISUALS







Seat fans

LED headlight cooling



he above information is "asis" and believed to be correct and accurate. Melevis disclaims any and all liability in connection with or arising out of the furnishing, application or use of the information or products; any and all liability, including without limitation, special, consequential or incidental damages; and any and liverantiles, express, statutory, implied, or by description, including warranties of fitness for particular purpose, non-infingement and metch entability. Meiosis reserves the right to change its any time and without holice. Users should obtain the latest version of the version of the simulation, special and express must further determine the suitability of a product to its application, including warranties of fitness for particular purpose. The transmission of the application is particular purpose. The application is a particular purpose. Export control regulators may apply and eport might regulate any includent the level of reliability in connection withing, the products are interded for use in normal commercial applications. Unless otherwise agreed upon in writing, the products are not designed, authorized or warranted to be suitable in application sequing extended there and enter the sime of the suitable in application requiring extended temperature angle and/or unusual environmental equirements. High reliability in outifications are model if the subsection of the suitable in applications and thirds. How member and the site of the suitable in applications are determed and there and the end of the suitable in applications are determed and the suitable sequence in the suitable sequence and the suitable sequence and the suitable may application sequence and