



Mechanical Dimensions: Inches [mm]

Tolerances ± 0.012 [0.3] Unless Otherwise Specified


Mounting Hole



Thickness	X	Y
0.03~0.05 [0.75~1.25]	0.83 [21.2 ± 0.1]	1.44 [36.6 ± 0.1]
0.05~0.08 [1.25~2.0]	0.83 [21.2 ± 0.1]	1.45 [36.8 ± 0.1]
0.08~0.12 [2.0~3.0]	0.83 [21.2 ± 0.1]	1.46 [37.0 ± 0.1]

Circuit Diagram

4P SPDT ON-OFF-ON (LED-D)



Electrical Specifications

Rating	21A 14V DC	
Contact Resistance	50m ohm Max	
Insulation Resistance	DC 500V 100M ohm Min	
Dielectric Strength	AC 1500V 1minute	
Operation Temperature	-20°C~85°C	

Material Specifications

Frame	Black, Nylon #66
Actuator	Black, Nylon #66
LED	Amber/Amber, LEDs (Dependent)

Rocker Switch

SRA2-1F-DC-1-AA



Rev Date of issue Revision Notes

Designed Approved

B	02-26-2020	Initial Drawing	RC	OF
---	------------	-----------------	----	----