

128Mb DDR SDRAM HY5DU281622FTP



Revision History

Revision No.	History	Draft Date	Remark
0.01	First version for internal review	Feb. 2006	
0.02	State Diagram modified	Apr. 2006	
0.03	Defined : IDD value	Apr. 2006	



DESCRIPTION

The HY5DU281622FT(P) is a 134,217,728-bit CMOS Double Data Rate(DDR) Synchronous DRAM, ideally suited for the main memory applications which requires large memory density and high bandwidth.

This Hynix 128Mb DDR SDRAMs offer fully synchronous operations referenced to both rising and falling edges of the clock. While all addresses and control inputs are latched on the rising edges of the CK (falling edges of the /CK), Data, Data strobes and Write data masks inputs are sampled on both rising and falling edges of it. The data paths are internally pipelined and 2-bit prefetched to achieve very high bandwidth. All input and output voltage levels are compatible with SSTL_2.

FEATURES

- VDD, VDDQ = 2.3V min ~ 2.7V max
 (Typical 2.5V Operation +/- 0.2V for DDR266, 333)
- VDD, VDDQ = 2.4V min ~ 2.7V max (Typical 2.6V Operation +0.1/- 0.2V for DDR400 and 400Mbps/pin product)
- All inputs and outputs are compatible with SSTL_2 interface
- Fully differential clock inputs (CK, /CK) operation
- · Double data rate interface
- Source synchronous data transaction aligned to bidirectional data strobe (DQS)
- x16 device has two bytewide data strobes (UDQS, LDQS) per each x8 I/O
- Data outputs on DQS edges when read (edged DQ)
 Data inputs on DQS centers when write (centered DQ)
- On chip DLL align DQ and DQS transition with CK transition
- DM mask write data-in at the both rising and falling edges of the data strobe

- All addresses and control inputs except data, data strobes and data masks latched on the rising edges of the clock
- Programmable CAS latency 2/2.5 (DDR266, 333) and 3 (DDR400 and 400Mbps/pin product) supported
- Programmable burst length 2/4/8 with both sequential and interleave mode
- Internal four bank operations with single pulsed /RAS
- · Auto refresh and self refresh supported
- tRAS lock out function supported
- 4096 refresh cycles/64ms
- JEDEC standard 400mil 66pin TSOP-II with 0.65mm pin pitch
- Lead free (*ROHS Compliant)

ORDERING INFORMATION

OPERATING FREQUENCY

Part No.	Configuration	Package
HY5DU281622F(L)TP-X*	8Mx16	400mil 66pin TSOP-II**

^{*} X means speed grade


Grade	Clock	Remark	
-5	200MH	łz@CL3	400Mbps/pin (maxi- mum Date rate)
-D43	200MF	łz@CL3	DDR400B (3-3-3)
-D4	200MH	łz@CL3	DDR400 (3-4-4)
- J	133MHz@CL2	166MHz @CL2.5 & @CL3	DDR333 (2.5-3-3) DDR333 (3-3-3)
- K	133MHz@CL2	133MHz@CL2.5	DDR266A (2-3-3)
- H	100MHz@CL2	133MHz@CL2.5	DDR266B (2.5-3-3)

^{**} Lead-free product

^{*}ROHS (Restriction Of Hazardous Substances)



PIN CONFIGURATION



ROW AND COLUMN ADDRESS INFORMATION

Organization : 2M x 16 x 4banks

Row Address: A0 - A11
Column Address: A0 - A8
Bank Address: BA0, BA1
Auto Precharge Flag: A10

Refresh : 4K

Rev. 0.03 /Jun. 2006 4



PIN DESCRIPTION


PIN	TYPE	DESCRIPTION
CK, /CK	Input	Clock: CK and /CK are differential clock inputs. All address and control input signals are sampled on the crossing of the positive edge of CK and negative edge of /CK. Output (read) data is referenced to the crossings of CK and /CK (both directions of crossing).
CKE	Input	Clock Enable: CKE HIGH activates, and CKE LOW deactivates internal clock signals, and device input buffers and output drivers. Taking CKE LOW provides PRECHARGE POWER DOWN and SELF REFRESH operation (all banks idle), or ACTIVE POWER DOWN (row ACTIVE in any bank). CKE is synchronous for POWER DOWN entry and exit, and for SELF REFRESH entry. CKE is asynchronous for SELF REFRESH exit, and for output disable. CKE must be maintained high throughout READ and WRITE accesses. Input buffers, excluding CK, /CK and CKE are disabled during POWER DOWN. Input buffers, excluding CKE are disabled during SELF REFRESH. CKE is an SSTL_2 input, but will detect an LVCMOS LOW level after VDD is applied.
/CS	Input	Chip Select: Enables or disables all inputs except CK, /CK, CKE, DQS and DM. All commands are masked when Chip Select is registered high. Chip Select provides for external bank selection on systems with multiple banks. Chip Select is considered part of the command code.
BAO, BA1	Input	Bank Address Inputs: BAO and BA1 define to which bank an ACTIVE, Read, Write or PRECHARGE command is being applied.
A0 ~ A11	Input	Address Inputs: Provide the row address for ACTIVE commands, and the column address and AUTO PRECHARGE bit for READ/WRITE commands, to select one location out of the memory array in the respective bank. A10 is sampled during a precharge command to determine whether the PRECHARGE applies to one bank (A10 LOW) or all banks (A10 HIGH). If only one bank is to be precharged, the bank is selected by BAO, BA1. The address inputs also provide the op code during a MODE REGISTER SET command. BAO and BA1 define which mode register is loaded during the MODE REGISTER SET command (MRS or EMRS).
/RAS, /CAS, / WE	Input	Command Inputs: /RAS, /CAS and /WE (along with /CS) define the command being entered.
DM (LDM,UDM)	Input	Input Data Mask: DM is an input mask signal for write data. Input data is masked when DM is sampled HIGH along with that input data during a WRITE access. DM is sampled on both edges of DQS. Although DM pins are input only, the DM loading matches the DQ and DQS loading. For the x16, LDM corresponds to the data on DQ0-Q7; UDM corresponds to the data on DQ8-Q15.
DQS (LDQS,UDQS)	I/O	Data Strobe: Output with read data, input with write data. Edge aligned with read data, centered in write data. Used to capture write data. For the x16, LDQS corresponds to the data on DQ0-Q7; UDQS corresponds to the data on DQ8-Q15.
DQ	I/O	Data input / output pin: Data bus
VDD / VSS	Supply	Power supply for internal circuits and input buffers.
VDDQ / VSSQ	Supply	Power supply for output buffers for noise immunity.
V <i>REF</i>	Supply	Reference voltage for inputs for SSTL interface.
NC	NC	No connection.

Rev. 0.03 /Jun. 2006 5



Functinal Block Diagram (8M x16)

4Banks x 2Mbit x 16I/O Double Data Rate Syncronous DRAM





SIMPLIFIED COMMAND TRUTH TABLE

Command		CKEn-1	CKEn	cs	RAS	CAS	WE	ADDR	A10 /AP	ва	Note
Extended Mode Register Set		Н	Х	L	L	L	L	OP code			1,2
Mode Regist	er Set	Н	Х	L	L	L	L	0	P code		1,2
Device Des	elect	Н	Х	Н	Х	Х	Х		Х		1
No Operat	tion	П	^	L	Н	Н	Н			I	
Bank Acti	ive	Н	Х	L	L	Н	Н	R/	4	V	1
Read		Н	Х	L	Н	L	Н	CA	L	V	1
Read with Autor	orecharge	П	^	L	П	L	П	CA	Н	v	1,3
Write		Н	Х	L	Н	L	L	CA	L	V	1
Write with Autor	Write with Autoprecharge		X	L	П	L	L	CA	Н	v	1,4
Precharge All	Precharge All Banks		х	L	L	Н	L	Х	Н	Х	1,5
Precharge selec	Precharge selected Bank						L	^	L	V	1
Read Burst	Stop	Н	Х	L	Н	Н	L	Х		1	
Auto Refre	esh	Н	Н	L	L	L	Н	Х		1	
	Entry	Н	L	L	L	L	Н				1
Self Refresh	Exit	L	Н	Н	Х	Х	Х		Χ		1
	EXIL	_	П	L	Н	Н	Н				!
	Entry	Н	L	Н	Х	Х	Х				1
Precharge	Entry	П	_	L	Н	Н	Н		Х		1
Power Down Mode	Exit	L	Н	Н	Х	Х	Х	X			1
ivioue	EXIL		"	L	Н	Н	Н				1
	Entry	Н	L	Н	Х	Х	Х				1
Active Power Down Mode	Entry			L	V	V	V	X			1
	Exit	L	Н)	K					1

(H=Logic High Level, L=Logic Low Level, X=Don't Care, V=Valid Data Input, OP Code=Operand Code, NOP=No Operation)



Note:

- 1. UDM, LDM states are Don't Care. Refer to below Write Mask Truth Table.(note 6)
- 2. OP Code(Operand Code) consists of A0~A11 and BA0~BA1 used for Mode Register setting during Extended MRS or MRS. Before entering Mode Register Set mode, all banks must be in a precharge state and MRS command can be issued after tRP period from Prechagre command.
- 3. If a Read with Auto-precharge command is detected by memory component in CK(n), then there will be no command presented to activate bank until CK(n+BL/2+tRP).
- 4. If a Write with Auto-precharge command is detected by memory component in CK(n), then there will be no command presented to activate bank until CK(n+BL/2+1+tDPL+tRP). Last Data-In to Prechage delay(tDPL) which is also called Write Recovery Time(tWR) is needed to guarantee that the last data have been completely written.
- 5. If A10/AP is High when Precharge command being issued, BA0/BA1 are ignored and all banks are selected to be precharged.
- 6. In here, Don't Care means logical value only, it doesn't mean 'Don't care for DC level of each signals'. DC level should be out of $V_{IHmin} \sim V_{ILmax}$

WRITE MASK TRUTH TABLE


Function	CKEn-1	CKEn	/CS, /RAS, /CAS, /WE	DM	ADD R	A10/ AP	ВА	Note		
Data Write	Н	Χ	Х	L		Χ		1,2		
Data-In Mask	Н	Х	Х	Н	X		Х			1,2

Note:

- 1. Write Mask command masks burst write data with reference to LDQS/UDQS(Data Strobes) and it is not related with read data. In case of x16 data I/O, LDM and UDM control lower byte(DQ0~7) and Upper byte(DQ8~15) respectively.
- 2. In here, Don't Care means logical value only, it doesn't mean 'Don't care for DC level of each signals'. DC level should be out of $V_{IHmin} \sim V_{ILmax}$



SIMPLIFIED STATE DIAGRAM





POWER-UP SEQUENCE AND DEVICE INITIALIZATION

DDR SDRAMs must be powered up and initialized in a predefined manner. Operational procedures other than those specified may result in undefined operation. Power must first be applied to VDD, then to VDDQ, and finally to VREF (and to the system VTT). VTT must be applied after VDDQ to avoid device latch-up, which may cause permanent damage to the device. VREF can be applied anytime after VDDQ, but is expected to be nominally coincident with VTT. Except for CKE, inputs are not recognized as valid until after VREF is applied. CKE is an SSTL_2 input, but will detect an LVCMOS LOW level after VDD is applied. Maintaining an LVCMOS LOW level on CKE during power-up is required to guarantee that the DQ and DQS outputs will be in the High-Z state, where they will remain until driven in normal operation (by a read access). After all power supply and reference voltages are stable, and the clock is stable, the DDR SDRAM requires a 200us delay prior to applying an executable command.

Once the 200us delay has been satisfied, a DESELECT or NOP command should be applied, and CKE should be brought HIGH. Following the NOP command, a PRECHARGE ALL command should be applied. Next a EXTENDED MODE REGISTER SET command should be issued for the Extended Mode Register, to enable the DLL, then a MODE REGISTER SET command should be issued for the Mode Register, to reset the DLL, and to program the operating parameters. After the DLL reset, tXSRD(DLL locking time) should be satisfied for read command. After the Mode Register set command, a PRECHARGE ALL command should be applied, placing the device in the all banks idle state.

Once in the idle state, two AUTO REFRESH cycles must be performed. Additionally, a MODE REGISTER SET command for the Mode Register, with the reset DLL bit deactivated low (i.e. to program operating parameters without resetting the DLL) must be performed. Following these cycles, the DDR SDRAM is ready for normal operation.


- Apply power VDD, VDDQ, VTT, VREF in the following power up sequencing and attempt to maintain CKE at LVC-MOS low state. (All the other input pins may be undefined.)
 - VDD and VDDQ are driven from a single power converter output.
 - VTT is limited to 1.44V (reflecting VDDQ(max)/2 + 50mV VREF variation + 40mV VTT variation.
 - VREF tracks VDDQ/2.
 - If the above criteria cannot be met by the system design, then the following sequencing and voltage relationship must be adhered to during power up.

Voltage description	Sequencing	Voltage relationship to avoid latch-up
V <i>DDQ</i>	After or with V <i>DD</i>	< V <i>DD</i> + 0.3V
VTT	After or with V <i>DDQ</i>	< V <i>DDQ</i> + 0.3V
VREF	After or with VDDQ	< V <i>DDQ</i> + 0.3V

- 2. Start clock and maintain stable clock for a minimum of 200usec.
- 3. After stable power and clock, apply NOP condition and take CKE high.
- 4. Issue Extended Mode Register Set (EMRS) to enable DLL.
- Issue Mode Register Set (MRS) to reset DLL and set device to idle state with bit A8=high. (An additional 200 cycles(tXSRD) of clock are required for locking DLL)
- 6. Issue Precharge commands for all banks of the device.
- 7. Issue 2 or more Auto Refresh commands.
- 8. Issue a Mode Register Set command to initialize the mode register with bit A8 = Low



Power-Up Sequence




* 200 cycle(tXSRD) of CK are required (for DLL locking) before Read Command



MODE REGISTER SET (MRS)

The mode register is used to store the various operating modes such as /CAS latency, addressing mode, burst length, burst type, test mode, DLL reset. The mode register is programed via MRS command. This command is issued by the low signals of /RAS, /CAS, /CS, /WE and BAO. This command can be issued only when all banks are in idle state and CKE must be high at least one cycle before the Mode Register Set Command can be issued. Two cycles are required to write the data in mode register. During the MRS cycle, any command cannot be issued. Once mode register field is determined, the information will be held until reset by another MRS command.





BURST DEFINITION

Burst Length	Starting Address (A2,A1,A0)	Sequential	Interleave
2	XX0	0, 1	0, 1
2	XX1	1, 0	1, 0
	X00	0, 1, 2, 3	0, 1, 2, 3
4	X01	1, 2, 3, 0	1, 0, 3, 2
4	X10	2, 3, 0, 1	2, 3, 0, 1
	X11	3, 0, 1, 2	3, 2, 1, 0
	000	0, 1, 2, 3, 4, 5, 6, 7	0, 1, 2, 3, 4, 5, 6, 7
	001	1, 2, 3, 4, 5, 6, 7, 0	1, 0, 3, 2, 5, 4, 7, 6
	010	2, 3, 4, 5, 6, 7, 0, 1	2, 3, 0, 1, 6, 7, 4, 5
8	011	3, 4, 5, 6, 7, 0, 1, 2	3, 2, 1, 0, 7, 6, 5, 4
0	100	4, 5, 6, 7, 0, 1, 2, 3	4, 5, 6, 7, 0, 1, 2, 3
	101	5, 6, 7, 0, 1, 2, 3, 4	5, 4, 7, 6, 1, 0, 3, 2
	110	6, 7, 0, 1, 2, 3, 4, 5	6, 7, 4, 5, 2, 3, 0, 1
	111	7, 0, 1, 2, 3, 4, 5, 6	7, 6, 5, 4, 3, 2, 1, 0

BURST LENGTH & TYPE

Read and write accesses to the DDR SDRAM are burst oriented, with the burst length being programmable. The burst length determines the maximum number of column locations that can be accessed for a given Read or Write command. Burst lengths of 2, 4 or 8 locations are available for both the sequential and the interleaved burst types. Reserved states should not be used, as unknown operation or incompatibility with future versions may result.

When a Read or Write command is issued, a block of columns equal to the burst length is effectively selected. All accesses for that burst take place within this block, meaning that the burst wraps within the block if a boundary is reached. The block is uniquely selected by A1-Ai when the burst length is set to two, by A2 -Ai when the burst length is set to four and by A3 -Ai when the burst length is set to eight (where Ai is the most significant column address bit for a given configuration). The remaining (least significant) address bit(s) is (are) used to select the starting location within the block. The programmed burst length applies to both Read and Write bursts.

Accesses within a given burst may be programmed to be either sequential or interleaved; this is referred to as the burst type and is selected via bit A3. The ordering of accesses within a burst is determined by the burst length, the burst type and the starting column address, as shown in Burst Definition Table



CAS LATENCY

The Read latency or CAS latency is the delay in clock cycles between the registration of a Read command and the availability of the first burst of output data. The latency can be programmed 2 or 2.5 clocks for DDR266/333 and 3 clocks for DDR400.

If a Read command is registered at clock edge n, and the latency is m clocks, the data is available nominally coincident with clock edge n + m.

Reserved states should not be used as unknown operation or incompatibility with future versions may result.

DLL RESET

The DLL must be enabled for normal operation. DLL enable is required during power up initialization, and upon returning to normal operation after having disabled the DLL for the purpose of debug or evaluation. The DLL is automatically disabled when entering self refresh operation and is automatically re-enabled upon exit of self refresh operation. Any time the DLL is enabled, 200 clock cycles must occur to allow time for the internal clock to lock to the externally applied clock before an any command can be issued.

OUTPUT DRIVER IMPEDANCE CONTROL


The normal drive strength for all outputs is specified to be SSTL_2, Class II. Hynix also supports a half strength driver option, intended for lighter load and/or point-to-point environments. Selection of the half strength driver option will reduce the output drive strength by 50% of that of the full strength driver. I-V curves for both the full strength driver and the half strength driver are included in this document.



EXTENDED MODE REGISTER SET (EMRS)

The Extended Mode Register controls functions beyond those controlled by the Mode Register; these additional functions include DLL enable/disable, output driver strength selection(optional). These functions are controlled via the bits shown below. The Extended Mode Register is programmed via the Mode Register Set command (BA0=1 and BA1=0) and will retain the stored information until it is programmed again or the device loses power.

The Extended Mode Register must be loaded when all banks are idle and no bursts are in progress, and the controller must wait the specified time before initiating any subsequent operation. Violating either of these requirements will result in unspecified operation.



^{*} This part do not support/QFC function, A2 must be programmed to Zero.



ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Rating	Unit
Operating Temperature (Ambient)	T <i>A</i>	0 ~ 70	°C
Storage Temperature	T <i>STG</i>	-55 ~ 150	°C
Voltage on VDD relative to VSS	V <i>DD</i>	-1.0 ~ 3.6	V
Voltage on VDDQ relative to VSS	V <i>DDQ</i>	-1.0 ~ 3.6	V
Voltage on inputs relative to VSS	V INPUT	-1.0 ~ 3.6	V
Voltage on I/O pins relative to VSS	V <i>IO</i>	-0.5 ~3.6	V
Output Short Circuit Current	105	50	mA
Soldering Temperature · Time	T <i>SOLDER</i>	260 · 10	°C · Sec

Note: Operation at above absolute maximum rating can adversely affect device reliability

DC OPERATING CONDITIONS (TA=0 to 70 °C, Voltage referenced to VSS = 0V)

	Parameter	Symbol	Min	Тур.	Max	Unit
Power Supply Volta	age (DDR200, 266, 333)	V <i>DD</i>	2.3	2.5	2.7	V
Power Supply Volta	age (DDR200, 266, 333) ¹	V <i>DDQ</i>	2.3	2.5	2.7	V
Power Supply Volta	age (DDR400)	V <i>DD</i>	2.4	2.6	2.7	V
Power Supply Volta	age (DDR400) ¹	V <i>DDQ</i>	2.4	2.6	2.7	V
Input High Voltage)	V <i>IH</i>	V <i>REF</i> + 0.15	-	V <i>DDQ</i> + 0.3	V
Input Low Voltage	2	V/L	-0.3	-	V <i>REF</i> - 0.15	V
Termination Voltage	je	V <i>TT</i>	V <i>REF</i> - 0.04	V <i>REF</i>	V <i>REF</i> + 0.04	V
Reference Voltage	3	V <i>REF</i>	0.49*VDDQ	0.5*VDDQ	0.51*VDDQ	V
Input Voltage Leve	el, CK and CK inputs	V //V(DC)	-0.3	-	VDDQ+0.3	V
Input Differential Voltage, CK and CK inputs ⁴		V <i>ID</i> (DC)	0.36	-	VDDQ+0.6	V
V-I Matching: Pullup to Pulldown Current Ratio ⁵		V/(RATIO)	0.71	-	1.4	-
Input Leakage Cur	Input Leakage Current ⁶		-2	-	2	uA
Output Leakage C	urrent ⁷	I <i>LO</i>	-5	=	5	uA
Normal Strength Output Driver	Output High Current (min V <i>DDQ</i> , min V <i>REF</i> , min V <i>TT</i>)	I <i>OH</i>	-16.8	-	-	mA
(V <i>OUT</i> =V <i>TT</i> ± 0.84)	Output Low Current (min V <i>DDQ</i> , max V <i>REF</i> , max V 77)	I <i>OL</i>	16.8	-	-	mA
Half Strength Output Driver (V <i>OUT</i> =V <i>TT</i> ± 0.68)	Output High Current (min V <i>DDQ</i> , min V <i>REF</i> , min V <i>TT</i>)	I <i>OH</i>	-13.6	-	-	mA
	Output Low Current (min V <i>DDQ</i> , max V <i>REF</i> , max V <i>TT</i>)	I <i>OL</i>	13.6	-	-	mA

Note

- 1. VDDQ must not exceed the level of VDD.
- 2. V/L (min) is acceptable -1.5V AC pulse width with \leq 5ns of duration.
- 3. VREF is expected to be equal to 0.5*VDDQ of the transmitting device, and to track variations in the dc level of the same. Peak to peak noise on VREF may not exceed \pm 2% of the DC value.
- 4. VID is the magnitude of the difference between the input level on CK and the input level on /CK.



- 5. The ratio of the pullup current to the pulldown current is specified for the same temperature and voltage, over the entire temperature and voltage range, for device drain to source voltages from 0.25V to 1.0V. For a given output, it represents the maximum difference between pullup and pulldown drivers due to process variation. The full variation in the ratio of the maximum to minimum pullup and pulldown current will not exceed 1/7 for device drain to source voltages from 0.1 to 1.0.
- 6. VIN=0 to VDD_r All other pins are not tested under VIN=0V.
- 7. DQs are disabled, VOUT=0 to VDDQ

IDD SPECIFICATION AND CONDITIONS (TA=0 to 70 °C, Voltage referenced to Vss = 0V)

Test Conditions

Test Condition	Symbol
Operating Current: One bank; Active - Precharge; tRC=tRC(min); tCK=tCK(min); DQ,DM and DQS inputs changing twice per clock cycle; address and control inputs changing once per clock cycle	I <i>DD0</i>
Operating Current: One bank; Active - Read - Precharge; Burst Length=2; tRC=tRC(min); tCK=tCK(min); address and control inputs changing once per clock cycle	I <i>DD1</i>
Precharge Power Down Standby Current: All banks idle; Power down mode; CKE=Low, tCK=tCK(min)	I <i>DD2P</i>
Idle Standby Current: /CS=High, All banks idle; t <i>CK</i> =t <i>CK</i> (min); CKE=High; address and control inputs changing once per clock cycle. V <i>IN</i> =V <i>REF</i> for DQ, DQS and DM	1 <i>DD2F</i>
Idle Quiet Standby Current: /CS>=Vih(min); All banks idle; CKE>=Vih(min); Addresses and other control inputs stable, Vin=Vref for DQ, DQS and DM	I <i>DD2Q</i>
Active Power Down Standby Current: One bank active; Power down mode; CKE=Low, tCK=tCK(min)	I <i>DD3P</i>
Active Standby Current: /CS=HIGH; CKE=HIGH; One bank; Active-Precharge; tRC=tRAS(max); tCK=tCK(min); DQ, DM and DQS inputs changing twice per clock cycle; Address and other control inputs changing once per clock cycle	I <i>DD3N</i>
Operating Current: Burst=2; Reads; Continuous burst; One bank active; Address and control inputs changing once per clock cycle; tCK=tCK(min); IOUT=0mA	I <i>DD4R</i>
Operating Current: Burst=2; Writes; Continuous burst; One bank active; Address and control inputs changing once per clock cycle; tCK=tCK(min); DQ, DM and DQS inputs changing twice per clock cycle	I <i>DD4W</i>
Auto Refresh Current: tRC=tRFC(min) - 8*tCK for DDR200 at 100Mhz, 10*tCK for DDR266A & DDR266B at 133Mhz; distributed refresh tRC=tRFC(min) - 14*tCK for DDR400 at 200Mhz	I <i>DD5</i>
Self Refresh Current: CKE =< 0.2V; External clock on; t <i>CK</i> =t <i>CK</i> (min)	I <i>DD6</i>
Operating Current - Four Bank Operation: Four bank interleaving with BL=4, Refer to the following page for detailed test condition	I <i>DD7</i>



DC CHARACTERISTICS II (TA=0 to 70 °C, Voltage referenced to Vss = 0V)

8Mx16 (2M x4Bank x16I/O)

			Speed					
Parameter	Symbo	Test Condition	5/ D43/ D4 J		K	Н	Unit	Note
			200	133	133	100	MHz	
Operating Current	1 <i>DD0</i>	One bank; Active - Precharge; tRC=tRC(min); tCK=tCK(min); DQ,DM and DQS inputs changing twice per clock cycle; address and control inputs changing once per clock cycle	120	110	100	100	mA	
Operating Current	I <i>DD1</i>	One bank; Active - Read - Precharge; Burst Length=2; tRC=tRC(min); tCK=tCK(min); address and control inputs changing once per clock cycle	120	110	100	100	mA	
Precharge Power Down Standby Current	1 <i>DD2P</i>	All banks idle; Power down mode; CKE=Low, t <i>CK</i> =t <i>CK</i> (min)	20		15		mA	
Idle Standby Current	I <i>DD2N</i>	V/N>=V/H(min) or V/N= <v and="" dm<="" dq,="" dqs="" for="" l(max)="" td=""><td colspan="2">60</td><td colspan="2">-</td><td>mA</td><td></td></v>	60		-		mA	
Idle Standby Current	1 <i>DD2F</i>	/CS=High, All banks idle; t <i>CK</i> =t <i>CK</i> (min); CKE=High; address and control inputs changing once per clock cycle. V /N=V REF for DQ, DQS and DM	60 50		50 45		mA	
Idle Quiet Standby Current	I <i>DD2Q</i>	/CS>=V/H(min); All banks idle; CKE>=V/H(min); Addresses and other control inputs stable, V/N=Vref for DQ, DQS and DM	60 -			mA		
Active Power Down Standby Current	1 <i>DD3P</i>	One bank active; Power down mode; CKE=Low, t <i>CK</i> =t <i>CK</i> (min)	20			mA		
Active Standby Current	I <i>DD3N</i>	/CS=HIGH; CKE=HIGH; One bank; Active- Precharge; tRC=tRAS(max); tCK=tCK(min); DQ, DM and DQS inputs changing twice per clock cycle; Address and other control inputs changing once per clock cycle	70	60	5	0	mA	



			S	peed			Unit	
Parameter	Symbo	Test Condition	5/ D43/ D4	J	К	Н	Oilit	Note
			200	133	133	100	MHz	
Operating Current	I <i>DD4R</i>	Burst=2; Reads; Continuous burst; One bank active; Address and control inputs changing once per clock cycle; tCK=tCK(min); IOUT=0mA	200	160	15	50		
Operating Current	I <i>DD4W</i>	Burst=2; Writes; Continuous burst; One bank active; Address and control inputs changing once per clock cycle; tCK=tCK(min); DQ, DM and DQS inputs changing twice per clock cycle	200	160	15	150		
Auto Refresh Current	I <i>DD5</i>	t <i>RC</i> =t <i>RFC</i> (min) - 14*t <i>CK</i> for DDR400 at 200Mhz	200	200 180 170		70		
Self Refresh Current	1 <i>DD6</i>	CKE =< 0.2V; External clock on; tCK=tCK(min)	3		2		mA	
Operating Current - Four Bank Operation	I <i>DD7</i>	Four bank interleaving with BL=4, Refer to the following page for detailed test condition	300	250	23	30	mA	
Random Read Current	I <i>DD7A</i>	4banks active read with activate every 20ns, AP(Auto Precharge) read every 20ns, BL=4, t <i>RCD</i> =3, I <i>OUT</i> =0 mA, 100% DQ, DM and DQS inputs changing twice per clock cycle; 100% addresses changing once per clock cycle	300		-		mA	



DETAILED TEST CONDITIONS FOR DDR SDRAM IDD1 & IDD7

IDD1: Operating current: One bank operation

1. Typical Case : VDD = 2.6V, T=25 °C

2. Worst Case : VDD = 2.7V, T = 0 °C

3. Only one bank is accessed with tRC(min), Burst Mode, Address and Control inputs on NOP edge are changing once per clock cycle. lout = 0mA

4. Timing patterns

- DDR400(200Mhz, CL=3) : t CK = 5ns, CL = 3, BL = 4, t RCD = 3*t CK, t RC = 11*t CK, t RAS = 8*t CK Read : A0 N N R0 N N P0 N N A0 N - repeat the same timing with random add

Legend : A=Activate, R=Read, W=Write, P=Precharge, N=NOP

IDD7 : Operating current: Four bank operation

1. Typical Case : VDD = 2.6V, T=25 °C

2. Worst Case : VDD = 2.7V, T = 0 °C

3. Four banks are being interleaved with tRC(min), Burst Mode, Address and Control inputs on NOP edge are not changing. lout = 0mA

4. Timing patterns

- DDR400(200Mhz, CL=3) : tCK = 5ns, CL = 3, BL = 4, tRRD = 2*tCK, tRCD = 3*tCK, Read with autoprecharge Read : A0 N A1 R0 A2 R1 A3 R2 N R3 A0 N A1 R0 - repeat the same timing with random address changing 50% of data changing at every burst

Legend: A=Activate, R=Read, W=Write, P=Precharge, N=NOP



AC OPERATING CONDITIONS (TA=0 to 70 °C, Voltage referenced to VSS = 0V)

Parameter	Symbol	Min	Max	Unit
Input High (Logic 1) Voltage, DQ, DQS and DM signals	V <i>IH</i> (AC)	V <i>REF</i> + 0.31	-	V
Input Low (Logic 0) Voltage, DQ, DQS and DM signals	V/L(AC)	-	V <i>REF</i> - 0.31	V
Input Differential Voltage, CK and /CK inputs ¹	V <i>ID</i> (AC)	0.7	V <i>DDQ</i> + 0.6	V
Input Crossing Point Voltage, CK and /CK inputs ²	V /X(AC)	0.5*V <i>DDQ</i> -0.2	0.5*V <i>DDQ</i> +0.2	V

Note:

- 1. VID is the magnitude of the difference between the input level on CK and the input on /CK.
- 2. The value of VIX is expected to equal 0.5*VDDQ of the transmitting device and must track variations in the DC level of the same.

AC OPERATING TEST CONDITIONS (TA=0 to 70°C, Voltage referenced to VSS = 0V)

Parameter	Value	Unit
Reference Voltage	V <i>DDQ</i> x 0.5	V
Termination Voltage	V <i>DDQ</i> x 0.5	V
AC Input High Level Voltage (VIH, min)	V <i>REF</i> + 0.31	V
AC Input Low Level Voltage (VIL, max)	V <i>REF</i> - 0.31	V
Input Timing Measurement Reference Level Voltage	V <i>REF</i>	V
Output Timing Measurement Reference Level Voltage	V <i>TT</i>	V
Input Signal maximum peak swing	1.5	V
Input minimum Signal Slew Rate	1	V/ns
Termination Resistor (RT)	50	Ω
Series Resistor (RS)	25	W
Output Load Capacitance for Access Time Measurement (CL)	30	pF

^{*}For more information about AC Overshoot/Undershoot Specifications, refer to "Device Operation" section in hynix website.



AC CHARACTERISTICS (note: 1 - 9 / AC operating conditions unless otherwise noted)

D		Cbl	-5 / D	43	D4		LINIT
Param	eter	Symbol	Min	Max	Min	Max	UNIT
Row Cycle Time		t <i>RC</i>	55	-	60	-	ns
Auto Refresh Row Cycle Time		t <i>RFC</i>	70	-	70	-	ns
Row Active Time		t <i>RAS</i>	40	70K	40	70K	ns
Active to Read with Delay	Auto Precharge	t <i>RAP</i>	t <i>RCD</i> or t <i>RAS</i> (min)	-	t <i>RCD</i> or t <i>RAS</i> (min)	-	ns
Row Address to Colu	ımn Address Delay	t <i>RCD</i>	15	-	18	-	ns
Row Active to Row A	Active Delay	t <i>RRD</i>	10	-	10	-	ns
Column Address to O Delay	Column Address	t <i>CCD</i>	1	-	1	-	t <i>CK</i>
Row Precharge Time)	t <i>RP</i>	15	-	18	-	ns
Write Recovery Time	9	t <i>WR</i>	15	-	15	-	ns
Internal Write to Rea Delay	ad Command	t <i>WTR</i>	2	-	2	-	t <i>CK</i>
Auto Precharge Writ Precharge Time ²²	e Recovery +	t <i>DAL</i>	(t <i>WR</i> /t <i>CK</i>) + (t <i>RP</i> /t <i>CK</i>)	-	(t <i>WR</i> /t <i>CK</i>) + (t <i>RP</i> /t <i>CK</i>)	-	t <i>CK</i>
Contain Object Conta	CL = 3		5	10	5	10	
System Clock Cycle Time ²⁴	CL = 2.5	t <i>CK</i>	-	-	-	-	ns
	CL = 2		-	-	-	-	ns
Clock High Level Wid	dth	t <i>CH</i>	0.45	0.55	0.45	0.55	t <i>CK</i>
Clock Low Level Wid	lth	t <i>CL</i>	0.45	0.55	0.45	0.55	t <i>CK</i>
Data-Out edge to Cl	ock edge Skew	t <i>AC</i>	-0.7	0.7	-0.7	0.7	ns
DQS-Out edge to Clo	ock edge Skew	t <i>DQSCK</i>	-0.55	0.55	-0.65	0.65	ns
DQS-Out edge to Da Skew ²¹	ita-Out edge	t <i>DQSQ</i>	-	0.4	-	0.4	ns
Data-Out hold time	from DQS ²⁰	t <i>QH</i>	t <i>HP</i> -t <i>QHS</i>	-	t <i>HP</i> -t <i>QHS</i>	-	ns
Clock Half Period ^{19,2}	0	t <i>HP</i>	min (t <i>CL</i> ,t <i>CH</i>)	-	min (t <i>CL</i> ,t <i>CH</i>)	-	ns
Data Hold Skew Fac	tor ²⁰	t <i>QHS</i>	-	0.5	-	0.5	ns
Valid Data Output W	/indow	t <i>DV</i>	t <i>QH</i> - t <i>D</i>	QSQ .	t <i>QH</i> - t <i>D</i>	QSQ .	ns



			J		К		Н		
Param	neter	Symbol	Min	Max	Min	Max	Min	Max	UNIT
Row Cycle Time		t <i>RC</i>	60	-	65	-	65	-	ns
Auto Refresh Ro	w Cycle Time	t <i>RFC</i>	72	-	75	-	75	-	ns
Row Active Time)	t <i>RAS</i>	42	70K	45	120K	50	120K	ns
Active to Read w Precharge Delay		t <i>RAP</i>	t <i>RCD</i> or t <i>RAS</i> (min)	-	t <i>RCD</i> or t <i>RAS</i> (min)	-	t <i>RCD</i> or t <i>RAS</i> (min)	-	ns
Row Address to Address Delay	Column	t <i>RCD</i>	18	-	20	-	20	-	ns
Row Active to Ro	ow Active Delay	t <i>RRD</i>	12	-	15	-	15	-	ns
Column Address Address Delay	to Column	t <i>CCD</i>	1	-	1	-	1	-	t <i>CK</i>
Row Precharge	Гіте	t <i>RP</i>	18	-	20	-	20	-	ns
Write Recovery	Time	t WR	15	-	15	-	15	-	ns
Internal Write to Command Delay		t <i>WTR</i>	1	-	1	-	1	-	t <i>CK</i>
Auto Precharge \ + Precharge Tim	•	t <i>DAL</i>	(tWR/tCK) + (tRP/tCK)	-	(tWR/tCK) + (tRP/tCK)	-	(tWR/tCK) + (tRP/tCK)	-	t <i>CK</i>
	CL = 3		6	12	-	-	-	-	
System Clock Cycle Time ²⁴	CL = 2.5	t <i>CK</i>	6	12	7.5	12	7.5	12	ns
Cycle Time	CL = 2		7.5	12	7.5	12	10	12	ns
Clock High Level	Width	t <i>CH</i>	0.45	0.55	0.45	0.55	0.45	0.55	tCK
Clock Low Level	Width	t <i>CL</i>	0.45	0.55	0.45	0.55	0.45	0.55	tCK
Data-Out edge t Skew	o Clock edge	t <i>AC</i>	-0.7	0.7	-0.75	0.75	-0.75	0.75	ns
DQS-Out edge to Skew	o Clock edge	t <i>DQSCK</i>	-0.6	0.6	-0.75	0.75	-0.75	0.75	ns
DQS-Out edge to edge Skew ²¹	o Data-Out	t <i>DQSQ</i>	-,	0.45	-,	0.5	-,	0.5	ns
Data-Out hold ti DQS ²⁰	me from	t <i>QH</i>	t <i>HP</i> -t <i>QHS</i>	-	t <i>HP</i> -t <i>QHS</i>	-	t <i>HP</i> -t <i>QHS</i>	-	ns
Clock Half Period	d ^{19,20}	t <i>HP</i>	min (t <i>CL</i> ,t <i>CH</i>)	-	min (t <i>CL</i> ,t <i>CH</i>)	-	min (t <i>CL</i> ,t <i>CH</i>)	-	ns
Data Hold Skew	Factor ²⁰	t <i>QHS</i>	-	0.55	-	0.75	-	0.75	ns
Valid Data Outpu	ut Window	t <i>DV</i>	t <i>QH</i> - t <i>D</i>	QSQ	t <i>QH</i> - t <i>D</i>	QSQ	t <i>QH</i> - t <i>D</i>	QSQ	ns



Parameter	Cymahal	-5 /	-D43	-1	D4	UNIT
Parameter	Symbol	Min	Max	Min	Max	UNII
Data-out high-impedance window from CK,/CK ¹⁰	t <i>HZ</i>	-	t <i>AC</i> (Max)	-	t <i>AC</i> (Max)	ns
Data-out low-impedance window from CK, /CK ¹⁰	t <i>LZ</i>	-0.7	0.7	-0.7	0.7	ns
Input Setup Time (fast slew rate) ^{14,16-18}	t <i>IS</i>	0.6	-	0.6	-	ns
Input Hold Time (fast slew rate) ^{14,16-18}	t <i>IH</i>	0.6	-	0.6	-	ns
Input Setup Time (slow slew rate) ¹⁵⁻¹⁸	t <i>IS</i>	0.7	-	0.7	-	ns
Input Hold Time (slow slew rate) ¹⁵⁻¹⁸	t <i>IH</i>	0.7	-	0.7	-	ns
Input Pulse Width ¹⁷	t <i>IPW</i>	2.2	-	2.2	-	ns
Write DQS High Level Width	t <i>DQSH</i>	0.35	-	0.35	-	t <i>CK</i>
Write DQS Low Level Width	t <i>DQSL</i>	0.35	-	0.35	-	t <i>CK</i>
Clock to First Rising edge of DQS-In	t <i>DQSS</i>	0.72	1.25	0.72	1.25	t <i>CK</i>
DQS falling edge to CK setup time	t <i>DSS</i>	0.2	-	0.2	-	t <i>CK</i>
DQS falling edge hold time from CK	t <i>DSH</i>	0.2	-	0.2	-	t <i>CK</i>
DQ & DM input setup time ²⁵	t <i>DS</i>	0.4	-	0.4	-	ns
DQ & DM input hold time ²⁵	t <i>DH</i>	0.4	-	0.4	-	ns
DQ & DM Input Pulse Width ¹⁷	t <i>DIPW</i>	1.75	-	1.75	-	ns
Read DQS Preamble Time	t <i>RPRE</i>	0.9	1.1	0.9	1.1	t <i>CK</i>
Read DQS Postamble Time	t <i>RPST</i>	0.4	0.6	0.4	0.6	t <i>CK</i>
Write DQS Preamble Setup Time ¹²	t <i>WPRES</i>	0	-	0	-	ns
Write DQS Preamble Hold Time	t WPREH	0.25	-	0.25	-	t <i>CK</i>
Write DQS Postamble Time ¹¹	t <i>WPST</i>	0.4	0.6	0.4	0.6	t <i>CK</i>
Mode Register Set Delay	t <i>MRD</i>	2	-	2	-	t <i>CK</i>
Exit Self Refresh to non-Read command ²³	t <i>XSNR</i>	75	-	75	-	ns
Exit Self Refresh to Read command	t <i>XSRD</i>	200	-	200	-	t <i>CK</i>
Average Periodic Refresh Interval ^{13,25}	t <i>REFI</i>	-	15.6	-	15.6	us



Parameter	Symbol		J	ı	(Н		UNIT
Parameter	Зупьог	Min	Max	Min	Max	Min	Max	UNII
Data-out high-impedance window from CK,/ CK ¹⁰	t <i>HZ</i>	-	t <i>AC</i> (Max)	-	t <i>AC</i> (Max)	-	t <i>AC</i> (Max)	ns
Data-out low-impedance window from CK, / CK ¹⁰	t <i>LZ</i>	-0.7	0.7	-0.75	0.75	-0.75	0.75	ns
Input Setup Time (fast slew rate) ^{14,16-18}	t <i>IS</i>	0.75	-	0.9	-	0.9	-	ns
Input Hold Time (fast slew rate) ^{14,16-18}	t <i>IH</i>	0.75	-	0.9	-	0.9	-	ns
Input Setup Time (slow slew rate) ¹⁵⁻¹⁸	t <i>/S</i>	0.8	-	1.0	-	1.0	-	ns
Input Hold Time (slow slew rate) ¹⁵⁻¹⁸	t <i>IH</i>	0.8	-	1.0	-	1.0	-	ns
Input Pulse Width ¹⁷	t IPW	2.2	-	2.2	-	2.2	-	ns
Write DQS High Level Width	t <i>DQSH</i>	0.35	-	0.35	-	0.35	-	t <i>CK</i>
Write DQS Low Level Width	t <i>DQSL</i>	0.35	-	0.35	-	0.35	-	t <i>CK</i>
Clock to First Rising edge of DQS-In	t <i>DQSS</i>	0.75	1.25	0.75	1.25	0.75	1.25	t <i>CK</i>
DQS falling edge to CK setup time	t <i>DSS</i>	0.2	-	0.2	-	0.2	-	t <i>CK</i>
DQS falling edge hold time from CK	t <i>DSH</i>	0.2	-	0.2	-	0.2	-	t <i>CK</i>
DQ & DM input setup time ²⁵	t <i>DS</i>	0.45	-	0.5	-	0.5	-	ns
DQ & DM input hold time ²⁵	t <i>DH</i>	0.45	-	0.5	-	0.5	-	ns
DQ & DM Input Pulse Width ¹⁷	t <i>DIPW</i>	1.75	-	1.75	-	1.75	-	ns
Read DQS Preamble Time	t <i>RPRE</i>	0.9	1.1	0.9	1.1	0.9	1.1	t <i>CK</i>
Read DQS Postamble Time	t <i>RPST</i>	0.4	0.6	0.4	0.6	0.4	0.6	t <i>CK</i>
Write DQS Preamble Setup Time ¹²	t WPRES	0	-	0	-	0	-	ns
Write DQS Preamble Hold Time	t WPREH	0.25	-	0.25	-	0.25	-	t <i>CK</i>
Write DQS Postamble Time ¹¹	t WPST	0.4	0.6	0.4	0.6	0.4	0.6	t <i>CK</i>
Mode Register Set Delay	t <i>MRD</i>	2	-	2	-	2	-	t <i>CK</i>
Exit Self Refresh to non-Read command ²³	t <i>XSNR</i>	75	-	75	-	75	=	ns
Exit Self Refresh to Read command	t <i>XSRD</i>	200	-	200	-	200	-	t <i>CK</i>
Average Periodic Refresh Interval ^{13,25}	t <i>REFI</i>	-	15.6	-	15.6	-	15.6	us

Rev. 0.03 /Jun. 2006 25



Note:

- 1. All voltages referenced to Vss.
- 2. Tests for ac timing, IDD, and electrical, ac and dc characteristics, may be conducted at nominal reference/supply voltage levels, but the related specifications and device operation are guaranteed for the full voltage range specified.
- 3. Below figure represents the timing reference load used in defining the relevant timing parameters of the part. It is not intended to be either a precise representation of the typical system environment nor a depiction of the actual load presented by a production tester. System designers will use IBIS or other simulation tools to correlate the timing reference load to a system environment. Manufacturers will correlate to their production test conditions (generally a coaxial transmission line terminated at the tester electronics).




Figure: Timing Reference Load

- 4. AC timing and IDD tests may use a VIL to VIHswing of up to 1.5 V in the test environment, but input timing is still referenced to VREF (or to the crossing point for CK, /CK), and parameter specifications are guaranteed for the specified ac input levels under normal use conditions. The minimum slew rate for the input signals is 1 V/ns in the range between VIL(ac) and VIH(ac).
- 5. The ac and dc input level specifications are as defined in the SSTL_2 Standard (i.e., the receiver will effectively switch as a result of the signal crossing the ac input level and will remain in that state as long as the signal does not ring back above (below) the dc input LOW (HIGH) level.
- 6. Inputs are not recognized as valid until VREF stabilizes. Exception: during the period before VREF stabilizes, CKE < 0.2VDDQ is recognized as LOW.
- 7. The CK, /CK input reference level (for timing referenced to CK, /CK) is the point at which CK and /CK cross; the input reference level for signals other than CK, /CK is VREF.
- 8. The output timing reference voltage level is VTT.
- 9. Operation or timing that is not specified is illegal and after such an event, in order to guarantee proper operation, the DRAM must be powered down and then restarted through the specified initialization sequence before normal operation can continue.
- 10. tHZ and tLZ transitions occur in the same access time windows as valid data transitions. These parameters are not referenced to a specific voltage level but specify when the device output is no longer driving (HZ), or begins driving (LZ).
- 11. The maximum limit for this parameter is not a device limit. The device will operate with a greater value for this parameter, but system performance (bus turnaround) will degrade accordingly.
- 12. The specific requirement is that DQS be valid (HIGH, LOW, or at some point on a valid transition) on or before this CK edge. A valid transition is defined as monotonic and meeting the input slew rate specifications of the device. When no writes were previously in progress on the bus, DQS will be transitioning from High-Z to logic LOW. If a previous write was in progress, DQS could be HIGH, LOW, or transitioning from HIGH to LOW at this time, depending on tDQSS.
- 13. A maximum of eight AUTO REFRESH commands can be posted to any given DDR SDRAM device.
- 14. For command/address input slew rate \geq 1.0 V/ns.
- 15. For command/address input slew rate \geq 0.5 V/ns and < 1.0 V/ns
- 16. For CK & /CK slew rate ≥ 1.0 V/ns (single-ended)
- 17. These parameters guarantee device timing, but they are not necessarily tested on each device. They may be guaranteed by device design or tester correlation.
- 18. Slew Rate is measured between VOH(ac) and VOL(ac).
- 19. Min (tCL, tCH) refers to the smaller of the actual clock low time and the actual clock high time as provided to the device (i.e. this value can be greater than the minimum specification limits for tCL and tCH).
 - For example, tCL and tCH are = 50% of the period, less the half period jitter (tJIT(HP)) of the clock source, and less the half period jitter due to crosstalk (tJIT(crosstalk)) into the clock traces.



20.tQH = tHP - tQHS, where:

tHP = minimum half clock period for any given cycle and is defined by clock high or clock low (tCH, tCL). tQHS accounts for 1) The pulse duration distortion of on-chip clock circuits; and 2) The worst case push--out of DQS on one transition followed by the worst case pull--in of DQ on the next transition, both of which are, separately, due to data pin skew and output pattern effects, and p-channel to n-channel variation of the output drivers.

21. tDQSQ:

Consists of data pin skew and output pattern effects, and p-channel to n-channel variation of the output drivers for any given cycle.

22. tDAL = (tWR/tCK) + (tRP/tCK)

For each of the terms above, if not already an integer, round to the next highest integer.

Example: For DDR266B at CL=2.5 and tCK=7.5 ns tDAL = ((15 ns / 7.5 ns) + (20 ns / 7.5 ns)) clocks = ((2) + (3)) clocks = 5 clocks

23. In all circumstances, tXSNR can be satisfied using

tXSNR = tRFCmin + 1*tCK

- 24. The only time that the clock frequency is allowed to change is during self-refresh mode.
- 25. If refresh timing or tDS/tDH is violated, data corruption may occur and the data must be re-written with valid data before a valid READ can be executed.



SYSTEM CHARACTERISTICS CONDITIONS for DDR SDRAMS

The following tables are described specification parameters that required in systems using DDR devices to ensure proper performannce. These characteristics are for system simulation purposes and are guaranteed by design.

Input Slew Rate for DQ/DM/DQS (Table a.)

AC CHARACTERISTIC	S	DDR	400	DDR	2333	DDR266		UNIT	Note
PARAMETER	Symbol	min	max	min	max	min	max	Oilli	Note
DQ/DM/DQS input slew rate measured between V/H(DC), V/L(DC) and V/L(DC), V/H(DC)	DCSLEW	0.5	4.0	0.5	4.0	0.5	4.0	V/ns	1,12

Address & Control Input Setup & Hold Time Derating (Table b.)

Input Slew Rate	Delta tIS	Delta tIH	UNIT	Note
0.5 V/ns	0	0	ps	9
0.4 V/ns	+50	0	ps	9
0.3 V/ns	+100	0	ps	9

DQ & DM Input Setup & Hold Time Derating (Table c.)

Input Slew Rate	Delta tDS	Delta tDH	UNIT	Note
0.5 V/ns	0	0	ps	11
0.4 V/ns	+75	0	ps	11
0.3 V/ns	+150	0	ps	11

DQ & DM Input Setup & Hold Time Derating for Rise/Fall Delta Slew Rate (Table d.)

Input Slew Rate	Delta tDS	Delta tDH	UNIT	Note
± 0.0 ns/V	0	0	ps	10
± 0.25 ns/V	+50	+50	ps	10
± 0.5 ns/V	+100	+100	ps	10

Output Slew Rate Characteristics (for x16 Device) (Table e.)

Slew Rate Characteristic	Typical Range (V/ns)	Minimum (V/ ns)	Maximum (V/ ns)	Note
Pullup Slew Rate	1.2 - 2.5	1.0	4.5	1,3,4,6,7,8
Pulldown Slew Rate	1.2 - 2.5	1.0	4.5	2,3,4,6,7,8

Output Slew Rate Matching Ratio Characteristics (Table f.)

Slew Rate Characteristic	DDR266A		DDR266B		Note	
Parameter	min	max	min	max	Note	
Output Slew Rate Matching Ratio (Pullup to Pulldown)	-	-	-	-	5,12	



Note:

1. Pullup slew rate is characterized under the test conditions as shown in below Figure.





Figure: Pullup Slew rate

2. Pulldown slew rate is measured under the test conditions shown in below Figure.



3. Pullup slew rate is measured between (VDDQ/2 - 320 mV \pm 250mV)

Pulldown slew rate is measured between (VDDQ/2 + 320mV \pm 250mV)

Pullup and Pulldown slew rate conditions are to be met for any pattern of data, including all outputs switching and only one output switching.

Example: For typical slew, DQ0 is switching

For minimum slew rate, all DQ bits are switching worst case pattern

For maximum slew rate, only one DQ is switching from either high to low, or low to high.

The remaining DQ bits remain the same as for previous state.

4. Evaluation conditions

Typical: 25 °C (Ambient), VDDQ = nominal, typical process

Minimum: 70 °C (Ambient), VDDQ = minimum, slow-slow process

Maximum: 0 °C (Ambient), VDDQ = Maximum, fast-fast process

- 5. The ratio of pullup slew rate to pulldown slew rate is specified for the same temperature and voltage, over the entire temperature and voltage range. For a given output, it represents the maximum difference between pullup and pulldown drivers due to process variation
- 6. Verified under typical conditions for qualification purposes.
- 7. TSOP-II package devices only.
- 8. Only intended for operation up to 256 Mbps per pin.
- 9. A derating factor will be used to increase tIS and tIH in the case where the input slew rate is below 0.5 V/ns as shown in Table b. The Input slew rate is based on the lesser of the slew rates determined by either VIH(AC) to VIL(AC) or VIH(DC) to VIL(DC), similarly for rising transitions.
- 10. A derating factor will be used to increase tDS and tDH in the case where DQ, DM, and DQS slew rates differ, as shown in Tables c & d. Input slew rate is based on the larger of AC-AC delta rise, fall rate and DC-DC delta rise, fall rate. Input slew rate is based on the lesser of the slew rates determined by either VIH(AC) to VIL(AC) or VIH(DC) to VIL(DC), similarly for rising transitions. The delta rise/fall rate is calculated as:

{1/(Slew Rate1)} - {1/(slew Rate2)}

For example:

If Slew Rate 1 is 0.5 V/ns and Slew Rate 2 is 0.4 V/ns, then the delta rise, fall rate is -0.5 ns/V. Using the table given, this would result in the need for an increase in tDS and tDH of 100ps.

- 11. Table c is used to increase tDS and tDH in the case where the I/O slew rate is below 0.5 V/ns. The I/O slew rate is based on the lesser of the AC-AC slew rate and the DC-DC slew rate. The input slew rate is based on the lesser of the slew rates determined by either VIH(ac) to VIL(AC) or VIH(DC) to VIL(DC), and similarly for rising transitions.
- 12. DQS, DM, and DQ input slew rate is specified to prevent double clocking of data and preserve setup and hold times. Signal transitions through the DC region must be monotonic.




CAPACITANCE (TA=25°C, f=100MHz)

Parameter	Pin	Symbol	Min	Max	Unit
Input Clock Capacitance	CK, /CK	CI1	2.0	3.0	pF
Delta Input Clock Capacitance	CK, /CK	Delta CI1	-	0.25	pF
Input Capacitance	All other input-only pins	CI1	2.0	3.0	pF
Delta Input Capacitance	All other input-only pins	Delta CI2	-	0.5	pF
Input / Output Capacitance	DQ, DQS, DM	CIO	4.0	5.0	pF
Delta Input / Output Capacitance	DQ, DQS, DM	Delta CIO	-	0.5	pF

Note:

- 1. VDD = min. to max., VDDQ = 2.3V to 2.7V, VODC = VDDQ/2, Vopeak-to-peak = 0.2V
- 2. Pins not under test are tied to GND.
- 3. These values are guaranteed by design and are tested on a sample basis only.


OUTPUT LOAD CIRCUIT





PACKAGE INFORMATION

400mil 66pin Thin Small Outline Package



Rev. 0.03 /Jun. 2006 31