- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers and Flat Packages, and Plastic and Ceramic DIPs
- Dependable Texas Instruments Quality and Reliability

#### description


These devices contain four independent 2-input AND gates. The open-collector outputs require pull-up resistors to perform correctly. They may be connected to other open-collector outputs to implement active-low wired-OR or active-high wired-AND functions. Open-collector devices are often used to generate higher VOH levels.

The SN5409, SN54LS09, and SN54S09 are characterized for operation over the full military temperature range of -55°C to 125°C. The SN7409, SN74LS09, and SN74S09 are characterized for operation from 0°C to 70°C.

#### FUNCTION TABLE (each gate)

INP	UTS	OUTPUT					
Α	В	Y					
н	Н	Н					
L	Х	L					
Х	L	L					


#### logic symbol




<sup>&</sup>lt;sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for D, J, N, and W packages.

SN5409, SN54LS09, SN54S09... J OR W PACKAGE SN7409... N PACKAGE SN74LS09, SN74S09... D OR N PACKAGE (TOP VIEW)




SN54LS09, SN54S09 . . . FK PACKAGE (TOP VIEW)





NC-No internal connection


#### logic diagram (positive logic)



#### schematics (each gate)







#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, VCC (see Note 1)		7 V
Input voltage: '09, 'S09		5.5 V
'LS09	· · · · · · · · · · · · · · · · · · ·	7 V
	· · · · · · · · · · · · · · · · · · ·	
Operating free-air temperature range:	SN54'	–55°C to 125°C
	SN74'	0°C to 70°C
Storage temperature range		–65°C to 150°C

NOTE 1; Voltage values are with respect to network ground terminal.

### SN5409, SN7409 QUADRUPLE 2 INPUT POSITIVE AND GATES WITH OPEN-COLLECTOR OUTPUTS

#### recommended operating conditions

	} :	SN5409			SN740	9	,,,,,,
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
V <sub>CC</sub> Supply voltage	4.5	5	5.5	4.75	5	5.25	٧
V <sub>IH</sub> High-level input voltage	2			2			V
V <sub>IL</sub> Low-level input voltage			0.8			8.0	٧
V <sub>OH</sub> High-level output voltage			5.5			5.5	٧
IOL Low-level output current			16			16	mΑ
TA Operating free-air temperature	- 55	-	125	0		70	°C

#### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN TYP\$ MAX	UNIT
VIK	VCC = MIN,	I <sub>I</sub> = - 12 mA	- 1,5	V
(он	V <sub>CC</sub> - MIN,	V <sub>1H</sub> = 2 V, V <sub>OH</sub> = 5,5 V	0.25	mA
VOL	V <sub>CC</sub> = MIN,	V <sub>IL</sub> = 0.8 V I <sub>OL</sub> = 16 mA	0.2 0.4	٧
lj.	VCC = MAX,	V <sub>j</sub> = 5.5 V	1	mΑ
Чн	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 2.4 V	40	μД
liL.	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 0.4 V	- 1.6	mA
ГССН	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 4.5 V	11 21	mА
ICCL	V <sub>CC</sub> = MAX,	V <sub>I</sub> = 0 V	20 33	mA

<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions. ‡ All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

### switching characteristics, V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C (see note 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	тҮР	MAX	UNIT
<sup>t</sup> P <b>L</b> H			0.45.5		21	32	ns
t <b>P</b> HL	A or B	A or B Y $H_L = 400 \Omega_r$	$H_L = 400 \Omega$ , $C_L = 15  pF$		16	24	пѕ

NOTE 2: Load circuits and voltage waveforms are shown in Section 1.

# SN54LS09, SN74LS09 QUADRUPLE 2-INPUT POSITIVE-AND GATES WITH OPEN-COLLECTOR OUTPUTS

#### recommended operating conditions

	] ;	SN54LS	09		SN74LS	i09	
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC Supply voltage	4.5	5	5.5	4.75	5	5.25	V
V <sub>IH</sub> High-level input voltage	2			2			V
V <sub>IL</sub> Low-level input voltage			0.7			8.0	V
VOH High-level output voltage			5.5			5.5	٧
IOL Low-level output current			4			8	mΑ
Тд Operating free-air temperature	- 55		125	0	•	70	°C

### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

******		TEST COND	TIONS +		SN54LS	09	SN74LS09			UNIT
PARAMETER		TEST CONDI	110145 [	MIN	TYP‡	MAX	MIN	TYP\$	MAX	UNII
VIK	V <sub>CC</sub> = MIN,	lı = — 18 mA				- 1.5			- 1.5	٧
юн	V <sub>CC</sub> = MIN,	V <sub>IH</sub> = 2 V,	V <sub>OH</sub> = 5.5 V			0.1			0.1	mΑ
	V <sub>CC</sub> = MIN,	V <sub>IL</sub> = MAX,	IOL = 4 mA		0.25	0.4		0.25	0.4	v
VOL	VCC = MIN,	VIL = MAX,	I <sub>OL</sub> = 8 mA				· · · · · · · · · · · · · · · · · · ·	0.35	0.5	1 *
11	V <sub>CC</sub> = MAX,	V <sub>I</sub> = 7 V				0.1			0.1	mA
ЧН	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 2.7 V				20			20	μΑ
IIL.	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 0.4 V	· · · · · · · · · · · · · · · · · · ·			- 0.4	***		- 0.4	mA
Іссн	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 4.5 V			2.4	4.8		2.4	4.8	mA
<sup> </sup> CCL	V <sub>CC</sub> = MAX,	V  = 0 V			4,4	8.8		4.4	8.8	mA

<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

#### switching characteristics, $V_{CC} = 5 \text{ V}$ , $T_A = 25^{\circ}\text{C}$ (see note 2)

PARAMETER	FROM (INPUT)	TO {QUTPUT}	TEST CON	TEST CONDITIONS				UNIT
t <sub>PLH</sub>	A or B	v	$R_1 = 2 k\Omega$ ,	C <sub>f</sub> = 15 pF		20	35	ns
₹PHL	7, 3, 3	,	11[ - 2 838,	CE - TapF		17	35	กร

NOTE 2: Load circuits and voltage waveforms are shown in Section 1.

<sup>‡</sup> All typical values are at  $V_{CC}$  = 5 V,  $T_{A}$  = 25°C.

# SN54S09, SN74S09 QUADRUPLE 2-INPUT POSITIVE-AND GATES WITH OPEN-COLLECTOR OUTPUTS

#### recommended operating conditions

		SN54S0	9		SN7450	19	
	MIN	NOM	MAX	MIN	NOM	MAX	TINU
V <sub>CC</sub> Supply voltage	4.5	5	5.5	4.75	5	5.25	V
V <sub>1H</sub> High-level input voltage	2			2			٧
V <sub>IL</sub> Low-level input voltage			0.8			0.8	v
VOH High-level output voltage			5.5	_		5.5	٧
IOL Low-level output current			20			20	mA
TA Operating free-air temperature	- 55		125	0		70	°C

### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS†	MIN TYP# MAX	TINU
ViK	V <sub>CC</sub> = MIN,	i <sub>1</sub> = - 18 mA	-1.2	V
ГОН	VCC = MIN,	V <sub>IH</sub> = 2 V, V <sub>OH</sub> = 5.5 V	0.25	mA
Vol	V <sub>CC</sub> = MIN,	V <sub>IL</sub> = 0.8 V, I <sub>OL</sub> = 20 mA	0.5	V
lj.	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 5.5 V	1	mA
<sup>1</sup> ін	V <sub>CC</sub> = MAX,	V <sub>I</sub> = 2,7 V	50	μА
li L	V <sub>CC</sub> = MAX,	V <sub>I</sub> = 0.5 V	-2	mA
1 <sub>ССН</sub>	V <sub>CC</sub> = MAX,	V <sub>1</sub> = 4.5 V	18 32	mA
ICCL	V <sub>CC</sub> = MAX,	V <sub>I</sub> = 0 V	32 57	mΑ

<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

### switching characteristics, $V_{CC} = 5 \text{ V}$ , $T_A = 25^{\circ}\text{C}$ (see note 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CON	TEST CONDITIONS		MAX	UNIT
<sup>‡</sup> PLH			R <sub>L</sub> = 280 Ω,	C <sub>I</sub> = 15 pF	6.5	10	ns
tPHL.	A or B			C[ - 19pr	6.5	10	ns
tPLH	AUrb	[	D - 200 C	C: = 50.05	9		ns
<sup>t</sup> PHL			RL = 280 Ω,	C <sub>L</sub> = 50 pF	9		ns

NOTE 2: Load circuits and voltage waveforms are shown in Section 1.

<sup>‡</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .





10-Jun-2014

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type	Package	Pins	Package	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
80019012A	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	80019012A SNJ54LS 09FK	Samples
8001901CA	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901CA SNJ54LS09J	Samples
8001901CA	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901CA SNJ54LS09J	Samples
8001901DA	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901DA SNJ54LS09W	Samples
8001901DA	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901DA SNJ54LS09W	Samples
SN54LS09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN54LS09J	Samples
SN54LS09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN54LS09J	Samples
SN54S09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN54S09J	Samples
SN54S09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SN54S09J	Samples
SN7409N	OBSOLET	E PDIP	N	14		TBD	Call TI	Call TI	0 to 70		
SN7409N	OBSOLET	E PDIP	N	14		TBD	Call TI	Call TI	0 to 70		
SN74LS09D	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09D	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09DE4	ACTIVE	SOIC	D	14		TBD	Call TI	Call TI	0 to 70		Samples
SN74LS09DE4	ACTIVE	SOIC	D	14		TBD	Call TI	Call TI	0 to 70		Samples
SN74LS09DG4	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09DG4	ACTIVE	SOIC	D	14	50	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09DR	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples





www.ti.com

10-Jun-2014

Orderable Device	Package Type Package Pins Package Eco Plan Lead/Ball Finish MSL Peak Temp Qty (2) (6) (3)		MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples					
SN74LS09DR	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09DRE4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	LS09	Samples
SN74LS09DRE4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM 0 to 70		LS09	Sample
SN74LS09DRG4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM 0 to 70		LS09	Sample
SN74LS09DRG4	ACTIVE	SOIC	D	14	2500	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM 0 to 70		LS09	Sample
SN74LS09J	OBSOLETI	E CDIP	J	14		TBD	Call TI	Call TI	0 to 70		
SN74LS09J	OBSOLETI	E CDIP	J	14		TBD	Call TI	Call TI	0 to 70		
SN74LS09N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type 0 to 70		SN74LS09N	Sample
SN74LS09N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74LS09N	Sample
SN74LS09N3	OBSOLETI	E PDIP	N	14		TBD	Call TI	Call TI 0 to 70			
SN74LS09N3	OBSOLETI	E PDIP	N	14		TBD	Call TI	Call TI	0 to 70		
SN74LS09NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74LS09N	Sample
SN74LS09NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74LS09N	Sample
SN74LS09NSR	ACTIVE	so	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	74LS09	Sample
SN74LS09NSR	ACTIVE	so	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	74LS09	Samples
SN74LS09NSRE4	ACTIVE	SO	NS	14		TBD	Call TI	Call TI	0 to 70		Sample
SN74LS09NSRE4	ACTIVE	SO	NS	14		TBD	Call TI	Call TI 0 to 70			Sample
SN74LS09NSRG4	ACTIVE	so	NS	14		TBD	Call TI	Call TI 0 to 70			Sample
SN74LS09NSRG4	ACTIVE	SO	NS	14		TBD	Call TI	Call TI	Call TI 0 to 70		Sample
SN74S09N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74S09N	Samples





www.ti.com

10-Jun-2014

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
SN74S09N	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74S09N	Samples
SN74S09NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74S09N	Samples
SN74S09NE4	ACTIVE	PDIP	N	14	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	0 to 70	SN74S09N	Sample
SN74S09NSR	ACTIVE	so	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	0 to 70	74S09	Sample
SN74S09NSR	ACTIVE	so	NS	14	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM 0 to 70		74S09	Sample
SNJ54LS09FK	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	80019012A SNJ54LS 09FK	Sample
SNJ54LS09FK	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	80019012A SNJ54LS 09FK	Sample
SNJ54LS09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901CA SNJ54LS09J	Sample
SNJ54LS09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901CA SNJ54LS09J	Sample
SNJ54LS09W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901DA SNJ54LS09W	Sample
SNJ54LS09W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	8001901DA SNJ54LS09W	Sample
SNJ54S09FK	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	SNJ54S 09FK	Sample
SNJ54S09FK	ACTIVE	LCCC	FK	20	1	TBD	POST-PLATE	N / A for Pkg Type	-55 to 125	SNJ54S 09FK	Sample
SNJ54S09J	ACTIVE	CDIP	J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ54S09J	Sample
SNJ54S09J	ACTIVE		J	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ54S09J	Sample
SNJ54S09W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ54S09W	Sampl
SNJ54S09W	ACTIVE	CFP	W	14	1	TBD	A42	N / A for Pkg Type	-55 to 125	SNJ54S09W	Sampl

<sup>(1)</sup> The marketing status values are defined as follows:





www.ti.com 10-Jun-2014

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF SN54LS09, SN54S09, SN74LS09, SN74S09:

Catalog: SN74LS09, SN74S09

Military: SN54LS09, SN54S09



### **PACKAGE OPTION ADDENDUM**

10-Jun-2014

#### NOTE: Qualified Version Definitions:

www.ti.com


- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

### PACKAGE MATERIALS INFORMATION


www.ti.com 14-Jul-2012

#### TAPE AND REEL INFORMATION

#### **REEL DIMENSIONS**



#### **TAPE DIMENSIONS**



A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### TAPE AND REEL INFORMATION

\*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LS09DR	SOIC	D	14	2500	330.0	16.4	6.5	9.0	2.1	8.0	16.0	Q1
SN74LS09NSR	SO	NS	14	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
SN74S09NSR	SO	NS	14	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1

**PACKAGE MATERIALS INFORMATION** 

www.ti.com 14-Jul-2012



\*All dimensions are nominal

7 til diriterierere are memiliar								
Device	Package Type	Package Drawing	Pins SPQ		Length (mm)	Width (mm)	Height (mm)	
SN74LS09DR	SOIC	D	14	2500	367.0	367.0	38.0	
SN74LS09NSR	SO	NS	14	2000	367.0	367.0	38.0	
SN74S09NSR	SO	NS	14	2000	367.0	367.0	38.0	

### 14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## W (R-GDFP-F14)

### CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP1-F14



### FK (S-CQCC-N\*\*)

### LEADLESS CERAMIC CHIP CARRIER

28 TERMINAL SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a metal lid.
- D. Falls within JEDEC MS-004



### N (R-PDIP-T\*\*)

### PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



### D (R-PDSO-G14)

#### PLASTIC SMALL OUTLINE



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AB.



# D (R-PDSO-G14)

### PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



#### **MECHANICAL DATA**

### NS (R-PDSO-G\*\*)

## 14-PINS SHOWN

#### PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

#### Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom Amplifiers amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors <a href="https://www.ti.com/omap">www.ti.com/omap</a> TI E2E Community <a href="https://example.com/omap">e2e.ti.com/omap</a>

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>