

AT24C01D and AT24C02D

I²C-Compatible (2-wire) Serial EEPROM 1-Kbit (128 x 8) or 2-Kbit (256 x 8)

DATASHEET

Features

- Low voltage operation
 - 1.7V (V_{CC} = 1.7V to 3.6V)
- Internally organized 128 x 8 (1K) or 256 x 8 (2K)
- I²C-Compatible (2-wire) serial interface
- Schmitt Triggers, filtered inputs for noise suppression
- Bidirectional data transfer protocol
- 400kHz (1.7V) and 1MHz (2.5V) compatibility
- Write Protect pin for full array hardware data protection
- Ultra low active current (1mA max) and standby current (0.8µA max)
- 8-byte Page Write mode
 - Partial page writes allowed
- Random and Sequential Read modes
- Self-timed write cycle within 5ms max
- High reliability
 - Endurance: 1,000,000 write cycles
 - Data retention: 100 years
- Green package options (Lead-free/Halide-free/RoHS Compliant)
 - 8-lead SOIC, 8-lead TSSOP, 8-pad UDFN, 8-lead PDIP,⁽¹⁾ 5-lead SOT23, and 8-ball VFBGA
- Die sale options: wafer form and tape and reel available

Description

The Atmel® AT24C01D/02D provides 1,024/2,048 bits of Serial Electrically Erasable and Programmable Read-Only Memory (EEPROM) organized as 128/256 words of eight bits each. The device's cascadable feature allows up to eight devices to share a common 2-wire bus. These device are optimized for use in many industrial and commercial applications where low-power and low-voltage operation are essential. Both devices are available in space-saving 8-lead SOIC, 8-lead TSSOP, 8-pad UDFN, 8-lead PDIP,⁽¹⁾ 5-lead SOT23, and 8-ball VFBGA packages. The entire family of packages operates from 1.7V to 3.6V.


Note: 1. Contact Atmel Sales for availability of this package.

1. Pin Descriptions and Pinouts

Table 1-1. Pin Descriptions


Pin Number	Pin Symbol	Pin Name and Functional Description	Asserted State	Pin Type
1, 2, 3 A ₀ , A ₁ , A ₂		Device Address Inputs: The A_0 , A_1 , and A_2 pins are used to select the hardware device address and correspond to the seventh, sixth, and fifth bit of the I^2C seven bit slave address. These pins can be directly connected to V_{CC} or GND, allowing up to eight devices on the same bus.	_	Input
		Refer to Note 1 for behavior of the pin when not connected.		
4	GND	Ground: The ground reference for the power supply. GND should be connected to the system ground.	_	Power
		Serial Data: The SDA pin is an open-drain bidirectional input/output pin used to serially transfer data to and from the device.		Inn. 4
5 SD	SDA	The SDA pin must be pulled-high using an external pull-up resistor (not to exceed $10K\Omega$ in value) and may be wire-ORed with any number of other open-drain or open-collector pins from other devices on the same bus.	_	Input/ Output
6	SCL	Serial Clock : The SCL pin is used to provide a clock to the device and to control the flow of data to and from the device. Command and input data present on the SDA pin is always latched in on the rising edge of SCL, while output data on the SDA pin is clocked out on the falling edge of SCL.	_	Input
		The SCL pin must either be forced high when the serial bus is idle or pulled-high using an external pull-up resistor.		
7	WP	Write Protect: Connecting the WP pin to GND will ensure normal write operations. When the WP pin is connected to VCC, all write operations to the memory are inhibited.	High	Input
		Refer to Note 1 for behavior of the pin when not connected.		
8	V _{CC}	Device Power Supply: The V_{CC} pin is used to supply the source voltage to the device. Operations at invalid V_{CC} voltages may produce spurious results and should not be attempted.	_	Power

Note: 1. If the A₀, A₁, A₂, or WP pins are not driven, they are internally pulled down to GND. In order to operate in a wide variety of application environments, the pull-down mechanism is intentionally designed to be somewhat strong. Once these pins are biased above the CMOS input buffer's trip point (~0.5 x V_{CC}), the pull-down mechanism disengages. Atmel recommends connecting these pins to a known state whenever possible.



Note: 1. Refer to "Device Addressing" on page 7 for details about addressing the SOT23 version of the device.

2. Device Block Diagram





3. Device Operation and Communication

The AT24C01D/02D operates as a slave device and utilizes a simple I²C-compatible 2-wire digital serial interface to communicate with a host controller, commonly referred to as the bus Master. The Master initiates and controls all Read and Write operations to the slave devices on the serial bus, and both the Master and the slave devices can transmit and receive data on the bus.

The serial interface is comprised of just two signal lines: Serial Clock (SCL) and Serial Data (SDA). The SCL pin is used to receive the clock signal from the Master, while the bidirectional SDA pin is used to receive command and data information from the Master as well as to send data back to the Master. Data is always latched into the AT24C01D/02D on the rising edge of SCL and always output from the device on the falling edge of SCL. Both the SCL and SDA pin incorporate integrated spike suppression filters and Schmitt Triggers to minimize the effects of input spikes and bus noise.

All command and data information is transferred with the Most-Significant Bit (MSB) first. During bus communication, one data bit is transmitted every clock cycle, and after eight bits (one byte) of data have been transferred, the receiving device must respond with either an acknowledge (ACK) or a no-acknowledge (NACK) response bit during a ninth clock cycle (ACK/NACK clock cycle) generated by the Master; Therefore, nine clock cycles are required for every one byte of data transferred. There are no unused clock cycles during any Read or Write operation, so there must not be any interruptions or breaks in the data stream during each data byte transfer and ACK or NACK clock cycle.

During data transfers, data on the SDA pin must only change while SCL is low, and the data must remain stable while SCL is high. If data on the SDA pin changes while SCL is high, then either a Start or a Stop condition will occur. Start and Stop conditions are used to initiate and end all serial bus communication between the Master and the slave devices. The number of data bytes transferred between a Start and a Stop condition is not limited and is determined by the Master. In order for the serial bus to be idle, both the SCL and SDA pins must be in the logic-high state at the same time.

3.1 Clock and Data Transition Requirements

The SDA pin is an open drain terminal and therefore must be pulled high with an external pull-up resistor. Data on the SDA pin may change only during SCL low time periods. Data changes during SCL high periods will indicate a Start or Stop condition as defined below.

3.2 Start and Stop Conditions

3.2.1 Start Condition

A Start condition occurs when there is a high-to-low transition on the SDA pin while the SCL pin is at a stable Logic 1 state and will bring the device out of standby mode. The Master uses a Start condition to initiate any data transfer sequence; therefore, every command must begin with a Start condition. The device will continuously monitor the SDA and SCL pins for a Start condition but will not respond unless one is detected. See Figure 3-1 for more details.

3.2.2 Stop Condition

A Stop condition occurs when there is a low-to-high transition on the SDA pin while the SCL pin is stable in the Logic 1 state. The Master can use the Stop condition to end a data transfer sequence with the AT24C01D/02D which will subsequently return to standby mode. The Master can also utilize a repeated Start condition instead of a Stop condition to end the current data transfer if the Master will perform another operation. See Figure 3-1 for more details.



3.3 Acknowledge and No-Acknowledge

After every byte of data is received, the receiving device must confirm to the Master that it has successfully received the data byte by responding with what is known as an acknowledge (ACK). An ACK is accomplished by the transmitting device first releasing the SDA line at the falling edge of the eighth clock cycle followed by the receiving device responding with a Logic 0 during the entire high period of the ninth clock cycle.

When the AT24C01D/02D is transmitting data to the Master, the Master can indicate that it is done receiving data and wants to end the operation by sending a Logic 1 response to the AT24C01D/02D instead of an ACK response during the ninth clock cycle. This is known as a no-acknowledge (NACK) and is accomplished by the Master sending a Logic 1 during the ninth clock cycle, at which point the AT24C01D/02D will release the SDA line so the Master can then generate a Stop condition.

The transmitting device, which can be the bus Master or the Serial EEPROM, must release the SDA line at the falling edge of the eighth clock cycle to allow the receiving device to drive the SDA line to a Logic 0 to ACK the previous 8-bit word. The receiving device must release the SDA line at the end of the ninth clock cycle to allow the transmitter to continue sending new data. A timing diagram has been provided in Figure 3-1 to better illustrate these requirements.




Figure 3-1. Start Condition, Data Transitions, Stop Condition and Acknowledge

3.4 Standby Mode

The AT24C01D/02D features a low power standby mode which is enabled when any one of the following occurs:

- A valid power-up sequence is performed (see Section 8.6, "Power-Up Requirements and Reset Behavior").
- A Stop condition is received by the device unless it initiates an internal write cycle (see Section 5.).
- At the completion of an internal write cycle (see Section 5., "Write Operations").
- An unsuccessful match of the device type identifier or hardware address in the Device Address byte occurs (see Section 4.1, "Device Addressing").
- The bus Master does not ACK the receipt of data read out from the device; instead it sends a NACK response (see Section 6., "Read Operations").




3.5 Software Reset

After an interruption in protocol, power loss, or system reset, any 2-wire part can be protocol reset by following these steps:

- 1. Create a Start condition,
- 2. Clock nine cycles,
- 3. Create another Start condition followed by a Stop condition as seen in Figure 3-2.

The device will be ready for the next communication after above steps have been completed.

Figure 3-2. Software Reset



4. Memory Organization

The AT24C01D is internally organized as 16 pages of 8 bytes each while the AT24C02D is organized as 32 pages of 8 bytes each.

4.1 Device Addressing

Accessing the device requires an 8-bit Device Address word following a Start condition to enable the device for a Read or Write operation. Since multiple slave devices can reside on the serial bus, each slave device must have its own unique address so that the Master can access each device independently.

The most significant four bits of the Device Address word is referred to as the device type identifier. The device type identifier `1010' (Ah) is required in bits seven through four of the Device Address byte (see Table 4-1.)

Following the 4-bit device type identifier are the hardware slave address bits, A_2 , A_1 , and A_0 . These bits can be used to expand the address space by allowing up to eight other Serial EEPROM devices on the same bus. The A_2 , A_1 , and A_0 values must correlate with the voltage level on the corresponding hardwired input pins, A_2 , A_1 , and A_0 . These hardwired address pins use an internal proprietary circuit that automatically biases each pin to a Logic 0 state if the pin is allowed to float. In order to operate in a wide variety of application environments, the pull-down mechanism is intentionally designed to be somewhat strong. Once the pin is biased above the CMOS input buffer's trip point (\sim 0.5 x V_{CC}), the pull-down mechanism disengages. Atmel recommends connecting the A_2 , A_1 , and A_0 pins to a known state whenever possible.

When using the SOT23 package, the A_2 , A_1 , and A_0 signals are not accessible and are left floating. The previously mentioned automatic pull-down circuit will set these signals to a Logic 0 state. As a result, to properly communicate with the device in the SOT23 package, the A_2 , A_1 , and A_0 software bits must always be set to Logic 0 for any operation. This requirement has been shown in Table 4-1.

The eighth bit of the Device Address (bit 0) is the Read/Write operation select bit. A Read operation is initiated if this bit is high and a Write operation is initiated if this bit is low.

Upon the successful comparison of the Device Address, the EEPROM will return an ACK. If a valid comparison is not made, the device will NACK and return to a standby state.

Table 4-1. Device Address Byte

	Device Type Identifier			Hardwa	Read/ Write			
Package	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
SOIC, TSSOP, UDFN, PDIP, VFBGA	1	0	1	0	A ₂	A ₁	A ₀	R/W
SOT23	1	0	1	0	0	0	0	R/W

For all operations except the Current Address Read, a Word Address byte must be transmitted to the device immediately following the Device Address byte. The Word Address byte contains a 7-bit (in the case of the AT24C01D) or 8-bit (in the case of the AT24C02D) memory array address, and is used to specify which location in the EEPROM to start reading or writing. Please refer to Table 4-2 to review these bit positions.

Table 4-2. Word Address Byte

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
A7 ⁽¹⁾	A6	A5	A4	A3	A2	A1	A0

Note: 1. The A7 bit is a don't care bit for the AT24C01D.

The relationship of the AC timing parameters with respect to SCL and SDA for the AT24C01D/02D are shown in the timing waveform in Figure 8-1 on page 14. The AC timing characteristics and specifications are outlined in Section 8.4 "AC Characteristics" on page 14.



5. Write Operations


All Write operations for the AT24C01D/02D begin with the Master sending a Start condition, followed by a Device Address byte with the R/\overline{W} bit set to '0', and then by the Word Address byte. The data value(s) to be written to the device immediately follow the Word Address byte.

5.1 Byte Write

The AT24C01D/02D supports the writing of single 8-bit bytes. Selecting a data word in the 1-Kbit memory requires a 7-bit word address while selecting a data word in the 2-Kbit memory requires an 8-bit word address.

Upon receipt of the proper Device Address and Word Address bytes, the EEPROM will send an Acknowledge. The device will then be ready to receive the first 8-bit data word. Following receipt of the 8-bit data word, the EEPROM will respond with an Acknowledge. The addressing device, such as a bus Master, must then terminate the Write operation with a Stop condition. At that time the EEPROM will enter an internally self-timed write cycle, which will complete within a time of t_{WR} , while the data is being programmed into the nonvolatile EEPROM. All inputs are disabled during this write cycle, and the EEPROM will not respond until the Write is complete.

Figure 5-1. Byte Write



5.2 Page Write


A Page Write operation allows up to eight bytes to be written in the same write cycle, provided all bytes are in the same row of the memory array (where address bits A7 through A3 are the same). Partial Page Writes of less than eight bytes are also allowed.

A Page Write is initiated the same way as a Byte Write, but the bus Master does not send a Stop condition after the first data word is clocked in. Instead, after the EEPROM acknowledges receipt of the first data word, the bus Master can transmit up to seven additional data words. The EEPROM will respond with an ACK after each data word is received. Once all data to be written has been sent to the device, the bus Master must issue a Stop condition (see Figure 5-2) at which time the internally self-timed write cycle will begin.

The lower three bits of the word address are internally incremented following the receipt of each data word. The higher order address bits are not incremented and retains the memory page row location. Page Write operations are limited to writing bytes within a single physical page, regardless of the number of bytes actually being written. When the incremented word address reaches the page boundary, the address counter will "roll-over" to the beginning of the same page. Nevertheless, creating a roll-over event should be avoided as previously loaded data in the page could become unintentionally altered.



Figure 5-2. Page Write




5.3 Acknowledge Polling

An Acknowledge Polling routine can be implemented to optimize time sensitive applications that would prefer not to wait the fixed maximum write cycle time (t_{WR}). This method allows the application to know immediately when the Serial EEPROM write cycle has completed, so a subsequent operation can be started.

Once the internally self-timed write cycle has started, an Acknowledge Polling routine can be initiated. This involves repeatedly sending a Start condition followed by a valid Device Address byte with the R/W bit set at Logic 0. The device will not respond with an ACK while the write cycle is ongoing. Once the internal write cycle has completed, the EEPROM will respond with an ACK, allowing a new Read or Write operation to be immediately initiated. A flow chart has been included below in Figure 5-3 to better illustrate this technique.

Figure 5-3. Acknowledge Polling Flow Chart






5.4 Write Cycle Timing

The length of the self-timed write cycle, or t_{WR} , is defined as the amount of time from the Stop condition that begins the internal Write operation, to the Start condition of the first Device Address byte sent to the AT24C01D/02D which it subsequently responds to with an ACK. Figure 5-4 has been included to show this measurement. During the internally self-timed write cycle, any attempts to read or write to the memory array will not be processed.

Figure 5-4. Write Cycle Timing



5.5 Write Protection

The AT24C01D/02D utilizes a hardware data protection scheme that allows the user to write protect the entire memory contents when the WP pin is at V_{CC} (or a valid V_{IH}). No write protection will be set if the WP pin is at GND or left floating.


Table 5-1. AT24C01D/02D Write Protect Behavior

WP Pin Voltage	Part of the Array Protected			
V _{CC}	Full Array			
GND	None — Write Protection Not Enabled			

The status of the WP pin is sampled at the Stop condition for every Byte Write or Page Write command prior to the start of an internally self-timed Write operation. Changing the WP pin state after the Stop condition has been sent will not alter or interrupt the execution of the write cycle. The WP pin state must be valid with respect to the associated setup (t_{SU.WP}) and hold (t_{HD.WP}) as shown in the Figure 5-5 below. The WP setup time is the amount of time that the WP state must be stable before the Stop condition is issued. The WP hold time is the amount of time after the Stop condition that the WP state must remain stable.

If an attempt is made to write to the device while the WP pin has been asserted, the device will acknowledge the Device Address, Word address, and Data bytes but no write cycle will occur when the Stop condition is issued, and the device will immediately be ready to accept a new Read or Write command.

Figure 5-5. Write Protect Setup and Hold Timing





6. Read Operations

Read operations are initiated the same way as Write operations with the exception the read/write select bit in the Device Address word must be a Logic 1. There are three Read operations:


- Current Address Read
- Random Address Read
- Sequential Read

6.1 Current Address Read

The internal data word address counter maintains the last address accessed during the last Read or Write operation, incremented by one. This address stays valid between operations as long as the V_{CC} is maintained to the part. The address roll-over during read is from the last byte of the last page to the first byte of the first page of the memory.

A Current Address Read operation will output data according to the location of the internal data word address counter. This is initiated with a Start condition, followed by a valid Device Address byte with the R/W bit set to Logic 1. The device will ACK this sequence and the current address data word is serially clocked out on the SDA line. All types of Read operations will be terminated if the bus Master does not respond with an ACK (it NACKs) during the ninth clock cycle. A Read instruction may be terminated at any point with a Stop condition which will force the device into standby mode.

Figure 6-1. Current Address Read




6.2 Random Read

A Random Read begins in the same way as a Byte Write operation does to load in a new data word address. This is known as a "dummy write" sequence. However, the Data Byte and the Stop condition of the Byte Write must be omitted to prevent the part from entering an internal write cycle. Once the Device Address and Word Address are clocked in and acknowledged by the EEPROM, the bus Master must generate another Start condition. The bus Master now initiates a Current Address Read by sending a Start condition, followed by a valid Device Address byte with the R/W bit set to Logic 1. The EEPROM will ACK the Device Address and serially clock out the data word on the SDA line. All types of Read operations will be terminated if the bus Master does not respond with an ACK (it NACKs) during the ninth clock cycle. A Read instruction may be terminated at any point with a Stop condition which will force the device into standby mode.




Figure 6-2. Random Read



6.3 Sequential Read

Sequential Reads are initiated by either a Current Address Read or a Random Read. After the bus Master receives a data word, it responds with an acknowledge. As long as the EEPROM receives an ACK, it will continue to increment the word address and serially clock out sequential data words. Figure 6-3 depicts a Sequential Read sequence that was initiated as a Current Address Read. When the maximum memory address is reached, the data word address will "roll over" and the sequential read will continue from the beginning of the memory array. All types of Read operations will be terminated if the bus Master does not respond with an ACK (it NACKs) during the ninth clock cycle. A Read instruction may be terminated at any point with a Stop condition which will force the device into standby mode.

Figure 6-3. Sequential Read, Initiated by a Current Address Read



7. Device Default Condition from Atmel

The AT24C01D/02D is delivered with the EEPROM array set to Logic 1, resulting in FFh data in all locations.



8. Electrical Specifications

8.1 Absolute Maximum Ratings

Temperature under Bias –55°C to +125°C
Storage Temperature65°C to +150°C
Supply Voltage with respect to ground0.5V to +4.10V
Voltage on any pin with respect to ground –0.6V to V _{CC} + 0.5V
DC Output Current 5.0mA

Functional operation at the "Absolute Maximum Ratings" or any other conditions beyond those indicated in Section 8.2 "DC and AC Operating Range" is not implied or guaranteed. Stresses beyond those listed under "Absolute Maximum Ratings" and/or exposure to the "Absolute Maximum Ratings" for extended periods may affect device reliability and cause permanent damage to the device.

The voltage extremes referenced in the "Absolute Maximum Ratings" are intended to accommodate short duration undershoot/overshoot pulses that the device may be subjected to during the course of normal operation and does not imply or guarantee functional device operation at these levels for any extended period of time.

8.2 DC and AC Operating Range

		AT24C01D and AT24C02D
Operating Temperature (Case)	Industrial Temperature Range	–40°C to +85°C
V _{CC} Power Supply	Low Voltage Grade	1.7V to 3.6V

8.3 DC Characteristics

Parameters are applicable over the operating range in Section 8.2, unless otherwise noted.

Symbol	Parameter	Test Condition		Min	Typical ⁽¹⁾	Max	Units
V _{CC}	Supply Voltage			1.7		3.6	V
	Supply Current Bood	$V_{CC} = 1.8V^{(2)}$	Read at 400kHz		0.08	0.3	mA
I _{CC1}	Supply Current, Read	V _{CC} = 3.6V	Read at 1MHz		0.15	0.5	mA
I _{CC2}	Supply Current, Write	V _{CC} = 3.6V	Write at 1MHz		0.20	1.0	mA
	Standby Current	$V_{CC} = 1.8V^{(2)}$	V = V or V		0.08	0.4	μA
I _{SB}	Standby Current	V _{CC} = 3.6V	$V_{IN} = V_{CC}$ or V_{SS}		0.10	0.8	μΑ
ILI	Input Leakage Current	$V_{IN} = V_{CC} \text{ or } V_{SS}$			0.10	3.0	μΑ
I _{LO}	Output Leakage Current	$V_{OUT} = V_{CC} \text{ or } V_{S}$	SS		0.05	3.0	μΑ
V _{IL}	Input Low Level ⁽²⁾			-0.6		V _{CC} x 0.3	V
V _{IH}	Input High Level ⁽²⁾			V _{CC} x 0.7		V _{CC} + 0.5	V
V _{OL1}	Output Low Level	V _{CC} = 1.7V	I _{OL} = 0.15mA			0.2	V
V _{OL2}	Output Low Level	V _{CC} = 3.0V	I _{OL} = 2.1mA			0.4	V

Notes: 1. Typical values characterized at $T_A = +25$ °C unless otherwise noted.

2. This parameter is characterized but is not 100% tested in production.



8.4 AC Characteristics


Parameters are applicable over operating range in Section 8.2, unless otherwise noted. Test conditions shown in Note 2.

		V _{CC} = 1.7V - 3.6V		V _{CC} = 2.	5V - 3.6V		
Symbol	Parameter	Min	Max	Min	Max	Units	
f _{SCL}	Clock Frequency, SCL		400		1000	kHz	
t _{LOW}	Clock Pulse Width Low	1300		500		ns	
t _{HIGH}	Clock Pulse Width High	600		400		ns	
t _l	Input Filter Spike Suppression (SCL,SDA) ⁽¹⁾		100		100	ns	
t _{AA}	Clock Low to Data Out Valid		900		450	ns	
t _{BUF}	Bus Free Time between Stop and Start ⁽¹⁾	1300		500		ns	
t _{HD.STA}	Start Hold Time	600		250		ns	
t _{SU.STA}	Start Set-up Time	600		250		ns	
t _{HD.DAT}	Data In Hold Time	0		0		ns	
t _{SU.DAT}	Data In Set-up Time	100		100		ns	
t _R	Inputs Rise Time ⁽¹⁾		300		100	ns	
t _F	Inputs Fall Time ⁽¹⁾		300		100	ns	
t _{SU.STO}	Stop Set-up Time	600		250		ns	
t _{SU.WP}	Write Protect Setup Time	600		100		ns	
t _{HD.WP}	Write Protect Hold Time	600		400		ns	
t _{DH}	Data Out Hold Time	50		50		ns	
t _{WR}	Write Cycle Time		5		5	ms	

Notes: 1. These parameters are determined through product characterization and are not tested 100% in production.

- 2. AC measurement conditions:
 - C_L: 100pF
 - R_{PUP} (bus line pull-up resistor to V_{CC}): 1.3 k Ω (1000kHz), 4k Ω (400kHz)
 - Input pulse voltages: 0.3 V_{CC} to 0.7 V_{CC}
 - Input rise and fall times: ≤ 50ns
 - Input and output timing reference voltages: 0.5 x V_{CC}

Figure 8-1. Bus Timing



8.5 Pin Capacitance⁽¹⁾

Applicable over recommended operating range from $T_A = 25$ °C, f = 1.0MHz, $V_{CC} = 3.6$ V

Symbol	Test Condition	Max	Units	Conditions
C _{I/O}	Input/Output Capacitance (SDA)	8	pF	V _{I/O} = 0V
C _{IN}	Input Capacitance (A ₀ , A ₁ , A ₂ , SCL)	6	pF	V _{IN} = 0V

Note: 1. This parameter is characterized but is not 100% tested in production.

8.6 Power-Up Requirements and Reset Behavior

During a power-up sequence, the V_{CC} supplied to the AT24C01D/02D should monotonically rise from GND to the minimum V_{CC} level as specified in Section 8.2 with no greater than a slew rate of $1V/\mu s$.

8.6.1 Device Reset

To prevent Write operations or other spurious events from happening during a power-up sequence, the AT24C01D/02D includes a Power-On-Reset (POR) circuit. Upon power-up, the device will not respond to any commands until the V_{CC} level crosses the internal voltage threshold (V_{POR}) that brings the device out of reset and into standby mode.

The system designer must ensure that instructions are not sent to the device until the V_{CC} supply has reached a stable value greater than or equal to the minimum V_{CC} level. Additionally, once the V_{CC} is greater than or equal to the minimum V_{CC} level, the bus Master must wait at least t_{PUP} before sending the first command to the device. See Table 8-1 for the values associated with these power-up parameters.

Table 8-1. Power-up Conditions

Symbol	Parameter	Min	Max	Units
t _{PUP}	Time required after V_{CC} is stable before the device can accept commands.	100		μs
V _{POR}	Power-On Reset Threshold Voltage		1.5	V
t _{POFF}	Minimum time at V _{CC} = 0V between power cycles.	1		ms

If an event occurs in the system where the V_{CC} level supplied to the AT24C01D/02D drops below the maximum V_{POR} level specified, it is recommended that a full power cycle sequence be performed by first driving the V_{CC} pin to GND, waiting at least the minimum t_{POFF} time, and then performing a new power-up sequence in compliance with the requirements defined in this section.

8.7 EEPROM Cell Performance Characteristics


Operation	Test Condition	Min	Max	Units
Write Endurance ⁽¹⁾	$T_A = 25^{\circ}C$, $V_{CC}(min) < V_{CC} < V_{CC}(max)$ Byte or Page Write Mode	1,000,000	_	Write Cycles
Data Retention ⁽²⁾	T _A = 55°C	100	_	Years

Notes: 1. Write endurance performance is determined through characterization and the qualification process.

2. The data retention capability is determined through qualification and checked on each device in production.



9. Ordering Code Detail





10. Ordering Information

Atmel Ordering Code	Lead Finish	Package	Voltage	Operation Range		
AT24C01D-SSHM-T ⁽¹⁾		8S1				
AT24C01D-SSHM-B ⁽²⁾		001				
AT24C01D-XHM-T ⁽¹⁾	NiPdAu (Lead-free/Halogen-free)	8X				
AT24C01D-XHM-B ⁽²⁾	(0.4				
AT24C01D-MAHM-T ⁽¹⁾		8MA2	1.7V to 3.6V	Industrial Temperature		
AT24C01D-PUM	Matte Tin	8P3		(-40°C to 85°C)		
AT24C01D-STUM-T ⁽¹⁾	(Lead-free/Halogen-free)	5TS1				
AT24C01D-CUM-T ⁽¹⁾	SnAgCu Ball (Lead-free/Halogen-free)	8U3-1				
AT24C01D-WWU11M ⁽³⁾	N/A	Wafer Sale				
A TO 4 COOP, COLUMN T(1)						
AT24C02D-SSHM-T ⁽¹⁾		8S1				
AT24C02D-SSHM-B ⁽²⁾						
AT24C02D-XHM-T ⁽¹⁾	NiPdAu (Lead-free/Halogen-free)	8X				
AT24C02D-XHM-B ⁽²⁾	(8X				
AT24C02D-MAHM-T ⁽¹⁾		8MA2	1.7V to 3.6V	Industrial Temperature		
AT24C02D-PUM	Matte Tin	8P3		(–40°C to 85°C)		
AT24C02D-STUM-T ⁽¹⁾	(Lead-free/Halogen-free)	5TS1				
AT24C02D-CUM-T ⁽¹⁾	SnAgCu Ball (Lead-free/Halogen-free)					
AT24C02D-WWU11M ⁽³⁾	N/A	Wafer Sale				


- Notes: 1. T = Tape and reel:
 - SOIC = 4K units per reel
 - TSSOP, UDFN, and SOT23 = 5K units per reel
 - 2. B = Bulk
 - SOIC and TSSOP = 100 units per tube
 - PDIP = 50 units per tube
 - 3. For wafer sales, please contact Atmel Sales.

	Package Type			
8S1	8-lead, 0.15" wide, Plastic Gull Wing Small Outline (JEDEC SOIC)			
8X	8-lead, 4.40mm body, Plastic Thin Shrink Small Outline Package (TSSOP)			
8MA2	8-pad, 2.00mm x 3.00mm body, 0.50mm Pitch, Ultra Thin Dual Flat No Lead (UDFN)			
8P3	8-lead, 0.30" wide, Plastic Dual Inline Package (PDIP)			
5TS1	5-lead, 2.90mm x 1.60mm body, Plastic Thin Shrink Small Outline (SOT23)			
8U3-1	8-ball, 1.50mm x 2.00mm body, 0.5mm pitch, Very thin Fine Ball Grid Array (VFBGA)			



11. Part Markings

AT24C01D and AT24C02D: Package Marking Information



Note 1: designates pin 1

Note 2: Package drawings are not to scale

 Catalog Number Truncation

 AT24C01D
 Truncation Code ###: 01D

 AT24C02D
 Truncation Code ###: 02D

Date Code	es			Voltages
Y = Year		M = Month	WW = Work Week of Assembly	% = Minimum Voltage
3: 2013	7: 2017	A: January	02: Week 2	M: 1.7V min
4: 2014	8: 2018	B: February	04: Week 4	
5: 2015	9: 2019			
6: 2016	0: 2020	L: December	52: Week 52	
Country	f A a a a malalur	L at Ni	unah a u	Crade/Load Finish Material

Country of Assembly	Lot Nullibel	Graue/Leau Fillisti Wateriai
@ = Country of Assembly	AAAA = Atmel Wafer Lot Number	H: Industrial/NiPdAu U: Industrial/Matte Tin/SnAgCu

Trace Code	Atmel Truncation
XX = Trace Code (Atmel Lot Numbers Correspond to Code) Example: AA, AB YZ, ZZ	AT: Atmel ATM: Atmel
	ATML: Atmel


12/20/13

Atmel	TITLE	DRAWING NO.	REV.
Package Mark Contact: DL-CSO-Assy_eng@atmel.com	24C01-02DSM , AT24C01D and AT24C02D Package Marking Information	24C01-02DSM	D




12. Packaging Information

12.1 8S1 — 8-lead JEDEC SOIC




TOP VIEW



SIDE VIEW

Notes: This drawing is for general information only. Refer to JEDEC Drawing MS-012, Variation AA for proper dimensions, tolerances, datums, etc.



END VIEW

COMMON DIMENSIONS (Unit of Measure = mm)

SYMBOL	MIN	NOM	MAX	NOTE
Α	1.35	_	1.75	
A1	0.10	_	0.25	
b	0.31	_	0.51	
С	0.17	_	0.25	
D	4.80	_	5.05	
E1	3.81	_	3.99	
E	5.79	_	6.20	
е		1.27 BSC	,	
L	0.40	_	1.27	
Ø	0°	_	8°	

6/22/11

A	tm	nel
		. •
-	•	

Package Drawing Contact: packagedrawings@atmel.com


TITLE


8S1, 8-lead (0.150" Wide Body), Plastic Gull Wing Small Outline (JEDEC SOIC)

GPC DRAWING NO. REV.
SWB 8S1 G




12.2 8X — 8-lead TSSOP





Side View

- Notes: 1. This drawing is for general information only. Refer to JEDEC Drawing MO-153, Variation AA, for proper dimensions, tolerances, datums, etc.
 - 2. Dimension D does not include mold Flash, protrusions or gate burrs. Mold Flash, protrusions and gate burrs shall not exceed 0.15mm (0.006in) per side.
 - 3. Dimension E1 does not include inter-lead Flash or protrusions. Inter-lead Flash and protrusions shall not exceed 0.25mm (0.010in) per side.
 - 4. Dimension b does not include Dambar protrusion. Allowable Dambar protrusion shall be 0.08mm total in excess of the b dimension at maximum material condition. Dambar cannot be located on the lower radius of the foot. Minimum space between protrusion and adjacent lead is 0.07mm.
 - 5. Dimension D and E1 to be determined at Datum Plane H.




COMMON DIMENSIONS (Unit of Measure = mm)


(Officer Measure Tillin)					
SYMBOL	MIN	NOM	MAX	NOTE	
Α	-	-	1.20		
A1	0.05	-	0.15		
A2	0.80	1.00	1.05		
D	2.90	3.00	3.10	2, 5	
E		6.40 BSC			
E1	4.30	4.40	4.50	3, 5	
b	0.19	_	0.30	4	
е		0.65 BSC			
L	0.45	0.60	0.75		
L1	1.00 REF				
С	0.09	-	0.20		


12/8/11

Atmel	TITLE	GPC	DRAWING NO.	REV.
Package Drawing Contact: packagedrawings@atmel.com	8X, 8-lead 4.4mm Body, Plastic Thin Shrink Small Outline Package (TSSOP)	TNR	8X	E

12.3 8MA2 — 8-pad UDFN







BOTTOM VIEW

Notes:

- 1. This drawing is for general information only. Refer to Drawing MO-229, for proper dimensions, tolerances, datums, etc.
- 2. The Pin #1 ID is a laser-marked feature on Top View.
- 3. Dimensions b applies to metallized terminal and is measured between 0.15 mm and 0.30 mm from the terminal tip. If the terminal has the optional radius on the other end of the terminal, the dimension should not be measured in that radius area.
- 4. The Pin #1 ID on the Bottom View is an orientation feature on the thermal pad.

COMMON DIMENSIONS (Unit of Measure = mm)

SYMBOL	MIN	NOM	MAX	NOTE
Α	0.50	0.55	0.60	
A1	0.0	0.02	0.05	
A2	-	-	0.55	
D	1.90	2.00	2.10	
D1	1.20	-	1.60	
Е	2.90	3.00	3.10	
E1	1.20	-	1.60	
b	0.18	0.25	0.30	3
С		1.52 REF		
L	0.30	0.35	0.40	
е	0.50 BSC			
K	0.20	-	-	

12/20/13

_		\sim	\sim
_	ш		_

Package Drawing Contact: packagedrawings@atmel.com **TITLE**


8MA2, 8-pad 2 x 3 x 0.6mm Body, Thermally Enhanced Plastic Ultra Thin Dual Flat No-Lead Package (UDFN)

DRAWING NO. REV. **GPC**


YNZ 8MA2 Ε




12.4 8P3 — 8-lead PDIP



Top View



End View



COMMON DIMENSIONS (Unit of Measure = inches)

SYMBOL	MIN	NOM	MAX	NOTE
Α			0.210	2
A2	0.115	0.130	0.195	
b	0.014	0.018	0.022	5
b2	0.045	0.060	0.070	6
b3	0.030	0.039	0.045	6
С	0.008	0.010	0.014	
D	0.355	0.365	0.400	3
D1	0.005			3
Е	0.300	0.310	0.325	4
E1	0.240	0.250	0.280	3
е	0.100 BSC			
eA	0.300 BSC			4
L	0.115	0.130	0.150	2


Notes:

- 1. This drawing is for general information only; refer to JEDEC Drawing MS-001, Variation BA for additional information.
- Dimensions A and L are measured with the package seated in JEDEC seating plane Gauge GS-3.
 D, D1 and E1 dimensions do not include mold Flash or protrusions. Mold Flash or protrusions shall not exceed 0.010 inch.
- 4. E and eA measured with the leads constrained to be perpendicular to datum.
- 5. Pointed or rounded lead tips are preferred to ease insertion.
- 6. b2 and b3 maximum dimensions do not include Dambar protrusions. Dambar protrusions shall not exceed 0.010 (0.25 mm).

06/21/11

Atmel	TITLE	GPC	DRAWING NO.	REV.
	8P3, 8-lead, 0.300" Wide Body, Plastic Dual	PTC	8P3	
Package Drawing Contact:	In-line Package (PDIP)	FIC	0F3	"
packagedrawings@atmel.com				

12.5 5ST1 — 5-lead SOT23



- Dimension D does not include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion. Interlead flash or protrusion shall not exceed 0.15 mm per side.
- The package top may be smaller than the package bottom. Dimensions D and E1 are determined at the outermost extremes of the plastic body exclusive of mold flash, tie bar burrs, gate burrs and interlead flash, but including any mismatch between the top and bottom of the plastic body.
- These dimensions apply to the flat section of the lead between 0.08 mm and 0.15 mm from the lead tip.
- 4. Dimension "b" does not include dambar protrusion. Allowable dambar protrusion shall be 0.08 mm total in excess of the "b" dimension at maximum material condition. The dambar cannot be located on the lower radius of the foot. Minimum space between protrusion and an adjacent lead shall not be less than 0.07 mm.

This drawing is for general information only. Refer to JEDEC Drawing MO-193, Variation AB for additional information.

COMMON DIMENSIONS (Unit of Measure = mm)


SYMBOL	MIN	NOM	MAX	NOTE
Α	-	-	1.00	
A1	0.00	-	0.10	
A2	0.70	0.90	1.00	
С	0.08	-	0.20	3
D	2.90 BSC		1,2	
Е	2.80 BSC		1,2	
E1	1.60 BSC		1,2	
L1	0.60 REF			
е	0.95 BSC			
e1	1.90 BSC			
b	0.30	-	0.50	3,4

5/31/12


Atmel	TITLE	GPC	DRAWING NO.	REV.
Package Drawing Contact: packagedrawings@atmel.com	5TS1, 5-lead 1.60mm Body, Plastic Thin Shrink Small Outline Package (Shrink SOT)	TSZ	5TS1	D



12.6 8U3-1 — 8-ball VFBGA



TOP VIEW



Notes:

- 1. This drawing is for general information only.
- 2. Dimension 'b' is measured at maximum solder ball diameter.

8 SOLDER BALLS

3. Solder ball composition shall be 95.5Sn-4.0Ag-.5Cu.

SIDE VIEW

COMMON DIMENSIONS (Unit of Measure - mm)

	,		· ·	
SYMBOL	MIN	NOM	MAX	NOTE
Α	0.73	0.79	0.85	
A1	0.09	0.14	0.19	
A2	0.40	0.45	0.50	
b	0.20	0.25	0.30	2
D	1.50 BSC			
E		2.0 BSC		
е	0.50 BSC			
e1	0.25 REF			
d	1.00 BSC			
d1	0.25 REF			

6/11/13

 tma	ı
CITIC	١

Package Drawing Contact: packagedrawings@atmel.com

TITLE

8U3-1, 8-ball, 1.50mm x 2.00mm body, 0.50mm pitch, Very Thin, Fine-Pitch Ball Grid Array Package (VFBGA)

GPC	DRAWING NO.	REV.
GXU	8U3-1	F

13. Revision History

Doc. No.	Date	Comments
8871B	03/2014	Correct pinouts from bottom to top view and grammatical changes. No changes to functional specification.
8871A	12/2013	Initial document release.





Atmel Corporation



F: (+1)(408) 436.4200







www.atmel.com

© 2014 Atmel Corporation. / Rev.: Atmel-8871B-SEEPROM-AT24C01D-02D-Datasheet_032014.

1600 Technology Drive, San Jose, CA 95110 USA

Atmel®, Atmel logo and combinations thereof, and others are registered trademarks or trademarks of Atmel Corporation or its subsidiaries. Other terms and product names may be trademarks of others.

T: (+1)(408) 441.0311

DISCLAIMER: The information in this document is provided in connection with Atmel products. No license, express or implied, by estoppel or otherwise, to any intellectual property right is granted by this document or in connection with the sale of Atmel products. EXCEPT AS SET FORTH IN THE ATMEL TERMS AND CONDITIONS OF SALES LOCATED ON THE ATMEL WEBSITE, ATMEL ASSUMES NO LIABILITY WHATSOEVER AND DISCLAIMS ANY EXPRESS, IMPLIED OR STATUTORY WARRANTY RELATING TO ITS PRODUCTS INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT. IN NO EVENT SHALL ATMEL BE LIABLE FOR ANY DIRECT, INDIRECT, CONSEQUENTIAL, PUNITIVE, SPECIAL OR INCIDENTAL DAMAGES (INCLUDING, WITHOUT LIMITATION, DAMAGES FOR LOSS AND PROFITS, BUSINESS INTERRUPTION, OR LOSS OF INFORMATION) ARISING OUT OF THE USE OR INABILITY TO USE THIS DOCUMENT, EVEN IF ATMEL HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. Atmel makes no representations or warranties with respect to the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and products descriptions at any time without notice. Atmel does not make any commitment to update the information contained herein. Unless specifically provided otherwise, Atmel products are not suitable for, and shall not be used in, automotive applications. Atmel products are not intended, authorized, or warranted for use as components in applications intended to support or sustain life.

SAFETY-CRITICAL, MILITARY, AND AUTOMOTIVE APPLICATIONS DISCLAIMER: Atmel products are not designed for and will not be used in connection with any applications where the failure of such products would reasonably be expected to result in significant personal injury or death ("Safety-Critical Applications") without an Atmel officer's specific written consent. Safety-Critical Applications include, without limitation, life support devices and systems, equipment or systems for the operation of nuclear facilities and weapons systems. Atmel products are not designed nor intended for use in military or aerospace applications or environments unless specifically designated by Atmel as military-grade. Atmel products are not designed nor intended for use in automotive applications unless specifically designated by Atmel as automotive-grade.