# 74HC4053; 74HCT4053 Triple 2-channel analog multiplexer/demultiplexer Rev. 9 — 10 February 2016 Prod

Product data sheet

## **General description**

The 74HC4053; 74HCT4053 is a triple single-pole double-throw analog switch (3x SPDT) suitable for use in analog or digital 2:1 multiplexer/demultiplexer applications. Each switch features a digital select input (Sn), two independent inputs/outputs (nY0 and nY1) and a common input/output (nZ). A digital enable input (E) is common to all switches. When E is HIGH, the switches are turned off. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of V<sub>CC</sub>.

#### **Features and benefits** 2.

- Wide analog input voltage range from –5 V to +5 V
- Complies with JEDEC standard no. 7A
- Low ON resistance:
  - 80  $\Omega$  (typical) at  $V_{CC} V_{EE} = 4.5 \text{ V}$
  - 70  $\Omega$  (typical) at  $V_{CC} V_{EE} = 6.0 \text{ V}$
  - 60  $\Omega$  (typical) at  $V_{CC} V_{EE} = 9.0 \text{ V}$
- Logic level translation: to enable 5 V logic to communicate with ±5 V analog signals
- Typical 'break before make' built-in
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V
  - CDM JESD22-C101E exceeds 1000 V
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

## **Applications**

- Analog multiplexing and demultiplexing
- Digital multiplexing and demultiplexing
- Signal gating





## 4. Ordering information


Table 1. Ordering information

Type number	Package	Package								
	Temperature range Name		Description	Version						
74HC4053D	−40 °C to +125 °C	SO16	plastic small outline package; 16 leads;	SOT109-1						
74HCT4053D			body width 3.9 mm							
74HC4053DB	−40 °C to +125 °C	SSOP16	plastic shrink small outline package; 16 leads;	SOT338-1						
74HCT4053DB			body width 5.3 mm							
74HC4053PW	−40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads;	SOT403-1						
74HCT4053PW			body width 4.4 mm							
74HC4053BQ	−40 °C to +125 °C	DHVQFN16	plastic dual in-line compatible thermal enhanced very	SOT763-1						
74HCT4053BQ			thin quad flat package; no leads; 16 terminals; body $2.5 \times 3.5 \times 0.85$ mm							

## 5. Functional diagram








## 6. Pinning information

#### 6.1 Pinning



## 6.2 Pin description

Table 2. Pin description

Symbol	Pin	Description
Ē	6	enable input (active LOW)
V <sub>EE</sub>	7	supply voltage
GND	8	ground supply voltage
S1, S2, S3	11, 10, 9	select input
1Y0, 2Y0, 3Y0	12, 2, 5	independent input or output
1Y1, 2Y1, 3Y1	13, 1, 3	independent input or output
1Z, 2Z, 3Z	14, 15, 4	common output or input
V <sub>CC</sub>	16	supply voltage

© Nexperia B.V. 2017. All rights reserved

## 7. Functional description

Table 3. Function table [1]

Inputs		Channel on
E	Sn	
L	L	nY0 to nZ
L	Н	nY1 to nZ
Н	X	switches off

<sup>[1]</sup> H = HIGH voltage level; L = LOW voltage level; X = don't care.

## 8. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to  $V_{SS} = 0 \text{ V (ground)}$ .

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage	<u>[1]</u>	-0.5	+11.0	V
I <sub>IK</sub>	input clamping current	$V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$	-	±20	mA
I <sub>SK</sub>	switch clamping current	$V_{SW} < -0.5 \text{ V or } V_{SW} > V_{CC} + 0.5 \text{ V}$	-	±20	mA
I <sub>SW</sub>	switch current	$-0.5 \text{ V} < \text{V}_{\text{SW}} < \text{V}_{\text{CC}} + 0.5 \text{ V}$	-	±25	mA
I <sub>EE</sub>	supply current		-	±20	mA
I <sub>CC</sub>	supply current		-	50	mA
I <sub>GND</sub>	ground current		-	-50	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	SO16, (T)SSOP16, and DHVQFN16 package	-	500	mW
Р	power dissipation	per switch	-	100	mW

<sup>[1]</sup> To avoid drawing  $V_{CC}$  current out of terminal nZ, when switch current flows into terminals nYn, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal nZ, no  $V_{CC}$  current will flow out of terminals nYn, and in this case there is no limit for the voltage drop across the switch, but the voltages at nYn and nZ may not exceed  $V_{CC}$  or  $V_{EE}$ .

## 9. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol Parameter		Conditions	Conditions 74HC4053		74	Unit			
			Min	Тур	Max	Min	Тур	Max	
V <sub>CC</sub>	supply voltage	see Figure 7 and Figure 8							
		V <sub>CC</sub> – GND	2.0	5.0	10.0	4.5	5.0	5.5	V
		$V_{CC} - V_{EE}$	2.0	5.0	10.0	2.0	5.0	10.0	V
VI	input voltage		GND	-	V <sub>CC</sub>	GND	-	V <sub>CC</sub>	V
V <sub>SW</sub>	switch voltage		V <sub>EE</sub>	-	V <sub>CC</sub>	V <sub>EE</sub>	-	V <sub>CC</sub>	V

74HC HCT4053

<sup>[2]</sup> For SO16 packages: above 70 °C the value of  $P_{tot}$  derates linearly with 8 mW/K. For SSOP16 and TSSOP16 packages: above 60 °C the value of  $P_{tot}$  derates linearly with 5.5 mW/K. For DHVQFN16 packages: above 60 °C the value of  $P_{tot}$  derates linearly with 4.5 mW/K.

 Table 5.
 Recommended operating conditions ...continued

Symbol	Parameter	Conditions	74HC4053			74HCT4053			Unit
			Min	Тур	Max	Min	Тур	Max	
T <sub>amb</sub>	ambient temperature		-40	+25	+125	-40	+25	+125	°C
Δt/ΔV	input transition rise and fall	V <sub>CC</sub> = 2.0 V	-	-	625	-	-	-	ns/V
rate	$V_{CC} = 4.5 \text{ V}$	-	1.67	139	-	1.67	139	ns/V	
		$V_{CC} = 6.0 \text{ V}$	-	-	83	-	-	-	ns/V
		$V_{CC} = 10.0 \text{ V}$	-	-	31	-	-	-	ns/V




Fig 7. Guaranteed operating area as a function of the supply voltages for 74HC4053




Fig 8. Guaranteed operating area as a function of the supply voltages for 74HCT4053

© Nexperia B.V. 2017. All rights reserved

#### 10. Static characteristics

#### Table 6. R<sub>ON</sub> resistance per switch for 74HC4053 and 74HCT4053

 $V_I = V_{IH}$  or  $V_{IL}$ ; for test circuit see Figure 9.

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nYn or nZ terminal, whichever is assigned as an output.

For 74HC4053:  $V_{CC}$  – GND or  $V_{CC}$  –  $V_{EE}$  = 2.0 V, 4.5 V, 6.0 V and 9.0 V.

For 74HCT4053:  $V_{CC}$  – GND = 4.5 V and 5.5 V,  $V_{CC}$  –  $V_{EE}$  = 2.0 V, 4.5 V, 6.0 V and 9.0 V.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
T <sub>amb</sub> = 25	°C	'					
R <sub>ON(peak)</sub>	ON resistance (peak)	$V_{is} = V_{CC}$ to $V_{EE}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	100	180	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	90	160	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	70	130	Ω
R <sub>ON(rail)</sub>	ON resistance (rail)	$V_{is} = V_{EE}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	150	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	80	140	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	70	120	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	60	105	Ω
		$V_{is} = V_{CC}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	150	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	90	160	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	80	140	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	65	120	Ω
ΔR <sub>ON</sub>	ON resistance mismatch	$V_{is} = V_{CC}$ to $V_{EE}$					
	between channels	V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	<u>[1]</u>	-	-	-	Ω
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V		-	100 180 90 160 70 130  150 - 80 140 70 120 60 105  150 - 90 160 80 140 65 120	Ω	
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V		-	8	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$		-	6	-	Ω
T <sub>amb</sub> = -4	0 °C to +85 °C						
R <sub>ON(peak)</sub>	ON resistance (peak)	$V_{is} = V_{CC}$ to $V_{EE}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	225	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	200	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	165	Ω

R<sub>ON</sub> resistance per switch for 74HC4053 and 74HCT4053 ...continued

 $V_I = V_{IH}$  or  $V_{IL}$ ; for test circuit see <u>Figure 9</u>.


 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

Vos is the output voltage at a nYn or nZ terminal, whichever is assigned as an output.

For 74HC4053:  $V_{CC}$  – GND or  $V_{CC}$  –  $V_{EE}$  = 2.0 V, 4.5 V, 6.0 V and 9.0 V. For 74HCT4053:  $V_{CC}$  – GND = 4.5 V and 5.5 V,  $V_{CC}$  –  $V_{EE}$  = 2.0 V, 4.5 V, 6.0 V and 9.0 V.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
R <sub>ON(rail)</sub>	ON resistance (rail)	$V_{is} = V_{EE}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	- 175 150 130 - 200 175 150 - 270 240 195 - 210 180 160	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-		Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	130	Ω
		$V_{is} = V_{CC}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	[1]	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	200	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	175	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	150	Ω
$T_{amb} = -4$	0 °C to +125 °C						
R <sub>ON(peak)</sub>	ON resistance (peak)	resistance (peak) V <sub>is</sub> = V <sub>CC</sub> to V <sub>EE</sub>					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	270	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	240	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	195	Ω
R <sub>ON(rail)</sub>	ON resistance (rail)	$V_{is} = V_{EE}$					
		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	<u>[1]</u>	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	210	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	180	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	160	Ω
		$V_{is} = V_{CC}$					
  -		$V_{CC} = 2.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 100 \mu\text{A}$	[1]	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	240	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	210	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}; I_{SW} = 1000 \mu\text{A}$		-	-	180	Ω

<sup>[1]</sup> When supply voltages (V<sub>CC</sub> - V<sub>EE</sub>) near 2.0 V the analog switch ON resistance becomes extremely non-linear. When using a supply of 2 V, it is recommended to use these devices only for transmitting digital signals.



#### Table 7. Static characteristics for 74HC4053

Voltages are referenced to GND (ground = 0 V).

V<sub>is</sub> is the input voltage at pins nYn or nZ, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T <sub>amb</sub> = 25	°C					
V <sub>IH</sub>	HIGH-level input	V <sub>CC</sub> = 2.0 V	1.5	1.2	-	V
	voltage	V <sub>CC</sub> = 4.5 V	3.15	2.4	-	V
		V <sub>CC</sub> = 6.0 V	4.2	3.2	-	V
		V <sub>CC</sub> = 9.0 V	6.3	4.7		V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 2.0 V	-	0.8	0.5	V
		V <sub>CC</sub> = 4.5 V	-	2.1	1.35	V
		V <sub>CC</sub> = 6.0 V	-	2.8	1.8	V
		V <sub>CC</sub> = 9.0 V	-	4.3	2.7	V
l <sub>l</sub>	input leakage current	$V_{EE} = 0 \text{ V}; V_I = V_{CC} \text{ or GND}$				
		V <sub>CC</sub> = 6.0 V	-	-	±0.1	μΑ
		V <sub>CC</sub> = 10.0 V	-	-	±0.2	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC}$ = 10.0 V; $V_{EE}$ = 0 V; $V_{I}$ = $V_{IH}$ or $V_{IL}$ ; $ V_{SW} $ = $V_{CC}$ - $V_{EE}$ ; see Figure 11				
		per channel	-	-	±0.1	μΑ
		all channels	-	-	±0.1	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_I = V_{IH}$ or $V_{IL}$ ; $ V_{SW}  = V_{CC} - V_{EE}$ ; $V_{CC} = 10.0$ V; $V_{EE} = 0$ V; see Figure 12	-	-	±0.1	μА

Table 7. Static characteristics for 74HC4053 ...continued

Voltages are referenced to GND (ground = 0 V).

 $V_{is}$  is the input voltage at pins nYn or nZ, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I <sub>CC</sub>	supply current	$V_{EE} = 0 \text{ V}; V_{I} = V_{CC} \text{ or GND}; V_{is} = V_{EE} \text{ or } V_{CC};$ $V_{os} = V_{CC} \text{ or } V_{EE}$				
		V <sub>CC</sub> = 6.0 V	-	-	8.0	μΑ
		V <sub>CC</sub> = 10.0 V	-	-	16.0	μА
Cı	input capacitance		-	3.5	-	pF
C <sub>sw</sub>	switch capacitance	independent pins nYn	-	5	-	pF
		common pins nZ	-	8	-	pF
T <sub>amb</sub> = -40	0 °C to +85 °C			1	1	
V <sub>IH</sub>	HIGH-level input	V <sub>CC</sub> = 2.0 V	1.5	-	-	V
	voltage	V <sub>CC</sub> = 4.5 V	3.15	-	-	V
		V <sub>CC</sub> = 6.0 V	4.2	-	-	V
		V <sub>CC</sub> = 9.0 V	6.3	-	-	V
V <sub>IL</sub>	LOW-level input	V <sub>CC</sub> = 2.0 V	-		0.5	V
	voltage	V <sub>CC</sub> = 4.5 V	-	-	1.35	V
		V <sub>CC</sub> = 6.0 V	-	-	1.8	V
		V <sub>CC</sub> = 9.0 V	-	-	2.7	V
I <sub>I</sub>	input leakage current	$V_{EE} = 0 \text{ V}; V_{I} = V_{CC} \text{ or GND}$				
		V <sub>CC</sub> = 6.0 V	-	-	±1.0	μΑ
		V <sub>CC</sub> = 10.0 V	-	-	±2.0	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Figure 11$				
		per channel	-	-	±1.0	μΑ
		all channels	-	-	±1.0	μА
I <sub>S(ON)</sub>	ON-state leakage current	$V_I = V_{IH}$ or $V_{IL}$ ; $ V_{SW}  = V_{CC} - V_{EE}$ ; $V_{CC} = 10.0$ V; $V_{EE} = 0$ V; see Figure 12	-	-	±1.0	μΑ
I <sub>CC</sub>	supply current	$V_{EE} = 0 \text{ V}; V_{I} = V_{CC} \text{ or GND}; V_{is} = V_{EE} \text{ or } V_{CC};$ $V_{os} = V_{CC} \text{ or } V_{EE}$				
		V <sub>CC</sub> = 6.0 V	-	-	80.0	μА
		V <sub>CC</sub> = 10.0 V	-	-	160.0	μΑ
T <sub>amb</sub> = -40	0 °C to +125 °C					
V <sub>IH</sub>	HIGH-level input	V <sub>CC</sub> = 2.0 V	1.5	-	-	V
	voltage	V <sub>CC</sub> = 4.5 V	3.15	-	-	V
		V <sub>CC</sub> = 6.0 V	4.2	-	-	V
		V <sub>CC</sub> = 9.0 V	6.3	-	-	V
V <sub>IL</sub>	LOW-level input	V <sub>CC</sub> = 2.0 V	-	-	0.5	V
	voltage	V <sub>CC</sub> = 4.5 V	-	-	1.35	V
		V <sub>CC</sub> = 6.0 V	-	-	1.8	V
		V <sub>CC</sub> = 9.0 V	-	-	2.7	V

#### Table 7. Static characteristics for 74HC4053 ... continued

Voltages are referenced to GND (ground = 0 V).

Vis is the input voltage at pins nYn or nZ, whichever is assigned as an input.

 $V_{os}$  is the output voltage at pins nZ or nYn, whichever is assigned as an output.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Iı	input leakage current	V <sub>EE</sub> = 0 V; V <sub>I</sub> = V <sub>CC</sub> or GND				
		V <sub>CC</sub> = 6.0 V	-	-	±1.0	μΑ
		V <sub>CC</sub> = 10.0 V	-	-	±2.0	μΑ
OFF-state leakage current		$V_{CC} = 10.0 \text{ V}$ ; $V_{EE} = 0 \text{ V}$ ; $V_{I} = V_{IH} \text{ or } V_{IL}$ ; $ V_{SW}  = V_{CC} - V_{EE}$ ; see Figure 11				
		per channel	-	-	±1.0	μΑ
		all channels	-	-	±1.0	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_I = V_{IH}$ or $V_{IL}$ ; $ V_{SW}  = V_{CC} - V_{EE}$ ; $V_{CC} = 10.0$ V; $V_{EE} = 0$ V; see Figure 12	-	-	±1.0	μΑ
I <sub>CC</sub>	supply current	$V_{EE} = 0 \text{ V}; V_{I} = V_{CC} \text{ or GND}; V_{is} = V_{EE} \text{ or } V_{CC};$ $V_{os} = V_{CC} \text{ or } V_{EE}$				
		V <sub>CC</sub> = 6.0 V	-	-	160.0	μΑ
		V <sub>CC</sub> = 10.0 V	-	-	320.0	μΑ

#### Table 8. Static characteristics for 74HCT4053

Voltages are referenced to GND (ground = 0 V).

Vis is the input voltage at pins nYn or nZ, whichever is assigned as an input.


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T <sub>amb</sub> = 25	°C				ı	
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	1.6	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	-	1.2	0.8	V
I <sub>I</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5$ V; $V_{EE} = 0$ V	-	-	±0.1	μА
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Figure } 11}{\text{Figure } 11}$				
		per channel	-	-	±0.1	μΑ
		all channels	-	-	±0.1	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Figure 12$	-	-	±0.1	μА
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		$V_{CC} = 5.5 \text{ V}; V_{EE} = 0 \text{ V}$	-	-	8.0	μΑ
		$V_{CC} = 5.0 \text{ V}; V_{EE} = -5.0 \text{ V}$	-	-	16.0	μΑ
Δl <sub>CC</sub>	additional supply current	per input; $V_I = V_{CC} - 2.1 \text{ V}$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 \text{ V}$ to 5.5 V; $V_{EE} = 0 \text{ V}$	-	50	180	μА
Cı	input capacitance		-	3.5	-	pF
C <sub>sw</sub>	switch capacitance	independent pins nYn	-	5	-	pF
		common pins nZ	-	8	-	pF

Table 8. Static characteristics for 74HCT4053 ...continued

Voltages are referenced to GND (ground = 0 V).


 $V_{is}$  is the input voltage at pins nYn or nZ, whichever is assigned as an input.

Symbol			Min	Тур	Max	Unit
T <sub>amb</sub> = -40	0 °C to +85 °C		_			
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	-	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.8	V
l <sub>l</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5$ V; $V_{EE} = 0$ V	-	-	±1.0	μΑ
I <sub>S(OFF)</sub> OFF-state leakage current		$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Figure } 11}{\text{Figure } 11}$				
		per channel	-	-	±1.0	μΑ
		all channels	-	-	±1.0	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Figure 12$	-	-	±1.0	μΑ
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		V <sub>CC</sub> = 5.5 V; V <sub>EE</sub> = 0 V	-	-	80.0	μΑ
		$V_{CC} = 5.0 \text{ V}; V_{EE} = -5.0 \text{ V}$	-	-	160.0	μΑ
$\Delta I_{CC}$	additional supply current	per input; $V_I = V_{CC} - 2.1 \text{ V}$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 \text{ V}$ to 5.5 V; $V_{EE} = 0 \text{ V}$	-	-	225	μΑ
T <sub>amb</sub> = -40	0 °C to +125 °C			•		
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	-	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.8	V
I <sub>I</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5$ V; $V_{EE} = 0$ V	-	-	±1.0	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Figure 11$				
		per channel	-	-	±1.0	μΑ
		all channels	-	-	±1.0	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10.0 \text{ V}; V_{EE} = 0 \text{ V}; V_I = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Figure 12$	-	-	±1.0	μΑ
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		V <sub>CC</sub> = 5.5 V; V <sub>EE</sub> = 0 V	-	-	160.0	μΑ
		$V_{CC} = 5.0 \text{ V}; V_{EE} = -5.0 \text{ V}$	-	-	320.0	μΑ
Δl <sub>CC</sub>	additional supply current	per input; $V_I = V_{CC} - 2.1 \text{ V}$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 \text{ V}$ to 5.5 V; $V_{EE} = 0 \text{ V}$	-	-	245	μΑ



 $V_{is} = V_{CC}$  and  $V_{os} = V_{EE}$ .  $V_{is} = V_{EE}$  and  $V_{os} = V_{CC}$ .

Fig 11. Test circuit for measuring OFF-state current



 $V_{is} = V_{CC}$  and  $V_{os} = \mbox{open-circuit}.$ 

 $V_{is} = V_{EE}$  and  $V_{os} =$  open-circuit.

Fig 12. Test circuit for measuring ON-state current

## 11. Dynamic characteristics

#### Table 9. Dynamic characteristics for 74HC4053

GND = 0 V;  $t_r = t_f = 6 \text{ ns}$ ;  $C_L = 50 \text{ pF}$ ; for test circuit see Figure 15.

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
<b>T</b> <sub>amb</sub> = <b>25</b>	°C					
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see <u>Figure 13</u> [1]				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	15	60	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	5	12	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	4	10	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	4	8	ns

Table 9. Dynamic characteristics for 74HC4053 ...continued

 $GND = 0 \text{ V}; t_r = t_f = 6 \text{ ns}; C_L = 50 \text{ pF}; \text{ for test circuit see } \underline{\textbf{Figure 15}}.$ 

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>on</sub>	turn-on time	$\overline{E}$ to $V_{os};R_{L}=\infty\Omega;see\underline{Figure14}$				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	60	220	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	20	44	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	17	-	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	16	37	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	31	ns
		Sn to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 14				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	75	220	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	25	44	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	21	-	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	20	37	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	31	ns
t <sub>off</sub>	turn-off time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	63	210	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	21	42	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	18	-	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	17	36	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	29	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	60	210	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	20	42	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	17	-	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	16	36	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	29	ns
C <sub>PD</sub>	power dissipation capacitance	per switch; $V_I = GND$ to $V_{CC}$	-	36	-	pF
T <sub>amb</sub> = -4	0 °C to +85 °C			I		
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 13				
•		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	75	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	15	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	13	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	10	ns

 Table 9.
 Dynamic characteristics for 74HC4053 ...continued

 $GND = 0 \text{ V}; t_r = t_f = 6 \text{ ns}; C_L = 50 \text{ pF}; \text{ for test circuit see } \underline{\textbf{Figure 15}}.$ 

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>on</sub>	turn-on time	$\overline{E}$ to $V_{os};R_{L}=\infty\Omega;see\underline{Figure14}$	2]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	275	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	55	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	47	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	39	ns
		Sn to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 14	2]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	275	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	55	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	47	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	39	ns
t <sub>off</sub>	turn-off time	$\overline{E}$ to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see $\underline{Figure 14}$	3]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	265	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	53	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	45	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	36	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14	3]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	265	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	53	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	45	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	36	ns
T <sub>amb</sub> = -4	10 °C to +125 °C		,			
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 13	1]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	90	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	18	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	15	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	12	ns
on	turn-on time	$\overline{E}$ to $V_{os};R_{L}=\infty\Omega;see\underline{Figure}14$	2]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	330	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	66	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	56	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	47	ns
		Sn to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 14	2]			
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	330	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	66	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	56	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	47	ns

#### Table 9. Dynamic characteristics for 74HC4053 ...continued

GND = 0 V;  $t_r = t_f = 6 \text{ ns}$ ;  $C_L = 50 \text{ pF}$ ; for test circuit see Figure 15.

V<sub>is</sub> is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nYn or nZ terminal, whichever is assigned as an output.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>off</sub>	turn-off time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	315	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	63	ns
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V}$	-	-	54	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	44	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V	-	-	315	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	63	ns
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V	-	-	54	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	44	ns

- [1] t<sub>pd</sub> is the same as t<sub>PHL</sub> and t<sub>PLH</sub>.
- [2]  $t_{on}$  is the same as  $t_{PZH}$  and  $t_{PZL}$ .
- [3]  $t_{off}$  is the same as  $t_{PHZ}$  and  $t_{PLZ}$ .
- [4]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu W$ ).

 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma \{(C_L + C_{sw}) \times V_{CC}^2 \times f_o\}$  where:

f<sub>i</sub> = input frequency in MHz;

 $f_o$  = output frequency in MHz;

N = number of inputs switching;

 $\Sigma \{(C_L + C_{sw}) \times V_{CC}^2 \times f_o\} = sum \text{ of outputs};$ 

C<sub>L</sub> = output load capacitance in pF;

C<sub>sw</sub> = switch capacitance in pF;

 $V_{CC}$  = supply voltage in V.

#### Table 10. Dynamic characteristics for 74HCT4053

GND = 0 V;  $t_r = t_f = 6 \text{ ns}$ ;  $C_L = 50 \text{ pF}$ ; for test circuit see <u>Figure 15</u>.

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nYn or nZ terminal, whichever is assigned as an output.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T <sub>amb</sub> = 25	°C			1		
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see <u>Figure 13</u> [1]				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	5	12	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	4	8	ns
t <sub>on</sub>	turn-on time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	27	48	ns
		$V_{CC} = 5.0 \text{ V}; V_{EE} = 0 \text{ V}; C_L = 15 \text{ pF}$	-	23	-	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	16	34	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	25	48	ns
		$V_{CC} = 5.0 \text{ V}; V_{EE} = 0 \text{ V}; C_L = 15 \text{ pF}$	-	21	-	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	16	34	ns

74HC HCT4053

Table 10. Dynamic characteristics for 74HCT4053 ...continued

 $GND = 0 \text{ V}; t_r = t_f = 6 \text{ ns}; C_L = 50 \text{ pF}; \text{ for test circuit see } \underline{\textbf{Figure 15}}.$ 

 $V_{is}$  is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>off</sub>	turn-off time	$\overline{E}$ to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see $\underline{Figure 14}$	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	24	44	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	20	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	31	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see <u>Figure 14</u>	[			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	22	44	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	-	19	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	15	31	ns
$C_{PD}$	power dissipation capacitance	per switch; $V_I = GND$ to $V_{CC} - 1.5 \text{ V}$	-	36	-	pF
$T_{amb} = -4$	0 °C to +85 °C					
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 13	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	15	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	10	ns
t <sub>on</sub>	turn-on time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see <u>Figure 14</u>	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	60	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	43	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	60	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	43	ns
t <sub>off</sub>	turn-off time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see <u>Figure 14</u>	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	55	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	39	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	55	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	39	ns
T <sub>amb</sub> = -4	0 °C to +125 °C		'			
t <sub>pd</sub>	propagation delay	$V_{is}$ to $V_{os}$ ; $R_L = \infty \Omega$ ; see Figure 13	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	18	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	12	ns
t <sub>on</sub>	turn-on time	$\overline{E}$ to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14	1			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	72	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	51	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14	!			
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	72	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-	51	ns

#### Table 10. Dynamic characteristics for 74HCT4053 ...continued

 $GND = 0 \text{ V; } t_r = t_f = 6 \text{ ns; } C_L = 50 \text{ pF; for test circuit see } Figure 15.$ 

Vis is the input voltage at a nYn or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nYn or nZ terminal, whichever is assigned as an output.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t <sub>off</sub>	turn-off time	$\overline{E}$ to V <sub>os</sub> ; R <sub>L</sub> = 1 k $\Omega$ ; see <u>Figure 14</u>				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	66	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	47	ns
		Sn to $V_{os}$ ; $R_L = 1 \text{ k}\Omega$ ; see Figure 14				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	-	66	ns
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	-	-	47	ns

- [1]  $t_{pd}$  is the same as  $t_{PHL}$  and  $t_{PLH}$ .
- [2] ton is the same as tPZH and tPZL.
- [3]  $t_{off}$  is the same as  $t_{PHZ}$  and  $t_{PLZ}$ .
- [4]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu W$ ).

$$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma \{(C_L + C_{sw}) \times V_{CC}^2 \times f_o\} \text{ where: }$$

 $f_i$  = input frequency in MHz;

f<sub>o</sub> = output frequency in MHz;


N = number of inputs switching;


 $\Sigma \{(C_L + C_{sw}) \times V_{CC}^2 \times f_o\} = \text{sum of outputs};$ 


C<sub>L</sub> = output load capacitance in pF;

C<sub>sw</sub> = switch capacitance in pF;

 $V_{CC}$  = supply voltage in V.







© Nexperia B.V. 2017. All rights reserved

Table 11. Test data

Test	Input			Load	Load		
	VI	V <sub>is</sub>	t <sub>r</sub> , t <sub>f</sub>		CL	R <sub>L</sub>	
			at f <sub>max</sub> other[1]				
t <sub>PHL</sub> , t <sub>PLH</sub>	[2]	pulse	< 2 ns	6 ns	50 pF	1 kΩ	open
$t_{PZH}, t_{PHZ}$	[2]	V <sub>CC</sub>	< 2 ns	6 ns	50 pF	1 kΩ	V <sub>EE</sub>
t <sub>PZL</sub> , t <sub>PLZ</sub>	[2]	V <sub>EE</sub>	< 2 ns	6 ns	50 pF	1 kΩ	V <sub>CC</sub>

- [1]  $t_r = t_f = 6$  ns; when measuring  $f_{max}$ , there is no constraint to  $t_r$  and  $t_f$  with 50 % duty factor.
- [2] V<sub>I</sub> values:
  - a) For 74HC4053:  $V_I = V_{CC}$
  - b) For 74HCT4053:  $V_1 = 3 V$

## 11.1 Additional dynamic characteristics

#### Table 12. Additional dynamic characteristics

Recommended conditions and typical values; GND = 0 V;  $T_{amb} = 25 \text{ °C}$ ;  $C_L = 50 \text{ pF}$ .  $V_{is}$  is the input voltage at pins nYn or nZ, whichever is assigned as an input.  $V_{os}$  is the output voltage at pins nYn or nZ, whichever is assigned as an output.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
d <sub>sin</sub>	sine-wave distortion	$f_i = 1 \text{ kHz}$ ; $R_L = 10 \text{ k}\Omega$ ; see Figure 16					
		$V_{is} = 4.0 \text{ V (p-p)}; V_{CC} = 2.25 \text{ V}; V_{EE} = -2.25 \text{ V}$		-	0.04	-	%
		$V_{is} = 8.0 \text{ V (p-p)}; V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$		-	0.02	-	%
		$f_i = 10 \text{ kHz}$ ; $R_L = 10 \text{ k}\Omega$ ; see Figure 16					
		$V_{is} = 4.0 \text{ V (p-p)}; V_{CC} = 2.25 \text{ V}; V_{EE} = -2.25 \text{ V}$		-	0.12	-	%
		$V_{is} = 8.0 \text{ V (p-p)}; V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$		-	0.06	-	%
$\alpha_{iso}$	isolation (OFF-state)	$R_L = 600 \Omega$ ; $f_i = 1 MHz$ ; see Figure 17					
		$V_{CC} = 2.25 \text{ V}; V_{EE} = -2.25 \text{ V}$	[1]	-	-50	-	dB
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	[1]	-	-50	-	dB
Xtalk	crosstalk	between two switches/multiplexers; $R_L = 600 \Omega$ ; $f_i = 1 MHz$ ; see Figure 18					
		$V_{CC} = 2.25 \text{ V}; V_{EE} = -2.25 \text{ V}$	[1]	-	-60	-	dB
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	[1]	-	-60	-	dB
V <sub>ct</sub>	crosstalk voltage	peak-to-peak value; between control and any switch; $R_L = 600 \ \Omega$ ; $f_i = 1 \ MHz$ ; $\overline{E}$ or Sn square wave between $V_{CC}$ and GND; $t_r = t_f = 6 \ ns$ ; see Figure 19					
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V		-	110	-	mV
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$		-	220	-	mV
f <sub>(-3dB)</sub>	-3 dB frequency response	$R_L = 50 \Omega$ ; see Figure 20					
		$V_{CC} = 2.25 \text{ V}; V_{EE} = -2.25 \text{ V}$	[2]	-	160	-	MHz
		$V_{CC} = 4.5 \text{ V}; V_{EE} = -4.5 \text{ V}$	[2]	-	170	-	MHz

- [1] Adjust input voltage  $V_{is}$  to 0 dBm level (0 dBm = 1 mW into 600  $\Omega$ ).
- [2] Adjust input voltage  $V_{is}$  to 0 dBm level at  $V_{os}$  for 1 MHz (0 dBm = 1 mW into 50  $\Omega$ ).

**Product data sheet** 






Fig 16. Test circuit for measuring sine-wave distortion



 $V_{CC}$  = 4.5 V; GND = 0 V;  $V_{EE}$  = –4.5 V;  $R_L$  = 600  $\Omega;$   $R_S$  = 1  $k\Omega.$ 


a. Test circuit





b. Isolation (OFF-state) as a function of frequency

Fig 17. Test circuit for measuring isolation (OFF-state)

© Nexperia B.V. 2017. All rights reserved








 $V_{CC}$  = 4.5 V; GND = 0 V;  $V_{EE}$  = –4.5 V;  $R_L$  = 50  $\Omega;$   $R_S$  = 1  $k\Omega.$ 

#### a. Test circuit



b. Typical frequency response


Fig 20. Test circuit for frequency response

© Nexperia B.V. 2017. All rights reserved

## 12. Package outline

#### SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1



UNIT	A max.	A <sub>1</sub>	A <sub>2</sub>	<b>A</b> <sub>3</sub>	bp	С	D <sup>(1)</sup>	E <sup>(1)</sup>	e	HE	L	Lp	Q	v	w	у	Z <sup>(1)</sup>	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	10.0 9.8	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01		0.0100 0.0075	0.39 0.38	0.16 0.15	0.05	0.244 0.228	0.041	0.039 0.016	0.028 0.020	0.01	0.01	0.004	0.028 0.012	0°

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.


OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT109-1	076E07	MS-012				<del>99-12-27</del> 03-02-19

Fig 21. Package outline SOT109-1 (SO16)

74HC\_HCT4053

#### SSOP16: plastic shrink small outline package; 16 leads; body width 5.3 mm

SOT338-1



#### Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT338-1		MO-150				<del>99-12-27</del> 03-02-19

Fig 22. Package outline SOT338-1 (SSOP16)

74HC\_HCT4053

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1



				,		-,												
UNIT	A max.	A <sub>1</sub>	A <sub>2</sub>	A <sub>3</sub>	bp	С	D <sup>(1)</sup>	E (2)	е	HE	L	Lp	Q	v	w	у	Z <sup>(1)</sup>	θ
mm	1.1	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	5.1 4.9	4.5 4.3	0.65	6.6 6.2	1	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.40 0.06	8° 0°

#### Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT403-1		MO-153				<del>99-12-27</del> 03-02-18

Fig 23. Package outline SOT403-1 (TSSOP16)

74HC\_HCT4053

DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 x 3.5 x 0.85 mm SOT763-1




Fig 24. Package outline SOT763-1 (DHVQFN16)

74HC\_HCT4053

## 13. Abbreviations

#### Table 13. Abbreviations

Acronym	Description			
CMOS	Complementary Metal-Oxide Semiconductor			
ESD	ElectroStatic Discharge			
HBM	Human Body Model			
MM	Machine Model			

## 14. Revision history

#### Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74HC_HCT4053 v.9	20160210	Product data sheet	-	74HC_HCT4053 v.8
Modifications:	Type numbers	s 74HC4053N and 74HCT	4053N (SOT38-4) re	emoved.
74HC_HCT4053 v.8	20120719	Product data sheet	-	74HC_HCT4053 v.7
Modifications:	<ul> <li>CDM added t</li> </ul>	o features.		
74HC_HCT4053 v.7	20111213	Product data sheet	-	74HC_HCT4053 v.6
Modifications:	Legal pages i	updated.		
74HC_HCT4053 v.6	20110511	Product data sheet	-	74HC_HCT4053 v.5
74HC_HCT4053 v.5	20110118	Product data sheet	-	74HC_HCT4053 v.4
74HC_HCT4053 v.4	20060509	Product data sheet	-	74HC_HCT4053 v.3
74HC_HCT4053 v.3	20060315	Product data sheet	-	74HC_HCT4053_CNV v.2
74HC_HCT4053_CNV v.2	19901201	Product specification	-	-

## 15. Legal information

#### 15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <a href="http://www.nexperia.com">http://www.nexperia.com</a>.

#### 15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

74HC HCT4053

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of

non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### 15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

#### 16. Contact information

For more information, please visit: http://www.nexperia.com

For sales office addresses, please send an email to: salesaddresses@nexperia.com

## 17. Contents

1	General description
2	Features and benefits
3	Applications
4	Ordering information
5	Functional diagram
6	Pinning information
6.1	Pinning
6.2	Pin description
7	Functional description
8	Limiting values
9	Recommended operating conditions
10	Static characteristics
11	Dynamic characteristics
11.1	Additional dynamic characteristics 20
12	Package outline
13	Abbreviations
14	Revision history
15	Legal information
15.1	Data sheet status
15.2	Definitions
15.3	Disclaimers
15.4	Trademarks
16	Contact information 3
17	Contents

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Nexperia:

74HC4053D 74HCT4053D 74HC4053DB 74HC4053PW 74HCT4053DB 74HCT4053N 74HCT4053PW

## NXP:

74HC4053BQ,115 74HC4053D,652 74HC4053DB,112 74HC4053DB,118 74HC4053D,653 74HC4053N,652 74HC4053PW,112 74HC4053PW,118 74HCT4053BQ,115 74HCT4053DB,112 74HCT4053DB,118 74HCT4053D,118 74HCT4053N,112 74HCT4053PW,112 74HCT4053PW,118