



Sample &

Buy







CSD86350Q5D

SLPS223F-MAY 2010-REVISED OCTOBER 2016

# CSD86350Q5D Synchronous Buck NexFET<sup>™</sup> Power Block

### 1 Features


- Half-Bridge Power Block
- 90% System Efficiency at 25 A
- Up to 40-A Operation
- High-Frequency Operation (up to 1.5 MHz)
- High-Density SON 5-mm × 6-mm Footprint
- Optimized for 5-V Gate Drive
- Low-Switching Losses
- Ultra-Low Inductance Package
- RoHS Compliant
- Halogen Free
- Lead-Free Terminal Plating

# 2 Applications

- Synchronous Buck Converters
  - High-Frequency Applications
  - High-Current, Low-Duty Cycle Applications
- Multiphase Synchronous Buck Converters
- POL DC-DC Converters
- IMVP, VRM, and VRD Applications

# 3 Description


The CSD86350Q5D NexFET<sup>™</sup> power block is an optimized design for synchronous buck applications offering high-current, high-efficiency, and high-frequency capability in a small 5-mm × 6-mm outline. Optimized for 5-V gate drive applications, this product offers a flexible solution capable of offering a high-density power supply when paired with any 5-V gate drive from an external controller/driver.




### **Device Information**<sup>(1)</sup>

DEVICE	MEDIA	QTY	PACKAGE	SHIP
CSD86350Q5D	13-Inch Reel	2500	SON	Таре
CSD86350Q5DT	7-Inch Reel	250	5.00-mm × 6.00-mm Plastic Package	and Reel

(1) For all available packages, see the orderable addendum at the end of the data sheet.



### Typical Power Block Efficiency and Power Loss





An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.

2

# **Table of Contents**

1 2		ures lications	
3		cription	
4	Rev	ision History	2
5	Spe	cifications	4
	5.1	Absolute Maximum Ratings	4
	5.2	Recommended Operating Conditions	4
	5.3	Thermal Information	4
	5.4	Power Block Performance	4
	5.5	Electrical Characteristics	5
	5.6	Typical Power Block Device Characteristics	6
	5.7	Typical Power Block MOSFET Characteristics	8
6	Арр	lication and Implementation1	1
	6.1	Application Information 1	1

Changes from Revision E (October 2011) to Revision F

7	Lay	out	16
	7.1	Layout Guidelines	. 16
	7.2	Layout Example	
8	Dev	ice and Documentation Support	18
	8.1	Documentation Support	. 18
	8.2	Receiving Notification of Documentation Updates.	. 18
	8.3	Community Resources	. 18
	8.4	Trademarks	. 18
	8.5	Glossary	. 18
9	Mec	hanical, Packaging, and Orderable	
		rmation	19
	9.1	Q5D Package Dimensions	. 19
	9.2	Land Pattern Recommendation	. 20
	9.3	Stencil Recommendation	. 20
	9.4	Q5D Tape and Reel Information	. 21

### **4** Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Added small reel option	1
Added footnote for pulsed current rating	
Changed Recommended PCB Design Overview section to Layout section	16
Added Device and Documentation Support section	
Changed MECHANICAL DATA section to Mechanical, Packaging, and Orderable In	formation section 19
Changes from Revision D (September 2011) to Revision E	Page
Changed "DIM a" Millimeter Max value From: 1.55 To: 1.5 and Inches Max value Free	om: 0.061 To: 0.059 19
Changes from Revision C (November 2010) to Revision D	Page
Replace R <sub>DS(on)</sub> with Z <sub>DS(on)</sub>	
Added Equivalent System Performance section	
Added Electrical Performance bullet	
Changes from Revision B (September 2010) to Revision C	Page
Added the Stencil Recommendation illustration	
Changes from Revision A (May 2010) to Revision B	Page
Updated Figure 6	
Updated Figure 7	
Updated Figure 8	
Updated Figure 9	

EXAS

Page

www.ti.com



SLPS223F-MAY 2010-REVISED OCTOBER 2016

#### Changes from Original (May 2010) to Revision A

|--|

•	Changed graph title From: TYPICAL EFFICIENCY vs POWER LOSS To: TYPICAL POWER BLOCK EFFICIENCY
	and POWER LOSS 1
•	Updated the Land Pattern Recommendation illustration

#### CSD86350Q5D

SLPS223F - MAY 2010 - REVISED OCTOBER 2016



www.ti.com

### **5** Specifications

### 5.1 Absolute Maximum Ratings

 $T_A = 25^{\circ}C$  (unless otherwise noted)<sup>(1)</sup>

		MIN	MAX	UNIT
	V <sub>IN</sub> to P <sub>GND</sub>	-0.8	25	
Voltage	T <sub>G</sub> to T <sub>GR</sub>	-8	10	V
	B <sub>G</sub> to P <sub>GND</sub>	-8	10	
Pulsed current rating, ID	M <sup>(2)</sup>		120	А
Power dissipation, P <sub>D</sub>			13	W
	Sync FET, I <sub>D</sub> = 100 A, L = 0.1 mH		500	ml
Avalanche energy, $E_{AS}$	Control FET, $I_D = 58 \text{ A}$ , L = 0.1 mH		168	- mJ
Operating junction, T <sub>J</sub>		-55	150	°C
Storage temperature, T <sub>S</sub>	ITG	-55	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Pulse duration  $\leq$  50 µs, duty cycle  $\leq$  1%.

## 5.2 Recommended Operating Conditions

 $T_A = 25^{\circ}$  (unless otherwise noted)

			MIN	MAX	UNIT
$V_{GS}$	Gate drive voltage		4.5	8	V
V <sub>IN</sub>	Input supply voltage			22	V
f <sub>SW</sub>	Switching frequency	$C_{BST} = 0.1 \ \mu F (min)$	200	1500	kHz
	Operating current			40	А
TJ	Operating temperature			125	°C

## 5.3 Thermal Information

#### $T_A = 25^{\circ}C$ (unless otherwise stated)

	THERMAL METRIC	MIN	TYP	MAX	UNIT
D	Junction-to-ambient thermal resistance (min Cu) <sup>(1)(2)</sup>			102	°C/W
$R_{ extsf{ heta}JA}$	Junction-to-ambient thermal resistance (max Cu) <sup>(1)(2)</sup>			50	°C/W
Р	Junction-to-case thermal resistance (top of package) <sup>(2)</sup>			20	°C/W
$R_{ ext{ heta}JC}$	Junction-to-case thermal resistance (P <sub>GND</sub> pin) <sup>(2)</sup>			2	°C/W

(1) Device mounted on FR4 material with 1-in<sup>2</sup> (6.45-cm<sup>2</sup>) Cu.

(2) R<sub>0JC</sub> is determined with the device mounted on a 1-in<sup>2</sup> (6.45-cm<sup>2</sup>), 2 oz (0.071-mm) thick Cu pad on a 1.5-in x 1.5-in (3.81-cm x 3.81-cm), 0.06-in (1.52-mm) thick FR4 board. R<sub>0JC</sub> is specified by design while R<sub>0JA</sub> is determined by the user's board design.

### 5.4 Power Block Performance

 $T_A = 25^\circ$  (unless otherwise noted)

	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
P <sub>LOSS</sub>	Power loss <sup>(1)</sup>			2.8		W
I <sub>QVIN</sub>	V <sub>IN</sub> quiescent current	$T_G$ to $T_{GR} = 0$ V B <sub>G</sub> to P <sub>GND</sub> = 0 V		10		μA


 Measurement made with six 10-µF (TDK C3216X5R1C106KT or equivalent) ceramic capacitors placed across V<sub>IN</sub> to P<sub>GND</sub> pins and using a high-current 5-V driver IC.

### 5.5 Electrical Characteristics


 $T_A = 25^{\circ}C$  (unless otherwise stated)

	DADAMETED	TEAT CONDITIONS	Q1 Control FET			Q2 Sync FET			
	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
STATIC	CHARACTERISTICS				•				
$BV_{DSS}$	Drain-to-source voltage	$V_{GS} = 0 \text{ V}, \text{ I}_{DS} = 250 \mu\text{A}$	25			25			V
I <sub>DSS</sub>	Drain-to-source leakage current	$V_{GS} = 0 V, V_{DS} = 20 V$			1			1	μA
I <sub>GSS</sub>	Gate-to-source leakage current	$V_{DS} = 0 V, V_{GS} = +10 / -8 V$			100			100	nA
V <sub>GS(th)</sub>	Gate-to-source threshold voltage	$V_{DS} = V_{GS}$ , $I_{DS} = 250 \ \mu A$	0.9	1.4	2.1	0.9	1.1	1.6	V
Z <sub>DS(on)</sub>	Drain-to-source on impedance			5			1.1		mΩ
9 <sub>fs</sub>	Transconductance	$V_{DS} = 10 \text{ V}, \text{ I}_{DS} = 20 \text{ A}$		103			132		S
DYNAM	IIC CHARACTERISTICS								
C <sub>ISS</sub>	Input capacitance <sup>(1)</sup>			1440	1870		3080	4000	pF
C <sub>OSS</sub>	Output capacitance <sup>(1)</sup>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 12.5 V, f = 1 MHz		645	840		1550	2015	pF
C <sub>RSS</sub>	Reverse transfer capacitance <sup>(1)</sup>			22	29		45	59	pF
R <sub>G</sub>	Series gate resistance <sup>(1)</sup>			1.4	2.8		1.4	2.8	Ω
Qg	Gate charge total (4.5 V) <sup>(1)</sup>			8.2	10.7		19.4	25	nC
Q <sub>gd</sub>	Gate charge – gate-to-drain	V <sub>DS</sub> = 12.5 V,		1			2.5		nC
Q <sub>gs</sub>	Gate charge – gate-to-source	$I_{DS} = 20 \text{ A}$		3.2			5.1		nC
Q <sub>g(th)</sub>	Gate charge at V <sub>th</sub>			1.9			2.8		nC
Q <sub>OSS</sub>	Output charge	$V_{DS} = 12 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$		9.9			28		nC
t <sub>d(on)</sub>	Turnon delay time			8			9		ns
t <sub>r</sub>	Rise time	V <sub>DS</sub> = 12.5 V, V <sub>GS</sub> = 4.5 V,		21			23		ns
t <sub>d(off)</sub>	Turnoff delay time	$I_{DS} = 20 \text{ A}, \text{ R}_{G} = 2 \Omega$		9			24		ns
t <sub>f</sub>	Fall time			2.3			21		ns
DIODE	CHARACTERISTICS								
$V_{SD}$	Diode forward voltage	I <sub>DS</sub> = 20 A, V <sub>GS</sub> = 0 V		0.85	1		0.77	1	V
Q <sub>rr</sub>	Reverse recovery charge	V <sub>dd</sub> = 12 V, I <sub>F</sub> = 20 A,		16			40		nC
t <sub>rr</sub>	Reverse recovery time	di/dt = 300 A/µs		22			32		ns

(1) Specified by design.



Max  $R_{\theta JA} = 50^{\circ}$ C/W when mounted on 1-in<sup>2</sup> (6.45-cm<sup>2</sup>) of 2-oz (0.071-mm) thick Cu.



Max  $R_{\theta JA} = 102^{\circ}C/W$ when mounted on minimum pad area of 2-oz (0.071-mm) thick Cu.




#### CSD86350Q5D

SLPS223F-MAY 2010-REVISED OCTOBER 2016

www.ti.com

### 5.6 Typical Power Block Device Characteristics


 $T_J = 125^{\circ}C$ , unless stated otherwise.



(1) The Typical Power Block System Characteristic curves are based on measurements made on a PCB design with dimensions of 4 in (W) x 3.5 in (L) x 0.062 in (H) and 6 copper layers of 1-oz copper thickness. See *Application and Implementation* for detailed explanation.



### **Typical Power Block Device Characteristics (continued)**



 $T_J = 125^{\circ}C$ , unless stated otherwise.




#### CSD86350Q5D

SLPS223F-MAY 2010-REVISED OCTOBER 2016

www.ti.com

### 5.7 Typical Power Block MOSFET Characteristics


 $T_A = 25^{\circ}C$ , unless stated otherwise.






### **Typical Power Block MOSFET Characteristics (continued)**

 $T_A = 25^{\circ}C$ , unless stated otherwise.



## **Typical Power Block MOSFET Characteristics (continued)**

 $T_A = 25^{\circ}C$ , unless stated otherwise.





### 6 Application and Implementation

#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 6.1 Application Information

#### 6.1.1 Equivalent System Performance

Many of today's high-performance computing systems require low-power consumption in an effort to reduce system operating temperatures and improve overall system efficiency. This has created a major emphasis on improving the conversion efficiency of today's synchronous buck topology. In particular, there has been an emphasis in improving the performance of the critical power semiconductor in the power stage of this application (see Figure 28). As such, optimization of the power semiconductors in these applications, needs to go beyond simply reducing R<sub>DS(ON)</sub>.




Figure 28. Equivalent System Schematic

The CSD86350Q5D is part of TI's power block product family which is a highly optimized product for use in a synchronous buck topology requiring high-current, high-efficiency, and high-frequency. It incorporates TI's latest generation silicon which has been optimized for switching performance, as well as minimizing losses associated with Q<sub>GD</sub>, Q<sub>GS</sub>, and Q<sub>RR</sub>. Furthermore, TI's patented packaging technology has minimized losses by nearly eliminating parasitic elements between the control FET and sync FET connections (see Figure 29). A key challenge solved by TI's patented packaging technology is the system-level impact of Common Source Inductance (CSI). CSI greatly impedes the switching characteristics of any MOSFET which in turn increases switching losses and reduces system efficiency. As a result, the effects of CSI need to be considered during the MOSFET selection process. In addition, standard MOSFET switching loss equations used to predict system efficiency need to be modified in order to account for the effects of CSI. Further details behind the effects of CSI and modification of switching loss equations are outlined in *Power Loss Calculation With Common Source Inductance Consideration for Synchronous Buck Converters* (SLPA009).



### **Application Information (continued)**





Figure 29. Elimination of Parasitic Inductances

The combination of TI's latest generation silicon and optimized packaging technology has created a benchmarking solution that outperforms industry standard MOSFET chipsets of similar  $R_{DS(ON)}$  and MOSFET chipsets with lower  $R_{DS(ON)}$ . Figure 30 and Figure 31 compare the efficiency and power loss performance of the CSD86350Q5D versus industry standard MOSFET chipsets commonly used in this type of application. This comparison purely focuses on the efficiency and generated loss of the power semiconductors only. The performance of CSD86350Q5D clearly highlights the importance of considering the effective AC on-impedance ( $Z_{DS(ON)}$ ) during the MOSFET selection process of any new design. Simply normalizing to traditional MOSFET  $R_{DS(ON)}$  specifications is not an indicator of the actual in-circuit performance when using TI's power block technology.





### **Application Information (continued)**

Table 1 below compares the traditional DC measured  $R_{DS(ON)}$  of CSD86350Q5D versus its  $Z_{DS(ON)}$ . This comparison takes into account the improved efficiency associated with TI's patented packaging technology. As such, when comparing TI's power block products to individually packaged discrete MOSFETs or dual MOSFETs in a standard package, the in-circuit switching performance of the solution must be considered. In this example, individually packaged discrete MOSFETs or dual MOSFETs or dual MOSFETs in a standard package would need to have DC measured  $R_{DS(ON)}$  values that are equivalent to CSD86350Q5D's  $Z_{DS(ON)}$  value in order to have the same efficiency performance at full load. Mid to light-load efficiency will still be lower with individually packaged discrete MOSFETs in a standard package.

DADAMETED	H	IS	LS		
PARAMETER	TYP	MAX	ТҮР	MAX	
Effective AC on-impedance ( $Z_{DS(ON)}$ ), $V_{GS}$ = 5 V	5	—	1.1	—	
DC measured $R_{DS(ON)}$ , $V_{GS}$ = 4.5 V	5	6.6	2	2.7	

### Table 1. Comparison of R<sub>DS(ON)</sub> vs. Z<sub>DS(ON)</sub>

The CSD86350Q5D NexFET<sup>™</sup> power block is an optimized design for synchronous buck applications using 5-V gate drive. The control FET and sync FET silicon are parametrically tuned to yield the lowest power loss and highest system efficiency. As a result, a new rating method is needed which is tailored towards a more systems-centric environment. System-level performance curves such as power loss, Safe Operating Area (SOA), and normalized graphs allow engineers to predict the product performance in the actual application.

### 6.1.2 Power Loss Curves

MOSFET centric parameters such as  $R_{DS(ON)}$  and  $Q_{gd}$  are needed to estimate the loss generated by the devices. In an effort to simplify the design process for engineers, Texas Instruments has provided measured power loss performance curves. Figure 1 plots the power loss of the CSD86350Q5D as a function of load current. This curve is measured by configuring and running the CSD86350Q5D as it would be in the final application (see Figure 32). The measured power loss is the CSD86350Q5D loss and consists of both input conversion loss and gate drive loss. Equation 1 is used to generate the power loss curve.

$$(V_{IN} \times I_{IN}) + (V_{DD} \times I_{DD}) - (V_{SW AVG} \times I_{OUT}) = Power Loss$$

(1)

The power loss curve in Figure 1 is measured at the maximum recommended junction temperatures of 125°C under isothermal test conditions.

### 6.1.3 Safe Operating Area (SOA) Curves

The SOA curves in the CSD86350Q5D data sheet provides guidance on the temperature boundaries within an operating system by incorporating the thermal resistance and system power loss. Figure 3 to Figure 5 outline the temperature and airflow conditions required for a given load current. The area under the curve dictates the safe operating area. All the curves are based on measurements made on a PCB design with dimensions of 4 in (W) × 3.5 in (L) × 0.062 in (T) and 6 copper layers of 1-oz copper thickness.

#### 6.1.4 Normalized Curves

The normalized curves in the CSD86350Q5D data sheet provides guidance on the power loss and SOA adjustments based on their application specific needs. These curves show how the power loss and SOA boundaries will adjust for a given set of systems conditions. The primary Y-axis is the normalized change in power loss and the secondary Y-axis is the change in system temperature required in order to comply with the SOA curve. The change in power loss is a multiplier for the power loss curve and the change in temperature is subtracted from the SOA curve.

TEXAS INSTRUMENTS

www.ti.com




Figure 32. Typical Application

#### 6.1.5 Calculating Power Loss and SOA

The user can estimate product loss and SOA boundaries by arithmetic means (see Design Example). Though the power loss and SOA curves in this data sheet are taken for a specific set of test conditions, the following procedure will outline the steps the user should take to predict product performance for any set of system conditions.

### 6.1.5.1 Design Example

**Operating Conditions:** 

- Output Current = 25 A
- Input Voltage = 7 V
- Output Voltage = 1 V
- Switching Frequency = 800 kHz
- Inductor = 0.2 µH

### 6.1.5.2 Calculating Power Loss

- Power loss at 25 A = 3.5 W (Figure 1)
- Normalized power loss for input voltage  $\approx$  1.07 (Figure 7)
- Normalized power loss for output voltage ≈ 0.95 (Figure 8)
- Normalized power loss for switching frequency ≈ 1.11 (Figure 6)
- Normalized power loss for output inductor ≈ 1.07 (Figure 9)
- Final calculated power loss = 3.5 W × 1.07 × 0.95 × 1.11 × 1.07 ≈ 4.23 W

### 6.1.5.3 Calculating SOA Adjustments

- SOA adjustment for input voltage ≈ 2°C (Figure 7)
- SOA adjustment for output voltage  $\approx -1.3$ °C (Figure 8)
- SOA adjustment for switching frequency  $\approx 2.8^{\circ}$ C (Figure 6)
- SOA adjustment for output inductor ≈ 1.6°C (Figure 9)
- Final calculated SOA adjustment = 2 + (-1.3) + 2.8 + 1.6 ≈ 5.1°C

In the design example above, the estimated power loss of the CSD86350Q5D would increase to 4.23 W. In addition, the maximum allowable board and/or ambient temperature would have to decrease by 5.1°C. Figure 33 graphically shows how the SOA curve would be adjusted accordingly.

- 1. Start by drawing a horizontal line from the application current to the SOA curve.
- 2. Draw a vertical line from the SOA curve intercept down to the board/ambient temperature.



3. Adjust the SOA board/ambient temperature by subtracting the temperature adjustment value.

In the design example, the SOA temperature adjustment yields a reduction in allowable board/ambient temperature of 5.1°C. In the event the adjustment value is a negative number, subtracting the negative number would yield an increase in allowable board/ambient temperature.




Figure 33. Power Block SOA

CSD86350Q5D SLPS223F – MAY 2010–REVISED OCTOBER 2016



### 7 Layout

#### 7.1 Layout Guidelines

There are two key system-level parameters that can be addressed with a proper PCB design: electrical and thermal performance. Properly optimizing the PCB layout will yield maximum performance in both areas. A brief description on how to address each parameter is provided.

#### 7.1.1 Electrical Performance

The power block has the ability to switch voltages at rates greater than 10 kV/µs. Special care must be then taken with the PCB layout design and placement of the input capacitors, driver IC, and output inductor.

- The placement of the input capacitors relative to the power block's VIN and PGND pins should have the highest priority during the component placement routine. It is critical to minimize these node lengths. As such, ceramic input capacitors need to be placed as close as possible to the VIN and PGND pins (see Figure 34). The example in Figure 34 uses 6 × 10-µF ceramic capacitors (TDK part C3216X5R1C106KT or equivalent). Notice there are ceramic capacitors on both sides of the board with an appropriate amount of vias interconnecting both layers. In terms of priority of placement next to the power block, C5, C7, C19, and C8 should follow in order.
- The driver IC should be placed relatively close to the power block gate pins. T<sub>G</sub> and B<sub>G</sub> should connect to the outputs of the driver IC. The T<sub>GR</sub> pin serves as the return path of the high-side gate drive circuitry and should be connected to the phase pin of the IC (sometimes called LX, LL, SW, PH, etc.). The bootstrap capacitor for the driver IC will also connect to this pin.
- The switching node of the output inductor should be placed relatively close to the power block VSW pins. Minimizing the node length between these two components will reduce the PCB conduction losses and actually reduce the switching noise level. In the event the switch node waveform exhibits ringing that reaches undesirable levels, the use of a boost resistor or RC snubber can be an effective way to easily reduce the peak ring level. The recommended boost resistor value will range between 1  $\Omega$  to 4.7  $\Omega$  depending on the output characteristics of driver IC used in conjunction with the power block. The RC snubber values can range from 0.5  $\Omega$  to 2.2  $\Omega$  for the R and 330 pF to 2200 pF for the C. Please refer to *Snubber Circuits: Theory, Design and Application* (SLUP100) for more details on how to properly tune the RC snubber values. The RC snubber should be placed as close as possible to the VSW node and PGND see Figure 34. <sup>(1)</sup>

#### 7.1.2 Thermal Performance

The power block has the ability to utilize the GND planes as the primary thermal path. As such, the use of thermal vias is an effective way to pull away heat from the device and into the system board. Concerns of solder voids and manufacturability problems can be addressed by the use of three basic tactics to minimize the amount of solder attach that will wick down the via barrel:

- Intentionally space out the vias from each other to avoid a cluster of holes in a given area.
- Use the smallest drill size allowed in your design. The example in Figure 34 uses vias with a 10-mil drill hole and a 16-mil capture pad.
- Tent the opposite side of the via with solder-mask.

In the end, the number and drill size of the thermal vias should align with the end user's PCB design rules and manufacturing capabilities.

<sup>(1)</sup> Keong W. Kam, David Pommerenke, "EMI Analysis Methods for Synchronous Buck Converter EMI Root Cause Analysis", University of Missouri – Rolla



# 7.2 Layout Example




Figure 34. Recommended PCB Layout (Top Down View)

TEXAS INSTRUMENTS

www.ti.com

### 8 Device and Documentation Support

#### 8.1 Documentation Support

#### 8.1.1 Related Documentation

For related documentation see the following:

- Power Loss Calculation With Common Source Inductance Consideration for Synchronous Buck Converters (SLPA009)
- Snubber Circuits: Theory, Design and Application (SLUP100)

### 8.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

#### 8.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 8.4 Trademarks

NexFET, E2E are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

#### 8.5 Glossary

#### SLYZ022 — TI Glossary.


This glossary lists and explains terms, acronyms, and definitions.



# 9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

### 9.1 Q5D Package Dimensions




DIM	MILLIMETERS		INCHES			
	MIN	МАХ	MIN	MAX		
а	1.40	1.5	0.055	0.059		
b	0.360	0.460	0.014	0.018		
С	0.150	0.250	0.006	0.010		
c1	0.150	0.250	0.006	0.010		
d	1.630	1.730	0.064	0.068		
d1	0.280	0.380	0.011	0.015		
d2	0.200	0.300	0.008	0.012		
d3	0.291	0.391	0.012	0.015		
D1	4.900	5.100	0.193	0.201		
D2	4.269	4.369	0.168	0.172		
E	4.900	5.100	0.193	0.201		
E1	5.900	6.100	0.232	0.240		
E2	3.106	3.206	0.122	0.126		
e	1.27 TYP		0.050 TYP			
f	0.396	0.496	0.016	0.020		
L	0.510	0.710	0.020	0.028		
θ	0.00	_	_	_		
К	0.812 TYP		0.032 TYP			

SLPS223F - MAY 2010 - REVISED OCTOBER 2016




www.ti.com

#### 9.2 Land Pattern Recommendation



NOTE: Dimensions are in mm (inches).

#### 9.3 Stencil Recommendation



M0208-01


NOTE: Dimensions are in mm (inches).

For recommended circuit layout for PCB designs, see *Reducing Ringing Through PCB Layout Techniques* (SLPA005).



M0191-01

### 9.4 Q5D Tape and Reel Information



A0 = 5.30 ±0.10 B0 = 6.50 ±0.10 K0 = 1.90 ±0.10

- NOTES: 1. 10-sprocket hole-pitch cumulative tolerance ±0.2.
  - 2. Camber not to exceed 1 mm in 100 mm, noncumulative over 250 mm.
  - 3. Material: black static-dissipative polystyrene.
  - 4. All dimensions are in mm, unless otherwise specified.
  - 5. Thickness: 0.30 ±0.05 mm.
  - 6. MSL1 260°C (IR and convection) PbF reflow compatible.


# PACKAGE MATERIALS INFORMATION

www.ti.com

Texas Instruments

### TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CSD86350Q5D	LSON- CLIP	DQY	8	2500	330.0	12.4	5.3	6.3	1.8	8.0	12.0	Q2
CSD86350Q5D	LSON- CLIP	DQY	8	2500	330.0	12.8	5.3	6.5	1.9	8.0	12.0	Q2
CSD86350Q5D	LSON- CLIP	DQY	8	2500	330.0	15.4	5.3	6.3	1.2	8.0	12.0	Q2

TEXAS INSTRUMENTS

www.ti.com

# PACKAGE MATERIALS INFORMATION

31-Mar-2016



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CSD86350Q5D	LSON-CLIP	DQY	8	2500	367.0	367.0	35.0
CSD86350Q5D	LSON-CLIP	DQY	8	2500	410.0	65.0	35.0
CSD86350Q5D	LSON-CLIP	DQY	8	2500	335.0	335.0	32.0

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications					
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive				
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications				
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers				
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps				
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy				
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial				
Interface	interface.ti.com	Medical	www.ti.com/medical				
Logic	logic.ti.com	Security	www.ti.com/security				
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense				
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video				
RFID	www.ti-rfid.com						
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com				
Wireless Connectivity	www.ti.com/wirelessconnectivity						

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated