

Data sheet acquired from Harris Semiconductor SCHS083B – Revised March 2003

## **CMOS Programmable Timer**

High-Voltage Types (20-Volt Rating)

■ CD4536B is a programmable timer consisting of 24 ripple-binary counter stages. The salient feature of this device is its flexibility. The device can count from 1 to 224 or the first 8 stages can be bypassed to allow an output, selectable by a 4-bit code, from any one of the remaining 16 stages. It can be driven by an external clock or an RC oscillator that can be constructed using onchip components. Input IN1 serves as either the external clock input or the input to the on-chip RC oscillator, OUT1 and OUT2 are connection terminals for the external RC components. In addition, an on-chip monostable circuit is provided to allow a variable pulse width output. Various timing functions can be achieved using combinations of these capabilities.

A logic 1 on the 8-BYPASS input enables a bypass of the first 8 stages and makes stage 9 the first counter stage of the last 16 stages. Selection of 1 of 16 outputs is accomplished by the decoder and the BCD inputs A, B, C and D. MONO IN is the timing input for the on-chip monostable oscillator. Grounding of the MONO IN terminal through a resistor of 10K ohms or higher, disables the one-shot circuit and connects the decoder directly to the DECODE OUT terminal. A resistor to VDD and a capacitor to ground from the MONO IN terminal enables the one-shot circuit and controls its pulse width.


A fast test mode is enabled by a logic 1 on 8-BYPASS, SET, and RESET. This mode

#### Features:

- 24 flip-flop stages —— counts from 2° to 2° 4
- Last 16 stages selectable by BCD select code
- Bypass input allows bypassing first 8 stages
- On-chip RC oscillator provision
- # Clock inhibit input
- Schmitt-trigger in clock line permits operation with very long rise and fall times
- On-chip monostable output provision
- Typical f<sub>CL</sub> = 3 MHz at V<sub>DD</sub> = 10 V
- Test mode allows fast test sequence
- Set and reset inputs
- Capable of driving two low power TTL loads, one lower-power Schottky load, or two HTL loads over the rated temperature range
- Standardized, symmetrical output characteristics
- 100% tested for quiescent current at 20 V
- 5-V, 10-V, and 15-V parametric ratings
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices"

divides the 24-stage counter into three 8-stage sections to facilitate a fast test sequence.

The CD4536B types are supplied in 16-lead hermetic dual-in-line ceramic packages (F3A suffix), 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (DW, DWR, and NSR suffixes), and 16-lead thin shrink small-outline packages (PW and PWR suffixes).



CD4536B Types

### RECOMMENDED OPERATING CONDITIONS

For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

CHARACTERISTIC	LIN	UNITS		
	Min.	Max.		
Supply-Voltage Range (For T <sub>A</sub> = Full Package Temperature				
Range)	3	18	V	

#### **DECODE OUT SELECTION TABLE**

В	С	В	A	NUMBER OF DIVIDER CHA	
		)	(	8-BYPASS = 0	8-BYPASS = 1
0	0	0	0	9	1
0	0	0	1	10	2
Q	0	1	0	11	3
0	0	1	1	12	4
0	1	0	0	13	5
0	1	0	1	. 14	6
0	1	1	0	15	7
0	1	1	1	16	8
1	0	0	0	17	9
1	0	0	1	18	10
1	0	1	0	19	11
1	0	1.	1	20	12
1	1	0	0	21	13
1	1	0	1	22	14
1	1	1	0	23	15
L	1	1	1	24	16

0 = Low Level 1 = High Level

MAXIMUM RATINGS, Absolute-Maximum Values:
DC SUPPLY-VOLTAGE RANGE, (VDD)
Voltages referenced to VSS Terminal)0.5V to +20V
INPUT VOLTAGE RANGE, ALL INPUTS0.5V to VDD +0.5V
DC INPUT CURRENT, ANY ONE INPUT ±10mA
POWER DISSIPATION PER PACKAGE (PD):
For T <sub>A</sub> = -55°C to +100°C 500mW
For TA = +100°C to +125°C Derate Linearity at 12mW/°C to 200mW
DEVICE DISSIPATION PER OUTPUT TRANSISTOR
FOR TA = FULL PACKAGE-TEMPERATURE RANGE (All Package Types) 100mW
OPERATING-TEMPERATURE RANGE (TA)55°C to +125°C
STORAGE TEMPERATURE RANGE (Tstg)65°C to +150°C
LEAD TEMPERATURE (DURING SOLDERING):
At distance 1/16 ± 1/32 inch (1.59 ± 0.79mm) from case for 10s max +265°C

CHARAC- TERISTIC	CONDITIONS			LIMITS AT INDICATED TEMPERATURES (°C)								
	V <sub>O</sub> (V)	V <sub>IN</sub> (V)	V <sub>DD</sub> (V)	-55	-40	+85	+125	Min.	+25 Typ.	Max.	S	
_		0,5	5	5	5	150	150	_	0.04	5	Г	
Quiescent Device	-, ,	0,10	10	10	10	300	300	_	0.04	10	میر	
Current,	_	0,15	15	20	20	600	600	,. <del>-</del>	0.04	- 20		
I <sub>DD</sub> Max.	-	0,20	20	100	100	3000	3000	- "	0.08	100	ļ .~	
0	0.4	0,5	5	0.64	0.61	0.42	0.36	0.51	1			
Output Low (Sink) Current IOL Min.	0.5	0,10	10	1.6	1.5	1.1	0.9	1.3	2.6			
	1.5	0,15	15	4.2	4	2.8	2.4	3.4	6.8	-		
O	4.6	0,5	5	-0.64	-0.61	-0.42	-0.36	<b>-</b> 0.51	-1	_	m	
Output High (Source)	2.5	0,5	5	-2	-1.8	-1.3	-1.15	-1.6	-3.2	-		
Current,	9.5	0,10	10	-1.6	-1.5	-1.1	-0.9	-1.3	-2.6	· - ·	] •	
OH Min!	13.5	0,15	15	-4.2	-4	-2.8	-2.4	-3.4	-6.8	-	Ī	
Output Voltage:	_	0,5	5	0.05				_	0	0.05		
Low-Level,	_	0,10	10		0		0	0.05	1			
VOL Max.	<del>,</del> .	.0,15	15		0	.05			0	0.05	١,	
Output	-	0,5	5		4	.95	4.95	s 5	_			
Voltage:	-	0,10	10		9	.95	, A	9.95	10	×-	1	
High-Level, V <sub>OH</sub> Min.	—	0,15	. 15		14	14.95	15	-				
	0.5,4.5	_	5			1.5		_	_	1.5	十	
Input Low Voltage	1,9		10		•	3				3	1	
	1.5,13.5		15			4			_	4	٦,	
Input High	0.5,4.5	-	5		₹,	3.5		3.5	_	<u> </u>	1	
Voltage,	1,9	-	10			. 7 :		7	-		1	
V <sub>IH</sub> Min.	1.5,13.5	-	15			11		- 11	-			
Input Current	_	0,18	18	±0.1	±0.1	±1	±1		±10 <sup>-5</sup>	±0.1	μ	




Fig. 1 - Functional block diagram.




Fig. 2—Typical output low (sink) current characteristics.




Fig. 3—Minimum output low (sink) current characteristics.




Fig. 4—Typical output high (source) current characteristics.




Fig. 5—Minimum output high (source) current characteristics.




Fig.6 - Logic diagram for CD4536B [continued on next page].

NOTE: 
$$f \approx \frac{1}{3R_T C_T}$$
,  $R_S \approx (5 \rightarrow 10) \times R_T$ 





Fig.6 - Logic diagram for CD4536B [continued from previous page].

The companies of the contraction of the contraction

The second of the second secon

# DYNAMIC ELECTRICAL CHARACTERISTICS, at $T_A=25\,^{\circ}C$ , Input $t_r$ , $t_f=20$ ns, $C_L=50$ pF, $R_L=200$ kQ

CHARACTERISTIC	V <sub>DD</sub>		LIMITS	;	HAUTO
- CHARACTERISTIC	(v)	Min.	Тур.	Max.	UNITS
Propagation Delay Times:	- 5	_	1	2	
Clock to Q1, 8-Bypass High	10	<b> </b>	0.5	1	μS
tphL, tpLH	15	-	0.35	0.7	. •
Clock to Q1, 8-Bypass Low	5		2.5	5	-
tPHL tPLH	10	_	0.8	1.6	μ8
	15	L <i>-</i> _	0.6	1.2	
Clock to Q16, TPHL tPLH	5	-	4	- 8	
	10		1.5	3	μS
	15		1	2	,
Qn to Qn + 1, tpHL, tpLH	5		150	300	
	10.	. —	75	150	ns
and the second s	15	_	50	100	_
Set to Q <sub>n</sub> , t <sub>PLH</sub>	5		300	600	
1 Bed 1	10	l .—	125	250	ns
	15	_	80	160	
Reset to Q <sub>n</sub> , t <sub>PHL</sub>	5		3	6	
	10	_	1	2	μS
	15	l —	0.75	1.5	
Transition Time, t <sub>THL</sub> , t <sub>TLH</sub>	5	_	100	200	
THE TEN	10	_	50	100	ns
	15		40	80	
Minimum Pulse Widths:	5	_	200	400	
Clock	10	_	75	150	ns
	15	_	50	100	
Set	5		200	400	
The state of the s	10	l —	100	200	ns
	15		60	120	
Reset	5	1	3	6	
**	10	<u> </u>	1	2	μS
	. 15		0.75	1.5	
Minimum Set Recovery Time,	5		2.5	5	_
The second se	10	·	1	2	μς
The second secon	15		0.6	1.6	
Minimum Reset Recovery Time,	5	_	3.5	7	
	10		1.5	3	μS
	15		1	2	
Maximum Clock Pulse Input	. 5	0.5	1	_	
Frequency, f <sub>GL</sub>	10	1.5	3	_	MHz
	15	2.5	5		
Maximum Clock Pulse Input	5,10,15				
Rise or Fall Time, t <sub>r</sub> , t <sub>f</sub>			nlimited		






Fig. 7-Typical propagation delay time as a function of load capacitance (CLOCK to Ω<sub>1</sub>, 8-BYPASS high).




Fig. 8—Typical propagation delay time as a function of load capacitance (CLOCK to Q<sub>1</sub>, 8-BYPASS low).




Fig. 9—Typical propagation delay time as a function of load capacitance (CLOCK to Q<sub>16</sub>, 8-BYPASS high).




Fig. 10—Typical propagation delay time as a function of load capacitance ( $Q_N$  to  $Q_{N+1}$ ).




Fig. 13—Typical RC oscillator frequency deviation as a function of ambient temperature (R<sub>S</sub> = 0).




Fig. 16—Typical pulse width as a function of external capacitance  $(V_{DD} = 10 \text{ V})$ .




Fig. 17—Typical pulse width as a function of external capacitance ( $V_{DD} = 15 \text{ V}$ ).




Fig. 11—Typical RC oscillator frequency deviation as a function of supply voltage.




Fig. 14—Typical RC oscillator frequency deviation as a function of ambient temperature (R<sub>S</sub> = 120 kΩ).




Fig. 12—Typical RC oscillator frequency deviation as a function of time constant resistance and capacitance.




Fig. 15—Typical pulse width as a function of external capacitance ( $V_{DD} = 5 \text{ V}$ ).

		F	unctional Tes	t Sequence	
		Inputs		Outputs	Comments
In 1	Set	Reset	8-Bypass	Decode Out Q1 thru Q24	All 24 steps are in Reset mode
_ 1	0	1	. 1	0	]
1	1	1	1	0	Counter is in three 8-stage section in parallel mode
0	1	1	1	0	First "1" to "0" transition of clock
1 0 —	1	1	1		255 "1" to "0" transitions are clocked in the counter
					<u> </u>
0	1	1 1	1	1	The 255 "1" to "0" transition
0	0	0	0	1	Counter converted back to 24 stages in series mode Set and Reset must be connected together and simultaneously go from "1"

#### **FUNCTIONAL TEST SEQUENCE**

Test Function (Figure 23) has been included for the reduction of test time required to exercise all 24 counter stages. This test function divides the counter into three 8-stage sections and 255 counts are

loaded in each of the 8-stage sections in parallel. All flip-flops are now at a "1". The counter is now returned to the normal 24-steps in series configuration. One more pulse is entered into In<sub>1</sub> which will cause the counter to ripple from an all "1" state to an all "0" state.

Counter Ripples from an all "1" state to

In 1 Switches to a "1"

an all "0" state




Fig. 18—Typical transition time as a function of load capacitance.





Fig. 20-Dynamic power dissipation test circuit and waveform.



19 — Typical dynamic power dissipation as a function of input pulse frequency.






Fig. 21—Switching time test circuit.





1 = High Level 0 = Low Level X = Don't Care




Fig. 22-Input waveforms for switching-time test circuit.




Fig. 23-Functional test circuit.




Fig. 24—Input-current test circuit.




Fig. 25-Input-voltage test circuit.




Fig. 26—Quiescent-device current test circuit.

#### **APPLICATIONS**




Fig. 27—Time interval configuration using external clock; set and clock inhibit functions.




Fig. 28—Time interval configuration using external clock; reset and output monostable to achieve a pulse output.





Fig. 29—Time interval configuration using onchip RC oscillator and reset input to initiate time interval.






Fig.30 — Application showing use of CD4098B and CD4536B to get decode pulse 8 clock pulses after Reset pulse.





Fig.31 — CD4536B Timing Diagram.

Dimensions and pad layout for CD4536BH.

Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils (10<sup>-3</sup> inch).







10-Jun-2014

#### **PACKAGING INFORMATION**

Orderable Device	Status	Package Type		Pins	_	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
CD4536BDW	ACTIVE	SOIC	DW	16	40	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4536BM	Samples
CD4536BDWR	ACTIVE	SOIC	DW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4536BM	Samples
CD4536BE	ACTIVE	PDIP	N	16	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-55 to 125	CD4536BE	Samples
CD4536BEE4	ACTIVE	PDIP	N	16	25	Pb-Free (RoHS)	CU NIPDAU	N / A for Pkg Type	-55 to 125	CD4536BE	Samples
CD4536BF3A	ACTIVE	CDIP	J	16	1	TBD	A42	N / A for Pkg Type	-55 to 125	CD4536BF3A	Samples
CD4536BNSR	ACTIVE	SO	NS	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4536B	Samples
CD4536BNSRG4	ACTIVE	SO	NS	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4536B	Samples
CD4536BPW	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM536B	Samples
CD4536BPWE4	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM536B	Samples
CD4536BPWR	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM536B	Samples
CD4536BPWRE4	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM536B	Samples
CD4536BPWRG4	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM536B	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

### **PACKAGE OPTION ADDENDUM**



10-Jun-2014

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes. **Pb-Free** (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CD4536B, CD4536B-MIL:

Catalog: CD4536B

Military: CD4536B-MIL

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

### PACKAGE MATERIALS INFORMATION

www.ti.com 26-Jan-2013

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
BO	Dimension designed to accommodate the component length
	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

All difficultions are norminal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD4536BDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
CD4536BNSR	SO	NS	16	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
CD4536BPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 26-Jan-2013



\*All dimensions are nominal

ń	7 III GITTIOTOTOTO GEO TIOTITICA							
	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
	CD4536BDWR	SOIC	DW	16	2000	367.0	367.0	38.0
	CD4536BNSR	SO	NS	16	2000	367.0	367.0	38.0
	CD4536BPWR	TSSOP	PW	16	2000	367.0	367.0	35.0

### **MECHANICAL DATA**

### NS (R-PDSO-G\*\*)

# 14-PINS SHOWN

#### PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



### 14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

PW (R-PDSO-G16)

### PLASTIC SMALL OUTLINE




- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
- E. Falls within JEDEC MO-153



# PW (R-PDSO-G16)


### PLASTIC SMALL OUTLINE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



SMALL OUTLINE INTEGRATED CIRCUIT



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040000-2/H





SOIC



- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing
- per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
- 5. Reference JEDEC registration MS-013.



SOIC



#### NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



#### NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



### N (R-PDIP-T\*\*)

### PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.