muRata

Reference Specification

MLCC radial lead type with epoxy coat (RDE Series)

Do not use these products in any automotivepower train or safety equipment including batterychargers for electric vehicles and plug-in hybrids.

Product specifications in this catalog are as of Dec.2014, and are subject to change or obsolescence without notice.


Please consult the approval sheet before ordering. Please read rating and Cautions first.

▲ CAUTION

1. OPERATING VOLTAGE

When DC-rated capacitors are to be used in AC or ripple current circuits, be sure to maintain the Vp-p value of the applied voltage or the Vo-p which contains DC bias within the rated voltage range. When the voltage is started to apply to the circuit or it is stopped applying, the irregular voltage may be generated for a transit period because of resonance or switching. Be sure to use a capacitor within rated voltage containing these irregular voltage.

When DC-rated capacitors are to be used in input circuits from commercial power source (AC filter), be sure to use Safety Recognized Capacitors because various regulations on withstand voltage or impulse withstand established for each equipment should be taken into considerations.



2. OPERATING TEMPERATURE AND SELF-GENERATED HEAT

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself.

When the capacitor is used in a high-frequency current, pulse current or the like, it may have the selfgenerated heat due to dielectric-loss. In case of Class 2 capacitors (Temp.Char. : F,X8L,X7R,X7S,X7T, Y5V), applied voltage should be the load such as self-generated heat is within 20 °C on <u>the condition of</u> <u>atmosphere temperature 25 °C</u>. Please contact us if self-generated heat is occurred with Class 1 capacitors (Temp.Char. : C0G,U2J,X8G). When measuring, use a thermocouple of small thermal capacity-K of ϕ 0.1mm and be in the condition where capacitor is not affected by radiant heat of other components and wind of surroundings. Excessive heat may lead to deterioration of the capacitor's characteristics and reliability.

3. Fail-safe

Be sure to provide an appropriate fail-safe function on your product to prevent a second damage that may be caused by the abnormal function or the failure of our product.

4. OPERATING AND STORAGE ENVIRONMENT

The insulating coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. And avoid exposure to moisture. Before cleaning, bonding, or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment. Store the capacitors where the temperature and relative humidity do not exceed 5 to 40 °C and 20 to 70%. Use capacitors within 6 months.

5. VIBRATION AND IMPACT

Do not expose a capacitor or its leads to excessive shock or vibration during use.

6. SOLDERING

When soldering this product to a PCB/PWB, do not exceed the solder heat resistance specification of the capacitor. Subjecting this product to excessive heating could melt the internal junction solder and may result in thermal shocks that can crack the ceramic element.

7. BONDING AND RESIN MOLDING, RESIN COAT

In case of bonding, molding or coating this product, verify that these processes do not affect the quality of capacitor by testing the performance of a bonded or molded product in the intended equipment. In case of the amount of applications, dryness / hardening conditions of adhesives and molding resins containing organic solvents (ethyl acetate, methyl ethyl ketone, toluene, etc.) are unsuitable, the outer coating resin of a capacitor is damaged by the organic solvents and it may result, worst case, in a short circuit.

The variation in thickness of adhesive or molding resin may cause a outer coating resin cracking and/or ceramic element cracking of a capacitor in a temperature cycling.

8. TREATMENT AFTER BONDING AND RESIN MOLDING, RESIN COAT

When the outer coating is hot (over 100 $^{\circ}$ C) after soldering, it becomes soft and fragile. So please be careful not to give it mechanical stress.

Failure to follow the above cautions may result, worst case, in a short circuit and cause fuming or partial dispersion when the product is used.

9. LIMITATION OF APPLICATIONS

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- 1. Aircraft equipment
- Undersea equipment
 Medical equipment
- 2. Aerospace equipment
- 4. Power plant control equipment
- 6. Transportation equipment (vehicles, trains, ships, etc.)8. Disaster prevention / crime prevention equipment
- 7. Traffic signal equipment
- 9. Data-processing equipment exerting influence on public
- 10. Application of similar complexity and/or reliability requirements to the applications listed in the above.

NOTICE

1. CLEANING (ULTRASONIC CLEANING)

To perform ultrasonic cleaning, observe the following conditions.


Rinse bath capacity : Output of 20 watts per liter or less.

Rinsing time : 5 min maximum.

Do not vibrate the PCB/PWB directly.

Excessive ultrasonic cleaning may lead to fatigue destruction of the lead wires.

- 2. Soldering and Mounting
 - 1) Allowable Conditions for Soldering Temperature and Time Perform soldering within tolerance range (shaded portion).



Dimension code

- (1) 0, 1, 2(F 2.5mm)
- (2) 0, 1, 2(F 5.0mm), 3, 4, W
- (3) 5, U

2) Insertion of the Lead Wire

- When soldering, insert the lead wire into the PCB without mechanically stressing the lead wire.
- Insert the lead wire into the PCB with a distance appropriate to the lead space.

3. CAPACITANCE CHANGE OF CAPACITORS

• Class 2 capacitors (Temp.Char. : F,X8L,X7R,X7S,X7T,Y5V)

Class 2 capacitors an aging characteristic, whereby the capacitor continually decreases its capacitance slightly if the capacitor leaves for a long time. Moreover, capacitance might change greatly depending on a surrounding temperature or an applied voltage. So, it is not likely to be able to use for the time constant circuit.

Please contact us if you need a detail information.

- 1. Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- 2. You are requested not to use our product deviating from this specification.

1. Application

This product specification is applied to Radial Lead Type Monolithic Ceramic Capacitors with epoxy coat used for General Electronic equipment.

2. Rating

• Part number configuration

	• Pa	ant numbe	er conligu	ration							
ex.)	RDE	es Temperature Rate		1H	103	K	K		K1	H03	В
	Series		cteristic	Rated voltage	Capacitance	Capacitance tolerance		nension code	Lead code	Individual specification code	Packing style code
	I I I	mperatur	Temp.			Cap. Change	Δ	Stand	hard	Operating	
		Code	Char.	IOP	np. Range	(Within%)	C	Terr		Temp. Range	
		R7	X7R	-5	5 ~ 125°C	+/-15		250	2C	-55 ~ 125°C	
		C7 X7S		-0	5 125 0	+/-22		25°C		-551-725 C	

• Rated voltage

Code	Rated voltage
1E	DC25V
1H	DC50V
2A	DC100V

Capacitance

The first two digits denote significant figures ; the last digit denotes the multiplier of 10 in pF. ex.) In case of 103.

 $10 \times 10^3 = 10000 \text{pF}$

• Capacitance tolerance

Code	Capacitance Tolerance
K	+/-10%
М	+/-20%

• Dimension code

Code	Dimensions (LxW) mm max.
0	4.0 x 3.5 (Lead code : K1, M1)
0	5.0 x 3.5 (Lead code : P1, S1)
1	4.5 x 3.5 (Lead code : K1, M1)
I	5.0 x 3.5 (Lead code : P1, S1)
2	5.5 x 4.0
3	5.5 x 5.0
W	5.5 x 7.5

• Lead code

Code	Lead style	Lead spacing (mm)
K1	Inside crimp type	5.0+/-0.8
M1	Inside crimp taping type	5.0+0.6/-0.2
P1	Outside crimp type	2.5+/-0.8
S1	Outside crimp taping type	2.5+0.4/-0.2

Lead wire is solder coated CP wire.


- Individual specification code Murata's control code Please refer to [Part number list].
- Packing style code


Code	Packing style
А	Taping type of Ammo
В	Bulk type

3. Marking

Temp. char.	: Letter code : C (X7R/X7S Char. Except dimension code : 0,1)
Capacitance	: 3 digit numbers
Capacitance tolerance	: Code
Rated voltage	: Letter code : 2 (DC25V only. Except dimension code : 0,1)
	Letter code : 5 (DC50V only. Except dimension code : 0,1)
	Letter code : 1 (DC100V only. Except dimension code : 0,1)
Company name code	: Abbreviation : M (Except dimension code : 0,1)

(Ex.)			
Rated voltage Dimension code	25V	50V	100V
0,1	104K	103K	224K
2	Gr 475 K2C	Gr 105 K5C	Gr 105 K1C
3,W	@226 K2C	@ 335 K5C	64225 K1C





	nber Murata Part Number		DC Rated Volt. (V)		Cap.		Dime	nsion ((mm)		Size	
Customer Part Number		T.C.		Cap.	tol.	L	W	W1	F	Т	Lead Code	qt (pc
	RDER71E104K0P1H03B	X7R	25	0.10µF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDEC71E224K0P1H03B	X7S	25	0.22µF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDEC71E474K0P1H03B	X7S	25	0.47µF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDEC71E105K0P1H03B	X7S	25	1.0µF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDEC71E225K1P1H03B	X7S	25	2.2µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	50
	RDEC71E475K2P1H03B	X7S	25	4.7µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDEC71E106K2P1H03B	X7S	25	10µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDEC71E226K3P1H03B	X7S	25	22µF	±10%	5.5	5.0	7.5	2.5	4.0	3P1	50
	RDER71H221K0P1H03B	X7R	50	220pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H331K0P1H03B	X7R	50	330pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H471K0P1H03B	X7R	50	470pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H681K0P1H03B	X7R	50	680pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H102K0P1H03B	X7R	50	1000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H152K0P1H03B	X7R	50	1500pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H222K0P1H03B	X7R	50	2200pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H332K0P1H03B	X7R	50	3300pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H472K0P1H03B	X7R	50	4700pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H682K0P1H03B	X7R	50	6800pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H103K0P1H03B	X7R	50	10000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H153K0P1H03B	X7R	50	15000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H223K0P1H03B	X7R	50	22000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H333K0P1H03B	X7R	50	33000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H473K0P1H03B	X7R	50	47000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H683K0P1H03B	X7R	50	68000pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H104K0P1H03B	X7R	50	0.10µF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER71H154K1P1H03B	X7R	50	0.15µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	50
	RDER71H224K1P1H03B	X7R	50	0.22µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	50
	RDER71H334K1P1H03B	X7R	50	0.33µF	$\pm 10\%$	5.0	3.5	5.0	2.5	3.15	1P1	50
	RDER71H474K1P1H03B	X7R	50	0.47µF	$\pm 10\%$	5.0	3.5	5.0	2.5	3.15	1P1	50
	RDER71H684K2P1H03B	X7R	50	0.68µF	$\pm 10\%$	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDER71H105K2P1H03B	X7R	50	1.0µF	$\pm 10\%$	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDER71H155K2P1H03B	X7R	50	1.5µF	$\pm 10\%$	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDER71H225K2P1H03B	X7R	50	2.2µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDER71H335K3P1H03B	X7R	50	3.3µF	±10%	5.5	5.0	7.5	2.5	4.0	3P1	50
	RDEC71H475K2P1H03B	X7S	50	4.7µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	50
	RDEC71H106K3P1H03B	X7S	50	10µF	±10%	5.5	5.0	7.5	2.5	4.0	3P1	50
	RDER72A221K0P1H03B	X7R	100	220pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER72A331K0P1H03B	X7R	100	330pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER72A471K0P1H03B	X7R	100	470pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50
	RDER72A681K0P1H03B	X7R	100	680pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	50

•Outside Crimp (Lead Code:P1)					ide Cri d Code							
F ± 0.8		95		F	B 0 f crimp		25.0 min. W max. K max. W1 max.		max.	: 0. 05	Jnit :	mm
Customer Part Number	Murata Part Number	T.C.	DC Rated Volt.	Cap.	Cap. tol.	. 1		nsion (,		Size Lead	Pack qty.
			(V)			L	W	W1	F	Т	Code	(pcs)
	RDER72A102K0P1H03B	X7R	100	1000pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A152K0P1H03B	X7R	100	1500pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A222K0P1H03B	X7R	100	2200pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A332K0P1H03B	X7R	100	3300pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A472K0P1H03B	X7R	100	4700pF	±10%	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A682K0P1H03B	X7R	100	6800pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A103K0P1H03B	X7R	100	10000pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A153K0P1H03B	X7R	100	15000pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A223K0P1H03B	X7R	100	22000pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	0P1	500
	RDER72A333K1P1H03B	X7R	100	33000pF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A473K1P1H03B	X7R	100	47000pF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A683K1P1H03B	X7R	100	68000pF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A104K1P1H03B	X7R	100	0.10µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A154K2P1H03B	X7R	100	0.15µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	500
	RDER72A224K1P1H03B	X7R	100	0.22µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A334K1P1H03B	X7R	100	0.33µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A474K1P1H03B	X7R	100	0.47µF	±10%	5.0	3.5	5.0	2.5	3.15	1P1	500
	RDER72A684K2P1H03B	X7R	100	0.68µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	500
	RDER72A105K2P1H03B	X7R	100	1.0µF	±10%	5.5	4.0	6.0	2.5	3.15	2P1	500
	RDEC72A155K3P1H03B	X7S	100	1.5µF		5.5	5.0	7.5	2.5	4.0		500
	RDEC72A225K3P1H03B	X7S	100	2.2µF	±10%	5.5	5.0	7.5	2.5	4.0	3P1	500
	RDER71E104K0K1H03B	X7R	25	0.10µF		4.0	3.5	6.0	5.0	2.5		500
	RDEC71E224K0K1H03B	X7S	25	0.22µF		4.0	3.5	6.0	5.0	2.5		500
	RDEC71E474K0K1H03B	X7S	25	0.47µF		4.0	3.5	6.0	5.0	2.5		500
	RDEC71E105K0K1H03B	X7S	25	1.0µF		4.0	3.5	6.0	5.0	2.5		500
	RDEC71E225K1K1H03B	X7S	25	2.2µF	±10%	4.5	3.5	5.0	5.0	3.15		500
	RDEC71E475K2K1H03B	X7S	25	4.7µF	±10%	5.5	4.0	6.0	5.0	3.15		500
	RDEC71E106K2K1H03B	X7S	25	10µF	±10%	5.5	4.0	6.0	5.0	3.15		500
	RDEC71E226K3K1H03B	X7S	25	22µF	±10%	5.5	5.0	7.5	5.0	4.0	-	500
	RDEC71E476MWK1H03B	X7S	25	22μι 47μF		5.5	7.5	10.0	5.0	4.0		500
	RDER71H221K0K1H03B	X7R	50	220pF		4.0	3.5	6.0	5.0	2.5		500
	RDER71H331K0K1H03B	X7R	50	330pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H471K0K1H03B	X7R	50	470pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H681K0K1H03B	X7R	50	680pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H102K0K1H03B	X7R	50	1000pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H152K0K1H03B	X7R	50	1500pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H222K0K1H03B	X7R	50	2200pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H332K0K1H03B	X7R	50	2200pF 3300pF	±10%	4.0	3.5	6.0	5.0	2.5		500
	RDER71H332K0K1H03B	X7R	50	· ·	±10%		3.5	6.0	5.0 5.0	2.5 2.5		500
			50	4700pF	- IU70	4.0	5.5	0.0	5.0	∠.0		300
	RDER71H682K0K1H03B	X7R	50	6800pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	500

				only								
- Inside Crimp (Lead Code:K1)												
F ± 0.8	x. T max. T max. xem xem ui ui ui ui ui ui ui ui to 0.5 ± 0.05	5									Unit :	mm
			DC				Dimo	noion	(
Customer Part Number	Murata Part Number	T.C.	Rated Volt. (V)	Cap.	Cap. tol.	L	W	wnsion (W1	F	т	Size Lead Code	Pac qty (pcs
	RDER71H103K0K1H03B	X7R	50	10000pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	500
	RDER71H153K0K1H03B	X7R	50	15000pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	500
	RDER71H223K0K1H03B	X7R	50	22000pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER71H333K0K1H03B	X7R	50	33000pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER71H473K0K1H03B	X7R	50	47000pF	$\pm 10\%$	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER71H683K0K1H03B	X7R	50	68000pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER71H104K0K1H03B	X7R	50	0.10µF		4.0	3.5		5.0	2.5		50
	RDER71H154K1K1H03B	X7R	50	0.15µF	±10%	4.5	3.5		5.0	3.15		50
	RDER71H224K1K1H03B	X7R	50	0.22µF	±10%	4.5	3.5		5.0	3.15		50
	RDER71H334K1K1H03B	X7R	50	0.33µF	±10%	4.5	3.5		5.0	3.15		50
	RDER71H474K1K1H03B	X7R	50	0.47µF	±10%	4.5	3.5		5.0	3.15		50
	RDER71H684K2K1H03B	X7R	50	0.68µF	±10%	5.5	4.0		5.0	3.15	2K1	50
	RDER71H105K2K1H03B	X7R	50	1.0µF	±10%	5.5	4.0		5.0	3.15		50
	RDER71H155K2K1H03B	X7R	50	1.5µF	±10%	5.5	4.0		5.0	3.15	2K1	50
	RDER71H225K2K1H03B RDER71H335K3K1H03B	X7R X7R	50 50	2.2µF 3.3µF	±10% ±10%	5.5 5.5	4.0 5.0		5.0 5.0	3.15 4.0	2K1 3K1	50 50
	RDEC71H475K2K1H03B	X7S	50	3.3μF 4.7μF	±10%	5.5	4.0		5.0	3.15	2K1	50
	RDEC71H106K3K1H03B	X7S	50	4.7μ 10μF	±10%	5.5	4.0 5.0		5.0	4.0		50
	RDEC71H226MWK1H03B	X7S	50	22µF		5.5	7.5		5.0			50
	RDER72A221K0K1H03B	X7R	100	220pF		4.0	3.5		5.0	2.5		50
	RDER72A331K0K1H03B	X7R	100	330pF		4.0	3.5		5.0	2.5		50
	RDER72A471K0K1H03B	X7R	100		±10%	4.0	3.5		5.0	2.5		50
	RDER72A681K0K1H03B	X7R	100	680pF		4.0	3.5		5.0	2.5		50
	RDER72A102K0K1H03B	X7R	100	1000pF		4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A152K0K1H03B	X7R	100	1500pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A222K0K1H03B	X7R	100	2200pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A332K0K1H03B	X7R	100	3300pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A472K0K1H03B	X7R	100	4700pF	±10%	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A682K0K1H03B	X7R	100	6800pF	$\pm 10\%$	4.0	3.5	6.0	5.0	2.5	0K1	50
	RDER72A103K0K1H03B	X7R	100	10000pF		4.0	3.5		5.0	2.5		50
	RDER72A153K0K1H03B	X7R	100	15000pF		4.0	3.5		5.0	2.5		50
	RDER72A223K0K1H03B	X7R	100	22000pF		4.0	3.5		5.0	2.5		50
	RDER72A333K1K1H03B	X7R	100	33000pF		4.5	3.5		5.0	3.15		50
	RDER72A473K1K1H03B	X7R	100	47000pF		4.5	3.5		5.0	3.15		50
		X7R	100	68000pF		4.5	3.5		5.0 5.0	3.15 3.15		50 50
	RDER72A683K1K1H03B		400	040 -	- 4000					~ 15		
	RDER72A104K1K1H03B	X7R	100	0.10µF		4.5	3.5					
	RDER72A104K1K1H03B RDER72A154K2K1H03B	X7R X7R	100	0.15µF	±10%	5.5	4.0	6.0	5.0	3.15	2K1	50
	RDER72A104K1K1H03B	X7R			±10% ±10%			6.0 5.0			2K1 1K1	50 50 50 50


				onny								
	ax. Tmax.											
et u. 8	25. 0 min. 25. 0 min. 25. 0 min. 25. 0 min. 25. 0 min. 25. 0 min. 25. 0 min.	i									Unit :	mm
		TO	DC Rated	0	Cap.		Dime	nsion	(mm)		Size	Pacl
Customer Part Number	Murata Part Number	T.C.	Volt. (V)	Cap.	tol.	L	W	W1	F	т	Lead Code	qty. (pcs)
	RDER72A684K2K1H03B	X7R	100	0.68µF	±10%	5.5	4.0	6.0	5.0	3.15	2K1	500
	RDER72A105K2K1H03B	X7R	100	1.0µF	$\pm 10\%$	5.5	4.0	6.0	5.0	3.15	2K1	500
	RDER72A105K2K1H03B RDEC72A155K3K1H03B	X7R X7S	100 100	1.0μF 1.5μF		5.5 5.5	4.0 5.0	6.0 7.5				
					±10%		5.0		5.0	4.0	3K1	500 500 500

		IVEI	eren	ce on	y								
• Outside Crim													
(Lead Code:S	,*)												
HO # 0.5			ax.										
		L											
		1		1							ι	Jnit : I	mm
			DC Rated	-			Di	mensio	on (mr	n)		Size	Pack
Customer Part Number	Murata Part Number	T.C.	volt. (V)	Cap.	Cap. tol.	L	W	W1	F	Т	H0	Lead Code	qty. (pcs)
	RDER71E104K0S1H03A	X7R	25	0.10µF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDEC71E224K0S1H03A	X7S	25	0.22µF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
-	RDEC71E474K0S1H03A	X7S	25	0.47µF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDEC71E105K0S1H03A	X7S	25	1.0µF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDEC71E225K1S1H03A	X7S	25	2.2µF	±10%	5.0	3.5	5.0	2.5	3.15	16.0	1S1	2000
	RDEC71E475K2S1H03A	X7S	25	4.7µF	±10%	5.5	4.0	6.0	2.5	3.15	16.0	2S1	2000
	RDEC71E106K2S1H03A	X7S	25	10µF		5.5	4.0	6.0	2.5	3.15	16.0		2000
	RDEC71E226K3S1H03A	X7S	25	22µF	±10%	5.5	5.0	7.5	2.5	4.0	16.0	3S1	1500
	RDER71H221K0S1H03A	X7R	50	220pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H331K0S1H03A	X7R	50	330pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H471K0S1H03A	X7R	50	470pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H681K0S1H03A	X7R	50	680pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H102K0S1H03A	X7R	50	1000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H152K0S1H03A	X7R	50	1500pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H222K0S1H03A	X7R	50	2200pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H332K0S1H03A	X7R	50	3300pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H472K0S1H03A	X7R	50	4700pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H682K0S1H03A	X7R	50	6800pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H103K0S1H03A	X7R	50	10000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H153K0S1H03A	X7R	50	15000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H223K0S1H03A	X7R	50	22000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H333K0S1H03A	X7R	50	33000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H473K0S1H03A	X7R	50	47000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H683K0S1H03A	X7R	50	68000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H104K0S1H03A	X7R	50	0.10µF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000
	RDER71H154K1S1H03A	X7R	50	· · · ·	±10%	5.0	3.5		2.5	3.15	16.0	1S1	2000
	RDER71H224K1S1H03A	X7R	50	0.22µF	±10%	5.0	3.5	5.0	2.5	3.15	16.0	1S1	2000
	RDER71H334K1S1H03A	X7R	50	0.33µF	±10%	5.0	3.5	5.0	2.5	3.15	16.0	1S1	2000
-	RDER71H474K1S1H03A	X7R	50	0.47µF	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000
-	RDER71H684K2S1H03A	X7R	50	0.68µF	±10%	5.5	4.0	6.0	2.5	3.15	16.0		2000
	RDER71H105K2S1H03A	X7R	50	1.0µF		5.5	4.0	6.0	2.5	3.15	16.0	2S1	2000
-	RDER71H155K2S1H03A	X7R	50	1.5µF	±10%	5.5	4.0	6.0	2.5	3.15			2000
	RDER71H225K2S1H03A	X7R	50	2.2µF		5.5	4.0	6.0	2.5	3.15	16.0		2000
	RDER71H335K3S1H03A	X7R	50	3.3µF	±10%	5.5	5.0	7.5	2.5	4.0	16.0		1500
	RDEC71H475K2S1H03A	X7S	50	· ·	±10%	5.5	4.0	6.0	2.5	3.15			2000
	RDEC71H106K3S1H03A	X7S	50	10µF	±10%	5.5	5.0		2.5	4.0	16.0		1500
	RDER72A221K0S1H03A	X7R	100	220pF		5.0	3.5		2.5	2.5	16.0		2000
	RDER72A331K0S1H03A	X7R	100	330pF		5.0	3.5		2.5	2.5			2000
	RDER72A471K0S1H03A	X7R	100	470pF		5.0	3.5		2.5	2.5			2000
	RDER72A681K0S1H03A	X7R	100	680pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000

Г

•Outside Crim				- 1	nside (Crimp	Tapin	ng							
(Lead Code:S	*)			((Lead Co	ode∶M	*)								
HO + 0.5	G. G. F ± 0.4 F ± 0.4					$\frac{1}{1} \max x$									
			DC								Ľ	Jnit : I			
Customer Part Number	Murata Part Number	T.C.	Rated volt. (V)	Cap.	Cap. tol.	L	Di W	mensio W1	on (mr F	n) T	H0	Size Lead Code	qty.		
	RDER72A102K0S1H03A	X7R	100	1000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000		
	RDER72A152K0S1H03A	X7R	100	1500pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000		
	RDER72A222K0S1H03A	X7R	100	2200pF	$\pm 10\%$	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000		
	RDER72A332K0S1H03A	X7R	100	3300pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000		
	RDER72A472K0S1H03A	X7R	100	4700pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0		2000		
	RDER72A682K0S1H03A	X7R	100	6800pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0	0S1	2000		
	RDER72A103K0S1H03A	X7R	100	10000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0		2000		
	RDER72A153K0S1H03A	X7R	100	15000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0		2000		
	RDER72A223K0S1H03A	X7R		22000pF	±10%	5.0	3.5	6.0	2.5	2.5	16.0		2000		
	RDER72A333K1S1H03A	X7R		33000pF	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000		
	RDER72A473K1S1H03A	X7R		47000pF	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000		
	RDER72A683K1S1H03A	X7R		68000pF	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000		
	RDER72A104K1S1H03A	X7R	100	0.10µF	±10%	5.0	3.5	5.0	2.5 2.5	3.15	16.0		2000		
	RDER72A154K2S1H03A RDER72A224K1S1H03A	X7R X7R	100 100	0.15µF	±10% ±10%	5.5 5.0	4.0 3.5	6.0 5.0	2.5 2.5	3.15 3.15	16.0 16.0		2000 2000		
	RDER72A334K1S1H03A	X7R	100	0.22µF 0.33µF	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000		
	RDER72A334K1S1H03A	X7R	100	0.33µi	±10%	5.0	3.5	5.0	2.5	3.15	16.0		2000		
	RDER72A684K2S1H03A	X7R	100	0.68µF		5.5	4.0	6.0	2.5	3.15	16.0		2000		
	RDER72A105K2S1H03A	X7R	100	· ·	±10%	5.5	4.0	6.0	2.5				2000		
	RDEC72A155K3S1H03A	X7S	100		±10%	5.5	5.0	7.5	2.5		16.0		1500		
	RDEC72A225K3S1H03A	X7S	100	2.2µF		5.5	5.0	7.5	2.5		16.0		1500		
	RDEC71E224K0M1H03A	X7S	25	0.22µF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDEC71E474K0M1H03A	X7S	25		±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000		
	RDEC71E105K0M1H03A	X7S	25	1.0µF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDEC71E225K1M1H03A	X7S	25	2.2µF	±10%	4.5	3.5	5.0	5.0	3.15	16.0	1M1	2000		
	RDEC71E475K2M1H03A	X7S	25	4.7µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000		
	RDEC71E106K2M1H03A	X7S	25	10µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000		
	RDEC71E226K3M1H03A	X7S	25	22µF	±10%	5.5	5.0	7.5	5.0	4.0	16.0	3M1	1500		
	RDEC71E476MWM1H03A	X7S	25	47µF	±20%	5.5	7.5	10.0	5.0	4.0	16.0	WM1	1500		
	RDER71E104K0M1H03A	X7R	25	0.10µF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000		
	RDER71H221K0M1H03A	X7R	50	220pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000		
	RDER71H331K0M1H03A	X7R	50	· ·	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000		
	RDER71H471K0M1H03A	X7R	50	470pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000		
	RDER71H681K0M1H03A	X7R	50	680pF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDER71H102K0M1H03A	X7R	50	1000pF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDER71H152K0M1H03A	X7R	50	1500pF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDER71H222K0M1H03A	X7R	50	2200pF		4.0	3.5	6.0	5.0	2.5	16.0		2000		
	RDER71H332K0M1H03A	X7R	50	3300pF		4.0	3.5	6.0	5.0		16.0		2000		
	RDER71H472K0M1H03A	X7R X7R	50 50	4700pF 6800pF		4.0 4.0	3.5 3.5	6.0 6.0	5.0 5.0	2.5 2.5	16.0 16.0		2000 2000		
	RDER71H682K0M1H03A														


		Ret	eren	ce on	у								
·Inside Crimp (Lead Code∶N													
	Lmax.		ax. ←									Jnit : r	mm
Customer Part Number	Murata Part Number	T.C.	DC Rated volt.	Cap.	Cap. tol.		Di	imensio	on (mr	n)		Size Lead	Pack qty.
			(V)			L	W	W1	F	Т	H0	Code	(pcs)
	RDER71H103K0M1H03A	X7R	50	10000pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0		2000
	RDER71H153K0M1H03A	X7R	50	15000pF	±10%	4.0	3.5		5.0	2.5	16.0		2000
	RDER71H223K0M1H03A	X7R	50	22000pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0		2000
	RDER71H333K0M1H03A	X7R	50	33000pF	±10%	4.0	3.5		5.0	2.5	16.0		2000
	RDER71H473K0M1H03A RDER71H683K0M1H03A	X7R X7R	50 50	47000pF 68000pF	±10% ±10%	4.0 4.0	3.5 3.5		5.0 5.0	2.5 2.5	16.0 16.0		2000
	RDER71H104K0M1H03A	X7R	50	0.10µF		4.0	3.5		5.0	2.5	16.0		2000
	RDER71H154K1M1H03A	X7R	50	0.15µF	±10%	4.5	3.5	5.0	5.0	3.15	16.0		2000
	RDER71H224K1M1H03A	X7R	50	0.22µF	±10%	4.5	3.5	5.0	5.0	3.15	16.0		2000
	RDER71H334K1M1H03A	X7R	50	0.33µF	±10%	4.5	3.5		5.0	3.15	16.0		2000
	RDER71H474K1M1H03A	X7R	50	0.47µF	±10%	4.5	3.5	5.0	5.0	3.15	16.0		2000
	RDER71H684K2M1H03A	X7R	50	0.68µF	±10%	5.5			5.0	3.15	16.0		2000
	RDER71H105K2M1H03A	X7R	50	1.0µF	±10%	5.5			5.0	3.15	16.0		2000
	RDER71H155K2M1H03A	X7R	50	1.5µF	±10%	5.5		6.0	5.0	3.15	16.0		2000
	RDER71H225K2M1H03A	X7R	50	2.2µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000
	RDER71H335K3M1H03A	X7R	50	3.3µF	±10%	5.5	5.0	7.5	5.0	4.0	16.0	3M1	1500
	RDEC71H475K2M1H03A	X7S	50	4.7µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000
	RDEC71H106K3M1H03A	X7S	50	10µF	±10%	5.5	5.0	7.5	5.0	4.0	16.0	3M1	1500
	RDEC71H226MWM1H03A	X7S	50	22µF	±20%	5.5	7.5	10.0	5.0	4.0	16.0	WM1	1500
	RDER72A221K0M1H03A	X7R	100	220pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A331K0M1H03A	X7R	100	330pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A471K0M1H03A	X7R	100	470pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A681K0M1H03A	X7R	100	680pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A102K0M1H03A	X7R	100	1000pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A152K0M1H03A	X7R	100	1500pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A222K0M1H03A	X7R	100	2200pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A332K0M1H03A	X7R	100	3300pF	$\pm 10\%$	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A472K0M1H03A	X7R	100	4700pF	$\pm 10\%$	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A682K0M1H03A	X7R	100	6800pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A103K0M1H03A	X7R	100	10000pF	±10%	4.0	3.5	6.0	5.0	2.5	16.0	0M1	2000
	RDER72A153K0M1H03A	X7R	100	15000pF		4.0	3.5		5.0	2.5	16.0		2000
	RDER72A223K0M1H03A	X7R	100	22000pF		4.0	3.5		5.0	2.5	16.0		2000
	RDER72A333K1M1H03A	X7R	100	33000pF		4.5	3.5		5.0	3.15	16.0		2000
	RDER72A473K1M1H03A	X7R	100	47000pF		4.5			5.0	3.15	16.0		2000
	RDER72A683K1M1H03A	X7R	100	68000pF		4.5			5.0	3.15	16.0		2000
	RDER72A104K1M1H03A	X7R	100	0.10µF		4.5			5.0	3.15	16.0		2000
	RDER72A154K2M1H03A	X7R	100	0.15µF		5.5			5.0	3.15	16.0		2000
	RDER72A224K1M1H03A	X7R	100	0.22µF		4.5			5.0	3.15	16.0		2000
	RDER72A334K1M1H03A	X7R	100	0.33µF		4.5			5.0	3.15	16.0		2000
	RDER72A474K1M1H03A	X7R	100	0.47µF	±10%	4.5	3.5	5.0	5.0	3.15	16.0	1M1	2000




											ι	Init : I	mm
Customer Part Number	Marcia Dari Nasalara		DC Rated		Con tol		Dimension (mm)					Size	Pack
Customer Part Number	Murata Part Number	T.C.	volt. (V)	Cap.	Cap. tol.	L	W	W1	F	Т	H0		qty. (pcs)
	RDER72A684K2M1H03A	X7R	100	0.68µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000
	RDER72A105K2M1H03A	X7R	100	1.0µF	±10%	5.5	4.0	6.0	5.0	3.15	16.0	2M1	2000
	RDEC72A155K3M1H03A	X7S	100	1.5µF	±10%	5.5	5.0	7.5	5.0	4.0	16.0	3M1	1500
	RDEC72A225K3M1H03A	X7S	100	2.2µF	±10%	5.5	5.0	7.5	5.0	4.0	16.0	3M1	1500
	RDEC72A475MWM1H03A	X7S	100	4.7µF	±20%	5.5	7.5	10.0	5.0	4.0	16.0	WM1	1500


5.SF	PECIFICATIO	ONS AND	TEST METHODS							
No.	Ite	m	Specification	Test Method						
1 2	Appearance Dimension an	d Marking	No defects or abnormalities Within the specified dimensions and Marking	Visual inspection. Visual inspection, Using Caliper.						
3	Dielectric Strength	Between Terminals	No defects or abnormalities	The capacitor should not be damaged when voltage in Table is applied between the terminations for 1 to 5 seconds. (Charge/Discharge current \leq 50mA.)						
				Rated voltage Test voltage						
				DC25V · DC50V 250% of the rated voltage						
				DC100V 200% of the rated voltage						
		Body Insulation	No defects or abnormalities	The capacitor is placed in a container with metal balls of 1mm diameter so that each terminal, short-circuit, is kept approximately 2mm from the balls, and voltage in Table is impressed for 1 to 5 seconds between capacitor terminals and metal balls. (Charge/Discharge current ≤ 50mA.) Rated voltage Test voltage DC25V • DC50V 250% of the rated voltage						
				DC100V 200% of the rated voltage						
4	Insulation Resistance (I.R.)	Between Terminals	10,000MΩ or 500MΩ·μF min. (Whichever is smaller)	The insulation resistance should be measured with a DC voltage not exceeding the rated voltage at norma temperature and humidity and within 2 minutes of charging. (Charge/Discharge current ≤ 50mA)						
5	Capacitance		Within the specified tolerance	The capacitance, D.F. should be measured at 25°C at the frequency and voltage shown in the table.						
6	Dissipation Fa	actor (D.F.)	X7R : 0.025 max.	Nominal Cap. Frequency Voltage						
			X7S : 0.125 max.	C \leq 10 μ F 1±0.1kHz AC1±0.2V(r.m.s.)						
				C>10 µ F 120±24Hz AC0.5±0.1V(r.m.s.)						
7	Temperature	Capacitance X7R : within ±15% Temperature X7S : within ±22% Characteristics ************************************		The capacitance change should be measured after 5 min. at each specified temperature stage. The ranges of capacitance change compared with the 25°C value over the temperature ranges shown in the table should be within the specified ranges.						
8	Terminal Tensile Termination r Strength Strength Ioosened		Termination not to be broken or loosened	As in the figure, fix the capacitor body, apply the force gradually to each lead in the radial direction of the capacitor until reaching 10N and then keep applied the force for 10 ± 1 seconds.						
		Bending Strength Termination not to be broken or loosened		Each lead wire should be subjected to a force of 2.5N and then be bent 90° at the point of egress in one direction. Each wire is then returned to the original position and bent 90° in the opposite direction at the rate of one bend per 2 to 3 seconds.						
9	Vibration Resistance	Appearance	No defects or abnormalities	The capacitor should be subjected to a simple harmonic motion having a total amplitude of 1.5mm, the frequency being varied uniformly, between the						
		Capacitance	Within the specified tolerance	the frequency being varied uniformly between the approximate limits of 10Hz and 55Hz.						
		D.F.	X7R : 0.025 max. X7S : 0.125 max.	The frequency range, from 10Hz to 55Hz and return to 10Hz, shall be traversed in approximately 1 minute This motion shall be applied for a period of 2 hours in each 3 mutually perpendicular directions (total of 6						

lo.	Iter	m	Specification	Test Method							
0	Solderability o	of Lead	Solder is deposited on unintermittentl immersed portion in axial direction covering 3/4 or more in circumferentia direction of lead wires.	ethanol (JIS K 8101) and rosin (JIS K 5902) (25%							
		•		245±5°C Lead Free Solder(Sn-3.0Ag-0.5Cu) 235±5°C H60A or H63A Eutectic Solder							
11	Resistance to Soldering Heat	Appearance Capacitance Change Dielectric Strength (Between terminals)	No defects or abnormalities X7R,X7S : Within ±10% No defects	 The lead wire is immersed in the melted solder 1.5 to 2mm from the main body at 350±10°C for 3.5±0.5 seconds. The specified items are measured after 24±2 hours. Pretreatment Perform a heat treatment at 150+0/-10°C for one hour and then set at room temperature for 24±2 							
2	Temperature Cycle	Appearance	No defects or abnormalities	hours. Repeat 5 cycles according to the 4 heat treatments listed in the following table.							
		Capacitance Change	X7R,X7S : Within±12.5%	Set at room temperature for 24 ± 2 hours, then measure.							
		D.F.	X7R : 0.05 max. X7S : 0.2 max.	Step 1 2 3 4							
		I.R.	1,000MΩ or 50MΩ·μF min. (Whichever is smaller)	Temp. domining Room Operating Room Temp. ±3							
		Dielectric Strength (Between Terminals)	No defects or abnormalities	 (min.) 30±3 3 max. 30±3 3 max. Pretreatment Perform a heat treatment at 150+0/-10°C for one hour and then set at room temperature for 24±2 hours. 							
3	Humidity	Appearance	No defects or abnormalities	Set the capacitor at 40±2°C and relative							
	(Steady State)	Capacitance Change D.F.	X7R,X7S : Within ±15% X7R : 0.05 max.	humidty 90 to 95% for 500+24/-0 hours. Remove and set for 24±2 hours at room temperature then measure.							
		I.R.	X7S : 0.2 max. 1,000MΩ or 50MΩ·μF min. (Whichever is smaller)	Pretreatment Perform a heat treatment at 150+0/-10°C for one hour and then set at room temperature for 24±2							
4	Humidity	Appearance	No defects or abnormalities	hours. Apply the rated voltage at 40±2°C and relative							
	Load	Capacitance Change	X7R,X7S : Within±15%	 humidity of 90 to 95% for 500+24/-0 hours. Remove and set for 24±2 hours at room temperature then measure. 							
		D.F.	X7R : 0.05 max. X7S : 0.2 max.	(Charge/Discharge current ≤ 50mA)							
		I.R.	500MΩ or 25MΩ·μF min. (Whichever is smaller)	 Pretreatment Perform a heat treatment at 150+0/-10°C for one hour and then set at room temperature for 24±2 hours. 							
15	High Temperature Load	Appearance Capacitance Change	No defects or abnormalities X7R,X7S : Within±15%	Apply 150% of the rated voltage at the maximum operating temperature ±3°C for 1000+48/-0 hours. Remove and set for 24±2 hours at room temperature							
		D.F.	X7R : 0.05 max. X7S : 0.2 max.	then measure. (Charge/Discharge current ≤ 50mA)							
		I.R.	1,000MΩ or 50 MΩ·μF min. (Whichever is smaller)	Pretreatment Apply test voltage for one hour at test temperature Remove and set at room temperature for 24±2 hou							
6	Solvent Resistance	Appearance	No defects or abnormalities	The capacitor should be fully immersed, unagitated, in reagent at 20 to 25°C for 30±5 sec. and then remove gently. Marking on the surface of the							
		Marking	Legible	 capacitor shall immendiately be visually examined. Reagent : Isopropyl alcohol 							






Outside crimp taping type < Lead code : S1 > Pitch of component 12.7mm / Lead spacing 2.5mm



Unit : mm

Item	Code	Dimensions	Remarks
Pitch of component	P	12.7+/-1.0	Kontanos
Pitch of sprocket hole	P0	12.7+/-0.2	
Lead spacing	F	2.5+0.4/-0.2	
Length from hole center to component center	P2	6.35+/-1.3	
Length from hole center to lead	P1	3.85+/-0.7	Deviation of progress direction
Deviation along tape, left or right defect	ΔS	0+/-2.0	They include deviation by lead bend .
Carrier tape width	W	18.0+/-0.5	
Position of sprocket hole	W1	9.0+0/-0.5	Deviation of tape width direction
Lead distance between reference and bottom plane	HO	16.0+/-0.5	
Protrusion length	l	0.5 max.	
Diameter of sprocket hole	D0	4.0+/-0.1	
Lead diameter	d	0.50+/-0.05	
Total tape thickness	t1	0.6+/-0.3	The side had a bala device to a statistic and
Total thickness of tape and lead wire	t2	1.5 max.	They include hold down tape thickness.
Deviction correspondence	∆h1	1.0 max.	
Deviation across tape	∆h2	1.0 max.	
Portion to cut in case of defect	L	11.0+0/-1.0	
Hold down tape width	W0	9.5 min.	
Hold down tape position	W2	1.5+/-1.5	
Coating extension on lead	е	Up to the end of c	rimp



EU RoHS and Halogen Free

This products of the following crresponds to EU RoHS and Halogen Free

(1) RoHS

EU RoHs 2011/65/EC compliance

maximum concentration values tolerated by weight in homogeneous materials •1000 ppm maximum Lead

- •1000 ppm maximum Mercury
- •100 ppm maximum Cadmium
- •1000 ppm maximum Hexavalent chromium
- •1000 ppm maximum Polybrominated biphenyls (PBB)
- •1000 ppm maximum Polybrominated diphenyl ethers (PBDE)

(2) Halogen-Free

The International Electrochemical Commission's (IEC) Definition of Halogen-Free (IEC 61249-2-21) compliance

- •900 ppm maximum chlorine
- •900 ppm maximum bromine
- •1500 ppm maximum total chlorine and bromine