



TO-252-3L



TO-220F-3L

ORDERING INFORMATION


Product	Marking	Package
SN78xxBDJ	SN78xxB	TO-252-3L
SN78xxBPI	SN78xxB	TO-220F-3L

▲ Marking Detail Information [TO-220F-3L]



- ① AUK Logo
- ② Grade & M Code & Y & M & DD
- ③ Device Code

[TO-252-3L]



- ① Device Code
- ② Year & Week Code, J = M Code

Description

The SN78xxB series are three-terminal positive regulators providing over 1A output current with internal current limiting, thermal shutdown and safe area protection. These regulators are useful in a wide range of applications. Although they are just fixed voltage regulators, the SN78xxB series can be used with external components to obtain adjustable voltages and Currents.

Application


- ◆ Consumer and personal electronics
- ◆ SMPS post-regulator / dc-to-dc modules
- ◆ High-efficiency linear power supplies

Features and Benefits


- ◆ Output Current up to 1.0A
- ◆ Output Voltage: 5, 6, 8, 9, 10, 12, 15, 18, 24V
- ◆ Built in OVP, CLP circuit.
- ◆ Built in TSD Protection.
- ◆ Output Transistor Safe Area Protection.
- ◆ Ultra High level of ESD [Built in ESD Protection Cell]

MM : 500V / HBM 5KV

Equivalent Circuit




◆ Pin Configuration



TO-252-3L

1: V_{IN}
 2: GND
 3: V_{OUT}
 4: GND



TO-220F-3L

1: V_{IN}
 2: GND
 3: V_{OUT}

◆ Product Line-up

Product Name	V_{OUT}	Operating Junction Temperature	Package
SN7805BDJ	5.0V	-40~125℃	TO-252-3L
SN7806BDJ	6.0V	-40~125℃	TO-252-3L
SN7808BDJ	8.0V	-40~125℃	TO-252-3L
SN7809BDJ	9.0V	-40~125℃	TO-252-3L
SN7810BDJ	10V	-40~125℃	TO-252-3L
SN7812BDJ	12V	-40~125℃	TO-252-3L
SN7815BDJ	15V	-40~125℃	TO-252-3L
SN7818BDJ	18V	-40~125℃	TO-252-3L
SN7824BDJ	24V	-40~125℃	TO-252-3L
SN7805BPI	5.0V	-40~125℃	TO-220F-3L
SN7806BPI	6.0V	-40~125℃	TO-220F-3L
SN7808BPI	8.0V	-40~125℃	TO-220F-3L
SN7809BPI	9.0V	-40~125℃	TO-220F-3L
SN7810BPI	10V	-40~125℃	TO-220F-3L
SN7812BPI	12V	-40~125℃	TO-220F-3L
SN7815BPI	15V	-40~125℃	TO-220F-3L
SN7818BPI	18V	-40~125℃	TO-220F-3L
SN7824BPI	24V	-40~125℃	TO-220F-3L

◆ Absolute Maximum Ratings (Ta = 25°C)

Parameter	Symbol	Limits		Unit
		TO-220F-3L	TO-252-3L	
Input Voltage	V _{IN}	40.0 (V _O =24V)		V
		35.0 (V _O =5 to 18V)		
Power Dissipation	P _d	2.0	1.3	W
Thermal Resistance Junction to Case	R _{θJC}	5	5	°C/W
Thermal Resistance Junction to Air	R _{θJA}	65	92	°C/W
Junction Temperature	T _J	150		°C
Operating Junction Temperature Range	T _{opr}	-40 ~ +125		°C
Storage Temperature Range	T _{stg}	-55 ~ +150		°C

Absolute maximum ratings indicate limits beyond which damage to the component may occur. Electrical specifications do not apply when operating the device outside of its operating ratings. The maximum allowable power dissipation is a function of the maximum junction temperature, T_{J(max)}, the junction-to-ambient thermal resistance, θ_{JA}, and the ambient temperature, T_A. The maximum allowable power dissipation at any ambient temperature is calculated using: PD(max) = (T_{J(max)} - T_A) ÷ θ_{JA}. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown.

◆ Electrical characteristics

($V_{IN}=10V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7805B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		4.80	5.00	5.20	V
		$7.5V \leq V_{IN} \leq 20.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		4.75	5.00	5.25	
Line Regulation	$\Delta V_{O(\Delta V)}$	$7.5V \leq V_{IN} \leq 25.0V$	$T_J = 25^{\circ}C$	-	4.0	100	mV
		$8.0V \leq V_{IN} \leq 12.0V$		-	1.6	50	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	9.0	100	mV
		$250mA \leq I_O \leq 750mA$		-	4.0	50	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	3.2	8.0	mA
Quiescent Current Change	ΔI_{QC}	$7.5V \leq V_{IN} \leq 25V$		-	0.3	1.3	mA
		$5.0mA \leq I_O \leq 1.0A$		-	0.03	0.5	
Ripple Rejection	RR	$8.0V \leq V_{IN} \leq 18.0V$ $f=120Hz$		62	73	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	42	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	15	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-0.8	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=11V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7806B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		5.75	6.00	6.25	V
		$8.5V \leq V_{IN} \leq 21V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		5.70	6.00	6.30	
Line Regulation	$\Delta V_{O(\Delta V)}$	$8.5V \leq V_{IN} \leq 25.0V$	$T_J = 25^{\circ}C$	-	5.0	120	mV
		$9.0V \leq V_{IN} \leq 13.0V$		-	1.5	60	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	9.0	120	mV
		$250mA \leq I_O \leq 750mA$		-	3.0	60	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.0	8.0	mA
Quiescent Current Change	ΔI_{QC}	$8.5V \leq V_{IN} \leq 25.0V$		-	-	1.3	mA
		$5.0mA \leq I_O \leq 1.0A$		-	-	0.5	
Ripple Rejection	RR	$9.0V \leq V_{IN} \leq 19.0V$ $f=120Hz$		59	75	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	45	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	19	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-0.8	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=14V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7808B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		7.70	8.00	8.30	V
		$10.5V \leq V_{IN} \leq 23.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		7.60	8.00	8.40	
Line Regulation	$\Delta V_{O(\Delta V_I)}$	$10.5V \leq V_{IN} \leq 25.0V$	$T_J = 25^{\circ}C$	-	5.0	160	mV
		$11.5V \leq V_{IN} \leq 17.0V$		-	2.0	80	
Load Regulation	$\Delta V_{O(\Delta I_L)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	10.0	160	mV
		$250mA \leq I_O \leq 750mA$		-	5.0	80	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.0	8.0	mA
Quiescent Current Change	ΔI_{QC}	$10.5V \leq V_{IN} \leq 25.0V$		-	0.5	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	0.05	0.5	
Ripple Rejection	RR	$11.5V \leq V_{IN} \leq 21.5V$ $f=120Hz$		56	73	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	52	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	17	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$,	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-0.8	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=15V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7809B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		8.65	9.00	9.35	V
		$11.5V \leq V_{IN} \leq 24.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		8.60	9.00	9.40	
Line Regulation	$\Delta V_{O(\Delta V_I)}$	$11.5V \leq V_{IN} \leq 25.0V$	$T_J = 25^{\circ}C$	-	6.0	180	mV
		$12.0V \leq V_{IN} \leq 17.0V$		-	2.0	90	
Load Regulation	$\Delta V_{O(\Delta I_L)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	12.0	180	mV
		$250mA \leq I_O \leq 750mA$		-	4.0	90	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.0	8.0	mA
Quiescent Current Change	ΔI_{QC}	$11.5V \leq V_{IN} \leq 26.0V$		-	-	1.3	mA
		$5.0mA \leq I_O \leq 1.0A$		-	-	0.5	
Ripple Rejection	RR	$12.0V \leq V_{IN} \leq 22.0V$ $f=120Hz$		56	71	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	58	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	17	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.0	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=16V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7810B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		9.60	10.00	10.40	V
		$12.5V \leq V_{IN} \leq 25.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		9.50	10.00	10.50	
Line Regulation	$\Delta V_{O(\Delta V)}$	$12.5V \leq V_{IN} \leq 25.0V$	$T_J = 25^{\circ}C$	-	10.0	200	mV
		$13.0V \leq V_{IN} \leq 18.0V$		-	3.0	100	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	12.0	200	mV
		$250mA \leq I_O \leq 750mA$		-	4.0	100	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.1	8.0	mA
Quiescent Current Change	ΔI_{QC}	$12.5V \leq V_{IN} \leq 29V$		-	-	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	-	0.5	
Ripple Rejection	RR	$13.0V \leq V_{IN} \leq 23.0V$ $f=120Hz$		56	71	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	58	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	17	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$,	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.0	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=19V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7812B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		11.50	12.00	12.50	V
		$14.5V \leq V_{IN} \leq 27.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		11.40	12.00	12.60	
Line Regulation	$\Delta V_{O(\Delta V)}$	$14.5V \leq V_{IN} \leq 30.0V$	$T_J = 25^{\circ}C$	-	10.0	240	mV
		$16.0V \leq V_{IN} \leq 22.0V$		-	3.0	120	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	11.0	240	mV
		$250mA \leq I_O \leq 750mA$		-	5.0	120	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.1	8.0	mA
Quiescent Current Change	ΔI_{QC}	$14.5V \leq V_{IN} \leq 30.0V$		-	0.5	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	0.1	0.5	
Ripple Rejection	RR	$15.0V \leq V_{IN} \leq 25.0V$ $f=120Hz$		55	71	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	76	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	15	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.0	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=23V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7815B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		14.40	15.00	15.60	V
		$17.5V \leq V_{IN} \leq 30.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		14.25	15.00	15.75	
Line Regulation	$\Delta V_{O(\Delta V)}$	$17.5V \leq V_{IN} \leq 30.0V$	$T_J = 25^{\circ}C$	-	11.0	300	mV
		$20.0V \leq V_{IN} \leq 26.0V$		-	3.0	150	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	12.0	300	mV
		$250mA \leq I_O \leq 750mA$		-	4.0	150	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.2	8.0	mA
Quiescent Current Change	ΔI_{QC}	$17.5V \leq V_{IN} \leq 30.0V$		-	-	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	-	0.5	
Ripple Rejection	RR	$18.5V \leq V_{IN} \leq 28.5V$ $f=120Hz$		54	70	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	90	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	19	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.0	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=27V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)

Characteristic	Symbol	Test Condition*		SN7818B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		17.30	18.00	18.70	V
		$21.0V \leq V_{IN} \leq 33.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		17.10	18.00	18.90	
Line Regulation	$\Delta V_{O(\Delta V)}$	$21.0V \leq V_{IN} \leq 33.0V$	$T_J = 25^{\circ}C$	-	15.0	360	mV
		$24.0V \leq V_{IN} \leq 30.0V$		-	5.0	180	
Load Regulation	$\Delta V_{O(\Delta I)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	15.0	360	mV
		$250mA \leq I_O \leq 750mA$		-	5.0	180	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.2	8.0	mA
Quiescent Current Change	ΔI_{QC}	$21.0V \leq V_{IN} \leq 33.0V$		-	-	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	-	0.5	
Ripple Rejection	RR	$22.0V \leq V_{IN} \leq 32.0V$ $f=120Hz$		53	69	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	110	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	22	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.0	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.

◆ Electrical characteristics

($V_{IN}=33V$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1 \mu F$, $I_{OUT} = 500mA$, $T_J=0^{\circ}C\sim 125^{\circ}C$; unless otherwise specified)


Characteristic	Symbol	Test Condition*		SN7824B			Unit
				Min.	Typ.	Max.	
Output Voltage**	V_O	$T_J = 25^{\circ}C$		23.00	24.00	25.00	V
		$27.0V \leq V_{IN} \leq 38.0V$ $5.0mA \leq I_O \leq 1.0A$, $P_D \leq 15W$		22.80	24.00	25.25	
Line Regulation	$\Delta V_{O(\Delta V_I)}$	$27.0V \leq V_{IN} \leq 38.0V$	$T_J = 25^{\circ}C$	-	17.0	480	mV
		$30.0V \leq V_{IN} \leq 36.0V$		-	6.0	240	
Load Regulation	$\Delta V_{O(\Delta I_L)}$	$5.0mA \leq I_O \leq 1.5A$	$T_J = 25^{\circ}C$	-	15.0	480	mV
		$250mA \leq I_O \leq 750mA$		-	5.0	240	
Quiescent Current	I_{QC}	$T_J = 25^{\circ}C$		-	5.2	8.0	mA
Quiescent Current Change	ΔI_{QC}	$27.0V \leq V_{IN} \leq 38.0V$		-	0.5	1.0	mA
		$5.0mA \leq I_O \leq 1.0A$		-	0.1	0.5	
Ripple Rejection	RR	$28.0V \leq V_{IN} \leq 38.0V$ $f=120Hz$		50	67	-	dB
Dropout Voltage	V_{DROP}	$I_O=1.0A$	$T_J=25^{\circ}C$	-	2.2	-	V
Output Noise Voltage	V_N	$10Hz \leq f \leq 100kHz$		-	60	-	$\mu V / V_O$
Output Resistance	r_O	$f=1.0kHz$		-	28	-	$m\Omega$
Short Circuit Current	I_{SC}	$V_I=35V$	$T_A=25^{\circ}C$	-	250	-	mA
Peak Output Current	I_{PK}	$T_J=25^{\circ}C$		-	1.8	-	A
Temperature coefficient of Output voltage	$\frac{\Delta V_O}{\Delta Temp}$	$I_O=5.0mA$		-	-1.5	-	$mV/^{\circ}C$

* Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible. Thermal effects must be taken into separately.

** This specification applies only for dc power dissipation permitted by absolute maximum ratings.


Typical Application

Fixed Output Regulator




- 1) C_{IN} should be required if regulators are located far from power supply filter
- 2) C_O improves output stability and transient response


Load Regulation




Constant Current Regulator



Adjustable Output



High Current Voltage Regulator



$$I_O = I_{IN} + \beta_{Q1}(I_{IN} - V_{BEQ1} / R_{IN})$$

Fig.1 Quiescent Current vs. Junction Temperature




Fig.2 Output Peak Current vs. Input to Output Differential




Fig.3 Output Voltage vs. Junction Temperature




Fig.4 Dropout Voltage vs. Junction Temperature




Fig.5 Line Transient Response






Fig.6 Load Transient Response




◆ TO-252-3L Outline Dimension (Unit: mm)




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 REF.		0.190 REF.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 REF.		0.114 REF.	
L2	1.400	1.700	0.055	0.067
L3	1.600 REF.		0.063 REF.	

※ Recommend PCB solder land [Unit: mm]



◆ TO-220F-3L Outline Dimension (Unit : mm)



SYMBOL	MILLIMETERS			NOTE
	MINIMUM	NOMINAL	MAXIMUM	
A	-	-	4.60	
A1	2.45	2.50	2.55	
A2	1.95	2.00	2.05	
b	0.65	0.75	0.85	
b1	1.07	1.27	1.47	
C	0.40	0.50	0.60	
C1	2.70	2.80	2.90	
D	9.90	10.00	10.10	
E	28.00	-	28.60	
E1	15.50	15.60	15.70	
E2	12.30	12.40	12.50	
E3	9.15	9.20	9.25	
F	3.30	3.40	3.50	
G	3.10	3.20	3.30	
e	2.54 BSC			
L	12.40	-	13.00	
L1	3.46 BSC			

The AUK Corp. products are intended for the use as components in general electronic equipment (Office and communication equipment, measuring equipment, home appliance, etc.).

Please make sure that you consult with us before you use these AUK Corp. products in equipments which require high quality and / or reliability, and in equipments which could have major impact to the welfare of human life(atomic energy control, airplane, spaceship, transportation, combustion control, all types of safety device, etc.). AUK Corp. cannot accept liability to any damage which may occur in case these AUK Corp. products were used in the mentioned equipments without prior consultation with AUK Corp..

Specifications mentioned in this publication are subject to change without notice.