

L9958

Low R_{DSON} SPI controlled H-Bridge

Datasheet - production data



Features

- Programmable current regulation peak threshold by SPI up to 8.6 A typ.
- Operating battery supply voltage 4.0 V to 28 V
- Operating V_{dd} supply voltage 4.5 V to 5.5 V
- All pins withstand 19 V, Vs and output pins withstand 40 V
- Full path R_{on} from 100 mΩ (at T_j = -40 °C) to 300 mΩ (at T_j =150 °C)
- Logic inputs TTL/CMOS-compatible
- Operating frequency up to 20 kHz
- 16-bit SPI interface for configuration/diagnostics, daisy chain capability
- Over temperature and short circuit protection
- V_S undervoltage disable function
- V_{dd} undervoltage and overvoltage protection
- V_{dd} overvoltage detection
- Open-load detection in ON condition
- Full diagnostics in OFF state
- Enable and disable input
- Low stand by current (<10 μA)
- Voltage and current slew-rate control for low EMI, programmable through SPI
- Available in three power packages

Description

The L9958 is an SPI controlled H-Bridge, designed for the control of DC and stepper motors in safety critical applications and under extreme environmental conditions. The H-Bridge is protected against over temperature, short circuits and has an undervoltage lockout for all the supply voltages V_{s} and V_{dd} , and for overvoltage on V_{dd} . All malfunctions cause the output stages to go tristate.

Detailed failure diagnostics on each channel is provided via SPI: short circuit to battery, short circuit to ground, short circuit overload, over temperature.

Open-load can be detected in ON condition, for the widest application ranges. Current regulation threshold can be set by SPI from 2.5 A to 8.6 A (Typ.), in 4 steps. Guaranteed accuracy is ± 10 % on all temp range, using an external reference resistor with 1% accuracy over all temp range.

Current limitation threshold is linearly reduced by temperature over 165 °C.and a thermal warning bit is set by SPI. The H-Bridge contains integrated free-wheel diodes. In case of free-wheeling condition, the low side transistor is switched on in parallel of its diode to reduce power dissipation.

A multiple wire bonding technique, as well as ST proprietary package design is making L9958 compatible with three power packages, for maximum flexibility:

PowerSO-20 package (medium power, JEDEC standard MO166);

PowerSO16 package (medium power, lower cost);

PowerSSO24 package (low power, very low cost JEDEC standard MO271A).

Table 1. Device summary

Order code	Package	Packing
L9958	PowerSO-20	Tube
L9958SB	PowerSO16	Tube
L9958XP	PowerSSO24	Tube

Contents

1	Bloc	k diagra	ım	6	
2	Pins	descrip	tion	7	
	2.1	Powers	SO-20	7	
	2.2	Power	SO16	8	
	2.3	Powers	SSO24	9	
3	Devi	ce desc	ription	10	
	3.1	Supply	range	10	
	3.2	Control	inputs	10	
		3.2.1	DI and EN inputs	10	
		3.2.2	DIR and PWM inputs	11	
	3.3	Serial p	peripheral interface (SPI)	12	
		3.3.1	Daisy chain operation	14	
	3.4	SPI tim	ing	14	
	3.5	SPI cor	mmunication failure	15	
	3.6	5 V and	d 3.3 V output compatibility	15	
4	Curr	ent regu	Ilation	16	
	4.1	Temper	rature-dependent current regulation	16	
	4.2	Current	t regulation with low-inductive loads	17	
	4.3	Slew ra	te control in case of current limitation on low-side	17	
5	Diag	nostics	and protections	19	
	5.1	Diagnosis reset strategy 1			
		5.1.1	Reset requests	19	
		5.1.2	Diagnosis reset bit	19	
	5.2	Protect	ion and on state diagnostics	20	
		5.2.1	Over-current on high-side - short to ground	20	
		5.2.2	Over-current on low-side - short to Vs	20	
		5.2.3	Short circuit over-load	20	
		5.2.4	Open load in on state		
		5.2.5	Over-temperature	21	



9	Revis	ion hist	ory	37
8	Packa	ige info	rmation	34
7	Applic	cation c	ircuit	33
		6.4.10	Timing characteristics	32
		6.4.9	Off-state diagnostic	
		6.4.8	Diagnostic of open-load in on-state	
		6.4.7	Current limitation and over-current detection	
		6.4.6	Over-temperature monitoring	
		6.4.5	Bridge output drivers	
		6.4.4	Digital inputs: TTL // 3.3V / 5V CMOS compatible	
		6.4.3	SPI	28
		6.4.2	Device supply monitoring	27
		6.4.1	Device supply	27
	6.4	Electrica	al characteristics	27
	6.3	Range c	of functionality	26
	6.2	Thermal	data	25
	6.1		e maximum ratings	
6		-	ecifications	
		-		
	5.4	H-Bridge	e functional status	
		5.3.2	Open load detection	23
		5.3.1	Off-state detection scheme	
	5.3	Off-state	e diagnosis	23
		5.2.9	Output short protection	22
		5.2.8	Vdd under-voltage detection	22
		5.2.7	Vdd over-voltage detection	
		5.2.6	Vs under-voltage shutdown	21



List of tables

Table 1.	Device summary	. 1
Table 2.	PowerSO-20 pin function	. 7
Table 3.	PowerSO16 pin function	. 8
Table 4.	PowerSSO24 pin function	. 9
Table 5.	Control pins EN, DI	
Table 6.	Control pins DIR, PWM.	11
Table 7.	Configuration protocol (CFG_REG)	13
Table 8.	Diagnosis protocol (DIA_REG)	13
Table 9.	Current limitation programmability	16
Table 10.	Slew rate control on low side MOS	18
Table 11.	Diagnosis reset strategy	19
Table 12.	Over-temperature	21
Table 13.	Vs under-voltage	22
Table 14.	Vdd over-voltage detection	22
Table 15.	Absolute maximum ratings	25
Table 16.	Thermal data	
Table 17.	Range of functionality	26
Table 18.	Device supply	27
Table 19.	Device supply monitoring	
Table 20.	SPI	
Table 21.	Digital inputs: TTL // 3.3V / 5V CMOS compatible	
Table 22.	Bridge output drivers.	
Table 23.	Over-temperature monitoring	
Table 24.	Current limitation and over-current detection	
Table 25.	Diagnostic of open-load in on-state	
Table 26.	Off-state diagnostic	
Table 27.	Timing characteristics	32
Table 28.	Document revision history.	37



L9958

List of figures

Figure 1.	Block diagram	. 6
Figure 2.	PowerSO-20 pin connection (top view).	. 7
Figure 3.	PowerSO16 pin connection (top view)	. 8
Figure 4.	PowerSSO24 pin connection (top view)	. 9
Figure 5.	H-Bridge configurations	
Figure 6.	SPI protocol structure	12
Figure 7.	FSI bit	12
Figure 8.	Daisy chain topology.	14
Figure 9.	SPI timing	14
Figure 10.	SPI zero clock communication	15
Figure 11.	Current limitation.	
Figure 12.	Temperature dependent current regulation	
Figure 13.	Current regulation with different loads	17
Figure 14.	Slew rate switching strategy	18
Figure 15.	Diagnostics for SCB / SCOL	20
Figure 16.	Open load in on state - Low-side current recirculation	21
Figure 17.	Battery voltage monitoring	22
Figure 18.	Off-state detection scheme	23
Figure 19.	Open load detection	23
Figure 20.	Off-state diagnostic principle.	24
Figure 21.	Thermal impedance (junction-ambient) of power packages	26
Figure 22.	Application circuit	
Figure 23.	PowerSO-20 mechanical data and package dimensions	34
Figure 24.	PowerSO16 mechanical data and package dimensions.	35
Figure 25.	PowerSSO24 mechanical data and package dimensions	36



1 Block diagram



Figure 1. Block diagram



2 Pins description

2.1 PowerSO-20

The exposed slug must be soldered on the PCB and connected to GND.

Pin N°	Name	Description
1	GND	Ground
2	SO	Serial out
3	VDDIO	Supply voltage for SPI
4	CS	Chip select
5	СР	Charge pump
6	VS	Supply voltage
7	DIR	Direction input
8	OUT1	Output 1
9	DI	Disable
10	GND	Ground
11	GND	Ground
12	EN	Enable
13	OUT2	Output 2
14	PWM	PWM input
15	REXT	External reference resistor
16	SI	Serial in
17	SCK	SPI clock
18	VDD	Supply voltage
19	N.C.	Not connected (To be connected to GND on the PCB)
20	GND	Ground

Table 2. PowerSO-20 pin function

Figure 2. PowerSO-20 pin connection (top v	iew)
--	------





2.2 PowerSO16

The exposed slug must be soldered on the PCB and connected to GND

Pin Nº	Name	Description
1	GND	Ground
2	SO	Serial Out
3	CS	Chip Select
4	СР	Charge pump
5	DIR	Direction Input
6	OUT1	Output 1
7	DI	Disable
8	PGND	Power Ground
9	EN	Enable
10	OUT2	Output 2
11	PWM	PWM Input
12	REXT	External Reference Resistor
13	VS	Supply Voltage
14	SI	Serial In
15	SCK	SPI Clock
16	VDD	Supply Voltage

Table 3	PowerSO16	nin	function
	1 0 0 0 0 0 1 0	pill	lanction

F	igure 3. I	PowerSO16	pin c	connection	(top view)





2.3 PowerSSO24

Although this package has two separate pins for the ground (pin 11 = PGND = Power Ground and pin 22 = GND = Logic Ground), the device is designed to work with shortening ground and is mandatory that the two pins have to be connected nearby the IC on the PCB.

The exposed slug must be soldered on the PCB and connected to GND.

Pin Nº	Name	Description
1, 2, 12, 13, 14, 23, 24	N.C.	Not Connected
3	SO	Serial Out
4	VDDIO	Supply Voltage for SPI
5	CS	Chip Select
6	CP	Supply Voltage for SPI
7	VS	Supply Voltage
8	DIR	Direction Input
9	OUT1	Output 1
10	DI	Disable
11	PGND	Power Ground
15	EN	Enable
16	OUT2	Output 2
17	PWM	PWM Input
18	REXT	External Reference Resistor
19	SI	Serial In
20	SCK	SPI Clock
21	VDD	Supply Voltage
22	GND	Ground

Table 4. PowerSSO24 pin function

Figure 4. PowerSS	O24 pin conne	ction (top vie	w)
I Iguic 4. I oncioo			·•• /





3 Device description

3.1 Supply range

The L9958 has an operating supply range from "Vs_uv" (battery monitoring) up to 28 V. However, the device is tested until 16 V; the functionality of the device is guaranteed until 28 V. The absolute maximum rating is defined to 40 V DC.

3.2 Control inputs

The bridge is controlled by the Inputs PWM, DIR, EN and DI.

All the digital inputs and outputs of the L9958 are compatible with 3.3 V and 5 V CMOS. The power stages output OUT1 and OUT2 are controlled by the direct inputs DIR and PWM as given in *Table 5*. The DIR input gives the direction of output current, while the PWM input controls whether the current is increased or reduced.

3.2.1 DI and EN inputs

The pin DI is internally pulled-up and high active. When DI is active (set to HIGH), the bridge is set to tristate, whatever the state of the DIR and PWM inputs. All the data stored in SPI registers are not reset and SPI communication with the MCU is still possible. When DI is inactive (set to LOW), the bridge is controlled by the DIR and PWM inputs.

The pin EN is internally pulled down and high active. When EN is inactive (set to LOW), the bridge is set to tri-state, whatever the state of the DIR and PWM inputs. All the data stored in SPI registers are not reset and SPI communication with the MCU is still possible. When EN is active (set to HIGH), the bridge is controlled by the DIR and PWM inputs. The coding is performed as shown in the next table. The state of the bridge is transferred in the diagnostic register in a bit called "ACT".

EN	DI	Bit "ACT"	Bridge status
0	0	0	Tri-state
0	1	1 0 Tri-state	
1	0	1	On-state
1	1	1 0 Tri-state	

Table 5. Control pins EN, DI



3.2.2 DIR and PWM inputs

The pins DIR and PWM are internally pulled down. The bridge is controlled by these two inputs according to the table below.

DIR	DIR PWM		OUT2	Bridge Status	
Н	Н	Н	L	Forward	
L	L	L	L	Freewheeling Low	
L	Н	L	Н	Reverse	
Н	L	L	L	Freewheeling low	



DIR=1, PWM=1 (Forward)	DIR=1, PWM=0 (Freewheeling LS)
DIR=0, PWM=1 (Reverse)	DIR=0, PWM=0 (Freewheeling LS)

Figure 5. H-Bridge configurations

The outputs can be disabled (set to tri-state) by the Disable and Enable inputs DI and EN. Input DI has an internal pull-up. Input EN has an internal pull-down. During freewheeling phase, an active freewheeling on the Low-Side MOS is automatically set, switching ON the power transistor in parallel to the internal freewheeling diode.

3.3 Serial peripheral interface (SPI)

The SPI is used for bidirectional communication with a control unit, allowing IC configuration, diagnosis and identification. L9958 can also be used in daisy-chain configuration (number of device in the daisy chain is not limited).

The SPI interface of L9958 is a slave SPI interface: the master is the μ C which provides CS and SCK to L9958.

Transfer format uses 16 bits word in case of single device configuration and multiple of 16 bits word in case of daisy chain configuration.

The first answer after Power-ON-Reset is the IC identifier.

A command sent by the μ C during transfer N is answered during transfer N+1. SO is clocked on SCK rising edge. SI is sampled on falling edge. When CS = '1' and during power-ON reset, SO is in tri-state. Otherwise, the SPI interface is always active.

Settings made by the SPI control word become active at the end of the SPI transmission and remain valid until a different control word is transmitted or a power on reset occurs.

At each SPI transmission, the diagnosis bits as currently valid in the error logic are transmitted. Details on diagnosis are described in *Section 5*.





Between CS falling edge and SCK rising edge, an internal signal called "FSI bit" is set asynchronously on SO output. This can be useful to have internal information on the device without stimulating the SCK clock. The definition of the FSI bit is presented in the diagnostics chapter.





Except the Enable / Disable bit ("ACT" pin), all the bits of diagnosis register are latched and can be released by:

- Diagnosis register read by SPI
- Power-On-Reset condition.

The coding for the Configuration and Diagnosis Registers is reported in the table below.

Bit	Name	Description	Config. value after reset
0 - LSB	RES	Reserved	—
1	DR	Diagnostic Reset Bit	0
2	CL_1	Bit1 for Regulation Current Level	0
3	CL_2	Bit2 for Regulation Current Level	1
4	RES	Reserved	—
5RES6RES7RES		Reserved	_
		Reserved	—
		Reserved	—
8	VSR	Voltage Slew Rate Control Value	0
9 ISR		Current Slew Rate Control Value	0
10	ISR_DIS	Current Slew Rate Control Disable	0
11	OL_ON	Open Load in ON state Enable	0
12	RES	Reserved	_
13	RES	Reserved	_
14	0	"0" to be written	—
15-MSB	0	"0" to be written	

Table 7. Configuration protocol (CFG_REG)

Table 8. Diagnosis protocol (DIA_REG)

Bit	Name	Description	Status after reset	Bit state	DR impact	H-bridge status
0-LSB	OL_OFF	Open Load in OFF condition	0	Latched	-	-
1	OL_ON	Open Load in ON condition	0	Latched	_	_
2	VS_UV	Vs undervoltage	0	Not latched	_	Hi-Z if "1"
3	VDD_OV	Vdd overvoltage	0	Latched	Х	Hi-Z if "1"
4	ILIM	Current Limitation reached	0	Latched	_	_
5	TWARN	Temperature warning	0	Latched	_	_
6	TSD	Over-temperature Shutdown	0	Latched	Х	Hi-Z if "1"
7	ACT	Bridge enable	1	Not latched	_	Hi-Z if "0"
8	OC_LS1	Over-Current on Low Side 1	0	Latched	Х	Hi-Z if "1"
9	OC_LS2	Over-Current on Low Side 2	0	Latched	Х	Hi-Z if "1"
10	OC_HS1	Over-Current on High Side 1	0	Latched	Х	Hi-Z if "1"
11	OC_HS2	Over-Current on High Side 2	0	Latched	Х	Hi-Z if "1"
12	Null	Not Used	-	-	_	_
13	Null	Not Used	_	_	_	_
14	SGND_OFF	Short to GND in OFF condition	0	Latched	_	_
15-MSB	SBAT_OFF	Short to Battery in OFF condition	0	Latched	_	_



3.3.1 Daisy chain operation

Several L9958 can be connected to one SPI connection in daisy chain operation to save μ C interface pins. The number of devices connected in daisy chain is unlimited.





3.4 SPI timing



3.5 SPI communication failure

In case of "no SCK edge" when CS = '0', the transfer is considered as valid: no error is returned to the μ C. The answer of last command is sent during next transfer.

When the number of SCK period is different from 0 or multiple of 16, next SPI answer is all zero.



Figure 10. SPI zero clock communication

3.6 5 V and 3.3 V output compatibility

In order to ensure a full compatibility with 5V and 3.3V MCU peripherals, the pin VDDIO is dedicated to supply the output buffer of SO. The overall current consumption on Vddio is "Ivddio". A parasitic current from the pin SO could flow through the pin VDDIO in case of over-voltage on SO pin vs. VDDIO pin.



4 Current regulation

To protect the actuator and limit power dissipation, a two-level chopper current limitation is integrated as shown in figure below. The current is measured by sense cells integrated in the low-side switches. As soon the upper current limit "IH" is reached, both low-side drivers are switched on to allow free-wheeling recirculation, until the lower current limit "IL" is reached. During the current regulation, all the slew rate controls are disabled in order to minimize the power dissipation. Four current limit levels can be set by the SPI control bits 0 and 1. In order to achieve very precise current threshold and ripple, an external resistance is required (1 % accuracy on all temp range/lifetime) to generate a current reference. Detailed values for current thresholds and ripple are reported in *Table 9*.



Figure 11. Current limitation

Table 9. Current	limitation	programmability
------------------	------------	-----------------

CL_2	CL_1	Current limit (typical values)	
0	0	2.5 A	
0	1	4 A	
1	0	6.6 A (default value)	
1	1	8.6 A	

4.1 Temperature-dependent current regulation

In order to reduce power dissipation and thus the junction temperature, above a temperature **Twarn** = 160 °C, current regulation high limit linearly decreases with temperature, to reach about 2.5 A at **Tsd** = 175 °C (shutdown temperature).

When this thermal threshold is reached during a current limitation phase, the information is stored and latched in a coding of bits called "**Twarn**". This bit can be reset only if the settings conditions ($T_j > T$ warn and $I_{LIM} = 0$) are not present anymore. This feature is mainly used to reduce the power dissipation and thus the junction temperature.





4.2 Current regulation with low-inductive loads

Each time output stages are turned off, an internal timing starts for duration **Toff-min**. Whenever turn-on is reached in a time Toff that is shorter than **Toff-min**, output stages are kept OFF, until **Toff-min** is reached.

In such case the ripple control could be not so precise as specified.



Figure 13. Current regulation with different loads

4.3 Slew rate control in case of current limitation on low-side

The slew rate control can be done on voltage and current or only on voltage. This can be selected by SPI through the bit ISR_DIS.

The slew rate of each high-side power transistor of the bridge is controlled either during turn-on and turn-off (current AND voltage slew rate). The same setting is applied for both switching. Moreover, this slew rate is configurable by SPI in order to get the best trade-off between conducted/radiated EMI and power dissipation during switching. The slew rate



selection can be done "on the fly" by SPI. The corresponding bits are called "**VSR**" and "**ISR**". No external component is needed to select the slew rate range. Only the power transistors not used for freewheeling can be adjusted, the two others can be controlled with a preset slew rate.

The couples of value defined to fulfill most of the application requirements are described in the table below. The required accuracy is ± 50 % for an output current from 1A to 8A and with output voltage up to 19 V. The overall delay implemented between high-side and low-side transistor switching must be adjusted automatically to avoid any cross-conduction through one half-bridge in all conditions.

Range	VSR	ISR	dV/dt (V/µs)	dl/dt (A/µs)
1 (default value)	0	0	4	3
2	0	1	4	0.3
3	1	0	2	3
4	1	1	2	0.3
No SR control	Not selectable		14	14

Table 10. Slew rate control on low side MOS

In case of current limitation and any detection that put the bridge in tri-state, the slew rate is not related anymore to the preset bits "**VSR**"; "**ISR**" but to a dedicated faster slew rate control named "SUPER FAST" mode. The automatic change from SPI selectable to SUPER FAST slew rate is described hereafter.





DocID17269 Rev 6



5 Diagnostics and protections

A detailed diagnostic of the H-bridge is available through SPI communication. The 16 bits diagnostic word is sent back to the MCU in return of a command word. The diagnostic word is used to report two kinds of information:

- H-Bridge failures:
 - Over-current on each transistor in on-state,
 - Vps under-voltage,
 - Vdd over-voltage,
 - Over-temperature,
 - Open-load in on-state,
 - Off-state diagnostic.
- H-bridge functional status:
 - Current limitation condition,
 - Current limitation decreasing condition,
 - Disable / Enable status.

5.1 Diagnosis reset strategy

5.1.1 Reset requests

Except "ACT" and "VS_UV" bits, all the others are latched and can only be released by:

- Transition from "Disable" to "Enable" on DI / EN pins,
- Diagnostic register read by SPI (see details on each failure release) depending on bit "DR",
- Power-On-Reset condition.

When the diagnostic register is reset, the bridge is switched back to normal mode driven by DIR and PWM. All the settings are kept as before the failure. In case of SPI read, no additional action on DI / EN is needed.

5.1.2 Diagnosis reset bit

In case of "DR" set to LOW (default value), all the bits of the diagnostic register can be reset by the three possibilities described in previous section.

In case of "DR" set to HIGH, the over-current, Vdd over-voltage and over-temperature diagnostic bits can NOT be reset by SPI read and therefore, the bridge is kept in tri-state until a transition from "Disable" to "Enable" on DI/EN pins or Power-on-Reset condition.

DR	Diagnosis reset strategy			
0	All diagnostic bits reset at each SPI reading (Default)			
1	Over current bits (811) + Temp. shutdown TSD bit (6) + Vdd over voltage bit (3) NOT reset by SPI			



5.2 **Protection and on state diagnostics**

L9958 is protected against short circuits, overload and invalid supply voltage by the following measures.

5.2.1 Over-current on high-side - short to ground

The high-side switches are protected against a short of the output to ground by an overcurrent shutdown. If a high-side switch is turned on and the current rises above the short circuit detection current **loc** all output transistors are turned off after a filter time **Toc_Is** and the error bits "overcurrent on high side 1 (2)", **OC_HS1** (**OC_HS2**) are stored in the internal status register.

5.2.2 Over-current on low-side - short to Vs

Due to the chopper current regulation, the low-side switches are already protected against a short to the supply voltage. To be able to distinguish a short circuit from normal current limit operation, the current limitation is deactivated for the blanking time t_b after the current has exceeded the current limit threshold IH. If the short circuit detection current I_{oc} is reached within this blanking time, a short circuit is detected. All output transistors are turned OFF and the according error bit "Over-Current on Low Side 1 (2)", OC_LS1 (OC_LS2) is set.

5.2.3 Short circuit over-load

If, during the Blanking time (t_b) of the current regulation mode, the current reaches the l_{oc} threshold; after a filtering time, the output MOS are switched OFF and the "Short circuit over load" can be checked by the reading of the overcurrent bits of the DIA_REG (please refer to *Table 8* bit 8, 9,10 and 11).





5.2.4 Open load in on state

To perform the Open Load diagnosis in ON state, the flag OL_ON has to be set high through SPI. After every open load diagnosis in ON state, the OL_ON flag is resetted, to perform a new open load diagnosis in ON state the OL_ON flag has to be set again.



This disable the turning on of the low-side drivers during current recirculation. The current flows through the body diode of the low-side MOS for a fixed time. At the end of this fixed time the Vout voltage is sampled and the possible open load condition detected (see *Figure 16*).



Figure 16. Open load in on state - Low-side current recirculation

5.2.5 Over-temperature

When **Twarn** is reached, thermal current reduction is activated, and the information is stored and latched. When **Tsd** is reached, the "**TSD**" bit is set and all output transistors are put in tri-state conditions as long as a reset is applied.

TSD	Comments	Bridge state	FSI
1	Tj > TSD	Tri-state-	1
0 (default)	Tj < TSD	-	0

5.2.6 Vs under-voltage shutdown

If the supply-voltage at the V_S pins falls below the under-voltage detection threshold **Vs_uv_off**, the outputs are set to tri-state and the error bit "Undervoltage at V_S" is set. A filtering time "**Tuv_Vs**" is implemented to avoid unwanted detection due to parasitic glitches. The information is transferred into the SPI register in a bit called "**VS_UV**". This bit is NOT latched. As soon as the voltage rises again above the Vs under-voltage threshold (hysteresis implemented), the bridge is switched back to normal mode driven by DIR and PWM. All the settings are kept as before the under-voltage event.





Figure 17. Battery voltage monitoring

Table 13. Vs under-voltage

vs_uv	Comments	Bridge state	FSI
1	Vs < Vs_uv_off	Hi Z	1 (not latched)
0 (default)	Vs > Vs_uv_on	-	0

5.2.7 Vdd over-voltage detection

Although the Vdd input pin and all I/O's are able to withstand up to 19 V, an over-voltage circuitry is implemented to ensure that the bridge is kept in tri-state when the Vdd voltage is higher than the Vdd overvoltage threshold "Vdd_ov_off" for duration longer than "Tov Vdd". The information is detected and stored into the SPI register in a bit called "VDD OV". The bridge is kept in tri-state as long as an appropriate reset is not requested (see Section 5.1).

VDD_OV	Comments	Bridge state	FSI				
1	Vdd > Vdd_ov_off	Hi-Z	1 (latched)				
0 (default)	Vdd < Vdd_ov_on	-	0				

5.2.8 Vdd under-voltage detection

When the Vdd voltage falls below the under-voltage detection threshold "Vdd_uv_off" for duration longer than "Tuv_vdd", the bridge is switched to tri-state. In such a condition, the L9958 is going in sleep mode. When the voltage increases above the threshold (hysteresis implemented), the L9958 starts with all the settings reset to their default values (Power On Reset).

5.2.9 **Output short protection**

The L9958 can sustain short on the outputs. In case of short to GND, short to battery or short between outputs the battery voltage cannot exceed 18 V. The connection of a 100 µF plus a 1µF decoupling capacitors as close as possible to V_s pin and the GND connection of the slug or of the exposed pad is mandatory to improve the robustness.



5.3 Off-state diagnosis

This diagnostic is performed in any off-state condition, just after ignition key-on or during an off-state phase occurring after an on-state phase of the bridge.

5.3.1 Off-state detection scheme

In order to avoid any wrong diagnostic, a filtering time "**Tdiag_off**" is applied before performing the detection if the bridge was in on-state before. This filtering time is not applied in case of detection after key on.



Figure 18. Off-state detection scheme

5.3.2 Open load detection

An equivalent resistor of 100 k Ω (typ.) is targeted for open-load detection.

In order to avoid any unwanted supply of the bridge through the high-side transistor body diode during off-state measurement, the current source is connected only if Vs is higher than the Vs under-voltage threshold.





The diagnostic is based on a closed loop voltage control on OUT1 and associated current measurement.

A voltage amplifier forces a constant voltage on OUT1 through two current sources (highside source and low-side current sink). The OUT2 is pulled-down through a constant current sink. Based on the current flowing out of the amplifier (Ip - In) compared to several current thresholds, open-load as well as short-circuit to ground and battery can be detected.







5.4 H-Bridge functional status

Three bits in the diagnosis register are used to give a feedback about the state of the H-Bridge. Status are Current Limitation (bit 4 "C_LIM"), Temperature Warning (bit 5 "T_WRN") and Bridge Enable Status (bit 7 "ACT"). Those bits do not report a failure but only a functional state of the H-bridge that could be useful to change the control strategy mainly in term of power dissipation.

6 Electrical specifications

6.1 Absolute maximum ratings

The component must withstand the overall following stimulus without any damage or latchup. Beyond these values, damage to the component may occur.

Symbol	Parameter	Test condition	Min.	Max.	Unit
V _{ps}	Supply voltage	Continuous Transient (0.5 s; I ≤ 10 A)	-1 -2	40 40	V
V _{dd}	Logic supply voltage	0 V < V _{ps} < 40 V	-0.3	19	V
V _{ddio}	SDO supply voltage	0 V < V _{ps} < 40 V	-0.3	19	V
Vi	Logic input voltage	0 V < V _{ps} < 40 V 0 V < V _{dd} < 19 V	-0.3	19	V
Vo	Logic output voltage	$\begin{array}{c} 0 \ V < V_{ps} < 40 \ V \\ 0 \ V < V_{dd} < 18.7 V \end{array}$	-0.3	Vddio+0.3	V
Output pins OUTx, VPS)	ESD Compliance	EIA/JESD22-A114-B	±4	-	kV
Input pins			±2	-	
-	ISO 7637 pulses	Cf. standards	-	-	-
-	Latch-up immunity	Jedec standard	-100	+100	mA

Table 15.	Absolute	maximum	ratings
-----------	----------	---------	---------

Note: In case of load dump condition, status of device outputs is kept unchanged.

6.2 Thermal data

Table 16. Thermal data

Symbol	Parameter	Test condition	Min.	Max.	Unit
Тj	Junction temperature	Failure condition	-40	OTsd	°C
		Lifetime	-40	150	C
T _{stg}	Storage temperature	-	-55	150	°C
T _{amb}	Ambient temperature	0 V < V _{ps} < 40 V	-40	125	°C
	Thermal resistance junction to case ⁽¹⁾	Package PowerSO-20	-	1	
R _{thj-case}		Package PowerSO16	-	1	°C/W
		Package PowerSSO24	-	2	

1. Guaranteed by design and package characterization.





Figure 21. Thermal impedance (junction-ambient) of power packages

6.3 Range of functionality

Within the range of functionality, all L9958 functionalities have to be guaranteed. All voltages refers to GND. Currents are positive into and negative out of the specified pin.

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit					
FR1	V _{ps}	Supply voltage	-	Vps_uv_off	14	28 ⁽¹⁾	V					
FR2	dV _{ps} /d _t	Supply voltage slew rate	-	-20	-	20	V/µs					
FR3	V _{dd}	Logic supply voltage	-	Vdd_uv_off	5	Vdd_ov_off	V					
FR4	dV _{dd} /d _t	Logic supply voltage slew rate	-	-	-	0.025 ⁽²⁾	V/µs					
FR5	Vi	Logic input voltage (SDI, SCLK, NCS, DI, EN, DIR, PWM)	See alsoTable 15: Absolute maximum ratings.	-0.3	-	Vdd_ov_off	V					
FR6	V _{ddio}	SDO output voltage	-	3	-	5.5	V					
FR7	f _{spi}	SPI clock frequency	-	-	-	5	MHz					

Table 17. Range of functionality

1. In load dump conditions V_{ps} ranges between 28V and 40V. During load dump, status of device outputs is kept unchanged,

2. To VDD pin are connected 10µF and 10nF (close to the pin) capacitors.



6.4 Electrical characteristics

 T_{case} = -40 °C to 125 °C unless otherwise specified,

 V_{dd} = 4.5 V to 5.5 V unless otherwise specified

 V_{ps} = 4 V to 28 V unless otherwise specified

All voltages refer to GND. Currents are positive into and negative out of the specified pin.

6.4.1 Device supply

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
		I _{ps} Power supply current	V _{dd} < 0.7 V; V _{ps} = 16 V from -40 °C to 25 °C	-	-	20	μA
1.1	I _{ps}		V _{dd} < 0.7 V; V _{ps} = 16 V at 125 °C	-	-	35	μA
			$F_{pwm} = 0, I_{out} = 0$	-	-	20	mA
1.2	I _{out}	Leakage current on output	Bridge in tri-state	-	-	100	μA
1.3	1	Logic-supply current	V _{dd} >V _{dd_uv_on} F _{PWM} = 0	-	-	5	mA
1.3	I _{CC}		F _{PWM} = 20 kHz (Average value)	-	-	5	mA

Table 18. Device supply

6.4.2 Device supply monitoring

Table 19. Device supply monitoring

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
2.1	V _{ps_uv_off}	V _{ps} under-voltage threshold	V _{ps} decreasing	-	-	4	V
2.2	V _{ps_uv_on}	V _{ps} under-voltage threshold	V _{ps} increasing	-	-	4.5	V
2.3	V _{ps_uv_hyst}	V _{ps} under-voltage hysteresis	-	0.1	-	-	V
2.4	T _{uv_vps}	V _{ps} under-voltage filtering time	V _{ps} decreasing	1	-	3	μs
2.5	V _{dd_uv_off}	V _{dd} under-voltage threshold	V _{dd} decreasing	3	-	3.7	V
2.6	V _{dd_uv_on}	V _{dd} under-voltage threshold	V _{dd} increasing	3.3	-	4	V
2.7	V _{dd_uv_hyst}	V _{dd} under-voltage hysteresis	-	0.1	-	-	V
2.8	T _{uv_Vdd}	V _{dd} under-voltage filtering time	V _{dd} decreasing	1	-	4	μs
2.9	V _{dd_ov_off}	V _{dd} over-voltage threshold	V _{dd} increasing	5.8	-	6.8	V
2.10	V _{dd-ov_on}	V _{dd} over-voltage threshold	V _{dd} decreasing	5.5	-	6.5	V
2.11	V _{dd_ov_hyst}	V _{dd} over-voltage hysteresis	-	0.1	-	-	V
2.12	T _{ov_Vdd}	V _{dd} over-voltage filtering time	V _{dd} increasing	60	100	140	μs



6.4.3 SPI

Table 20. SPI										
Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit			
3.1	f _{spi}	Clock frequency (50 % duty cycle)	-	-	-	5	MHz			
3.2	т.,	SDO transition speed, 20-80 %	V_{sdo} = 5V, C_{load} = 50 pF ⁽¹⁾	5	-	30	ns			
0.2	T _{sdo_trans}		V_{sdo} = 5 V, C_{load} = 150 pF	5	-	50	ns			
3.3	T _{clh}	Minimum time SCLK = HIGH	-	75	-		ns			
3.4	T _{cll}	Minimum time SCLK = LOW	-	75	-		ns			
3.5	T _{pcld}	Propagation delay (SCLK to data at 10% of SDO rising edge)	-	-	-	40	ns			
3.6	T _{csdv}	NCS = LOW to data at SDO active	-	-	-	85	ns			
3.7	T _{sclch}	SCLK low before NCS low (setup time SCLK to NCS change H/L)	-	75	-	-	ns			
3.8	T _{hclcl}	SCLK change L/H after NCS = low	-	75	-	-	ns			
3.9	T _{scld}	SDI input setup time (SCLK change H/L after SDI data valid)	-	40	-	-	ns			
3.10	T _{hcld}	SDI input hold time (SDI data hold after SCLK change H/L)	-	40	-	-	ns			
3.11	T _{scici}	SCLK low before NCS high	-	100	-	-	ns			
3.12	T _{hclch}	SCLK high after NCS high	-	100	-	-	ns			
3.13	T _{pchdz}	NCS L/H to SDO @ high impedance	-	-	-	75	ns			
3.14	Tonncs	NCS min. high time	-	300	-		ns			
3.15	-	Capacitance at SDI, SCLK; NCS	-	-	-	14	pF			
0.10	-	Capacitance at SDO	-	-	-	19	pF			
3.16	T _{fncs}	NCS Filter time will be ignored) Guaranteed by design (Pulses = TfNCS	Guaranteed by design	10	-	40	ns			
3.17	V _{ddio}	Supply voltage for SDO output buffer	-	3	-	5.5	V			
3.18	I _{vddio}	Current consumption on Vddio	(2)	-	-	1	mA			
3.19	sdo_H	High output level on SDO	I _{sdo} = 1.5 mA	V _{ddio} - 0.4	-	-	V			
3.20	sdo_L	Low output level on SDO	I _{sdo} = 2 mA	-	-	0.4	V			
3.21	I _{sdo}	Tri state leakage current	NCS = HIGH V _{DDIO} = 5 V	-5	-	5	μA			

Table 20. SPI

1. Not tested – guaranteed by C_{load} = 150 pF measurement

2. Measured for PSO16 at wafer sort level only.

L9958



6.4.4 Digital inputs: TTL // 3.3V / 5V CMOS compatible

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
4.1	V _{ih}	Input voltage HIGH	-	2	-	Vdd+0.3	V
4.2	V _{il}	Input voltage LOW	-	-0.3	-	0.8	V
4.3		Hysteresis of input voltage	-	200	-	-	mV
		Input current source for: DI /	V _{in} = 0 V	-100	-	-30	
4.4	I _{inl}	NCS / SCLK / SDI	V _{in} = 5 V No back supply allowed	-	-	5	μA
4.5	I	Input current sink for: EN / DIR / PWM	V _{in} = 5 V	30	-	100	μA
4.5	' inh		V _{in} = 0 V	-5	-	-	
	V _{rext}		-	-	1.24	-	V
4.6		R _{ext} External resistor	-	-	10	-	kΩ
	R _{ext}		Overall tolerance can be taken as 3.5 %	-	1	-	%

Table 21. Digital inputs: TTL // 3.3V / 5V CMOS compatible

6.4.5 Bridge output drivers

Table 22. Bridge output drivers

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
5.1	P	R High-side transistor R . L	T _j = 150 °C, I _{out} = 3 A 4 V < V _{ps} < 5 V	-	-	300	mΩ
5.1	'∿dson_h		T _j = 150 °C, I _{out} = 3 A V _{ps} > 5 V	-	-	150	11152
5.2	_	R I I ow-side transistor R I	T _j = 150 °C, I _{out} = 3 A 4 V < V _{ps} < 5 V	-	-	300	mΩ
5.2	r∿dson_l		T _j = 150 °C, I _{out} = 3 A V _{ps} > 5 V	-	-	150	11152
5.3	V _{bd_h}	Body diode forward voltage drop high-side transistor	I _{diode} = 3 A	-	1.2	2	V
5.4	V _{bd_I}	Body diode forward voltage drop low-side transistor	I _{diode} = 3 A	-	1.2	2	V



6.4.6 Over-temperature monitoring

Table 23.	Over-tem	perature	monitoring
	•••••	poracaro	

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
6.1	OTwarn	Over-temperature warning -		150	-	170	°C
6.2	OTsd	Over-temperature shut-down -		170	-	200	°C
6.3	OThyst	Over-temperature hysteresis -		10	-	-	°C
6.4	T _{TSD}	Over-temperature filtering time Guaranteed by clock measurement		-	36	-	μs

6.4.7 Current limitation and over-current detection

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
			CL1:0 = 00; -40 °C ≤ T _j ≤ 150 °C	2	2.5	3.1	
			CL1:0 = 01; -40 °C ≤ T _j ≤ 150 °C	3.5	4	4.85	
			CL1:0 = 10; -40 °C ≤ T _j < 25 °C	5.5	6.75	8	
7.1	I _{lim_H}	Current limitation high threshold	CL1:0 = 10; 25 °C ≤ T _j ≤ 150 °C	5.5	6.6	7.7	A
			CL1:0 = 11; -40 °C ≤ T _j < 25 °C	7.8	9.1	10.4	
			CL1:0 = 11; 25 °C ≤ T _j ≤ 150°C	7.6	8.6	9.6	
			CL1:0 = XX, T _j = OTsd	2	2.5	3	
	7.2 I _{lim_L}	Current limitation low I _{lim_L} threshold	CL1:0 = 0X; -40 °C ≤ T _j ≤ 150 °C	I _{lim_H} –0.2	I _{lim_H} − 0.5	I _{lim_H} - 0.8	
			CL1:0 = 10; -40°C ≤ T _j < 25 °C	I _{lim_H} 0.35	l _{lim_H} - 0.65	l _{lim_H} - 0.95	
7.2			CL1:0 = 10; 25 °C ≤ T _j ≤ 150°C	I _{lim_H} 0.35	l _{lim_H} - 0.55	l _{lim_H} - 0.85	А
			CL1:0 = 11; -40°C ≤ T _j < 25°C	I _{lim_H} –0.4	I _{lim_H} - 0.7	I _{lim_H} -1	
			CL1:0 = 11; 25 °C ≤ T _j ≤ 150°C	I _{lim_H} –0.4	l _{lim_H} - 0.55	l _{lim_H} - 0.95	
7.3	T _{limh}	High current limitation threshold filtering time	can be included in T _{blanck}	0.1	-	1	μs
7.4	T _{liml}	Low current limitation threshold filtering time	-	1	-	3	μs
7.5	T _{offmin}	Current limitation delay time	-	30	-	45	μs
7.6	Τ _b	Blanking time	-	4.9	-	8.7	μs

Table 24. Current limitation and over-current detection



Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
		loc_ls loc-hs threshold High-side over-current threshold	CL1:0 = 0X; -40 °C ≤ T _j ≤ 150 °C	5.5	7.7	11	
			CL1:0 = 1X; -40°C ≤ T _j < 25 °C	9.3	12	16.5	
7.7			CL1:0 = 1X; 25 °C ≤ T _j ≤ 150°C	9.3	11.5	14	
			CL1:0 = 0X; CL1:0 = 10; -40 °C ≤ T _j ≤ 150 °C	l _{lim_h} +2	-	-	
			CL1:0 = 11; -40 °C ≤ T _j ≤ 150 °C	I _{lim_h} +1.3	-	-	
7.8	Toc_ls Toc_hs	Low-side & high-side over-current detection filtering time	-	0.8	-	2.5	μs

 Table 24. Current limitation and over-current detection (continued)

6.4.8 Diagnostic of open-load in on-state

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
			T _j = -40 °C (go-no-go functional test)	50	-	120	
8.1	ls_OL-on	Current source	T _j = 25 °C to 150 °C (go-no-go functional test)	50	-	100	μA
8.2	Tmeas_on	Detection time (settling time)	-	-	3	5	μs

Table 25. Diagnostic of open-load in on-state

6.4.9 Off-state diagnostic

Pos.	Symbol	Parameter Test condition		Min.	Тур.	Max.	Unit
9.1	R _{OL}	Load detection threshold		10	60	200	kΩ
9.2	Tdiag_off	Delay time before enabling off- state diagnostic structure diagnostic structure diagnostic structure		100	125	150	ms
9.3	T _{diag-off_1}	Off-state diag filtering time when OUT 1 and/or 2 decrease from V _{ps} used each time OUT pins are released from Vps (after release of SCB, after Tdiag_off) Guaranteed through SCAN		2.4	3	3.6	ms
9.4	T _{diag_off_2}	Off-state diagnostic filtering time on failure detection One symmetric filter for each failure type (OL, SCG, SCB) Guaranteed through SCAN		200	250	300	μs
9.5	T _{clock}	Oscillator frequency -		4	-	6	MHz

Table 26. Off-state diagnostic



6.4.10 Timing characteristics

Pos.	Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
10.1	f _{pwm}	PWM frequency	-	-	-	20	kHz
	T _{don}	Delay time for switch-on	$ \begin{array}{l} R_{load} @ \ I_{out} = 3 \ A \\ PWM \rightarrow 90\% \ V_{out} \ (or \\ 10 \ \% \ I_{out}) \end{array} $	-	-	10	μs
10.2	T _{doff}	Delay time for switch-off	$ \begin{array}{l} R_{\text{load}} @ \ I_{\text{out}} = 3 \ A \\ PWM \rightarrow 10 \ \% \ V_{\text{out}} \ (\text{or} \\ 90\% \ lout) \end{array} $	-	-	10	μs
	ΔT_d	Delay time: symmetry	PWM accuracy = 1% @ 2kHz	-	-	5	μs
10.3	T _{d_dis}	Disable delay time	DI / EN \rightarrow 90% OUTx @ I _{out} = 3 A	-	-	6	μs
10.4	T _{d_en}	Enable delay time	DI / EN \rightarrow 10 % OUT	-	-	6	μs
10.5	T _{d_pow}	Power-on delay time	$\begin{array}{l} \text{DIR= PWM=EN=1 /} \\ \text{DI=0 no load / } V_{PS} = \\ V_{dd} \text{ increasing} \\ V_{ps} = V_{dd} \rightarrow 10 \ \% \ V_{out1} \\ (= V_{ps}) \end{array}$	-	-	200	μs
10.6	T _{d_filter}	DI / EN digital filter time	-	1	-	3	μs
10.7	T _{rise_H}	Low-side transistor rise time	Non selectable by SPI	0.04	-	0.2	μs
10.8	T _{fall_H}	Low-side transistor fall time	Non selectable by SPI	1	-	3	μs
		Voltage slew rate for high-side	super fast mode	7	14	24	
10.9	dV _{out/} d _t	transistors (Measurement is performed	VSR = 0	2	4	6	V/µs
		between 30 % and 70 % of the slope)	VSR = 1	1	2	3	
		Current slew rate for high-side	ISR=0	1.5	3	4.5	
10.10	dl _{out} /d _t (dl _{out} /d _t transistors (Measurement is performed between 40 % and 60 % of the slope)	ISR=1	0.15	0.3	0.45	A/µs
10.11	T _{diag}	Timing for reliable diagnostic	Guaranteed through SCAN pattern	35	-	55	μs

Table 27. Timing characteristics



7 Application circuit





1. The above application diagram shows all the suggested components for a proper device operation.



8 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*.

 $ECOPACK^{\mathbb{R}}$ is an ST trademark.



Figure 23. PowerSO-20 mechanical data and package dimensions

DocID17269 Rev 6





Figure 24. PowerSO16 mechanical data and package dimensions





Figure 25. PowerSSO24 mechanical data and package dimensions



9 Revision history

Date	Revision	Changes
16-Mar-2010	1	Initial release.
08-Apr-2011	2	Updated Table 27: Timing characteristics on page 32 (Pos. 10.8).
03-Aug-2011	3	Updated Table 17, Table 20, Table 24 and Table 27.
23-Mar-2012	4	Updated: Table 17: Range of functionality; Table 20: SPI.
19-Sep-2013	5	Updated disclaimer.
05-Dec-2013	6	Updated <i>Table 24: Current limitation and over-current detection</i> pag 31.

57

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries. Information in this document supersedes and replaces all information previously supplied. The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2013 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

DocID17269 Rev 6

