February 2009

TLE4976-1K / TLE4976L

High Precision Hall Effect Switch with Current Interface

Data Sheet

Rev. 2.0

Sense & Control



Never stop thinking

Edition 2009-02-12

Published by Infineon Technologies AG 81726 Munich, Germany © 2009 Infineon Technologies AG All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



Revision History: 2009-02-12, Rev. 2.0

Previous	s Version: V1.1
Page	Subjects (major changes since last revision)
	H" version substituted by "K" version
6, 7	timing and output switching diagram inserted

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:

sensors@infineon.com





Table of Contents

Table of Contents

1	Product Description
1.1	Overview
1.2	Features
1.3	Target Applications 3
2	Functional Description
2.1	General
2.2	Pin Configuration (top view)
2.3	Pin Description
2.4	Block Diagram
2.5	Functional Block Description
2.6	Timing Diagram and Output Switching 6
3	Specification
3.1	Application Circuit
3.2	Absolute Maximum Ratings
3.3	Operating Range
3.4	Electrical and Magnetic Characteristics 10
4	Package Information
4.1	Package Outline
4.2	Footprint
4.3	Distance between Chip and Package
4.4	Package Marking



High Precision Hall Effect Switch with Current Interface

TLE4976-1K TLE4976L

1 **Product Description**

1.1 Overview

The TLE4976-1K and TLE4976L are high precision unipolar Hall switches with a two wire, 6mA/14mA current interface in a SMD or leaded package. A chopped measurement principle provides high stability switching thresholds for operating temperatures between -40°C and 150°C.

1.2 Features

- 3.0V to 24V supply voltage operation
- High sensitivity and high stability of the magnetic switching points
- High resistance to mechanical stress by Active Error Compensation
- Reverse battery protection (-18V)
- Superior temperature stability
- Peak temperatures up to 195°C without damage
- Low jitter (typ. 1µs)
- High ESD performance (± 8kV HBM)
- Digital output signal with current modulation 6mA / 14mA
- Unipolar version
- SMD package SC59 (SOT23 compatible): TLE4976-1K
- Leaded package PG-SSO-3-2: TLE4976L

1.3 Target Applications

The sensor targets all applications where a high precision unipolar magnetic switch is required (e.g. position sensing). Due to the current interface the number of wires required in the application is minimized thus saving costs and increasing reliability. This is specially helpful in all applications where the microcontroller is not on the same PCB as the Hall switch but in some distance.

Product Name	Product Type	Ordering Code	Package		
TLE4976-1K	Hall Effect Switch	SP000475038	SC59		
TLE4976L	Hall Effect Switch	SP000012951	PG-SSO-3-2		







Functional Description

2 Functional Description

2.1 General

The TLE4976-1K and the TLE4976L are integrated circuit Hall-effect sensors designed specifically for highly accurate applications. Precise magnetic switching thresholds and high temperature stability are achieved by active error compensation circuits and chopper techniques on the chip. The IC has a current interface with a 6mA / 14mA output.

2.2 Pin Configuration (top view)



Figure 1 Pin Configuration and Center of Sensitive Area

2.3 Pin Description

Table 1 Pin Description for TLE4976-1K (SC59)

Pin No.	Symbol	Function	Comment	
1	Vs	Supply voltage		
2	N.C.	No internal connection		
3	GND	Ground		

Table 2 Pin Description for TLE4976L (PG-SSO-3-2)

Pin No.	Symbol	Function	Comment
1	Vs	Supply voltage	
2	GND	Ground	
3	N.C.	No internal connection	



TLE4976-1K TLE4976L

Functional Description

2.4 Block Diagram



Figure 2 Functional Block Diagram

2.5 Functional Block Description

The chopped Hall IC switch comprises a Hall probe, bias generator, compensation circuits, oscillator and output transistor.

The bias generator provides currents for the Hall probe and the active circuits. Compensation circuits stabilize the temperature behavior and reduce technology variations.

The Active Error Compensation rejects offsets in signal stages and the influence of mechanical stress to the Hall probe caused by molding and soldering processes and other thermal stresses in the package.

This chopper technique together with the threshold generator and the comparator ensure high accurate magnetic switching points.

The current consumption depends on the switching status.



Functional Description

2.6 Timing Diagram and Output Switching

The output switching is different for the TLE4976-1K and TLE4976L. It is explained in the following section.

TLE4976-1K:



Figure 3 Timing Diagram of TLE4976-1K



Figure 4 Output Switching of TLE4976-1K



Functional Description

TLE4976L:



Figure 5 Timing Diagram of TLE4976L







3.1 Application Circuit

The advantage of the current interface is, that only two wires are necessary to connect the sensor.

At least one series resistor is required to convert the two output states of the Hall sensor from current consumption to a voltage information.

A typical value for R_L is 100 Ω . This gives a typical signal voltage level V_{SIG} = 0.8V in the *Off* state and 1.4V in the *On* state.

If the sensor is operated in an application environment with disturbances on the supply line, an additional series resistor R_S is recommended. The maximum value for the series resistor R_S can be calculated using the following formula:

$$\boldsymbol{R}_{\text{Smax}} = \frac{\boldsymbol{V}_{\text{Supplymin}} - \boldsymbol{V}_{\text{Smin}}}{\boldsymbol{I}_{\text{Shighmax}}} - \boldsymbol{R}_{\text{L}}$$

 $V_{S_{min}}$ is the minimal supply voltage which might occur due to disturbances on the supply line V_S .

Example: $V_{Supplymin}$ = 6V; V_{Smin} = 3V; R_L = 100 Ω ; $I_{Shighmax}$ = 17mA : R_{Smax} = 76.5 Ω



Figure 7 Application Circuit



3.2 Absolute Maximum Ratings

Table 3 Absolute Maximum Rating Parameters

Parameter	Symbol	Lim	it Values	Unit	Note / Test Condition	
		Min.	Max.			
Supply voltage	V _s	- 18	18	V		
		- 18	24		for 1h, $R_s+R_L > 75\Omega$	
		– 18	26		for 5min, $R_S + R_L > 75\Omega$	
Supply current through protection device	I _S	- 50	+50	mA		
Junction temperature	Tj	_	155	°C	for 2000h (not additive)	
	1	_	165		for 1000h (not additive)	
		_	175		for 168h (not additive)	
		-	195		for 3 x 1h (additive)	
Storage temperature	T _s	- 40	150	°C		
Magnetic flux density	В	-	unlimited	mT		

Attention: Stresses above the max. values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit.

Table 4ESD Protection¹⁾

Parameter	Symbol	Lim	Limit Values		Note / Test Condition	
		Min.	Max.			
ESD Voltage	V _{ESD}	±8		kV	HBM, R = 1.5kΩ, C = 100pF $T_A = 25^{\circ}C$	

 Human Body Model (HBM) tests according to: EOS/ESD Association Standard S5.1-1993 and Mil. Std. 883D method 3015.7

3.3 Operating Range

The following operating conditions must not be exceeded in order to ensure correct operation of the Hall Effect Switch.

All parameters specified in the following sections refer to these operating conditions unless otherwise mentioned.

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Тур.	Max.		
Supply voltage	Vs	3		18	V	
		3		24		for 5 min, $R_s + R_L > 100\Omega$
Junction temperature	Tj	- 40		150	°C	
				175		for 168h

Table 5 Operating Conditions Parameters



3.4 Electrical and Magnetic Characteristics

Product characteristics involve the spread of values guaranteed within the specified voltage and ambient temperature range. Typical characteristics are the median of the production.

Parameter	Symbol	Values			Unit	Note / Test Condition	
		Min.	Тур.	Max.			
Supply current low	I _{SLOW}	5	6	7	mA	TLE4976-1K: B < B_{RP} TLE4976L: B > B_{RP} V _S = 3V 18V	
Supply current high	I _{SHiGH}	12	14	17	mA	TLE4976-1K: B > B _{OP} TLE4976L: B < B _{OP} V _S = 3V 18V	
Reverse current	I _{SR}	0	-	0.2	mA	V _S = -18V	
Output fall time	t _f	_	0.4	1.6	μs	R _S = 100Ω	
Output rise time	t _r	_	0.4	1.6	μs	-	
Chopper frequency	f _{osc}	_	320	_	kHz		
Switching freq.	f _{SW}	0	-	15 ²⁾	kHz		
Delay time ³⁾	t _d	_	13	-	μs		
Output jitter ⁴⁾	t _{QJ}	-	1	-	μs_{RMS}	Typical value for square wave signal 1kHz	
Power-on time ⁵⁾	t _{PON}	_	13	_	μs	$V_{\rm S} \ge 3.0 V$	
Thermal resistance6)	R _{thJA}		100		K/W	SC59	
				190		PG-SSO-3-2	

Table 6	General	Electrical	Characteristics ¹⁾

1) over operating range, unless otherwise specified. Typical values correspond to $V_s = 12V$ and $T_A = 25^{\circ}C$

2) To operate the sensor at the max. switching frequency, the value of the magnetic signal amplitude must be 1.4 times higher than for static fields. This is due to the - 3dB corner frequency of the low pass filter in the signal path

3) Systematic delay between magnetic threshold reached and output switching

4) Jitter is the unpredictable deviation of the output switching delay

5) Time from applying $V_S \geq 3.0V$ to the sensor until the output state is valid

6) Thermal resistance from junction to ambient

Calculation of the ambient temperature:

e.g. for V_S = 12.0V, R_S = 100W, I_{SHIGHtyp} = 14mA : Power Dissipation: P_{DIS} = 148.4mW. In T_A = T_j - (R_{thJA} x P_{DIS}) = 175°C - (100K/W x 0.15W) Resulting max. ambient temperature: T_A = 160°C



Parameter	Symbol	Т _ј [°С]	Values			Unit	Note /
			Min.	Тур.	Max.		Test Condition
Operating point	B _{OP}	-40 150	5.5	9.25	11.0	mT	TLE4976-1K
		-40	1.1	4.1	6.1		TLE4976L
		25	1.0	4.0	6.0		
		150	0.9	3.8	5.8		
Release point	B _{RP}	-40 150	5.0	7.25	10.5	mT	TLE4976-1K
		-40	3.1	6.1	8.2		TLE4976L
		25	3.0	6.0	8.0		
		150	2.9	5.8	7.7		
Hysteresis	B _{HYS}	-40 150	0.5	2.0	3.0	mT	TLE4976-1K
		-40	-	-	-		TLE4976L
		25	0.5	2.0	3.5		
		150	-	-	-		
Temperature compensation of	T _c		-	0	-	ppm/°C	TLE4976-1K
magnetic thresholds			-	-200	-		TLE4976L
Repeatability of magnetic thresholds ²⁾	B _{REP}		-	40	-	μT_{RMS}	Typ. value for $\Delta B / \Delta t$ > 12 mT/ms

Table 7Magnetic Characteristics¹⁾

1) over operating range, unless otherwise specified. Typical values correspond to V_s = 12 V.

2) B_{REP} is equivalent to the noise constant

Field Direction Definition

Positive magnetic fields are defined with the south pole of the magnet to the branded side of package.







Package Information

4 Package Information

4.1 Package Outline



Figure 9 SC59 Package Outline (All dimensions in mm)



Package Information



Figure 10 PG-SSO-3-2 Package Outline (All dimensions in mm)



TLE4976-1K TLE4976L

Package Information

4.2 Footprint



Figure 11 Footprint SC59



Package Information

4.3 Distance between Chip and Package



Figure 12 Distance between chip and package: left: TLE4976-1K, right: TLE4976L

4.4 Package Marking



Figure 13 Marking of TLE4976-1K and TLE4976L

www.infineon.com