

Data Sheet

ADG1433/ADG1434

FEATURES

- 4.7 Ω maximum on resistance at 25°C
- 0.5 Ω on-resistance flatness
- Fully specified at ±15 V/+12 V/±5 V
- 3 V logic-compatible inputs
- Up to 115 mA continuous current per channel
- Rail-to-rail operation
- Break-before-make switching action
- 16-/20-lead TSSOP and 4 mm × 4 mm LFCSP

APPLICATIONS

- Relay replacement
- Audio and video routing
- Automatic test equipment
- Data acquisition systems
- Temperature measurement systems
- Avionics
- Battery-powered systems
- Communication systems
- Medical equipment

GENERAL DESCRIPTION


The ADG1433 and ADG1434 are monolithic industrial CMOS (iCMOS®) analog switches comprising three independently selectable single-pole, double-throw (SPDT) switches and four independently selectable SPDT switches, respectively.

All channels exhibit break-before-make switching action that prevents momentary shorting when switching channels. An EN input on the ADG1433 (LFCSP and TSSOP) and ADG1434 (LFCSP only) enables or disables the device. When disabled, all channels are switched off.

The iCMOS modular manufacturing process combines high voltage, complementary metal-oxide semiconductor (CMOS), and bipolar technologies. It enables the development of a wide range of high performance analog ICs capable of 33 V operation in a footprint that no other generation of high voltage devices has been able to achieve. Unlike analog ICs using a conventional CMOS process, iCMOS components can tolerate high supply voltages while providing increased performance, dramatically lower power consumption, and reduced package size.

The ultralow on resistance and on resistance flatness of these switches make them ideal solutions for data acquisition and gain switching applications, where low distortion is critical. iCMOS construction ensures ultralow power dissipation, making the devices ideally suited for portable and battery-powered instruments.


FUNCTIONAL BLOCK DIAGRAMS



SWITCHES SHOWN FOR A 1 INPUT LOGIC.

06181-001


Figure 1. ADG1433 TSSOP and LFCSP



SWITCHES SHOWN FOR A 1 INPUT LOGIC.

06181-002

Figure 2. ADG1434 TSSOP



SWITCHES SHOWN FOR A 1 INPUT LOGIC.

06181-101

Figure 3. ADG1434 LFCSP

Rev. E

Document Feedback

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

TABLE OF CONTENTS

Features	1	Absolute Maximum Ratings	7
Applications.....	1	Thermal Resistance	7
General Description	1	ESD Caution.....	7
Functional Block Diagrams.....	1	Pin Configurations and Function Descriptions	8
Revision History	2	Typical Performance Characteristics	10
Specifications.....	3	Test Circuits.....	13
± 15 V Dual Supply	3	Terminology	15
12 V Single Supply.....	5	Outline Dimensions.....	16
± 5 V Dual Supply	6	Ordering Guide	17

REVISION HISTORY

8/2016—Rev. D to Rev. E

Changes to Analog Inputs Parameter and Digital Inputs Parameter, Table 4.....	7
--	---

3/2016—Rev. C to Rev. D

Changed CP-20-4 to CP-20-10 and CP-16-13 to CP-16-26	Throughout
Changes to Figure 5 and Table 6.....	8
Changes to Figure 6, Figure 7, and Table 8	9
Changes to Figure 27	13
Changes to Figure 31, Figure 32, and Figure 33	14
Updated Outline Dimensions	16
Changes to Ordering Guide	17

6/2009—Rev. B to Rev. C

Updated Outline Dimensions	16
Changes to Ordering Guide	17

3/2009—Rev. A to Rev. B

Change to I_{DD} Parameter, Table 1	4
Change to I_{DD} Parameter, Table 2	5
Updated Outline Dimensions, Figure 39	17

6/2008—Rev. 0 to Rev. A

Added Continuous Current per Channel Parameter, Table 1	4
Added Continuous Current per Channel Parameter, Table 2	5
Added Continuous Current per Channel Parameter, Table 3	6
Changes to Table 4	7
Changes to Figure 30	13
Updated Outline Dimensions	16
Changes to Ordering Guide	17

10/2006—Revision 0: Initial Version

SPECIFICATIONS **$\pm 15\text{ V DUAL SUPPLY}$**

$V_{DD} = +15\text{ V} \pm 10\%$, $V_{SS} = -15\text{ V} \pm 10\%$, $GND = 0\text{ V}$, unless otherwise noted.

Table 1.

Parameter	+25°C	-40°C to +85°C	-40°C to +125°C ¹	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range				V	
On Resistance, R_{ON}	4 4.7	5.7	6.7	Ω typ Ω max	$V_S = \pm 10\text{ V}$, $I_S = -10\text{ mA}$; see Figure 25
On Resistance Match Between Channels, ΔR_{ON}	0.5 0.78	0.85	1.1	Ω typ Ω max	$V_{DD} = +13.5\text{ V}$, $V_{SS} = -13.5\text{ V}$
On Resistance Flatness, $R_{FLAT(ON)}$	0.5 0.72	0.77	0.92	Ω typ Ω max	$V_S = \pm 10\text{ V}$, $I_S = -10\text{ mA}$
LEAKAGE CURRENTS					
Source Off Leakage, I_S (Off)	± 0.04 ± 0.3	± 0.6	± 3	nA typ nA max	$V_{DD} = +16.5\text{ V}$, $V_{SS} = -16.5\text{ V}$
Drain Off Leakage, I_D (Off)	± 0.04 ± 0.3	± 0.6	± 3	nA typ nA max	$V_D = \pm 10\text{ V}$, $V_S = \pm 10\text{ V}$; see Figure 26
Channel On Leakage, I_D , I_S (On)	± 0.05 ± 0.4	± 0.8	± 8	nA typ nA max	$V_S = V_D = \pm 10\text{ V}$; see Figure 27
DIGITAL INPUTS					
Input High Voltage, V_{IH}			2.0	V min	
Input Low Voltage, V_{IL}			0.8	V max	
Input Current, I_{IL} or I_{IH}	± 0.005		± 0.1	μA typ μA max	$V_{IN} = V_{GND}$ or V_{DD}
Digital Input Capacitance, C_{IN}	3			pF typ	
DYNAMIC CHARACTERISTICS²					
Transition Time, t_{TRANS}	140 170	200	230	ns typ ns max	$R_L = 100\text{ }\Omega$, $C_L = 35\text{ pF}$
Break-Before-Make Time Delay, t_D	40		30	ns typ ns min	$V_S = 10\text{ V}$, see Figure 28
$t_{ON}(\overline{EN})$	140 170	200	230	ns typ ns max	$R_L = 100\text{ }\Omega$, $C_L = 35\text{ pF}$
$t_{OFF}(\overline{EN})$	60 75	85	90	ns typ ns max	$V_{S1} = V_{S2} = 10\text{ V}$, see Figure 29
Charge Injection	-50			pC typ	$R_L = 100\text{ }\Omega$, $C_L = 35\text{ pF}$
Off Isolation	-70			dB typ	$V_S = 10\text{ V}$, see Figure 30
Channel-to-Channel Crosstalk	-70			dB typ	$R_L = 100\text{ }\Omega$, $C_L = 35\text{ pF}$
Total Harmonic Distortion, THD + N	0.025			% typ	$R_L = 110\text{ }\Omega$, 15V p-p, $f = 20\text{ Hz}$ to 20 kHz , see Figure 34
-3 dB Bandwidth	200			MHz typ	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, see Figure 33
Insertion Loss	0.24			dB typ	$R_L = 50\text{ }\Omega$, $C_L = 5\text{ pF}$, $f = 1\text{ MHz}$, see Figure 33
C_S (Off)	12			pF typ	$f = 1\text{ MHz}$
C_D (Off)	22			pF typ	$f = 1\text{ MHz}$
C_D , C_S (On)	72			pF typ	$f = 1\text{ MHz}$

Parameter	+25°C	-40°C to +85°C	-40°C to +125°C ¹	Unit	Test Conditions/Comments
POWER REQUIREMENTS					
I _{DD}	0.001		1	µA typ µA max	V _{DD} = +16.5 V, V _{SS} = -16.5 V Digital inputs = 0 V or V _{DD}
I _{DD}	260		475	µA typ µA max	Digital inputs = 5 V
I _{SS}	0.001		1	µA typ µA max	Digital inputs = 0 V, 5 V, or V _{DD}
V _{DD} /V _{SS}			±4.5/±16.5	V min/max	GND = 0 V
Continuous Current per Channel ²					V _{DD} = +13.5 V, V _{SS} = -13.5 V
ADG1433	115	75	40	mA max	
ADG1434	100	65	40	mA max	

¹ Temperature range for Y version: -40°C to +125°C.² Guaranteed by design, not subject to production test.

12 V SINGLE SUPPLY

$V_{DD} = 12 \text{ V} \pm 10\%$, $V_{SS} = 0 \text{ V}$, GND = 0 V, unless otherwise noted.

Table 2.

Parameter	+25°C	-40°C to +85°C	-40°C to +125°C ¹	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range				V	
On Resistance, R_{ON}	6	9.5	0 to V_{DD}	Ω typ	$V_S = 0 \text{ V}$ to 10 V, $I_S = -10 \text{ mA}$, see Figure 25
	8		11.2	Ω max	$V_{DD} = 10.8 \text{ V}$, $V_{SS} = 0 \text{ V}$
On Resistance Match Between Channels, ΔR_{ON}	0.55	0.85		Ω typ	$V_S = 0 \text{ V}$ to 10 V, $I_S = -10 \text{ mA}$
	0.82		1.1	Ω max	
On Resistance Flatness, $R_{FLAT(ON)}$	1.5	2.5		Ω typ	$V_S = 0 \text{ V}$ to 10 V, $I_S = -10 \text{ mA}$
	2.5		2.8	Ω max	
LEAKAGE CURRENTS					
Source Off Leakage, I_S (Off)	± 0.04			nA typ	$V_{DD} = 13.2 \text{ V}$
	± 0.3	± 0.6	± 3	nA max	$V_S = 1 \text{ V}/10 \text{ V}$, $V_D = 10 \text{ V}/1 \text{ V}$, see Figure 26
Drain Off Leakage, I_D (Off)	± 0.04			nA typ	$V_S = 1 \text{ V}/10 \text{ V}$, $V_D = 10 \text{ V}/1 \text{ V}$, see Figure 26
	± 0.3	± 0.6	± 3	nA max	
Channel On Leakage, I_D , I_S (On)	± 0.06			nA typ	$V_S = V_D = 1 \text{ V}$ or 10 V, see Figure 27
	± 0.4	± 0.8	± 8	nA max	
DIGITAL INPUTS					
Input High Voltage, V_{IH}			2.0	V min	
Input Low Voltage, V_{IL}			0.8	V max	
Input Current, I_{IL} or I_{IH}	± 0.005		± 0.1	μA typ	$V_{IN} = V_{GND}$ or V_{DD}
Digital Input Capacitance, C_{IN}	4			pF typ	
DYNAMIC CHARACTERISTICS ²					
Transition Time, t_{TRANS}	200			ns typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
	255	310	350	ns max	$V_S = 8 \text{ V}$, see Figure 28
Break-Before-Make Time Delay, t_D	80		55	ns typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
				ns min	$V_{S1} = V_{S2} = 8 \text{ V}$, see Figure 29
$t_{ON}(\overline{EN})$	210			ns typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
	270	320	360	ns max	$V_S = 8 \text{ V}$, see Figure 30
$t_{OFF}(\overline{EN})$	70			ns typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
	86	95	105	ns max	$V_S = 8 \text{ V}$, see Figure 30
Charge Injection	-10			pC typ	$V_S = 6 \text{ V}$, $R_S = 0 \Omega$, $C_L = 1 \text{ nF}$, see Figure 31
Off Isolation	-70			dB typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, $f = 1 \text{ MHz}$, see Figure 32
Channel-to-Channel Crosstalk	-70			dB typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, $f = 1 \text{ MHz}$, see Figure 34
-3 dB Bandwidth	135			MHz typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, see Figure 33
Insertion Loss	0.5			dB typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, $f = 1 \text{ MHz}$, see Figure 33
C_S (Off)	25			pF typ	$f = 1 \text{ MHz}$
C_D (Off)	45			pF typ	$f = 1 \text{ MHz}$
C_D , C_S (On)	80			pF typ	$f = 1 \text{ MHz}$
POWER REQUIREMENTS					
I_{DD}	0.002			μA typ	$V_{DD} = 13.2 \text{ V}$
			1	μA max	Digital inputs = 0 V or V_{DD}
I_{DD}	260		475	μA typ	Digital inputs = 5 V
			5/16.5	μA max	
V_{DD}				V min/max	$V_{SS} = 0 \text{ V}$, GND = 0 V
Continuous Current per Channel ²					$V_{DD} = +10.8 \text{ V}$, $V_{SS} = 0 \text{ V}$
ADG1433	100	65	40	mA max	
ADG1434	85	60	35	mA max	

¹ Temperature range for Y version: -40°C to +125°C.² Guaranteed by design, not subject to production test.

±5 V DUAL SUPPLY

$V_{DD} = +5 \text{ V} \pm 10\%$, $V_{SS} = -5 \text{ V} \pm 10\%$, GND = 0 V, unless otherwise noted.

Table 3.

Parameter	+25°C	-40°C to +85°C	-40°C to +125°C ¹	Unit	Test Conditions/Comments
ANALOG SWITCH					
Analog Signal Range					
On Resistance (R_{ON})	7 9	10.5	12	V Ω typ Ω max	$V_s = \pm 4.5 \text{ V}$, $I_s = -10 \text{ mA}$, see Figure 25
On Resistance Match Between Channels (ΔR_{ON})	0.55 0.78	0.91	1.1	Ω typ Ω max	$V_{DD} = +4.5 \text{ V}$, $V_{SS} = -4.5 \text{ V}$
On Resistance Flatness, $R_{FLAT(ON)}$	1.5 2.5	2.5	3	Ω typ Ω max	$V_s = \pm 4.5 \text{ V}$, $I_s = -10 \text{ mA}$
LEAKAGE CURRENTS					
Source Off Leakage, I_s (Off)	±0.02 ±0.3	±0.6	±3	nA typ nA max	$V_{DD} = +5.5 \text{ V}$, $V_{SS} = -5.5 \text{ V}$
Drain Off Leakage, I_D (Off)	±0.02 ±0.3	±0.6	±3	nA typ nA max	$V_D = \pm 4.5 \text{ V}$, $V_s = \pm 4.5 \text{ V}$, see Figure 26
Channel On Leakage, I_D , I_s (On)	±0.04 ±0.4	±0.8	±8	nA typ nA max	$V_D = \pm 4.5 \text{ V}$, $V_s = \pm 4.5 \text{ V}$, see Figure 26
DIGITAL INPUTS					
Input High Voltage, V_{IH}			2.0	V min	
Input Low Voltage, V_{IL}			0.8	V max	
Input Current, I_{IL} or I_{IH}	±0.005		±0.1	μA typ μA max	$V_{IN} = V_{GND}$ or V_{DD}
Digital Input Capacitance, C_{IN}	4			pF typ	
DYNAMIC CHARACTERISTICS ²					
Transition Time, t_{TRANS}	315 430	480	550	ns typ ns max	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
Break-Before-Make Time Delay, t_D	90		55	ns typ ns min	$V_s = 5 \text{ V}$, see Figure 28
$t_{ON}(\overline{EN})$	325	490	545	ns typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
$t_{OFF}(\overline{EN})$	425 150 200	55	240	ns max ns typ ns max	$V_{S1} = V_{S2} = 5 \text{ V}$, see Figure 29
Charge Injection	-10			pC typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
Off Isolation	-70			dB typ	$V_s = 5 \text{ V}$, see Figure 30
Channel-to-Channel Crosstalk	-70			dB typ	$R_L = 100 \Omega$, $C_L = 35 \text{ pF}$
Total Harmonic Distortion, THD + N	0.06			% typ	$V_s = 0 \text{ V}$, $R_s = 0 \Omega$, $C_L = 1 \text{ nF}$, see Figure 31
-3 dB Bandwidth	145			MHz typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, $f = 1 \text{ MHz}$, see Figure 32
Insertion Loss	0.5			dB typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, $f = 1 \text{ MHz}$, see Figure 34
C_S (Off)	18			pF typ	$R_L = 110 \Omega$, 5 V p-p , $f = 20 \text{ Hz to } 20 \text{ kHz}$, see Figure 35
C_D (Off)	32			pF typ	$R_L = 50 \Omega$, $C_L = 5 \text{ pF}$, see Figure 33
C_D , C_S (On)	80			pF typ	$f = 1 \text{ MHz}$
POWER REQUIREMENTS					
I_{DD}	0.002		1	μA typ μA max	$V_{DD} = +5.5 \text{ V}$, $V_{SS} = -5.5 \text{ V}$
I_{SS}	0.001		1	μA typ μA max	Digital inputs = 0 V, 5 V, or V_{DD}
V_{DD}/V_{SS}			±4.5/±16.5	V min/max	Digital inputs = 0 V, 5 V, or V_{DD}
Continuous Current per Channel ²					
ADG1433	95	60	35	mA max	GND = 0 V
ADG1434	85	55	35	mA max	$V_{DD} = +4.5 \text{ V}$, $V_{SS} = -4.5 \text{ V}$

¹ Temperature range for Y version: -40°C to +125°C.² Guaranteed by design, not subject to production test.

ABSOLUTE MAXIMUM RATINGS

T_A = 25°C, unless otherwise noted.

Table 4.

Parameter	Rating
V _{DD} to V _{SS}	35 V
V _{DD} to GND	-0.3 V to +25 V
V _{SS} to GND	-25 V to +0.3 V
Analog Inputs ¹	V _{SS} – 0.3 V to V _{DD} + 0.3 V or 30 mA (whichever occurs first)
Digital Inputs ¹	GND – 0.3 V to V _{DD} + 0.3 V or 30 mA (whichever occurs first)
Peak Current, S or D (Pulsed at 1 ms, 10% Duty Cycle Maximum)	250 mA
Continuous Current, S or D ²	Data + 15%
Operating Temperature Range Industrial (Y Version)	-40°C to +125°C
Storage Temperature Range	-65°C to +150°C
Junction Temperature	150°C
Reflow Soldering Peak Temperature (Pb-Free)	260 (+ 0 to -5)°C

¹ Overvoltages at A, EN, S, or D pins are clamped by internal diodes. Current must be limited to the maximum ratings given.

² See data given in the Specifications section (see Table 1 to Table 3).

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

Only one absolute maximum rating may be applied at any one time.

THERMAL RESISTANCE

θ_{JA} is specified for the worst-case conditions, that is, a device soldered in a circuit board for surface-mount packages.

Table 5.

Package Type	θ _{JA}	θ _{Jc}	Unit
TSSOP	150.4	50	°C/W
LFCSP	30.4	N/A ¹	°C/W

¹ N/A means not applicable.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS




Figure 4. ADG1433 TSSOP Pin Configuration




Figure 5. ADG1433 LFCSP Pin Configuration

Table 6. ADG1433 Pin Function Descriptions

Pin No.		Mnemonic	Description
TSSOP	LFCSP		
1	15	V _{DD}	Most Positive Power Supply Potential.
2	16	S1A	Source Terminal 1A. Can be an input or an output.
3	1	D1	Drain Terminal 1. Can be an input or an output.
4	2	S1B	Source Terminal 1B. Can be an input or an output.
5	3	S2B	Source Terminal 2B. Can be an input or an output.
6	4	D2	Drain Terminal 2. Can be an input or an output.
7	5	S2A	Source Terminal 2A. Can be an input or an output.
8	6	IN2	Logic Control Input 2.
9	7	IN3	Logic Control Input 3.
10	8	S3A	Source Terminal 3A. Can be an input or an output.
11	9	D3	Drain Terminal 3. Can be an input or an output.
12	10	S3B	Source Terminal 3B. Can be an input or an output.
13	11	V _{SS}	Most Negative Power Supply Potential. In single-supply applications, it can be connected to ground.
14	12	EN	Active Low Digital Input. When high, the device is disabled and all switches are off. When low, INx logic inputs determine the on switches.
15	13	IN1	Logic Control Input 1.
16	14	GND	Ground (0 V) Reference.
N/A ¹	0	EPAD	Exposed Pad. The exposed pad is tied to the substrate, V _{SS} .

¹ N/A means not applicable.

Table 7. ADG1433 Truth Table

EN	INx	SxA	SxB
1	X	Off	Off
0	0	Off	On
0	1	On	Off




Figure 6. ADG1434 TSSOP Pin Configuration




Figure 7. ADG1434 LFCSP Pin Configuration

Table 8. ADG1434 Pin Function Descriptions

Pin No.		Mnemonic	Description
TSSOP	LFCSP		
1	19	IN1	Logic Control Input 1.
2	20	S1A	Source Terminal 1A. Can be an input or an output.
3	1	D1	Drain Terminal 1. Can be an input or an output.
4	2	S1B	Source Terminal 1B. Can be an input or an output.
5	3	V _{SS}	Most Negative Power Supply Potential. In single-supply applications, it can be connected to ground.
6	4	GND	Ground (0 V) Reference.
7	5	S2B	Source Terminal 2B. Can be an input or an output.
8	6	D2	Drain Terminal 2. Can be an input or an output.
9	7	S2A	Source Terminal 2A. Can be an input or an output.
10	8	IN2	Logic Control Input 2.
11	9	IN3	Logic Control Input 3.
12	10	S3A	Source Terminal 3A. Can be an input or an output.
13	11	D3	Drain Terminal 3. Can be an input or an output.
14	12	S3B	Source Terminal 3B. Can be an input or an output.
15	N/A ¹	NIC	No Internal Connection.
16	13	V _{DD}	Most Positive Power Supply Potential.
17	14	S4B	Source Terminal 4B. Can be an input or an output.
18	15	D4	Drain Terminal 4. Can be an input or an output.
19	16	S4A	Source Terminal 4A. Can be an input or an output.
20	17	IN4	Logic Control Input 4.
N/A ¹	18	EN	Active Low Digital Input. When high, the device is disabled and all switches are off. When low, INx logic inputs determine the on switches.
N/A ¹	0	EPAD	Exposed Pad. The exposed pad is tied to the substrate, V _{SS} .

¹ N/A means not applicable.







Table 9. ADG1434 TSSOP Truth Table







INx	SxA	SxB
0	Off	On
1	On	Off






Table 10. ADG1434 LFCSP Truth Table

EN	INx	SxA	SxB
1	X	Off	Off
0	0	Off	On
0	1	On	Off


TYPICAL PERFORMANCE CHARACTERISTICS

Figure 8. On Resistance as a Function of V_D (V_S), Dual SupplyFigure 11. On Resistance as a Function of V_D (V_S) for Different Temperatures, ±15 V Dual SupplyFigure 9. On Resistance as a Function of V_D (V_S), Dual SupplyFigure 12. On Resistance as a Function of V_D (V_S) for Different Temperatures, ±5 V Dual SupplyFigure 10. On Resistance as a Function of V_D (V_S), Single SupplyFigure 13. On Resistance as a Function of V_D (V_S) for Different Temperatures, 12 V Single Supply







TEST CIRCUITS



06181-021




06181-022




06181-023


NIC = NO INTERNAL CONNECTION.



06181-024



06181-025



06181-026





Figure 31. Charge Injection


06181-027



NIC = NO INTERNAL CONNECTION.

Figure 32. Off Isolation


06181-028




NIC = NO INTERNAL CONNECTION.

Figure 33. Bandwidth

06181-029

CHANNEL TO CHANNEL CROSSTALK = $20 \log \frac{V_{OUT}}{V_S}$

06181-030

 $THD + NOISE = V_S\ p-p$

06181-031

TERMINOLOGY

R_{ON}

Ohmic resistance between Terminal D and Terminal S.

ΔR_{ON}

The difference between the R_{ON} of any two channels.

R_{FLAT(ON)}

The difference between the maximum and minimum value of on resistance as measured.

I_s (Off)

Source leakage current when the switch is off.

I_D (Off)

Drain leakage current when the switch is off.

I_D, I_s (On)

Channel leakage current when the switch is on.

V_D (V_s)

Analog voltage on Terminal D and Terminal S.

C_s (Off)

Channel input capacitance for off condition.

C_D (Off)

Channel output capacitance for off condition.

C_D, C_s (On)

On switch capacitance.

C_{IN}

Digital input capacitance.

t_{ON} (EN̄)

Delay time between the 50% and 90% points of the digital input and switch on condition.

t_{OFF} (EN̄)

Delay time between the 50% and 90% points of the digital input and switch off condition.

t_{TRANS}

Delay time between the 50% and 90% points of the digital inputs and the switch on condition when switching from one address state to another.

t_{BBM}

Off time measured between the 80% point of both switches when switching from one address state to another.

V_{IL}

Maximum input voltage for Logic 0.

V_{IH}

Minimum input voltage for Logic 1.

I_{IL} (I_{IH})

Input current of the digital input.

I_{DD}

Positive supply current.

I_{SS}

Negative supply current.

Off Isolation

A measure of unwanted signal coupling through an off channel.

Charge Injection

A measure of the glitch impulse transferred from the digital input to the analog output during switching.

Bandwidth

The frequency at which the output is attenuated by 3 dB.

On Response

The frequency response of the on switch.

Total Harmonic Distortion + Noise (THD + N)

The ratio of the harmonic amplitude plus noise of the signal to the fundamental.

AC Power Supply Rejection Ratio (ACPSRR)

A measure of the ability of a device to avoid coupling noise and spurious signals that appear on the supply voltage pin to the output of the switch. The dc voltage on the device is modulated by a sine wave of 0.62 V p-p. The ratio of the amplitude of signal on the output to the amplitude of the modulation is the ACPSRR.

OUTLINE DIMENSIONS





Figure 36. 16-Lead Thin Shrink Small Outline Package [TSSOP]
(RU-16)

Dimensions shown in millimeters



COMPLIANT TO JEDEC STANDARDS MO-220-WGGC.

Figure 37. 16-Lead Lead Frame Chip Scale Package [LFCSP]
4 mm × 4 mm Body and 0.75 mm Package Height
(CP-16-26)

Dimensions shown in millimeters




Figure 38. 20-Lead Thin Shrink Small Outline Package [TSSOP]
(RU-20)

Dimensions shown in millimeters




Figure 39. 20-Lead Lead Frame Chip Scale Package [LFCSP]
4 mm × 4 mm Body and 0.75 mm Package Height
(CP-20-10)

061609-B

ORDERING GUIDE

Model ¹	Temperature Range	Description	EN Pin	Package Option
ADG1433YRUZ	-40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	Yes	RU-16
ADG1433YRUZ-REEL	-40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	Yes	RU-16
ADG1433YRUZ-REEL7	-40°C to +125°C	16-Lead Thin Shrink Small Outline Package [TSSOP]	Yes	RU-16
ADG1433YCPZ-REEL	-40°C to +125°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	Yes	CP-16-26
ADG1433YCPZ-REEL7	-40°C to +125°C	16-Lead Lead Frame Chip Scale Package [LFCSP]	Yes	CP-16-26
ADG1434YRUZ	-40°C to +125°C	20-Lead Thin Shrink Small Outline Package [TSSOP]	No	RU-20
ADG1434YRUZ-REEL	-40°C to +125°C	20-Lead Thin Shrink Small Outline Package [TSSOP]	No	RU-20
ADG1434YRUZ-REEL7	-40°C to +125°C	20-Lead Thin Shrink Small Outline Package [TSSOP]	No	RU-20
ADG1434YCPZ-REEL	-40°C to +125°C	20-Lead Lead Frame Chip Scale Package [LFCSP]	Yes	CP-20-10
ADG1434YCPZ-REEL7	-40°C to +125°C	20-Lead Lead Frame Chip Scale Package [LFCSP]	Yes	CP-20-10

¹ Z = RoHS Compliant Part.

NOTES

NOTES

NOTES