Notice for TAIYO YUDEN Products

[For High Quality and/or Reliability Equipment (Automotive Electronic Equipment / Industrial Equipment)]

Please read this notice before using the TAIYO YUDEN products.

!\ REMINDERS

Product information in this catalog is as of October 2018. All of the contents specified herein are subject to change without notice due to technical improvements, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

- Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available.
- Please conduct validation and verification of our products in actual condition of mounting and operating environment before using our products.
- The products listed in this catalog are intended for use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment), medical equipment classified as Class I or II by IMDRF, industrial equipment, and automotive interior applications, etc. Please be sure to contact TAIYO YUDEN for further information before using the products for any equipment which may directly cause loss of human life or bodily injury (e.g., transportation equipment including, without limitation, automotive powertrain control system, train control system, and ship control system, traffic signal equipment, medical equipment classified as Class III by IMDRF).

Please do not incorporate our products into any equipment requiring high levels of safety and/or reliability (e.g., aerospace equipment, aviation equipment*, medical equipment classified as Class IV by IMDRF, nuclear control equipment, undersea equipment, military equipment).

*Note: There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.

When our products are used even for high safety and/or reliability-required devices or circuits of general electronic equipment, it is strongly recommended to perform a thorough safety evaluation prior to use of our products and to install a protection circuit as necessary.

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

- Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.
- Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a fault or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement.
- The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.
- Caution for Export
 Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

Automotive Application Guide

We classify automotive electronic equipment into the following four application categories and set usable application categories for each of our products. When using our products for automotive electronic equipment, please be sure to check such application categories and use our products accordingly. Should you have any questions on this matter, please contact us.

| Category | Automotive Electronic Equipment (Typical Example) |
|----------------|--|
| | Engine ECU (Electronically Controlled Fuel Injector) |
| | Cruise Control Unit |
| | • 4WS (4 Wheel Steering) |
| POWERTRAIN | Automatic Transmission |
| | Power Steering |
| | HEV/PHV/EV Core Control (Battery, Inverter, DC-DC) |
| | Automotive Locator (Car location information providing device), etc. |
| | ABS (Anti-Lock Brake System) |
| SAFETY | • ESC (Electronic Stability Control) |
| SALLII | • Airbag |
| | ADAS (Equipment that directly controls running, turning and stopping), etc. |
| | • Wiper |
| | Automatic Door |
| | • Power Window |
| | Keyless Entry System |
| BODY & CHASSIS | • Electric Door Mirror |
| | • Interior Lighting |
| | • LED Headlight |
| | • TPMS (Tire Pressure Monitoring System) |
| | Anti-Theft Device (Immobilizer), etc. |
| | Car Infotainment System |
| INFOTAINMENT | • ITS/Telematics System |
| | • Instrument Cluster |
| | • ADAS (Sensor, Equipment that is not interlocked with safety equipment or powertrain), etc. |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

MULTILAYER CERAMIC CAPACITORS





■PART NUMBER

| J | М | K | 3 | 1 | 6 | Δ | В | J | 1 | 0 | 6 | М | L | Н | Т | Δ |
|---|---|---|---|---|---|----------|---|---|---|---|---|---|---|----|-----|----|
| 1 | 2 | 3 | | 4 | | 5 | (| 3 | | 7 | | 8 | 9 | 10 | 11) | 12 |

△=Blank space

| (1)Rate | d voltage |
|---------|-----------|
| | |

| Code | Rated voltage[VDC] |
|------|--------------------|
| Α | 4 |
| J | 6.3 |
| L | 10 |
| Е | 16 |
| Т | 25 |
| G | 35 |
| U | 50 |
| Н | 100 |
| Q | 250 |
| S | 630 |

3End termination

| Code | End termination | | | | | |
|--------------------------------|---|--|--|--|--|--|
| K | Plated | | | | | |
| J | Soft Termination | | | | | |
| S | Cu Internal Electrodes (For High Frequency) | | | | | |
| F High Reliability Application | | | | | | |

| | Z/Series name | |
|---|---------------|---|
| | Code | Series name |
| Ī | М | Multilayer ceramic capacitor |
| | V | Multilayer ceramic capacitor for high frequency |
| | W | LW reverse type multilayer capacitor |

(4) Dimension (1 x W)

| (| 4)Dimension (L X | (W) | |
|---|------------------|----------------------|------------|
| | Туре | Dimensions (L×W)[mm] | EIA (inch) |
| | 063 | 0.6 × 0.3 | 0201 |
| | 105 | 1.0 × 0.5 | 0402 |
| | | 0.52 × 1.0 ※ | 0204 |
| | 107 | 1.6 × 0.8 | 0603 |
| | | 0.8 × 1.6 ※ | 0306 |
| | 010 | 2.0 × 1.25 | 0805 |
| | 212 | 1.25 × 2.0 💥 | 0508 |
| | 316 | 3.2 × 1.6 | 1206 |
| | 325 | 3.2 × 2.5 | 1210 |
| | 432 | 4.5 × 3.2 | 1812 |
| | | | |

Note: ※LW reverse type(□WK) only

5Dimension tolerance

| Code | Туре | L[mm] | W[mm] | T[mm] |
|------|------|-----------------|---------------------|-----------------|
| Δ | ALL | Standard | Standard | Standard |
| | 063 | 0.6±0.05 | 0.3±0.05 | 0.3±0.05 |
| | 105 | 1.0±0.10 | 0.5±0.10 | 0.5±0.10 |
| | 107 | 1.6+0.15/-0.05 | 0.8+0.15/-0.05 | 0.8+0.15/-0.05 |
| Α | 212 | 2.0+0.15/-0.05 | 1.25+0.15/-0.05 | 0.85±0.10 |
| | 212 | 2.0+0.15/ -0.05 | 1.25 + 0.15/ - 0.05 | 1.25+0.15/-0.05 |
| | 316 | 3.2±0.20 | 1.6±0.20 | 1.6±0.20 |
| | 325 | 3.2±0.30 | 2.5±0.30 | 2.5±0.30 |
| | 105 | 1.0+0.15/-0.05 | 0.5+0.15/-0.05 | 0.5+0.15/-0.05 |
| | 107 | 1.6+0.20/-0 | 0.8+0.20/-0 | 0.8+0.20/-0 |
| В | 212 | 2.0+0.20/-0 | 1.25+0.20/-0 | 0.85±0.10 |
| | 212 | 2.0+0.20/ -0 | 1.25 + 0.20/ - 0 | 1.25+0.20/-0 |
| | 316 | 3.2±0.30 | 1.6±0.30 | 1.6±0.30 |
| | 105 | 1.0+0.20/-0 | 0.5+0.20/-0 | 0.5+0.20/-0 |
| С | 107 | 1.6+0.25/-0 | 0.8+0.25/-0 | 0.8+0.25/-0 |
| | 212 | 2.0+0.25/-0 | 1.25+0.25/-0 | 1.25+0.25/-0 |
| | 212 | 2.0±0.15 | 1.25±0.15 | 0.85±0.15 |
| K | 316 | 3.2±0.20 | 1.6±0.20 | 1.15±0.20 |
| r. | 310 | 3.2 ± 0.20 | 1.0 ± 0.20 | 1.6±0.20 |
| | 325 | 3.2±0.50 | 2.5±0.30 | 2.5±0.30 |

Note: cf. STANDARD EXTERNAL DIMENSIONS

Δ= Blank space

6Temperature characteristics code

■ High dielectric type

| Code | Applicable | | Applicable standard | | | | Temperature range[°C] | Ref. Temp.[°C] | Capacitance change | Capacitance tolerance | Tolerance code |
|------|------------|----------------------|---------------------|-------------------|----------------|-----------|--------------------------|----------------|--------------------|--------------------------|-------------------|
| | | | | 0.5 | 1.450/ | ±10% | K | | | | |
| BJ | EIA | X5R | −55 ~ + 85 | 25 | ±15% | ±20% | М | | | | |
| C6 | EIA | X6S | -55 ~ +105 | 25 | ±22% | ±10% | K | | | | |
| | LIA | 703 | 33.4 103 | 23 | ±2270 | ±20% | М | | | | |
| В7 | EIA | X7R -55~+125 25 ±15% | ±10% | K | | | | | | | |
| | LIA | 7/1 | 33.4 1 123 | 23 | ±1370 | ±20% | М | | | | |
| C7 | EIA | X7S | -55 ~ +125 | 25 | ±22% | ±10% | K | | | | |
| | LIA | 7/3 | 33.4 1 123 | 23 | ± 22% | ±20% | М | | | | |
| D7 E | EIA | FIA V7T | EIA X7T −55~+125 | -55 ~ +125 | 25 | +22%/-33% | ±10% | K | | | |
| | ĭ | A/1 | 35.4 1 123 | 25 | 1 22 70/ 33 70 | ±20% | М | | | | |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

■Temperature compensating type

| Code | | cable dard | Temperature range [°C] | Ref. Temp.[°C] | Capacitance change | Capacitance tolerance | Tolerance code |
|------|-----|---------------|------------------------|----------------|--------------------|--------------------------|-------------------|
| | | | | | | ±0.1pF | В |
| | JIS | CG | | 20 | | ±0.25pF | С |
| CG | | | -55 ~ +125 | | 0±30ppm/°C | ±0.5pF | D |
| CG | | | -55~+125 | | | ±1pF | F |
| | EIA | C0G | | 25 | | ±2% | G |
| | | | | | | ±5% | J |

7Nominal capacitance

| Code (example) | Nominal capacitance |
|-------------------|---------------------|
| 0R5 | 0.5pF |
| 010 | 1pF |
| 100 | 10pF |
| 101 | 100pF |
| 102 | 1,000pF |
| 103 | 0.01 <i>μ</i> F |
| 104 | 0.1 μ F |
| 105 | 1.0 <i>μ</i> F |
| 106 | 10 μ F |
| 107 | 100 μ F |

Note : R=Decimal point

8 Capacitance tolerance

| Code | Capacitance tolerance |
|------|-----------------------|
| Α | ±0.05pF |
| В | ±0.1pF |
| С | ±0.25pF |
| D | ±0.5pF |
| G | ±2% |
| J | ±5% |
| K | ±10% |
| М | ±20% |

Thickness

| Code | Thickness[mm] |
|------|-----------------------|
| Р | 0.3 |
| Т | 0.3 |
| V | 0.5 |
| С | 0.7(107type or more) |
| Α | 0.8 |
| D | 0.85(212type or more) |
| F | 1.15 |
| G | 1.25 |
| L | 1.6 |
| N | 1.9 |
| M | 2.5 |

®Special code

| Code | Special code |
|------|------------------------------------|
| Н | MLCC for Industrial and Automotive |


11)Packaging


| O: | | | | | | | | | |
|------|--|--|--|--|--|--|--|--|--|
| Code | Packaging | | | | | | | | |
| F | ϕ 178mm Taping (2mm pitch) | | | | | | | | |
| R | ϕ 178mm Embossed Taping (4mm pitch) | | | | | | | | |
| Т | φ 178mm Taping (4mm pitch) | | | | | | | | |
| P | ϕ 178mm Taping (4mm pitch, 1000 pcs/reel) | | | | | | | | |
| • | 325 type (Thickness code M) | | | | | | | | |

12Internal code

| G. Internal Socie | | | | | | | | | | |
|-------------------|---------------|--|--|--|--|--|--|--|--|--|
| Code | Internal code | | | | | | | | | |
| Δ | Standard | | | | | | | | | |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).





| | | Dime | nsion [mm] (inch) | | | |
|------------------------------|----------------------------|----------------------------|----------------------------|----|--|--|
| Type(EIA) | L | W | T | *1 | е | |
| □MK063(0201) | 0.6±0.03 (0.024±0.001) | 0.3±0.03 (0.012±0.001) | 0.3±0.03 (0.012±0.001) | Т | 0.15±0.05 (0.006±0.002) | |
| □MK105(0402) □MF105(0402) | 1.0±0.05 (0.039±0.002) | 0.5±0.05 (0.020±0.002) | 0.5±0.05 (0.020±0.002) | ٧ | 0.25±0.10 (0.010±0.004) | |
| □WK105(0204)※ | 0.52±0.05 (0.020±0.002) | 1.0±0.05 (0.039±0.002) | 0.3±0.05 (0.012±0.002) | Р | 0.18±0.08 (0.007±0.003) | |
| □MK107(0603) □MF107(0603) | 1.6±0.10 (0.063±0.004) | 0.8±0.10 (0.031±0.004) | 0.8±0.10 (0.031±0.004) | Α | 0.35±0.25 (0.014±0.010) | |
| □MJ107(0603) | 1.6±0.10 (0.063±0.004) | 0.8±0.10 (0.031±0.004) | 0.8±0.10 (0.031±0.004) | Α | 0.35+0.3/-0.25 (0.014+0.012/-0.010) | |
| □VS107(0603) | 1.6±0.10 (0.063±0.004) | 0.8±0.10 (0.031±0.004) | 0.7±0.10 (0.028±0.004) | С | 0.35±0.25 (0.014±0.010) | |
| □WK107(0306)※ | 0.8±0.10 (0.031±0.004) | 1.6±0.10 (0.063±0.004) | 0.5±0.05 (0.020±0.002) | ٧ | 0.25±0.15 (0.010±0.006) | |
| □MK212(0805) | 2.0±0.10 | 1.25±0.10 | 0.85±0.10 (0.033±0.004) | D | 0.5±0.25 | |
| □MF212(0805) | (0.079±0.004) | (0.049±0.004) | 1.25±0.10 (0.049±0.004) | G | (0.020±0.010) | |
| | 2.0±0.10 | 1.25±0.10 | 0.85±0.10 (0.033±0.004) | D | 0.5+0.35/-0.25 | |
| □MJ212(0805) | (0.079 ± 0.004) | (0.049±0.004) | 1.25±0.10 (0.049±0.004) | G | (0.020+0.014/-0.010) | |
| □VS212(0805) | 2.0±0.10 (0.079±0.004) | 1.25±0.10 (0.049±0.004) | 0.85±0.10 (0.033±0.004) | D | 0.5±0.25 (0.020±0.010) | |
| □WK212(0508)※ | 1.25±0.15 (0.049±0.006) | 2.0±0.15 (0.079±0.006) | 0.85±0.10 (0.033±0.004) | D | 0.3±0.2 (0.012±0.008) | |
| □MK316(1206) | 3.2±0.15 | 1.6±0.15 | 1.15±0.10 (0.045±0.004) | F | 0.5+0.35/-0.25 | |
| □MF316(1206) | (0.126 ± 0.006) | (0.063±0.006) | 1.6±0.20 (0.063±0.008) | L | (0.020+0.014/-0.010) | |
| □MJ316(1206) | 3.2±0.15 | 1.6±0.15 | 1.15±0.10 (0.045±0.004) | F | 0.6+0.4/-0.3 | |
| ШМЈ316(1206) | (0.126±0.006) | (0.063±0.006) | 1.6±0.20 (0.063±0.008) | L | (0.024+0.016/-0.012) | |
| | | | 1.15±0.10 (0.045±0.004) | F | | |
| □MK325(1210) □MF325(1210) | 3.2±0.30 (0.126±0.012) | 2.5±0.20 (0.098±0.008) | 1.9±0.20 (0.075±0.008) | N | 0.6±0.3 (0.024±0.012) | |
| | | | 098±0.008) | | | |
| ПМ 1225 (1210) | 3.2±0.30 | 2.5±0.20 | 1.9±0.20 (0.075±0.008) | N | 0.6+0.4/-0.3 | |
| □MJ325(1210) | (0.126±0.012) | (0.098±0.008) | 2.5±0.20 (0.098±0.008) | М | (0.024 + 0.016 / -0.012) | |
| □MK432(1812) | 4.5±0.40 | 3.2±0.30 | 2.5±0.20 | М | 0.9±0.6 | |

 (0.098 ± 0.008)

 (0.035 ± 0.024)

(0.177±0.016) (0.126 ± 0.012) Note : X. LW reverse type, *1.Thickness code

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

STANDARD QUANTITY

| Time | EIA (inch) | Dime | nsion | Standard qu | uantity[pcs] |
|------|------------|------|-------|--------------------|--------------------|
| Type | EIA (Inch) | [mm] | Code | Paper tape | Embossed tape |
| 063 | 0201 | 0.3 | Т | 15000 | _ |
| 105 | 0402 | 0.5 | ٧ | 10000 | |
| 105 | 0204 ※ | 0.30 | Р | 10000 | _ |
| | | 0.7 | С | 4000 | _ |
| | | 0.8 | Α | 4000 | _ |
| | 0603 | 0.8 | Α | 3000 | |
| 107 | 0003 | 0.8 | A | (Soft Termination) | |
| | | 0.8 | А | _ | 3000 |
| | | 0.0 | A | _ | (Soft Termination) |
| | 0306 ※ | 0.50 | ٧ | _ | 4000 |
| | | 0.85 | D | 4000 | _ |
| | 0805 | 1.25 | G | Paper tape | 3000 |
| 212 | 0803 | 1.25 | G | | 2000 |
| | | 1.20 | G | _ | (Soft Termination) |
| | 0508 ※ | 0.85 | D | 4000 | _ |
| 316 | 1006 | 1.15 | F | _ | 3000 |
| 310 | 1206 | 1.6 | L | _ | 2000 |
| | | 1.15 | F | | 2000 |
| 325 | 1210 | 1.9 | N | _ | 2000 |
| | | 2.5 | М | _ | 500(T), 1000(P) |
| 432 | 1812 | 2.5 | М | _ | 500 |

Note: ※.LW Reverse type(□WK)

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

- · All the Multilayer Ceramic Capacitors of the catalog lineup are RoHS compliant.
- Capacitance tolerance code is applied to □ of part number.
- · All the Multilayer Ceramic Capacitors in the catalog lineup are applicable for reflow-soldering.

Note)

- The exchange of individual specifications is necessary depending on the application and circuit condition. Please contact Taiyo Yuden sales channels.
- *1: Automotive (AEC-Q200 Qualified) products for BODY & CHASSIS, and INFOTAINMENT. Please check "Automotive Application Guide" for further details before using the products.

All the Multilayer Ceramic Capacitors of *1 marks are tested based on the test conditions and methods defined in AEC-Q200 by family item.

125°C products: AEC-Q200 Grade1 (we conduct the evaluation at the test condition of Grade1.) 105°C products: AEC-Q200 Grade2 (we conduct the evaluation at the test condition of Grade2.)

85°C products: AEC-Q200 Grade3 (we conduct the evaluation at the test condition of Grade3.)

Please consult with TAIYO YUDEN's official sales channel for the details of the product specification and AEC-Q200 test results, etc.,

and please review and approve TAIYO YUDEN's product specification before ordering.

- *2: Industrial products and Medical products
- *3: For standard case size, please kindly refer to @Dimension, @Dimension tolerance, @Thickness and STANDARD EXTERNAL DIMENSIONS.

Multilayer Ceramic Capacitors (High dielectric type)

●105TYPE (Demension:1.0 × 0.5mm JIS:1005 EIA:0402)

[Temperature Characteristic BJ: $X5R(-55\sim+85^{\circ}C)$] 0.5mm thickness(V)

| Part number 1 | Part number 2 | Rated voltage | Temper characte | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|--------------------------------------|---------------|---------------|--|------------|--------------------|------------------------------|--------------|------------------------|----------------------------|--------|
| UMK105 BJ471 VHF | | 2.3 | | X5R | 470 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ471 VHF | | + | - | X5R X5R | 1000 p | ±10, ±20 ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ152 VHF | | | | X5R X5R | 1500 p | | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| | | | | X5R X5R | | ±10, ±20 | | 200 | | *1, *2 |
| UMK105 BJ222 VHF | | 4 | | | 2200 p | ±10, ±20 | 2.5 | | 0.5±0.05 | |
| UMK105 BJ332 VHF | | | - | X5R | 3300 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ472 VHF | | 50 | | X5R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ682 VHF | | 4 | | X5R | 6800 p | ±10, ±20 | 2.5 | 150 | 0.5±0.05 | *1, *2 |
| UMK105 BJ103 VHF | | 4 | | X5R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ223 VHF | | 4 | | X5R | 0.022 μ | ±10, ±20 | 5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ473 VHF | | 4 | | X5R | 0.047 μ | ±10, ±20 | 5 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 BJ104 VHF | | | | X5R | 0.1 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 BJ472[VHF | | 4 | | X5R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| TMK105 BJ682[]VHF | | 4 | | X5R | 6800 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| TMK105 BJ103[VHF | | 1 | | X5R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 BJ153[VHF | | 1 | | X5R | 0.015 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 BJ223[VHF | | 25 | | X5R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 BJ333[]VHF | | 1 20 | | X5R | 0.033 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 BJ473[VHF | | 1 | | X5R | 0.047 μ | $\pm 10, \pm 20$ | 3.5 | 150 | 0.5 ± 0.05 | *1, *2 |
| TMK105 BJ104[]VHF | | 1 | | X5R | 0.1 μ | $\pm 10, \pm 20$ | 5 | 150 | 0.5 ± 0.05 | *1, *2 |
| TMK105 BJ224[VHF | | 1 | | X5R | 0.22 μ | $\pm 10, \pm 20$ | 10 | 150 | 0.5 ± 0.05 | *1, *2 |
| TMK105ABJ474[]VHF | | | | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.10 | *1, *2 |
| EMK105 BJ103 VHF | | | | X5R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| EMK105 BJ153 VHF | | Ī | | X5R | 0.015 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| EMK105 BJ223∏VHF | | Ī | | X5R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| EMK105 BJ333 UHF | | Ī | | X5R | 0.033 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 BJ473 UHF | | 16 | | X5R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 BJ104∏VHF | | 1 | | X5R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 BJ224 VHF | | 1 | | X5R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| EMK105ABJ474∏VHF | | 1 | | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.10 | *1. *2 |
| EMK105 BJ105∏VHF | | † | | X5R | 1 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1. *2 |
| LMK105 BJ333∏VHF | | | | X5R | 0.033 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| LMK105 BJ473∏VHF | | 1 | | X5R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| LMK105 BJ104∏VHF | | 1 | | X5R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1. *2 |
| LMK105 BJ224 VHF | | 10 | | X5R | 0.22 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1. *2 |
| LMK105ABJ474∏VHF | | † '- | | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.10 | *1, *2 |
| LMK105 BJ105∏VHF | | † | | X5R | 1 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| LMK105ABJ225∏VHF | | † | | X5R | 2.2 µ | ±10, ±20 | 10 | 150 | 0.5±0.10 | *1, *2 |
| JMK105 BJ104∏VHF | | | + | X5R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 BJ224 VHF | | † | | X5R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 BJ474 VHF | | † | h | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 BJ474 VHF | | 6.3 | | X5R | 1 μ | ±10, ±20 ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 BJ105UVHF | | | | X5R X5R | 2.2 μ | ±10, ±20 ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 BJ225UVHF JMK105BBJ475MVHF | | + | - | X5R X5R | 2.2 μ | ±10, ±20 ±20 | 10 | 150 | 0.5±0.05 0.5+0.15/-0.05 | *1, *2 |
| AMK105BBJ475MVHF | | 1 | - | X5R X5R | 4.7 μ 2.2 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| AMK105 BJ225UVHF AMK105BBJ475MVHF | | 4 | | X5R X5R | | | 10 | 150 | 0.5±0.05 0.5+0.15/-0.05 | , |
| AMK105BBJ475MVHF AMK105CBJ106MVHF | | | | X5R X5R | 4.7 μ | ±20 | 10 | 150 | | *1, *2 |
| AMV 102CR3 100MAHE | | 1 | | XSK | 10 μ | ±20 | 10 | 150 | 0.5+0.20/-0 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 0.5mm thickness(V)

| Part number 1 | Part number 2 | Rated voltage | Tempera | | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|----------|---------|-------------|---------------|-------------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | characte | ristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| UMK105 B7221 □VHF | | | | X7R | 220 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7331 □VHF | | | | X7R | 330 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7471 □VHF | | | | X7R | 470 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7681 □VHF | | | | X7R | 680 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7102 UVHF | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7152 UVHF | | | | X7R | 1500 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7222 ☐VHF | | 50 | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7332 UHF | | 50 | | X7R | 3300 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7472 UHF | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 150 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7682 ☐VHF | | | | X7R | 6800 p | ±10, ±20 | 2.5 | 150 | 0.5 ± 0.05 | *1, *2 |
| UMK105 B7103 UHF | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| UMK105 B7223 UHF | | | | X7R | 0.022 μ | ±10, ±20 | 10 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 B7473 UHF | | | | X7R | 0.047 μ | ±10, ±20 | 10 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 B7104 UHF | | | | X7R | 0.1 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 B7472 UHF | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 B7682 UHF | | | | X7R | 6800 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 B7103 UHF | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| TMK105 B7153 UHF | | 25 | | X7R | 0.015 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 B7223 UHF | | 25 | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 B7333 UHF | | | | X7R | 0.033 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 B7473 UHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| TMK105 B7104 UHF | | | | X7R | 0.1 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 B7103 UHF | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5±0.05 | *1, *2 |
| EMK105 B7153 VHF | | | | X7R | 0.015 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 B7223 UHF | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 B7333 □VHF | | 16 | | X7R | 0.033 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 B7473 UHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| EMK105 B7104 UHF | | | | X7R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5 ± 0.05 | *1, *2 |
| EMK105 B7224 UHF | | | | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.5 ± 0.05 | *1, *2 |
| LMK105 B7473 VHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5±0.05 | *1, *2 |
| LMK105 B7104[]VHF | | 10 | | X7R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| LMK105 B7224 VHF | | 1 | | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 B7104[]VHF | | | | X7R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| JMK105 B7224[]VHF | | 6.3 | | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1. *2 |
| JMK105 B7474[]VHF | | 1 | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| AMK105 B7474□VHF | | 4 | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

【Temperature Characteristic BJ : X5R(−55~+85°C)】 0.8mm thickness(A)

| Part number 1 | Part number 2 | Rated voltage [V] | Tempe charact | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|-------------------|---------------|----------------------|------------------|-----|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| JMK107 BJ104[]AHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| JMK107 BJ224[]AHT | | 50 | | X5R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| JMK107 BJ474∏AHT | | 30 | | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| JMK107ABJ105[AHT | | | | X5R | 1 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| GMK107 BJ223∏AHT | | | | X5R | 0.022 μ | ±10, ±20 | 2.5 | 200 | 0.8 ± 0.10 | *1, *2 |
| GMK107 BJ473∏AHT | | | | X5R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8 ± 0.10 | *1, *2 |
| GMK107 BJ104∏AHT | | 35 | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, *2 |
| GMK107 BJ224∏AHT | | - 35 | | X5R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| GMK107ABJ474∏AHT | | | | X5R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| GMK107 BJ105∏AHT | | | | X5R | 1 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| MK107 BJ223[AHT | | | | X5R | 0.022 μ | ±10, ±20 | 2.5 | 200 | 0.8±0.10 | *1, *2 |
| MK107 BJ473[AHT | | | | X5R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| MK107 BJ104 AHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, * |
| MK107 BJ224 AHT | | 25 | | X5R | 0.22 μ | ±10, ±20 | 5 | 150 | 0.8 ± 0.10 | *1, * |
| MK107 BJ474[AHT | | | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, *2 |
| MK107 BJ105∏AHT | | | | X5R | 1 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| MK107BBJ225∏AHT | | | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| MK107 BJ104[AHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, * |
| MK107 BJ224 AHT | | | | X5R | 0.22 μ | ±10, ±20 | 5 | 150 | 0.8±0.10 | *1, * |
| MK107 BJ474[AHT | | 16 | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| MK107 BJ105 AHT | | 16 | | X5R | 1 μ | ±10, ±20 | 5 | 150 | 0.8±0.10 | *1, *2 |
| MK107ABJ225[AHT | | | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| MK107BBJ475[AHT | | | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| MK107 BJ474[AHT | | | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, *2 |
| MK107 BJ105[AHT | | | | X5R | 1 μ | ±10, ±20 | 5 | 150 | 0.8 ± 0.10 | *1, *2 |
| .MK107 BJ225[]AHT | | 10 | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, * |
| .MK107 BJ475[]AHT | | | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, * |
| MK107BBJ106MAHT | | | | X5R | 10 μ | ±20 | 10 | 150 | 0.8+0.20/-0 | *1, * |
| IMK107 BJ105∏AHT | | | | X5R | 1 μ | ±10, ±20 | 5 | 150 | 0.8±0.10 | *1, *2 |
| IMK107 BJ225∏AHT | | | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| IMK107 BJ475∏AHT | | 6.3 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| JMK107ABJ106∏AHT | | 7 | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| AMK107ABJ106∏AHT | | 4 | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| AMK107BBJ226MAHT | | 4 | | X5R | 22 μ | ±20 | 10 | 150 | 0.8+0.20/-0 | *1. *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : X7R($-55 \sim +125^{\circ}$ C), C7 : X7S($-55 \sim +125^{\circ}$ C), D7 : X7T($-55 \sim +125^{\circ}$ C)] 0.8mm thickness(A)

| L terriperature errara | Controlle By TytyTtt | 00 1 120 | e,, e, i,,,,e, | 00 1 120 07, | B / 1 / (/) () | , | 2 0.0 | 000 (7 17 | |
|------------------------|----------------------|---------------|-----------------|--------------|-------------------|-------|-------------------|------------------|--------|
| D | D | Rated voltage | Temperature | Capacitance | Capacitance | tan δ | HTLT | *3 - 7 | N1 . |
| Part number 1 | Part number 2 | [V] | characteristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| UMK107 B7102∏AHT | | | X7R | 1000 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7152∏AHT | | | X7R | 1500 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7222∏AHT | | 1 | X7R | 2200 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7332∏AHT | | | X7R | 3300 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7472∏AHT | | | X7R | 4700 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7682∏AHT | | | X7R | 6800 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7103∏AHT | | 50 | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7153∏AHT | | 30 | X7R | 0.015 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7223∏AHT | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7333∏AHT | | | X7R | 0.033 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7473[]AHT | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 B7683∏AHT | | | X7R | 0.068 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| UMK107 B7104[]AHT | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| UMK107 C7224∏AHTE | | | X7S | 0.22 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| GMK107 B7473∏AHT | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| GMK107 B7104□AHT | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| GMK107 B7224∏AHT | | 35 | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| GMK107 B7474[]AHT | | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| GMK107AB7105[]AHT | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| TMK107 B7223[]AHT | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 200 | 0.8±0.10 | *1, *2 |
| TMK107 B7473∏AHT | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| TMK107 B7104□AHT | | 25 | X7R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, *2 |
| TMK107 B7224□AHT | | 25 | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| TMK107 B7474[]AHT | | 1 | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8 ± 0.10 | *1, *2 |
| TMK107AB7105∏AHT | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8+0.15/-0.05 | *1, *2 |
| EMK107 B7473[AHT | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| EMK107 B7104∏AHT | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| EMK107 B7224□AHT | | 16 | X7R | 0.22 μ | ±10, ±20 | 5 | 150 | 0.8±0.10 | *1, *2 |
| EMK107 B7474[]AHT | | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| EMK107 B7105[AHT | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| LMK107 B7224[]AHT | | | X7R | 0.22 μ | ±10, ±20 | 5 | 150 | 0.8±0.10 | *1, *2 |
| LMK107 B7474[]AHT | | 10 | X7R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 0.8±0.10 | *1, *2 |
| LMK107 B7105[]AHT | | 10 | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| LMK107BD7225[]AHT | | 1 | X7T | 2.2 μ | ±10, ±20 | 10 | 200 | 0.8+0.20/-0 | *1, *2 |
| JMK107 B7105[]AHT | | 0.0 | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| JMK107 B7225[]AHTR | | 6.3 | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1, *2 |
| | | | | | | | | | |

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 1.25mm thickness(G)

| Part number 1 | Part number 2 | Rated voltage | Temper | rature | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|----------|----------|-------------|---------------|-------------|-------------------|------------------|--------|
| Fart number 1 | Fart Humber 2 | [V] | characte | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | |
| UMK212 BJ104[]GHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| UMK212 BJ224 GHT | | 50 | | X5R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| UMK212 BJ474[]GHT | | 50 | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| UMK212 BJ105 GHT | | | | X5R | 1 μ | ±10, ±20 | 5 | 150 | 1.25±0.10 | *1, *2 |
| GMK212 BJ104[]GHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| GMK212 BJ224[]GHT | | | | X5R | 0.22 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| GMK212 BJ474[]GHT | | 35 | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| GMK212 BJ105[]GHT | | | | X5R | 1 μ | ±10, ±20 | 5 | 150 | 1.25±0.10 | *1, *2 |
| GMK212BBJ225[]GHT | | | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |
| TMK212 BJ104 GHT | | | | X5R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| TMK212 BJ224 GHT | | | | X5R | 0.22 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| TMK212 BJ474[]GHT | | | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| TMK212 BJ105 GHT | | 25 | | X5R | 1 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| TMK212 BJ225 GHT | | | | X5R | 2.2 μ | ±10, ±20 | 5 | 150 | 1.25±0.10 | *1, *2 |
| TMK212BBJ475[]GHT | | | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |
| TMK212BBJ106 GHT | | | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |
| EMK212 BJ105 GHT | | | | X5R | 1 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| EMK212 BJ225∏GHT | | 16 | | X5R | 2.2 μ | ±10, ±20 | 5 | 150 | 1.25±0.10 | *1, *2 |
| EMK212ABJ475 GHT | | 10 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| EMK212BBJ106 GHT | | | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |
| LMK212 BJ225∏GHT | | | | X5R | 2.2 μ | ±10, ±20 | 5 | 200 | 1.25±0.10 | *1, *2 |
| LMK212ABJ475 GHT | | 10 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| LMK212ABJ106∏GHT | | | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| JMK212ABJ475[]GHT | | | | X5R | 4.7 μ | ±10, ±20 | 5 | 200 | 1.25+0.15/-0.05 | *1, *2 |
| JMK212ABJ106∏GHT | | 6.3 | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| JMK212BBJ226MGHT | | | | X5R | 22 μ | ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |
| AMK212ABJ226MGHT | | 4 | | X5R | 22 μ | ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| AMK212BBJ476MGHT | | 4 | | X5R | 47 μ | ±20 | 10 | 150 | 1.25+0.20/-0 | *1, *2 |

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 0.85mm thickness(D)

| Part number 1 | Part number 2 | Rated voltage [V] | Temperature | | Capacitance | Capacitance | $tan \delta$ | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|----------------------|-------------|----------|-------------|---------------|--------------|-------------------|------------------|--------|
| Part number 1 | Fart Humber 2 | | characte | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| EMK212 BJ105□DHT | | | | X5R | 1 μ | ±10, ±20 | 5 | 200 | 0.85 ± 0.10 | *1, *2 |
| EMK212ABJ225 DHT | | 16 | | X5R | 2.2 μ | ±10, ±20 | 5 | 150 | 0.85±0.10 | *1, *2 |
| EMK212BBJ475□DHT | | | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 0.85±0.10 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.25mm thickness(G)

| Part number 1 | Part number 2 | Rated voltage [V] | Tempe charact | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|--------------------|---------------|-------------------|------------------|-----|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| UMK212 B7103[]GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| UMK212 B7153[GHT | | | | X7R | 0.015 μ | $\pm 10, \pm 20$ | 2.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| UMK212 B7223 GHT | | | | X7R | 0.022 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| UMK212 B7333 GHT | | | | X7R | 0.033 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| UMK212 B7473 GHT | | 50 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| UMK212 B7683 GHT | | 30 | | X7R | 0.068 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| UMK212 B7104[]GHT | | | | X7R | 0.1 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| UMK212 B7224 GHT | | | | X7R | 0.22 μ | $\pm 10, \pm 20$ | 3.5 | 150 | 1.25 ± 0.10 | *1, *2 |
| UMK212 C7474[]GHTE | | | | X7S | 0.47 μ | $\pm 10, \pm 20$ | 3.5 | 150 | 1.25 ± 0.10 | *1, *2 |
| UMK212 B7105 GHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| GMK212 B7224[]GHT | | 35 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| GMK212 B7105[]GHT | | 00 | | X7R | 1 μ | $\pm 10, \pm 20$ | 10 | 150 | 1.25 ± 0.10 | *1, *2 |
| TMK212 B7224[]GHT | | | | X7R | 0.22 μ | $\pm 10, \pm 20$ | 3.5 | 150 | 1.25 ± 0.10 | *1, *2 |
| TMK212 B7334[]GHT | | | | X7R | 0.33 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| TMK212 B7474[]GHT | | 25 | | X7R | 0.47 μ | $\pm 10, \pm 20$ | 3.5 | 150 | 1.25 ± 0.10 | *1, *2 |
| TMK212 B7105 GHTR | | | | X7R | 1 μ | $\pm 10, \pm 20$ | 10 | 150 | 1.25 ± 0.10 | *1, *2 |
| TMK212 B7225[]GHT | | | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| EMK212 B7224[]GHT | | | | X7R | 0.22 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| EMK212 B7334[]GHT | | | | X7R | 0.33 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| EMK212 B7474[]GHT | | 16 | | X7R | 0.47 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.25 ± 0.10 | *1, *2 |
| EMK212 B7105 GHTR | | 10 | | X7R | 1 μ | $\pm 10, \pm 20$ | 10 | 150 | 1.25 ± 0.10 | *1, *2 |
| EMK212 B7225[]GHT | | | | X7R | 2.2 μ | $\pm 10, \pm 20$ | 10 | 150 | 1.25 ± 0.10 | *1, *2 |
| EMK212AB7475 GHT | | | | X7R | 4.7 μ | $\pm 10, \pm 20$ | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |
| LMK212 B7105 GHTR | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| LMK212 B7225 GHT | | 10 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| LMK212 B7475 GHT | | | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| JMK212 B7475∏GHT | | 6.3 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1, *2 |
| JMK212AB7106 GHT | | 0.5 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1, *2 |

316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

[Temperature Characteristic BJ : X5R(-55~+85°C)] 1.6mm thickness(L)

| | D | Rated voltage | Tempe | erature | Capacitance | Capacitance | tan δ | HTLT | *3 - 3 | |
|-------------------|---------------|---------------|---------|-----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | teristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| UMK316 BJ474[LHT | | | | X5R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 BJ105[]LHT | | 50 | | X5R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 BJ225[]LHT | | 50 | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| UMK316ABJ475[]LHT | | | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| GMK316 BJ105∏LHT | | | | X5R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| GMK316 BJ225∏LHT | | 35 | | X5R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| GMK316 BJ475∏LHT | | 30 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| GMK316BBJ106[LHT | | | | X5R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| TMK316 BJ225∏LHT | | | | X5R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| TMK316 BJ475∏LHT | | 25 | | X5R | 4.7 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| TMK316 BJ106∏LHT | | | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| EMK316 BJ225∏LHT | | | | X5R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| EMK316 BJ475 LHT | | 16 | | X5R | 4.7 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| EMK316 BJ106∏LHT | | 16 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| EMK316BBJ226MLHT | | | | X5R | 22 μ | ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| LMK316 BJ475∏LHT | | | | X5R | 4.7 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| LMK316 BJ106∏LHT | | 10 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| LMK316ABJ226∏LHT | | | | X5R | 22 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| JMK316 BJ106∏LHT | | | | X5R | 10 μ | ±10, ±20 | 5 | 200 | 1.6±0.20 | *1, *2 |
| JMK316ABJ226[]LHT | | 6.3 | | X5R | 22 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| JMK316ABJ476MLHT | | 0.3 | | X5R | 47 μ | ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| JMK316BBJ107MLHT | | 1 | | X5R | 100 μ | ±20 | 10 | 150 | 1.6±0.30 | *2 |
| AMK316ABJ107MLHT | | 4 | | X5R | 100 μ | ±20 | 10 | 150 | 1.6±0.20 | *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : X7R($-55 \sim +125 ^{\circ}$ C), C7 : X7S($-55 \sim +125 ^{\circ}$ C)] 1.6mm thickness(L)

| Part number 1 | Part number 2 | Rated voltage | Temperat | ture | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|-------------|-------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | characteris | stics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| UMK316 B7473 LHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7683[LHT | | I | | X7R | 0.068 μ | ±10, ±20 | 2.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7104 LHT | | I | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7154 LHT | | I | | X7R | 0.15 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7224 LHT | | 50 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7334 LHT | | 30 | | X7R | 0.33 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7474 LHT | | | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7105 LHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| UMK316 B7225 LHT | | Ĭ | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| UMK316AC7475 LHTE | | Ĭ | | X7S | 4.7 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| GMK316 B7105□LHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| GMK316 B7225[]LHT | | 35 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| GMK316AB7475[]LHT | | | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| TMK316 B7105[]LHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| TMK316 B7225[]LHT | | 25 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| TMK316AB7475[]LHT | | 25 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| TMK316AB7106[]LHT | | | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| EMK316 B7225□LHT | | | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| EMK316AB7475 LHT | | 16 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| EMK316AB7106 LHT | | Ĭ | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| LMK316 B7475[]LHT | | 10 | | X7R | 4.7 μ | ±10, ±20 | 5 | 150 | 1.6±0.20 | *1, *2 |
| LMK316AB7106[]LHT | | 10 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| JMK316AB7106 LHT | | 6.3 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| JMK316AB7226[]LHT | | 0.3 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| AMK316AB7226 LHT | | 4 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| AMK316AC7476MLHT | | T * | | X7S | 47 μ | ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic BJ : X5R(-55~+85°C)] 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| UMK325 BJ106∏MHP | | 50 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| GMK325 BJ106□MHP | | 35 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| TMK325 BJ106 MHP | | 25 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| EMK325 BJ226 MHP | | 16 | | X5R | 22 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| EMK325ABJ476∏MHP | | 10 | | X5R | 47 μ | ±10, ±20 | 10 | 150 | 2.5±0.30 | *1, *2 |
| LMK325 BJ226∏MHP | | | | X5R | 22 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| LMK325 BJ476∏MHP | | 10 | | X5R | 47 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| LMK325ABJ107MMHP | | Ī | | X5R | 100 μ | ±20 | 10 | 150 | 2.5 ± 0.30 | *2 |
| JMK325 BJ476∏MHP | | 6.3 | | X5R | 47 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| JMK325ABJ107MMHP | | 0.3 | | X5R | 100 μ | ±20 | 10 | 150 | 2.5 ± 0.30 | *2 |
| AMK325ABJ107MMHP | | 4 | | X5R | 100 μ | ±20 | 10 | 150 | 2.5 ± 0.30 | *2 |
| AMK325ABJ227MMHP | | 4 | | X5R | 220 μ | ±20 | 10 | 150 | 2.5 ± 0.30 | *2 |

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 1.9mm thickness(N)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| UMK325 BJ475□NHT | | 50 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |
| GMK325 BJ225MNHT | | 35 | | X5R | 2.2 μ | ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| GMK325 BJ475[NHT | | 30 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |
| TMK325 BJ475□NHT | | 25 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |
| EMK325 BJ475MNHT | | 16 | | X5R | 4.7 μ | ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| EMK325 BJ106∏NHT | | 10 | | X5R | 10 μ | ±10, ±20 | 5 | 150 | 1.9±0.20 | *1, *2 |

[Temperature Characteristic C6 : $X6S(-55\sim+105^{\circ}C)$] 2.5mm thickness(M)

| <u>- </u> | • | | · • | | | | | | |
|--|---------------|----------------------|-----------------------------|--------------------|------------------------------|--------------|------------------------|------------------|------|
| Part number 1 | Part number 2 | Rated voltage [V] | Temperature characteristics | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
| JMK325AC6107MMHP | | 6.3 | X6S | 100 // | +20 | 10 | 150 | 25+030 | *2 |

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | NI.A. |
|--------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number I | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| UMK325 B7225∏MHP | | | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| UMK325 B7335∏MHP | | 50 | | X7R | 3.3 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| UMK325 B7475∏MHP | | 50 | | X7R | 4.7 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1, *2 |
| UMK325AB7106∏MHP | | Ī | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 2.5±0.30 | *1, *2 |
| GMK325AB7106□MHP | | 35 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 2.5±0.30 | *1, *2 |
| TMK325 B7335[]MHP | | | | X7R | 3.3 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| TMK325AB7106 MHPR | | 25 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 2.5±0.30 | *1, *2 |
| TMK325 B7226[]MHP | | | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| EMK325 B7226 MHP | | 16 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| LMK325 B7226[]MHP | | 10 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| JMK325 B7226□MHPR | | 6.3 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |
| JMK325 B7476[]MHPR | | 0.3 | | X7R | 47 μ | ±10, ±20 | 10 | 150 | 2.5±0.20 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : X7R(-55~+125°C)] 1.9mm thickness(N)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| UMK325 B7105□NHT | | 50 | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| GMK325 B7225[]NHT | | 35 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| GMK325 B7475□NHTR | | 33 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |
| TMK325 B7475∏NHT | | 25 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |
| EMK325 B7475[]NHT | | 16 | | X7R | 4.7 μ | ±10, ±20 | 3.5 | 150 | 1.9±0.20 | *1, *2 |
| EMK325 B7106□NHTR | | 10 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.9±0.20 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Multilayer Ceramic Capacitors (Temperature compensating type)

●063TYPE (Dimension:0.6 × 0.3mm JIS:0603 EIA:0201)

[Temperature Characteristic $CG: CG/C0G(-55 \sim +125^{\circ}C)$] 0.3mm thickness(T)

| Part number 1 | Part number 2 | Rated voltage | | erature | Capacitance | Capacitance | Q [at 1MHz] | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|---------------|---------|-----------|-------------|--------------|----------------|-------------------|------------------|--------|
| | | [V] | charact | teristics | [F] | tolerance | (Min) | Rated voltage x % | THOMISON DINING | |
| UMK063 CG0R5CTHF | | | CG | COG | 0.5 p | ±0.25pF | 410 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG010CTHF | | | CG | C0G | 1 p | ±0.25pF | 420 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG1R5CTHF | | | CG | C0G | 1.5 p | ±0.25pF | 430 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG020CTHF | | | CG | COG | 2 p | ±0.25pF | 440 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG030CTHF | | | CG | COG | 3 p | ±0.25pF | 460 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG040CTHF | | | CG | C0G | 4 p | ±0.25pF | 480 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG050CTHF | | | CG | C0G | 5 p | ±0.25pF | 500 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG060DTHF | | | CG | C0G | 6 p | ±0.5pF | 520 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG070DTHF | | | CG | COG | 7 p | ±0.5pF | 540 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG080DTHF | | | CG | COG | 8 p | ±0.5pF | 560 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG090DTHF | | | CG | COG | 9 p | $\pm 0.5 pF$ | 580 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG100DTHF | | 50 | CG | C0G | 10 p | ±0.5pF | 600 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG120JTHF | | 30 | CG | C0G | 12 p | ±5% | 640 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG150JTHF | | | CG | C0G | 15 p | ±5% | 700 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG180JTHF | | | CG | COG | 18 p | ±5% | 760 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG220JTHF | | | CG | C0G | 22 p | ±5% | 840 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG270JTHF | | | CG | COG | 27 p | ±5% | 940 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG330JTHF | | | CG | C0G | 33 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG390JTHF | | | CG | C0G | 39 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG470JTHF | | | CG | C0G | 47 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG560JTHF | | | CG | C0G | 56 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG680JTHF | | | CG | C0G | 68 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG820JTHF | | | CG | C0G | 82 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| UMK063 CG101JTHF | | | CG | COG | 100 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| TMK063 CG121JTHF | | | CG | COG | 120 p | ±5% | 1000 | 200 | 0.3±0.03 | *1, *2 |
| TMK063 CG151JTHF | | 25 | CG | C0G | 150 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| TMK063 CG181JTHF | | 20 | CG | C0G | 180 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |
| TMK063 CG221JTHF | | | CG | C0G | 220 p | ±5% | 1000 | 200 | 0.3 ± 0.03 | *1, *2 |

●105TYPE (Dimension:1.0 × 0.5mm JIS:1005 EIA:0402)

【Temperature Characteristic CG: CG/C0G(−55~+125°C)】 0.5mm thickness(V)

| I Temperature Charac | cteristic od . od/ c | Jud (— 33.4 T | - 123 C, | / J 0.5111 | III triickness (V) | | | 1 | | |
|----------------------|----------------------|----------------|----------|-------------------|--------------------|-------------|--------------------|-------------------|------------------|--------|
| D | D | Rated voltage | Tempe | erature | Capacitance | Capacitance | Q | HTLT | *3 = 3 | N |
| Part number 1 | Part number 2 | [V] | charac | teristics | [F] | tolerance | [at 1MHz] (Min) | Rated voltage x % | Thickness*3 [mm] | Note |
| UMK105 CG0R5CVHF | | | CG | COG | 0.5 p | ±0.25pF | 410 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG010CVHF | | 1 | CG | COG | 1 p | ±0.25pF | 420 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG1R5CVHF | | 1 | CG | COG | 1.5 p | ±0.25pF | 430 | 200 | 0.5±0.05 | *1. *2 |
| UMK105 CG020CVHF | | 1 | CG | COG | 2 p | ±0.25pF | 440 | 200 | 0.5±0.05 | *1. *2 |
| UMK105 CG030CVHF | | | CG | COG | 3 p | ±0.25pF | 460 | 200 | 0.5±0.05 | *1. *2 |
| UMK105 CG040CVHF | | | CG | COG | 4 p | ±0.25pF | 480 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG050CVHF | | 1 | CG | COG | 5 p | ±0.25pF | 500 | 200 | 0.5±0.05 | *1. *2 |
| UMK105 CG060DVHF | | | CG | COG | 6 p | ±0.5pF | 520 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG070DVHF | | 1 | CG | COG | 7 p | ±0.5pF | 540 | 200 | 0.5±0.05 | *1. *2 |
| UMK105 CG080DVHF | | | CG | COG | 8 p | ±0.5pF | 560 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG090DVHF | | | CG | COG | 9 p | ±0.5pF | 580 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG100DVHF | | | CG | COG | α 10 | ±0.5pF | 600 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG120JVHF | | | CG | COG | 12 p | ±5% | 640 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG150JVHF | | | CG | COG | 15 p | ±5% | 700 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG180JVHF | | | CG | COG | 18 p | ±5% | 760 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG220JVHF | | | CG | COG | 22 p | ±5% | 840 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG270JVHF | | | CG | COG | 27 p | ±5% | 940 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG330JVHF | | 50 | CG | COG | 33 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG390JVHF | | 50 | CG | COG | 39 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG470JVHF | | | CG | COG | 47 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG560JVHF | | | CG | COG | 56 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG680JVHF | | | CG | COG | 68 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG820JVHF | | | CG | C0G | 82 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG101JVHF | | | CG | COG | 100 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG121JVHF | | | CG | C0G | 120 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG151JVHF | | | CG | C0G | 150 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG181JVHF | | | CG | C0G | 180 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG221JVHF | | | CG | COG | 220 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG271JVHF | | | CG | COG | 270 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG331JVHF | | | CG | COG | 330 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG391JVHF | | | CG | C0G | 390 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG471JVHF | | | CG | COG | 470 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG561JVHF | | | CG | COG | 560 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG681JVHF | | | CG | COG | 680 p | ±5% | 1000 | 200 | 0.5±0.05 | *1, *2 |
| UMK105 CG821JVHF | | | CG | COG | 820 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |
| UMK105 CG102JVHF | | | CG | C0G | 1000 p | ±5% | 1000 | 200 | 0.5 ± 0.05 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Medium-High Voltage Multilayer Ceramic Capacitors

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic B7 : X7R($-55 \sim +125 ^{\circ}$ C), C7 : X7S($-55 \sim +125 ^{\circ}$ C)] 0.8mm thickness(A)

| Part number 1 | Part number 2 | Rated voltage | Temperatu | re | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|--------------------|---------------|---------------|--------------|------|-------------|---------------|-------------|-------------------|------------------|--------|
| rart number i | Fart Humber 2 | [V] | characterist | tics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| HMK107 B7102[]AHT | | | X | 7R | 1000 p | ±10, ±20 | 3.5 | 200 | 0.8 ± 0.10 | *1, *2 |
| HMK107 B7152[]AHT | | | Х | 7R | 1500 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7222 AHT | | | Х | 7R | 2200 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7332∏AHT | | | Х | 7R | 3300 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7472[]AHT | | | Х | 7R | 4700 p | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7682∏AHT | | | X | 7R | 6800 p | ±10, ±20 | 3.5 | 200 | 0.8 ± 0.10 | *1, *2 |
| HMK107 B7103[]AHT | | 100 | X | 7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7153[]AHT | | | Х | 7R | 0.015 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7223[]AHT | | | X | 7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7333 AHT | | | X | 7R | 0.033 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7473∏AHT | | | Х | 7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 B7104[]AHT | | | X | 7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1, *2 |
| HMK107 C7224[]AHTE | | | X | .7S | 0.22 μ | ±10, ±20 | 3.5 | 150 | 0.8 ± 0.10 | *1, *2 |

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic B7 : X7R($-55 \sim +125 ^{\circ}$ C), C7 : X7S($-55 \sim +125 ^{\circ}$ C)] 1.25mm thickness(G)

| | | 1 120 0,7 0,7 1,7,7 0 00 | | | | | | | | |
|-------------------|---------------|--------------------------|----------|----------|--------------------|------------------------------|--------------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | Rated voltage [V] | Tempe | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT | Thickness*3 [mm] | Note |
| | | [4] | Citatacu | 61134163 | 0.3 | tolerance [70] | [/0] | Rated voltage x % | | |
| HMK212 B7472 GHT | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7682∏GHT | | | | X7R | 6800 p | ±10, ±20 | 2.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7103∏GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7153∏GHT | | | | X7R | 0.015 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7223∏GHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7333∏GHT | | 100 | | X7R | 0.033 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7473∏GHT | | 100 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7683∏GHT | | ţ | | X7R | 0.068 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7104□GHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 B7224∏GHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1, *2 |
| HMK212 C7474∏GHTE | | | | X7S | 0.47 μ | ±10, ±20 | 3.5 | 150 | 1.25±0.10 | *1, *2 |
| HMK212BC7105∏GHTE | | | | X7S | 1 μ | ±10, ±20 | 3.5 | 150 | 1.25+0.20/-0 | *1, *2 |
| QMK212 B7472 GHT | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 150 | 1.25±0.10 | *1, *2 |
| QMK212 B7682 GHT | | | | X7R | 6800 p | ±10, ±20 | 2.5 | 150 | 1.25±0.10 | *1, *2 |
| QMK212 B7103 GHT | | 250 | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 150 | 1.25±0.10 | *1, *2 |
| QMK212 B7153 GHT | | | | X7R | 0.015 μ | ±10, ±20 | 2.5 | 150 | 1.25±0.10 | *1, *2 |
| QMK212 B7223 GHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 150 | 1.25±0.10 | *1, *2 |

[Temperature Characteristic B7 : $X7R(-55 \sim +125 ^{\circ}C)$] 0.85mm thickness(D)

| Part number 1 | Part number 2 | Rated voltage | Temper | ature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|----------|---------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | characte | ristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| HMK212 B7102[]DHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.85 ± 0.10 | *1, *2 |
| HMK212 B7152[]DHT | | 100 | | X7R | 1500 p | ±10, ±20 | 2.5 | 200 | 0.85 ± 0.10 | *1, *2 |
| HMK212 B7222 DHT | | 100 | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.85 ± 0.10 | *1, *2 |
| HMK212 B7332[]DHT | | | | X7R | 3300 p | ±10, ±20 | 2.5 | 200 | 0.85 ± 0.10 | *1, *2 |
| QMK212 B7102[DHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 150 | 0.85 ± 0.10 | *1, *2 |
| QMK212 B7152 DHT | | 250 | | X7R | 1500 p | ±10, ±20 | 2.5 | 150 | 0.85 ± 0.10 | *1, *2 |
| QMK212 B7222 DHT | | 250 | | X7R | 2200 p | ±10, ±20 | 2.5 | 150 | 0.85 ± 0.10 | *1, *2 |
| QMK212 B7332 DHT | | | | X7R | 3300 р | ±10, ±20 | 2.5 | 150 | 0.85 ± 0.10 | *1, *2 |

316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

[Temperature Characteristic B7 : X7R($-55 \sim +125^{\circ}$ C), C7 : X7S($-55 \sim +125^{\circ}$ C)] 1.6mm thickness(L)

| Part number 1 | Part number 2 | Rated voltage | Temperature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|-----------------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | characteristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| HMK316 B7473[]LHT | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7683[]LHT | | | X7R | 0.068 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7104[]LHT | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7154□LHT | | | X7R | 0.15 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7224□LHT | | 100 | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7334□LHT | | | X7R | 0.33 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7474□LHT | | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316 B7105□LHT | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1, *2 |
| HMK316AC7225∏LHTE | | | X7S | 2.2 μ | ±10, ±20 | 3.5 | 150 | 1.6±0.20 | *1, *2 |
| QMK316 B7223 LHT | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| QMK316 B7333[LHT | | | X7R | 0.033 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| QMK316 B7473[LHT | | 250 | X7R | 0.047 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| QMK316 B7683[LHT | | | X7R | 0.068 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| QMK316 B7104[LHT | | | X7R | 0.1 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.20 | *1, *2 |
| SMK316 B7153[]LHT | | 630 | X7R | 0.015 μ | ±10, ±20 | 2.5 | 120 | 1.6±0.20 | *1, *2 |
| SMK316 B7223 LHT | | 030 | X7R | 0.022 μ | ±10, ±20 | 2.5 | 120 | 1.6±0.20 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.15mm thickness(F)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | $	an\delta$ | HTLT | ·· *3 r 1 | Note | |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------------|-------------------|------------------|--------|---|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note | |
| SMK316 B7102 FHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | |
| SMK316 B7152[]FHT | | | | X7R | 1500 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | |
| SMK316 B7222 FHT | | | | X7R | 2200 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | _ |
| SMK316 B7332[]FHT | | 630 | | X7R | 3300 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | |
| SMK316 B7472 FHT | | Ī | | X7R | 4700 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | |
| SMK316 B7682∏FHT | | Ī | | X7R | 6800 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | |
| SMK316 B7103∏FHT | · | Ī | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 | _ |

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic B7 : X7R($-55 \sim +125 ^{\circ}$ C), C7 : X7S($-55 \sim +125 ^{\circ}$ C)] 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage [V] | erature eristics | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|--------------------|---------------|----------------------|---------------------|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| HMK325 B7225∏MHP | | 100 | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| HMK325 C7475[]MHPE | | 100 | X7S | 4.7 μ | ±10, ±20 | 3.5 | 150 | 2.5±0.20 | *1, *2 |

| Part number 1 | Part number 2 | Rated voltage | Temper | ature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|----------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| rart number i | Fart number 2 | [V] | characte | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| HMK325 B7224□NHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMK325 B7474□NHT | | 100 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMK325 B7684□NHT | | 100 | | X7R | 0.68 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMK325 B7105□NHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| QMK325 B7473[NHT | | | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMK325 B7104[]NHT | | 250 | | X7R | 0.1 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMK325 B7154[]NHT | | 250 | | X7R | 0.15 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMK325 B7224[]NHT | | | | X7R | 0.22 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| SMK325 B7223 NHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 120 | 1.9±0.20 | *1, *2 |
| SMK325 B7333 NHT | | 630 | | X7R | 0.033 μ | ±10, ±20 | 2.5 | 120 | 1.9±0.20 | *1, *2 |
| SMK325 B7473[NHT | | | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 120 | 1.9±0.20 | *1, *2 |

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.15mm thickness(F)

| Part number 1 | Part number 2 | Rated voltage [V] | erature eristics | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note | |
|-------------------|---------------|----------------------|-------------------------|--------------------|---------------------------|--------------|------------------------|------------------|--------|--|
| HMK325 B7104[]FHT | | 100 | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.15±0.10 | *1, *2 | |

432TYPE (Dimension:4.5 × 3.2mm JIS:4532 EIA:1812)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage | Temperatur | re | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|---------------|-----|-------------|---------------|-------------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | characteristi | ics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| HMK432 B7474□MHT | | | X | 7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| HMK432 B7105 MHT | | 100 | X | 7R | 1 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| HMK432 B7155□MHT | | 100 | X | 7R | 1.5 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| HMK432 B7225 MHT | | | X | 7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1, *2 |
| QMK432 B7104[]MHT | | | X | 7R | 0.1 μ | ±10, ±20 | 2.5 | 150 | 2.5±0.20 | *1, *2 |
| QMK432 B7224[]MHT | | 250 | X | 7R | 0.22 μ | ±10, ±20 | 2.5 | 150 | 2.5±0.20 | *1, *2 |
| QMK432 B7334[]MHT | | 230 | X | 7R | 0.33 μ | ±10, ±20 | 2.5 | 150 | 2.5±0.20 | *1, *2 |
| QMK432 B7474[]MHT | | | X | 7R | 0.47 μ | ±10, ±20 | 2.5 | 150 | 2.5±0.20 | *1, *2 |
| SMK432 B7473 MHT | | | X | 7R | 0.047 μ | ±10, ±20 | 2.5 | 120 | 2.5±0.20 | *1, *2 |
| SMK432 B7683 MHT | | 630 | X | 7R | 0.068 μ | ±10, ±20 | 2.5 | 120 | 2.5±0.20 | *1, *2 |
| SMK432 B7104 MHT | | | X | 7R | 0.1 μ | ±10, ±20 | 2.5 | 120 | 2.5±0.20 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Medium-High Voltage Multilayer Ceramic Capacitors for High Frequency Applications

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic $CG: CG/C0G(-55 \sim +125^{\circ}C)$] 0.7mm thickness(C)

| Part number 1 | Part number 2 | Rated voltage | | erature | Capacitance | Capacitance | Q [at 1MHz] | HTLT | Thickness*3 [mm] | Note |
|--------------------------------------|----------------|---------------|--------|-----------|--------------|------------------------------|----------------|-------------------|----------------------|--------|
| T are number 1 | T dre Hamber 2 | [V] | charac | teristics | [F] | tolerance | (Min) | Rated voltage x % | Triickriess [illili] | 14010 |
| QVS107 CG0R2[]CHT | | | CG | C0G | 0.2 p | ±0.05pF, ±0.1pF | 804 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R3[CHT | | | CG | C0G | 0.3 p | ±0.05pF, ±0.1pF | 806 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R4[]CHT | | | CG | C0G | 0.4 p | $\pm 0.05 pF$, $\pm 0.1 pF$ | 808 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R5[CHT | | | CG | C0G | 0.5 p | ±0.1pF, ±0.25pF | 810 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R6[CHT | | | CG | C0G | 0.6 p | ±0.1pF, ±0.25pF | 812 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R7[CHT | | | CG | C0G | 0.7 p | ±0.1pF, ±0.25pF | 814 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CGR75 CHT | | | CG | C0G | 0.75 p | ±0.1pF, ±0.25pF | 815 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R8□CHT | | | CG | C0G | 0.8 p | ±0.1pF, ±0.25pF | 816 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG0R9[CHT | | | CG | C0G | 0.9 p | ±0.1pF, ±0.25pF | 818 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG010[CHT | | | CG | C0G | 1 p | ±0.1pF, ±0.25pF | 820 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R1 CHT | | | CG | C0G | 1.1 p | $\pm 0.1 pF$, $\pm 0.25 pF$ | 822 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R2□CHT | | | CG | C0G | 1.2 p | ±0.1pF, ±0.25pF | 824 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R3∏CHT | | | CG | C0G | 1.3 p | ±0.1pF, ±0.25pF | 826 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R5∏CHT | | | CG | C0G | 1.5 p | ±0.1pF, ±0.25pF | 830 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R6☐CHT | | | CG | C0G | 1.6 p | ±0.1pF, ±0.25pF | 832 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG1R8☐CHT | | | CG | C0G | 1.8 p | ±0.1pF, ±0.25pF | 836 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG020[CHT | <u></u> | 1 | CG | C0G | 2 p | ±0.1pF, ±0.25pF | 840 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG2R2[]CHT | | | CG | C0G | 2.2 p | ±0.1pF, ±0.25pF | 844 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG2R4[]CHT | | | CG | COG | 2.4 p | ±0.1pF, ±0.25pF | 848 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG2R7[]CHT | | | CG | C0G | 2.7 p | ±0.1pF, ±0.25pF | 854 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG030[]CHT | | | CG | COG | 3 p | ±0.1pF, ±0.25pF | 860 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG3R3[]CHT | | | CG | COG | 3.3 p | ±0.1pF, ±0.25pF | 866 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG3R6∏CHT | | | CG | COG | 3.6 p | ±0.1pF, ±0.25pF | 872 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG3R9∏CHT | | | CG | COG | 3.9 p | ±0.1pF, ±0.25pF | 878 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG4R3[]CHT | | | CG | COG | 4.3 p | ±0.1pF, ±0.25pF | 886 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG4R7∏CHT | | | CG | COG | 4.7 p | ±0.1pF, ±0.25pF | 894 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG5R1∏CHT | | | CG | COG | 5.1 p | ±0.25pF, ±0.5pF | 902 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG5R6☐CHT | | | CG | COG | 5.6 p | ±0.25pF, ±0.5pF | 912 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG6R2∏CHT | | 250 | CG | COG | 6.2 p | ±0.25pF, ±0.5pF | 924 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG6R8∏CHT | | 250 | CG | COG | 6.8 p | ±0.25pF, ±0.5pF | 936 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG7R5∏CHT | | | CG | COG | 7.5 p | ±0.25pF, ±0.5pF | 950 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG8R2∏CHT | | | CG | COG | 8.2 p | ±0.25pF, ±0.5pF | 964 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG9R1∏CHT | | | CG | COG | 9.1 p | ±0.25pF, ±0.5pF | 982 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG100[CHT | | | CG | COG | 10 p | ±2%, ±5% | 1000 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG110JCHT | | | CG | COG | 11 p | ±5% | 1020 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG120JCHT | | | CG | COG | 12 p | ±5% | 1040 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG130JCHT | | | CG | COG | 13 p | ±5% | 1060 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG150JCHT | | | CG | COG | 15 p | ±5% | 1100 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG160JCHT | | | CG | COG | 16 p | ±5% | 1120 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG180JCHT | | 1 | CG | COG | 18 p | ±5% | 1160 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG200JCHT | | 1 | CG | C0G | 20 p | ±5% | 1200 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG220JCHT | | | CG | C0G | 22 p | ±5% | 1240 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG240JCHT | | 1 | CG | COG | 24 p | ±5% | 1280 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG270JCHT | | 1 | CG | COG | 27 p | ±5% | 1340 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG300JCHT | | 1 | CG | COG | 30 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG330JCHT | | 1 | CG | COG | 33 p | ±5% | 1400 | 200 | 0.7±0.10 | *1. *2 |
| QVS107 CG360JCHT | | 1 | CG | COG | 36 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG390JCHT | | 1 | CG | COG | 39 p | ±5% | 1400 | 200 | 0.7±0.10 | *1. *2 |
| QVS107 CG430JCHT | | 1 | CG | COG | 43 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG470JCHT | | 1 | CG | COG | 47 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG510JCHT | | 1 | CG | COG | 51 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG560JCHT | | 1 | CG | COG | 56 p | ±5% | 1400 | 200 | 0.7±0.10 0.7±0.10 | *1, *2 |
| QVS107 CG5003CHT | | 1 | CG | COG | 62 p | ±5% | 1400 | 200 | 0.7±0.10 | *1, *2 |
| QVS107 CG680JCHT | | 1 | CG | COG | 68 p | ±5% | 1400 | 200 | 0.7±0.10 0.7±0.10 | *1, *2 |
| QVS107 CG0503CHT | | 1 | CG | COG | 75 p | ±5% | 1400 | 200 | 0.7±0.10 0.7±0.10 | *1, *2 |
| QVS107 CG820JCHT | | 1 | CG | COG | 75 p 82 p | ±5% | 1400 | 200 | 0.7±0.10 0.7±0.10 | *1, *2 |
| QVS107 CG820JCHT QVS107 CG910JCHT | | 1 | CG | COG | 82 p 91 p | ±5% | 1400 | 200 | 0.7±0.10 0.7±0.10 | *1, *2 |
| | | 1 | J | COG | 100 p | ± 5%0 | 1400 | 200 | 0.7 ± 0.10 | 71, ↑∠ |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic CG: CG/C0G(-55~+125°C)] 0.85mm thickness(D)

| Temperature Charac | cteristic CG : CG/C | COG(−55~+ | -125°C) |] 0.85r | nm thickness(D |) | | | | |
|--|---------------------------------------|----------------------|----------|----------------|--------------------|------------------------------------|----------------|-------------------|------------------------|------------------|
| Part number 1 | Part number 2 | Rated voltage [V] | Tempe | | Capacitance [F] | Capacitance tolerance | Q [at 1MHz] | HTLT | Thickness*3 [mm] | Note |
| | | ۲۸۱ | | | | | (Min) | Rated voltage x % | | |
| QVS212 CG0R3[DHT | | 1 | CG | C0G | 0.3 p | $\pm 0.1 pF$, $\pm 0.25 pF$ | 806 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG0R4[DHT | | ↓ | CG | C0G | 0.4 p | $\pm 0.1 pF$, $\pm 0.25 pF$ | 808 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG0R5[DHT | | 4 | CG | C0G | 0.5 p | $\pm 0.1 pF$, $\pm 0.25 pF$ | 810 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG0R6□DHT | | ↓ | CG | C0G | 0.6 p | ±0.1pF, ±0.25pF | 812 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG0R7 DHT | | 4 | CG | COG | 0.7 p | ±0.1pF, ±0.25pF | 814 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CGR75 DHT | | 4 | CG | COG | 0.75 p | ±0.1pF, ±0.25pF | 815 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG0R8 DHT | | - | CG | C0G C0G | 0.8 p | ±0.1pF, ±0.25pF | 816 818 | 200 | 0.85±0.10 | *1, *2 *1, *2 |
| QVS212 CG0R9[]DHT QVS212 CG010[]DHT | | + | CG CG | COG | 0.9 p | ±0.1pF, ±0.25pF | 820 | 200 200 | 0.85±0.10 0.85±0.10 | *1, *2 |
| QVS212 CG010[]DHT | | + | CG | COG | 1 p 1.1 p | ±0.1pF, ±0.25pF ±0.1pF, ±0.25pF | 820 | 200 | 0.85±0.10 0.85±0.10 | *1, *2 |
| QVS212 CG1R1DHT | | + | CG | COG | 1.1 p | ±0.1pF, ±0.25pF | 824 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG1R3 DHT | | + | CG | COG | 1.3 p | ±0.1pF, ±0.25pF | 826 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG1R5∏DHT | | † | CG | COG | 1.5 p | ±0.1pF, ±0.25pF | 830 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG1R6 DHT | | † | CG | COG | 1.6 p | ±0.1pF, ±0.25pF | 832 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG1R8[]DHT | | † | CG | COG | 1.8 p | ±0.1pF, ±0.25pF | 836 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG020 DHT | | † | CG | COG | 2 p | ±0.1pF, ±0.25pF | 840 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG2R2[]DHT | | 1 | CG | COG | 2.2 p | ±0.1pF, ±0.25pF | 844 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG2R4[DHT | | 1 | CG | COG | 2.4 p | ±0.1pF, ±0.25pF | 848 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG2R7[]DHT | | 1 | CG | COG | 2.7 p | ±0.1pF, ±0.25pF | 854 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG030 DHT | | 1 | CG | COG | 3 p | ±0.1pF, ±0.25pF | 860 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG3R3[]DHT | | 1 | CG | COG | 3.3 p | ±0.1pF, ±0.25pF | 866 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG3R6 DHT | | 1 | CG | COG | 3.6 p | ±0.1pF, ±0.25pF | 872 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG3R9[]DHT | | 1 | CG | COG | 3.9 p | ±0.1pF, ±0.25pF | 878 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG4R3[]DHT | | <u> </u> | CG | COG | 4.3 p | ±0.1pF, ±0.25pF | 886 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG4R7[DHT | | 1 | CG | C0G | 4.7 p | ±0.1pF, ±0.25pF | 894 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG5R1 DHT | | 1 | CG | C0G | 5.1 p | ±0.25pF, ±0.5pF | 902 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG5R6 DHT | | 1 | CG | C0G | 5.6 p | $\pm 0.25 pF, \pm 0.5 pF$ | 912 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG6R2DHT | | ↓ | CG | C0G | 6.2 p | $\pm 0.25 pF$, $\pm 0.5 pF$ | 924 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG6R8 DHT | | 250 | CG | COG | 6.8 p | $\pm 0.25 pF$, $\pm 0.5 pF$ | 936 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG7R5 DHT | | ↓ | CG | COG | 7.5 p | ±0.25pF, ±0.5pF | 950 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG8R2 DHT | | ↓ | CG | COG | 8.2 p | ±0.25pF, ±0.5pF | 964 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG9R1 DHT | | 4 | CG | COG | 9.1 p | ±0.25pF, ±0.5pF | 982 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG100JDHT | | 4 | CG | COG | 10 p | ±5% | 1000 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG110JDHT | | 4 | CG | COG | 11 p | ±5% | 1020 1040 | 200 200 | 0.85±0.10 0.85±0.10 | *1, *2 |
| QVS212 CG120JDHT QVS212 CG130JDHT | | + | CG CG | C0G C0G | 12 p 13 p | ±5% ±5% | 1040 | 200 | 0.85±0.10 0.85±0.10 | *1, *2 *1, *2 |
| QVS212 CG150JDHT | | + | CG | COG | 15 p | ±5% | 1100 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG160JDHT | | † | CG | COG | 16 p | ±5% | 1120 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG180JDHT | | † | CG | COG | 18 p | ±5% | 1160 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG200JDHT | | † | CG | COG | 20 p | ±5% | 1200 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG220JDHT | | † | CG | COG | 22 p | ±5% | 1240 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG240JDHT | | 1 | CG | COG | 24 p | ±5% | 1280 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG270JDHT | | 1 | CG | COG | 27 p | ±5% | 1340 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG300JDHT | | 1 | CG | COG | 30 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG330JDHT | | 1 | CG | COG | 33 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG360JDHT | | 1 | CG | COG | 36 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG390JDHT | | 1 | CG | COG | 39 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG430JDHT | | Ĭ | CG | COG | 43 p | ±5% | 1400 | 200 | 0.85 ± 0.10 | *1, *2 |
| QVS212 CG470JDHT | · · · · · · · · · · · · · · · · · · · | 1 | CG | COG | 47 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG510JDHT | <u> </u> | 1 | CG | COG | 51 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG560JDHT | · | 1 | CG | C0G | 56 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG620JDHT | <u> </u> | 1 | CG | C0G | 62 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG680JDHT | · | <u>↓</u> | CG | COG | 68 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG750JDHT | | _ | CG | COG | 75 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG820JDHT | | _ | CG | COG | 82 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG910JDHT | | 4 | CG | COG | 91 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |
| QVS212 CG101JDHT | | 1 | CG | C0G | 100 p | ±5% | 1400 | 200 | 0.85±0.10 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Soft Termination Multilayer Ceramic Capacitors

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 0.8mm thickness(A)

| Dest south of | D | Rated voltage | Tempe | erature | Capacitance | Capacitance | tan δ | HTLT | *3 5 3 | N.A. |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| TMJ107BB7473[]AHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| TMJ107BB7104∏AHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| TMJ107BB7224 AHT | | 25 | | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| TMJ107BB7474 AHT | | | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| TMJ107CB7105∏AHR | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8+0.25/-0 | *1, *2 |
| GMJ107BB7473□AHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| GMJ107BB7104□AHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| GMJ107BB7224□AHT | | 35 | | X7R | 0.22 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| GMJ107BB7474□AHT | | | | X7R | 0.47 μ | ±10, ±20 | 10 | 150 | 0.8+0.20/-0 | *1, *2 |
| GMJ107CB7105∏AHR | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8+0.25/-0 | *1, *2 |
| UMJ107AB7102□AHT | | | | X7R | 1000 p | ±10, ±20 | 3.5 | 200 | 0.8+0.15/-0.05 | *1, *2 |
| UMJ107AB7222∏AHT | | | | X7R | 2200 p | ±10, ±20 | 3.5 | 200 | 0.8+0.15/-0.05 | *1, *2 |
| UMJ107BB7472∏AHT | | | | X7R | 4700 p | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| UMJ107BB7103[AHT | | 50 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| UMJ107BB7223[]AHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| UMJ107BB7473[]AHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| UMJ107BB7104[]AHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| HMJ107AB7102∏AHT | | | | X7R | 1000 p | ±10, ±20 | 3.5 | 200 | 0.8+0.15/-0.05 | *1, *2 |
| HMJ107AB7222∏AHT | | | | X7R | 2200 p | ±10, ±20 | 3.5 | 200 | 0.8+0.15/-0.05 | *1, *2 |
| HMJ107BB7472[]AHT | | | | X7R | 4700 p | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| HMJ107BB7103[]AHT | | 100 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| HMJ107BB7223[]AHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| HMJ107BB7473∏AHT | | 1 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |
| HMJ107BB7104[]AHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8+0.20/-0 | *1, *2 |

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

 $\begin{tabular}{l} \textbf{[} Temperature Characteristic B7: X7R(-55~+125^{\circ}C), C7: X7S(-55~+125^{\circ}C)] & 0.85mm thickness(D), 1.25mm thickness(G) \\ \end{tabular}$

| Part number 1 | Part number 2 | Rated voltage | Tempe | erature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|--------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| JMJ212CB7106 GHT | | 6.3 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| EMJ212CB7225∏GHT | | 16 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| EMJ212CB7475 GHT | | 10 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| TMJ212CB7225 GHT | | 25 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| GMJ212CB7105∏GHT | | 35 | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| UMJ212BB7103[]GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| UMJ212BB7223[]GHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| UMJ212BB7473[]GHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| UMJ212BB7104[]GHT | | 50 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| UMJ212BB7224[]GHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| UMJ212CC7474 GHTE | | | | X7S | 0.47 μ | ±10, ±20 | 3.5 | 150 | 1.25+0.25/-0 | *1, *2 |
| UMJ212CB7105∏GHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 1.25+0.25/-0 | *1, *2 |
| HMJ212KB7102 DHT | | | | X7R | 1000 p | ±10, ±20 | 3.5 | 200 | 0.85±0.15 | *1, *2 |
| HMJ212KB7222 DHT | | | | X7R | 2200 p | ±10, ±20 | 3.5 | 200 | 0.85 ± 0.15 | *1, *2 |
| HMJ212BB7472∏GHT | | | | X7R | 4700 p | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212BB7103∏GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212BB7223∏GHT | | 100 | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212BB7473∏GHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212BB7104 GHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212BB7224 GHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25+0.20/-0 | *1, *2 |
| HMJ212CC7474[]GHTE | | | | X7S | 0.47 μ | ±10, ±20 | 3.5 | 150 | 1.25+0.25/-0 | *1, *2 |
| QMJ212KB7102 DHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 150 | 0.85 ± 0.15 | *1, *2 |
| QMJ212KB7222 DHT | | | | X7R | 2200 p | ±10, ±20 | 2.5 | 150 | 0.85±0.15 | *1, *2 |
| QMJ212BB7472 GHT | | 250 | | X7R | 4700 p | ±10, ±20 | 2.5 | 150 | 1.25+0.20/-0 | *1, *2 |
| QMJ212BB7103 GHT | | | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 150 | 1.25+0.20/-0 | *1, *2 |
| QMJ212BB7223[]GHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 150 | 1.25+0.20/-0 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

[Temperature Characteristic B7: X7R(-55~+125°C), C7: X7S(-55~+125°C)] 1.15mm thickness(F), 1.6mm thickness(L)

| I Temperature Charac | cteristic b/: A/R(- | -33~ + 123 (| 5), 67: | X/3(- | 35~ + 125 C/] | 1.15mm thickne | ess(r), i. | omm thickness (| L) | |
|----------------------|---------------------|-------------------------|---------|-----------|---------------|----------------|------------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | Rated voltage | Tempe | erature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
| Fart number 1 | Fart Humber 2 | [V] | charac | teristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| LMJ316BB7226 LHT | | 10 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| EMJ316BB7475[]LHT | | 16 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| EMJ316BB7106[]LHT | | 10 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| TMJ316BB7474 LHT | | | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| TMJ316BB7475[LHT | | 25 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| TMJ316BB7106[LHT | | Ī | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| GMJ316BB7474□LHT | | | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| GMJ316AB7225 LHT | | 35 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| GMJ316BB7475 LHT | | 33 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| GMJ316BB7106□LHT | | 1 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.30 | *1, *2 |
| UMJ316BB7473[]LHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| UMJ316BB7104[]LHT | | Ī | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| UMJ316BB7224[]LHT | | Ī | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| UMJ316BB7474[]LHT | | 50 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| UMJ316BB7105[]LHT | |] | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| UMJ316AB7225[]LHT | | 1 | | X7R | 2.2 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1, *2 |
| UMJ316BC7475[LHTE | | | | X7S | 4.7 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.30 | *1, *2 |
| HMJ316 B7102[FHT | | | | X7R | 1000 p | ±10, ±20 | 3.5 | 200 | 1.15±0.10 | *1, *2 |
| HMJ316 B7222[]FHT | | 1 | | X7R | 2200 p | ±10, ±20 | 3.5 | 200 | 1.15±0.10 | *1, *2 |
| HMJ316 B7472[FHT | | 1 | | X7R | 4700 p | ±10, ±20 | 3.5 | 200 | 1.15±0.10 | *1, *2 |
| HMJ316KB7103[FHT | | 1 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.15±0.20 | *1, *2 |
| HMJ316BB7223[]LHT | |] | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BB7473[LHT | | 100 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BB7104[]LHT | | 1 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BB7224[]LHT | | 1 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BB7474[]LHT | | 1 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BB7105[]LHT | | 1 | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.30 | *1, *2 |
| HMJ316BC7225□LHTE | | | | X7S | 2.2 μ | ±10, ±20 | 3.5 | 150 | 1.6±0.30 | *1, *2 |
| QMJ316 B7102 FHT | | 1 | | X7R | 1000 p | ±10, ±20 | 2.5 | 150 | 1.15±0.10 | *1, *2 |
| QMJ316 B7222 FHT | | 1 | | X7R | 2200 p | ±10, ±20 | 2.5 | 150 | 1.15±0.10 | *1, *2 |
| QMJ316 B7472 FHT | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 150 | 1.15±0.10 | *1, *2 |
| QMJ316KB7103[FHT | | 250 | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 150 | 1.15±0.20 | *1, *2 |
| QMJ316BB7223 LHT | | 1 | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.30 | *1, *2 |
| QMJ316BB7473[]LHT | | 1 | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.30 | *1, *2 |
| QMJ316BB7104[]LHT | | | | X7R | 0.1 μ | ±10, ±20 | 2.5 | 150 | 1.6±0.30 | *1, *2 |
| SMJ316 B7102[]FHT | • | 1 | | X7R | 1000 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 |
| SMJ316 B7222[]FHT | • | 1 | | X7R | 2200 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 |
| SMJ316 B7472[FHT | | 630 | | X7R | 4700 p | ±10, ±20 | 2.5 | 120 | 1.15±0.10 | *1, *2 |
| SMJ316KB7103[FHT | | 1 | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 120 | 1.15±0.20 | *1, *2 |
| SMJ316BB7223[]LHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 120 | 1.6±0.30 | *1, *2 |

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic B7 : X7R($-55 \sim +125^{\circ}$ C), C7 : X7S($-55 \sim +125^{\circ}$ C)] 1.9mm thickness(N), 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|--------------------|---------------|---------------|---------|----------|-------------|------------------|-------------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| JMJ325KB7476 MHP | | 6.3 | | X7R | 47 μ | ±10, ±20 | 10 | 150 | 2.5 ± 0.30 | *1, *2 |
| EMJ325KB7226 MHP | | 16 | | X7R | 22 μ | ±10, ±20 | 10 | 150 | 2.5 ± 0.30 | *1, *2 |
| TMJ325AB7475[]MHP | | 25 | | X7R | 4.7 μ | ±10, ±20 | 5 | 150 | 2.5±0.30 | *1, *2 |
| TMJ325KB7106☐MHP | | 25 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 2.5±0.30 | *1, *2 |
| GMJ325AB7475 MHP | | 35 | | X7R | 4.7 μ | ±10, ±20 | 5 | 150 | 2.5±0.30 | *1, *2 |
| GMJ325KB7106[]MHP | | 33 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 2.5 ± 0.30 | *1, *2 |
| UMJ325AB7225[]MHP | | | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5 ± 0.30 | *1, *2 |
| UMJ325AB7475[]MHP | | 50 | | X7R | 4.7 μ | $\pm 10, \pm 20$ | 5 | 150 | 2.5±0.30 | *1, *2 |
| UMJ325KB7106 MHP | | | | X7R | 10 μ | $\pm 10, \pm 20$ | 10 | 150 | 2.5 ± 0.30 | *1, *2 |
| HMJ325 B7223[NHT | | 1 | | X7R | 0.022 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325 B7473[NHT | | 1 | | X7R | 0.047 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325 B7104[NHT | | 1 | | X7R | 0.1 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325 B7224[NHT | | 100 | | X7R | 0.22 μ | $\pm 10, \pm 20$ | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325 B7474[NHT | | 100 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325 B7105[NHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1, *2 |
| HMJ325AB7225[MHP | | | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.30 | *1, *2 |
| HMJ325KC7475[]MHPE | | | | X7S | 4.7 μ | ±10, ±20 | 3.5 | 150 | 2.5±0.30 | *1, *2 |
| QMJ325 B7223[NHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMJ325 B7473[NHT | | 250 | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMJ325 B7104[NHT | | 230 | | X7R | 0.1 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| QMJ325 B7224[NHT | | | | X7R | 0.22 μ | ±10, ±20 | 2.5 | 150 | 1.9±0.20 | *1, *2 |
| SMJ325 B7223[NHT | | 630 | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 120 | 1.9±0.20 | *1, *2 |
| SMJ325 B7473[]NHT | | 000 | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 120 | 1.9±0.20 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

LW Reversal Decoupling Capacitors (LWDCTM)

●105TYPE (Dimension:0.52 × 1.0mm JIS:0510 EIA:0204)

[Temperature Characteristic BJ : $X5R(-55\sim+85^{\circ}C)$] 0.3mm thickness(P)

| Part number 1 | Part number 2 | Rated voltage [V] | erature eristics | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|------------------|---------------|----------------------|---------------------|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| TWK105 BJ104MPHF | | 25 | X5R | 0.1 μ | ±20 | 5 | 150 | 0.3 ± 0.05 | *1, *2 |
| EWK105 BJ224MPHF | | 16 | X5R | 0.22 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| LWK105 BJ474MPHF | | 10 | X5R | 0.47 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| AWK105 BJ105MPHF | | 4 | X5R | 1 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |

[Temperature Characteristic C6: X6S(-55~+105°C), C7: X7S(-55~+125°C] 0.3mm thickness(P)

| D | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| EWK105 C6104MPHF | | 16 | | X6S | 0.1 μ | ±20 | 5 | 150 | 0.3 ± 0.05 | *1, *2 |
| LWK105 C7104MPHF | | 10 | | X7S | 0.1 μ | ±20 | 5 | 150 | 0.3 ± 0.05 | *1, *2 |
| LWK105 C6224MPHF | | 10 | | X6S | 0.22 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| JWK105 C7104MPHF | | | | X7S | 0.1 μ | ±20 | 5 | 150 | 0.3 ± 0.05 | *1, *2 |
| JWK105 C7224MPHF | | 6.3 | | X7S | 0.22 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| JWK105 C6474MPHF | | | | X6S | 0.47 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| AWK105 C7224MPHF | | 4 | | X7S | 0.22 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |
| AWK105 C6474MPHF | | 7 | | X6S | 0.47 μ | ±20 | 10 | 150 | 0.3 ± 0.05 | *1, *2 |

●107TYPE (Dimension:0.8 × 1.6mm JIS:0816 EIA:0306)

[Temperature Characteristic BJ : $X5R(-55\sim+85^{\circ}C)$] 0.5mm thickness(V)

| Part number 1 | Part number 2 | Rated voltage [V] | erature eristics | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|------------------|---------------|----------------------|---------------------|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| LWK107 BJ105MVHT | | 10 | X5R | 1 μ | ±20 | 10 | 150 | 0.5 ± 0.05 | *1, *2 |
| JWK107 BJ225MVHT | | 6.3 | X5R | 2.2 μ | ±20 | 10 | 150 | 0.5 ± 0.05 | *1, *2 |
| JWK107 BJ475MVHT | | 0.5 | X5R | 4.7 μ | ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |

[Temperature Characteristic B7 : X7R($-55 \sim +125^{\circ}$ C), C6 : X6S($-55 \sim +105^{\circ}$ C), C7 : X7S($-55 \sim +125^{\circ}$ C)] 0.5mm thickness(V)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|--------|
| Farcillumber | Fart number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| TWK107 B7104MVHT | | 25 | | X7R | 0.1 μ | ±20 | 5 | 150 | 0.5 ± 0.05 | *1, *2 |
| EWK107 B7224MVHT | | 16 | | X7R | 0.22 μ | ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| EWK107 B7474MVHT | | 10 | | X7R | 0.47 μ | ±20 | 5 | 150 | 0.5±0.05 | *1, *2 |
| LWK107 B7474MVHT | | 10 | | X7R | 0.47 μ | ±20 | 5 | 150 | 0.5 ± 0.05 | *1, *2 |
| JWK107 C7105MVHT | | 6.3 | | X7S | 1 μ | ±20 | 10 | 150 | 0.5±0.05 | *1, *2 |
| AWK107 C6225MVHT | | 4 | | X6S | 2.2 μ | ±20 | 10 | 150 | 0.5 ± 0.05 | *1, *2 |
| AWK107 C6475MVHT | | 4 | | X6S | 4.7 μ | ±20 | 10 | 150 | 0.5 ± 0.05 | *1, *2 |

212TYPE (Dimension:1.25 × 2.0mm JIS:1220 EIA:0508)

[Temperature Characteristic BJ : $X5R(-55 \sim +85^{\circ}C)$] 0.85mm thickness(D)

| Part number 1 | Part number 2 | Rated voltage [V] | Temper characte | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|------------------|---------------|-------------------|--------------------|-----|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| LWK212 BJ475 DHT | | 10 | | X5R | 4.7 μ | ±10, ±20 | 10 | 150 | 0.85±0.10 | *1, *2 |
| JWK212 BJ106MDHT | | 6.3 | | X5R | 10 μ | ±20 | 10 | 150 | 0.85±0.10 | *1, *2 |
| AWK212 BJ226MDHT | | 4 | | X5R | 22 μ | ±20 | 10 | 150 | 0.85±0.10 | *1, *2 |

[Temperature Characteristic C6 : $X6S(-55 \sim +105^{\circ}C)$] 0.85mm thickness(D)

| Part number 1 | Part number 2 | Rated voltage [V] | Temper characte | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|-------------------|---------------|----------------------|--------------------|-----|--------------------|------------------------------|--------------|------------------------|------------------|--------|
| JWK212 C6475[]DHT | | 6.3 | | X6S | 4.7 μ | ±10, ±20 | 10 | 150 | 0.85 ± 0.10 | *1, *2 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

- · All the Multilayer Ceramic Capacitors of the catalog lineup are RoHS compliant.
- Capacitance tolerance code is applied to □ of part number.
- All the Multilayer Ceramic Capacitors in the catalog lineup are applicable for reflow-soldering.

- The exchange of individual specifications is necessary depending on the application and circuit condition. Please contact Taiyo Yuden sales channels.

 *1: Automotive (AEC-Q200 Qualified) products for POWERTRAIN, and SAFETY. Please check "Automotive Application Guide" for further details before using the products.

: AEC-Q200 qualified>

All the Multilayer Ceramic Capacitors of *1 marks are tested based on the test conditions and methods defined in AEC-Q200 family item.

125°C products: AEC-Q200 Grade1 (we conduct the evaluation at the test condition of Grade1.)

Please consult with TAIYO YUDEN's official sales channel for the details of the product specification and AEC-Q200 test results, etc.,

and please review and approve TAIYO YUDEN's product specification before ordering.

• *3: For standard case size, please kindly refer to @Dimension, @Dimension tolerance, @Thickness and STANDARD EXTERNAL DIMENSIONS.

High Reliability Application Multilayer Ceramic Capacitors

●105TYPE (Demension:1.0 × 0.5mm JIS:1005 EIA:0402)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 0.5mm thickness(V)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | *3 5 3 | Note |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| UMF105 B7102 UHF | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| UMF105 B7222 □VHF | | 50 | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| UMF105 B7472 UHF | | 30 | | X7R | 4700 p | ±10, ±20 | 2.5 | 150 | 0.5 ± 0.05 | *1 |
| UMF105 B7103[]VHF | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| TMF105 B7102 VHF | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| TMF105 B7222 VHF | | | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| TMF105 B7472 VHF | | 25 | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| TMF105 B7103[]VHF | | 23 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| TMF105 B7223 VHF | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 150 | 0.5 ± 0.05 | *1 |
| TMF105 B7473[]VHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 150 | 0.5 ± 0.05 | *1 |
| EMF105 B7102 VHF | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7222 VHF | | | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7472 VHF | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7103[]VHF | | 16 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7223[]VHF | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7473[]VHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| EMF105 B7104[]VHF | | | | X7R | 0.1 μ | ±10, ±20 | 5 | 150 | 0.5 ± 0.05 | *1 |
| LMF105 B7102[]VHF | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| LMF105 B7222 UHF | | | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 0.5 ± 0.05 | *1 |
| LMF105 B7472[]VHF | | | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 0.5±0.05 | *1 |
| LMF105 B7103[]VHF | | 10 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| LMF105 B7223[]VHF | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| LMF105 B7473[]VHF | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 0.5 ± 0.05 | *1 |
| LMF105 B7104[]VHF | | | | X7R | 0.1 μ | ±10, ±20 | 5 | 200 | 0.5±0.05 | *1 |

●107TYPE (Dimension:1.6 × 0.8mm JIS:1608 EIA:0603)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 0.8mm thickness(A)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | $	an\delta$ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------------|-------------------|------------------|------|
| Part Humber 1 | Fart Humber 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| UMF107 B7223[]AHT | | 50 | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| UMF107 B7104[]AHT | | 30 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| TMF107 B7223□AHT | | 25 | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| TMF107 B7104□AHT | | 23 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| EMF107 B7223□AHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| EMF107 B7104□AHT | | 16 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| EMF107 B7105∏AHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1 |
| LMF107 B7223∏AHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| LMF107 B7104∏AHT | | 10 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 0.8±0.10 | *1 |
| LMF107 B7105∏AHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 0.8±0.10 | *1 |
| | | | | | | | | | | |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

212TYPE (Dimension:2.0 × 1.25mm JIS:2012 EIA:0805)

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.25mm thickness(G)

| Part number 1 | Part number 2 | Rated voltage [V] | Tempe charact | | Capacitance [F] | Capacitance tolerance [%] | tan δ [%] | HTLT Rated voltage x % | Thickness*3 [mm] | Note |
|-------------------|---------------|----------------------|------------------|-----|--------------------|------------------------------|--------------|------------------------|------------------|------|
| HMF212 B7103 GHT | | 100 | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| HMF212 B7223∏GHT | | 100 | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7103∏GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7223 GHT | | Ī | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7473 GHT | | 50 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7104 GHT | |] 30 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7224[]GHT | | [| | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| UMF212 B7105[]GHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1 |
| TMF212 B7103 GHT | | | | X7R | 0.01 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| TMF212 B7223 GHT | | | | X7R | 0.022 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| TMF212 B7473 GHT | | 25 | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| TMF212 B7104 GHT | | 25 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| TMF212 B7224 GHT | | [| | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| TMF212 B7105 GHT | | | | X7R | 1 μ | ±10, ±20 | 10 | 200 | 1.25±0.10 | *1 |
| EMF212 B7473 GHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| EMF212 B7104 GHT | | [| | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| EMF212 B7224 GHT | | 16 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| EMF212 B7105 GHT | | [| | X7R | 1 μ | ±10, ±20 | 10 | 200 | 1.25±0.10 | *1 |
| EMF212AB7475 GHT | | | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25+0.15/-0.05 | *1 |
| LMF212 B7473 GHT | | | | X7R | 0.047 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| LMF212 B7104 GHT | | | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| LMF212 B7224 GHT | | 10 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.25±0.10 | *1 |
| LMF212 B7105 GHT | | I | | X7R | 1 μ | ±10, ±20 | 10 | 200 | 1.25±0.10 | *1 |
| LMF212 B7475 GHT | | | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.25±0.10 | *1 |

316TYPE (Dimension:3.2 × 1.6mm JIS:3216 EIA:1206)

 $\begin{tabular}{ll} \textbf{[Temperature Characteristic B7: X7R($-55$$$$\sim$+125$$^\circ$$C)]} & 1.15 mm thickness(F) \end{tabular}$

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness [mm] | Note |
| HMF316 B7102[]FHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| HMF316 B7222 FHT | | 100 | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| HMF316 B7472 FHT | | 100 | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| HMF316 B7103[]FHT | | | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| UMF316 B7102[]FHT | | | | X7R | 1000 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| UMF316 B7222[]FHT | | 50 | | X7R | 2200 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| UMF316 B7472[]FHT | | 30 | | X7R | 4700 p | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |
| UMF316 B7103[]FHT | | | | X7R | 0.01 μ | ±10, ±20 | 2.5 | 200 | 1.15±0.10 | *1 |

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 1.6mm thickness(L)

| Part numbe | r 1 | Part number 2 | Rated voltage | | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-----------------|-----|-----------------|---------------|---------|----------|-------------|---------------|-------|-------------------|-------------------|-------|
| i di ci idilibe | | T di C Hamber 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | THICKNESS [IIIII] | 14000 |
| HMF316 B7104□l | _HT | | 100 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1 |
| UMF316 B7104[]I | _HT | | 50 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1 |
| UMF316 B7105∏I | _HT | | 50 | | X7R | 1 μ | ±10, ±20 | 3.5 | 150 | 1.6±0.20 | *1 |
| TMF316 B7104[]L | _HT | | 25 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.6±0.20 | *1 |
| TMF316AB7475 | LHT | | 25 | | X7R | 4.7 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1 |
| EMF316AB7106 | LHT | | 16 | | X7R | 10 μ | ±10, ±20 | 10 | 150 | 1.6±0.20 | *1 |
| JMF316AB7106[] | LHT | | 6.3 | · | X7R | 10 μ | ±10, ±20 | 10 | 200 | 1.6±0.20 | *1 |

325TYPE (Dimension:3.2 × 2.5mm JIS:3225 EIA:1210)

[Temperature Characteristic B7 : X7R($-55\sim+125^{\circ}$ C)] 2.5mm thickness(M)

| Part number 1 | Part number 2 | Rated voltage | Tempe | rature | Capacitance | Capacitance | tan δ | HTLT | Thickness*3 [mm] | Note |
|-------------------|---------------|---------------|---------|----------|-------------|---------------|-------|-------------------|------------------|------|
| Part number 1 | Part number 2 | [V] | charact | eristics | [F] | tolerance [%] | [%] | Rated voltage x % | Inickness [mm] | Note |
| HMF325 B7225 MHP | | 100 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 150 | 2.5±0.20 | *1 |
| UMF325 B7225 ☐MHP | | 50 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1 |
| UMF325 B7475 ☐MHP | | 30 | | X7R | 4.7 μ | ±10, ±20 | 5 | 150 | 2.5±0.20 | *1 |
| TMF325 B7225[]MHP | | 25 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1 |
| TMF325 B7475[]MHP | | 23 | | X7R | 4.7 μ | ±10, ±20 | 5 | 200 | 2.5±0.20 | *1 |
| EMF325 B7225[]MHP | | 16 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5 ± 0.20 | *1 |
| EMF325 B7475[]MHP | | 10 | | X7R | 4.7 μ | ±10, ±20 | 5 | 200 | 2.5±0.20 | *1 |
| LMF325 B7225 MHP | | 10 | | X7R | 2.2 μ | ±10, ±20 | 3.5 | 200 | 2.5±0.20 | *1 |
| LMF325 B7475[]MHP | | 10 | | X7R | 4.7 μ | ±10, ±20 | 5 | 200 | 2.5±0.20 | *1 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

[Temperature Characteristic B7 : $X7R(-55 \sim +125^{\circ}C)$] 1.9mm thickness(N)

| Part number 1 | Part number 2 | Rated voltage | Temperat | ure | Capacitance | Capacitance | tan δ | HTLT | *3 5 3 | Note |
|-------------------|---------------|---------------|-------------|-------|-------------|---------------|-------|-------------------|------------------|------|
| Part number 1 | Part number 2 | [V] | characteris | stics | [F] | tolerance [%] | [%] | Rated voltage x % | Thickness*3 [mm] | Note |
| HMF325 B7223[NHT | | 100 | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 200 | 1.9±0.20 | *1 |
| HMF325 B7473[NHT | | 100 | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 200 | 1.9±0.20 | *1 |
| UMF325 B7223[NHT | | | | X7R | 0.022 μ | ±10, ±20 | 2.5 | 200 | 1.9±0.20 | *1 |
| UMF325 B7473[NHT | | I | | X7R | 0.047 μ | ±10, ±20 | 2.5 | 200 | 1.9±0.20 | *1 |
| UMF325 B7104[NHT | | 50 | | X7R | 0.1 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| UMF325 B7224[NHT | |] 30 | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1 |
| UMF325 B7474[]NHT | | | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| UMF325 B7105□NHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1 |
| TMF325 B7224 NHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1 |
| TMF325 B7474 NHT | | 25 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1 |
| TMF325 B7105□NHT | | Ī | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| EMF325 B7224□NHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| EMF325 B7474□NHT | | 16 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| EMF325 B7105□NHT | | Ī | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| LMF325 B7224□NHT | | | | X7R | 0.22 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| LMF325 B7474□NHT | | 10 | | X7R | 0.47 μ | ±10, ±20 | 3.5 | 200 | 1.9 ± 0.20 | *1 |
| LMF325 B7105[NHT | | | | X7R | 1 μ | ±10, ±20 | 3.5 | 200 | 1.9±0.20 | *1 |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■PACKAGING

1)Minimum Quantity


| T (514) | Thick | ness | Standard of | quantity [pcs] |
|------------------------------|---------|------|-------------|-----------------|
| Type(EIA) | mm | code | Paper tape | Embossed tape |
| □MK021(008004) | 0.105 | V | | F0000 |
| □VS021(008004) | 0.125 | К | _ | 50000 |
| ☐MK042(01005) | 0.2 | C, D | | 40000 |
| □VS042(01005) | 0.2 | С | | 40000 |
| ☐MK063(0201) | 0.3 | P,T | 15000 | _ |
| □WK105(0204) ※ | 0.3 | Р | 10000 | _ |
| | 0.13 | Н | _ | 20000 |
| Thu(105(0400) | 0.18 | E | _ | 15000 |
| ☐MK105(0402) | 0.2 | С | 20000 | _ |
| □MF105(0402) | 0.3 | Р | 15000 | _ |
| | 0.5 | ٧ | 10000 | _ |
| □VK105(0402) | 0.5 | W | 10000 | _ |
| □MK107(0603) | 0.45 | K | 4000 | _ |
| □WK107(0306) ※ | 0.5 | V | _ | 4000 |
| □MF107(0603) | 0.8 | Α | 4000 | _ |
| □VS107(0603) | 0.7 | С | 4000 | _ |
| □MJ107(0603) | 0.8 | Α | 3000 | 3000 |
| □MK212(0805) | 0.45 | K | 4000 | |
| □WK212(0508) ※ | 0.85 | D | 4000 | _ |
| □MF212(0805) | 1.25 | G | _ | 3000 |
| □VS212(0805) | 0.85 | D | 4000 | _ |
| [] N. 104.0(0.005) | 0.85 | D | 4000 | _ |
| □MJ212(0805) | 1.25 | G | _ | 2000 |
| DM (040(4000) | 0.85 | D | 4000 | _ |
| ☐MK316(1206) | 1.15 | F | _ | 3000 |
| □MF316(1206) | 1.6 | L | _ | 2000 |
| The 1040(4000) | 1.15 | F | _ | 3000 |
| □MJ316(1206) | 1.6 | L | _ | 2000 |
| | 0.85 | D | | |
| DM/205(1010) | 1.15 | F | | 2000 |
| □MK325(1210) □MF325(1210) | 1.9 | N | | 2000 |
| | 2.0max. | Υ | | |
| | 2.5 | М | _ | 1000 |
| □MJ325(1210) | 1.9 | N | _ | 2000 |
| □INIO9520(1510) | 2.5 | М | _ | 500(T), 1000(P) |
| □MK432(1812) | 2.5 | М | _ | 500 |

Note:


K LW Reverse type.

**No bottom tape for pressed carrier tape Card board carrier tape Top tape Base tape Sprocket hole Chip cavity Base tape Chip cavity

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




3 Representative taping dimensions




| Type(EIA) | Chip | Cavity | Insertion Pitch | Tape Th | nickness |
|---------------------|------|--------|-----------------|----------|----------|
| Type(EIA) | Α | В | F | Т | T1 |
| □MK063(0201) | 0.37 | 0.67 | | 0.45max. | 0.42max. |
| □WK105(0204) ※ | | | 2.0±0.05 | 0.45max. | 0.42max. |
| □MK105(0402) (*1 C) | 0.65 | 1.15 | 2.0±0.05 | 0.4max. | 0.3max. |
| □MK105(0402) (*1 P) | | | | 0.45max. | 0.42max. |

Note *1 Thickness, C:0.2mm ,P:0.3mm. * LW Reverse type.

Unit:mm



| Type(EIA) | Chip | Cavity | Insertion Pitch | Tape Thickness |
|---------------|------|--------|-----------------|----------------|
| Type(EIA) | Α | В | F | Т |
| ☐MK105 (0402) | | | | |
| ☐MF105 (0402) | 0.65 | 1.15 | 2.0 ± 0.05 | 0.8max. |
| □VK105 (0402) | | | | |
| | • | | | Unit:mm |




This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| Type(EIA) | Chip (| Cavity | Insertion Pitch | Tape Thickness |
|----------------|--------|--------|-----------------|----------------|
| Type(EIA) | Α | В | F | Т |
| ☐MK107(0603) | | | | |
| □WK107(0306) ※ | 1.0 | 1.8 | | 1.1max. |
| ☐MF107(0603) | | | 40+01 | |
| ☐MK212(0805) | 1.65 | 0.4 | 4.0±0.1 | |
| □WK212(0508) ※ | 1.65 | 2.4 | | 1.1max. |
| ☐MK316(1206) | 2.0 | 3.6 | | |


Note: Taping size might be different depending on the size of the product. X LW Reverse type.

Unit:mm



| Type(EIA) | Chip (| Cavity | Insertion Pitch | Tape Ti | nickness |
|----------------|--------|--------|-----------------|---------|----------|
| Type(EIA) | Α | В | F | K | Т |
| ☐MK021(008004) | 0.135 | 0.27 | | | |
| □VS021(008004) | 0.135 | 0.27 | 1.0±0.02 | 0.5max. | 0.25max. |
| ☐MK042(01005) | 0.23 | 0.43 | 1.0 ± 0.02 | o.omax. | 0.25max. |
| □VS042(01005) | 0.23 | 0.43 | | | |


Unit:mm



| Type(EIA) | Chip (| Cavity | Insertion Pitch | Tape Th | nickness |
|------------------------------|--------|--------|-----------------|---------|----------|
| Type(EIA) | Α | В | F | K | Т |
| ☐MK105(0402) | 0.6 | 1.1 | 2.0±0.1 | 0.6max | 0.2±0.1 |
| □WK107(0306) ※ | 1.0 | 1.8 | | 1.3max. | 0.25±0.1 |
| ☐MK212(0805) ☐MF212(0805) | 1.65 | 2.4 | | | |
| ☐MK316(1206) ☐MF316(1206) | 2.0 | 3.6 | 4.0±0.1 | 3.4max. | 0.6max. |
| ☐MK325(1210) ☐MF325(1210) | 2.8 | 3.6 |] | | |

Note: ※ LW Reverse type. Unit:mm


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




| Type(EIA) | Chip (| Cavity | Insertion Pitch | Tape Th | nickness |
|--------------|--------|--------|-----------------|---------|----------|
| Type(EIA) | Α | В | F | K | Т |
| ☐MK325(1210) | 3.1 | 4.0 | 8.0±0.1 | 4.0max. | 0.6max. |
| ☐MK432(1812) | 3.7 | 4.9 | 8.0±0.1 | 4.0max. | 0.6max. |

Unit:mm

4 Trailer and Leader



⑤Reel size




| Α | В | С | D | E | R |
|------------------|-----------------|-----------------------|-------------------|---------|-----|
| ϕ 178 ± 2.0 | <i>ф</i> 50min. | ϕ 13.0 \pm 0.2 | ϕ 21.0 ± 0.8 | 2.0±0.5 | 1.0 |

| | T | W |
|----------------|---------|--------|
| 4mm wide tape | 1.5max. | 5±1.0 |
| 8mm wide tape | 2.5max. | 10±1.5 |
| 12mm wide tape | 2.5max. | 14±1.5 |

Unit:mm

6Top Tape Strength

The top tape requires a peel-off force of 0.1 to 0.7N in the direction of the arrow as illustrated below.



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Multilayer Ceramic Capacitors

■RELIABILITY DATA

| | mperature Range | Standard | | | | |
|-----------------------|----------------------------------|---------------------|--------------|----------------------|---------------------------|--------------|
| | Temperature Compensating(Class1) | | −55 to + | -125°C | | |
| | Compensating (Class I) | High Frequency Type | | | | |
| | | | | | | |
| | | | | Specification | Temperature Range |) |
| | | | BJ | В | −25 to +85°C | |
| pecified | | | | X5R | -55 to +85°C | |
| /alue | | | B7 | X7R | −55 to +125°C | |
| | High Permittivity (Class2) | | C6 | X6S | −55 to +105°C | |
| | | | C7 | X7S | -55 to +125℃ | |
| | | | D7 | X7T | -55 to +125°C | |
| | | | LD(※) | X5R | −55 to +85°C | |
| | | | Note: 🔆 | LD Low distortion hi | gh value multilayer ceran | nic capacito |
| | | | | | | |
| | | | | | | |
| Storage Cor | nditions | | | | | |
| | T | Standard | | | | |
| | Temperature Compensating(Class1) | | −55 to + | -125°C | | |
| | Compensating (Class I) | High Frequency Type | | | | |
| | | | | Specification | Temperature Range | ÷ |
| | | | BJ | В | −25 to +85°C | |
| pecified | | | В | X5R | −55 to +85°C | |
| alue | | | B7 | X7R | −55 to +125°C | |
| | High Permittivity (Class2) |) | C6 | X6S | -55 to +105°C | |
| | | | C7 | X7S | −55 to +125°C | |
| | | | D7 | X7T | −55 to +125°C | |
| | | | LD(※) | X5R | −55 to +85°C | |
| | | | Note: 🔆 | LD Low distortion hi | gh value multilayer ceran | nic capacit |
| | | | • | | | |
| Rated Voltag | Υ <u>Α</u> | | | | | |
| Mateu Volta | | 0 | 50) (D.O. 05 | | | |
| Specified | Temperature | Standard | 50VDC, 25 | VDC | | |
| /alue | Compensating(Class1) | High Frequency Type | 50VDC, 25 | VDC | | |
| 2.00 | High Permittivity (Class2) | | 50VDC, 35 | VDC, 25VDC, 16VDC | C, 10VDC, 6.3VDC, 4VDC, | , 2.5VDC |
| | | | | | | |
| Withstanding | y Voltage (Between terminal | 2) | | | | |
| . withstanding | voltage (between terminal | | | | | |
| D | Temperature | Standard | | | | |
| Specified | Compensating(Class1) | High Frequency Type | No breakdo | own or damage | | |
| 'alue | High Permittivity (Class2) | | | | | |
| | , , | | ass 1 | | ass 2 | |
| est | Applied voltage | | volta×3 | | ass 2 oltage × 2.5 | |
| ฮรเ | Applied voltage | Rated | | 1 to 5 sec. | ortage ^ Z.0 | |
| | Duration | | | | 1 | |
| lethods and emarks | Duration Charge/discharge currer | | | 50mA max. | | |

Standard Temperature 10000 $M\,\Omega$ min. ${\sf Compensating}({\sf Class1})$ High Frequency Type Specified Value C \leq 0.047 μ F : 10000 M Ω min. High Permittivity (Class2) Note 1 C>0.047 μ F : 500M Ω • μ F : Rated voltage Test Applied voltage Methods and Duration : 60±5 sec. Remarks Charge/discharge current : 50mA max.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 6. Capacitance | (Tolerance) | | | | | |
|------------------------|----------------------------|--|------------------------------|---------------------------------------|--|-------------------------|
| Specified Value | Temperature | Standard | C □ U □ SL | 0.2pF≦C≦5pF 0.2pF≦C≦10pF C>10pF | : ±0.25pF : ±0.5pF : ±5% or ±10% | |
| | Compensating(Class1) | High Frequency Type | СН | 0.3pF≦C≦2pF C>2pF | : ±0.1pF : ±5% | |
| | High Permittivity (Class2) | BJ, B7, C6, C7, D7, LD($\overset{\cdot}{\times}$): $\pm 10\%$ or $\pm 20\%$ Note: $\overset{\cdot}{\times}$ LD Low distortion high value multilayer ceramic capacitor | | | | |
| | | | Class 1 | | Cla | ass 2 |
| - . | | Standard | Standard High Frequency Type | | C≦10 µF | C>10 µF |
| Test | Preconditioning | | None | | Thermal treatment (a | t 150°C for 1hr) Note 2 |
| Methods and Remarks | Measuring frequency | | 1MHz±10% | | 1kHz±10% | 120±10Hz |
| Remarks | Measuring voltage Note | | 0.5 to ! | 5Vrms | 1±0.2Vrms | 0.5±0.1rms |
| | Bias application | | | | one | |

| Specified Value | Temperature | | Standard | | OpF: Q≥400+20C OpF: Q≥1000 (C:No | ominal capacitance) | | |
|--------------------|-----------------------------------|---------------------|--------------|---------|-------------------------------------|---|----------|--|
| | Compensating(Class1) | High Frequency Type | | Refer | to detailed specification | | | |
| | High Permittivity (Class2) Note 1 | | | BJ, B | 7, C6, C7, D7:2.5% max. | | | |
| | | | | Class 1 | | Class 2 | | |
| | | | Standard | | High Frequency Type | C≦10 <i>µ</i> F | C>10 µF | |
| | Preconditioning | | | None | | Thermal treatment (at 150°C for 1hr) Note 2 | | |
| Test | Measuring frequey | | 1MHz±10% | | 1GHz | 1kHz±10% | 120±10Hz | |
| Methods and | Measuring voltage Note 1 | | 0.5 to 5Vrms | | 1±0.2Vrms | 0.5±0.1Vrms | | |
| Remarks | Bias application | Bias application | | | None | | | |
| | High Frequency Type | | | | | | | |
| | Measuring equipment | : HP | 4291A | | | | | |
| | Measuring jig | : HP | 16192A | | | | | |

| | | | Temperature Characteristic [ppm/°C] | | | C] Tole | erance [ppm/°C] |
|-----------|-------------------------------------|---------------------|-------------------------------------|-----------------|--------------------|------------------|--------------------|
| | | | C□: | 0 | CG,CH, CJ, (| СК | G: ±30 H: ±60 |
| | Temperature Compensating(Class1) | Standard | U□ : | — 750 | UJ, UK | | J: ±120 K: ±250 |
| | | | SL : | +350 to −100 | 0 | | |
| | | High Frequency Type | Tem | perature Charac | cteristic [ppm/° | C] Tole | erance [ppm/°C] |
| | | | C□: | 0 | CH | | H: ±60 |
| Specified | | | | Specification | Capacitance | Reference | Temperature Range |
| Value | | | | opcomodicion | change | temperature | Tomporacaro riango |
| | | | BJ | В | ±10% | 20°C | −25 to +85°C |
| | | | | X5R | ±15% | 25°C | -55 to +85°C |
| | | | В7 | X7R | ±15% | 25°C | −55 to +125°C |
| | High Permittivity (Class2) | | C6 | X6S | ±22% | 25°C | −55 to +105°C |
| | | | C7 | X7S | ±22% | 25°C | −55 to +125°C |
| | | | D7 | X7S | +22/-33% | 25°C | −55 to +125°C |
| | | | | X5R | ±15% | 25°C | −55 to +85°C |
| | | | Note: | VID Low diete | rtion high value i | multilavar aaran | io consoiter |

Class 1

Capacitance at 20° C and 85° C shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation.

$$\frac{(C_{85}-C_{20})}{C_{20}\times\Delta T} \times 10^{6} (ppm/^{\circ}C) \qquad \Delta T = 65$$

Test Methods and Remarks Class 2

Capacitance at each step shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the following equation

| Step | В | X5R, X7R, X6S, X7S, X7T | | | | |
|------|-------------------------------|-------------------------|--|--|--|--|
| 1 | Minimum operat | ing temperature | | | | |
| 2 | 20°C | 25°C | | | | |
| 3 | Maximum operating temperature | | | | | |
| | | | | | | |

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

 $\frac{(C-C_2)}{C_2} \times 100(\%)$

C : Capacitance in Step 1 or Step 3

C2 : Capacitance in Step 2

| 9. Deflection | | | | |
|--------------------|----------------------|---------------------|--------------------------------|---|
| Specified Value | Temperature | I Standard I '' | | : No abnormality : Within $\pm 5\%$ or ± 0.5 pF, whichever is larger. |
| | Compensating(Class1) | High Frequency Type | Appearance Cpaitance change | : No abnormality : Within±0.5 pF |
| | | | Appearance | : No abnormality |


High Permittivity (Class2)


Capacitance change : Within ±12.5%(BJ, B7, C6, C7, D7, LD(※))

Note: XLD Low distortion high value multilayer ceramic capacitor

Test Methods and Remarks

| | Multilayer Ceramic Capacitors | | | | | |
|-----------|----------------------------------|-----------------|--|--|--|--|
| | 042, 063, ^{※1} 105 Type | The other types | | | | |
| Board | Glass epoxy-resin substrate | | | | | |
| Thickness | 0.8mm | 1.6mm | | | | |
| Warp | 1mm (Soft Termination type:3mm) | | | | | |
| Duration | 10 sec. | | | | | |





(Unit: mm)

Capacitance measurement shall be conducted with the board bent

| 10. Body Stren | 10. Body Strength | | | | | | |
|--------------------------------|---|---------------------|---------------------------|--|--|--|--|
| | Temperature | Standard | - | | | | |
| Specified Value | Compensating(Class1) | High Frequency Type | No mechanical damage. | | | | |
| Value | High Permittivity (Class2) | | | | | | |
| Test Methods and Remarks | High Frequency Type Applied force : 5N Duration : 10 sec. | Pres ← A → | R0.5 Pressing Jig Chip A | | | | |

| 11. Adhesive S | 11. Adhesive Strength of Terminal Electrodes | | | | | | | |
|--------------------|--|---------------------|----------------------|---|--|--|--|--|
| | Temperature | Standard | | | | | | |
| Specified Value | Compensating(Class1) | High Frequency Type | No terminal separati | No terminal separation or its indication. | | | | |
| | High Permittivity (Class2) | | | | | | | |
| | | Multilayer Ceram | ic Capacitors | Hooked jig | | | | |
| Test | | 042, 063 Type | 105 Type or more | | | | | |
| Methods and | Applied force | 2N | 5N | R=05 Doard | | | | |
| Remarks | Duration | 30±5 | sec. |] ←Chip | | | | |
| | | | | Chip Chip | | | | |

| 12. Solderabilit | у | | | | |
|------------------------|----------------------------|---------------------|--|----------------|----------------|
| | Temperature | Standard | At least 95% of terminal electrode is covered by | | |
| Specified Value | Compensating(Class1) | High Frequency Type | | | by new solder. |
| Value | High Permittivity (Class2) |) | | | |
| - . | Eutectic s | | Eutectic solder Lead-free solder | | |
| Test | Solder type | H60A or H | 63A | Sn-3.0Ag-0.5Cu | |
| Methods and Remarks | Solder temperature | 230±5° | С | 245±3°C | |
| Remarks | Duration | | 4±1 sec. | | |

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 13. Resistance | to Soldering | | | | |
|------------------------|-------------------------|---------------------|--|--|---|
| Specified Value | Temperature | Standard | Appearance Capacitance change Q Insulation resistance Withstanding voltage | : No abnormality : Within ±2.5% or ±0 : Initial value : Initial value (between terminals) | .25pF, whichever is larger. : No abnormality |
| | Compensating(Class1) | High Frequency Type | Appearance Capacitancecange Q Insulation resistance Withstanding voltage | : No abnormality : Within ±2.5% : Initial value : Initial value (between terminals) | : No abnormality |
| | High Permittivity(Class | 2) Note 1 | Appearance Capactace change Dissipation factor Insulation resistance Withstanding voltage Note: **LD Low distort | : No abormality : Within ±7.5%(BJ, B' : Initial value : Initial value (between terminals): tion high value multilaye | No abnormality |
| | | lss 1 | | | |
| | | 042, 063 Type | 105 Type | | |
| | Preconditioning | | None | | |
| | Preheating | 150°C, 1 to 2 min. | 80 to 100°C, 2 to 5 min. 150 to 200°C, 2 to 5 min. | | |
| | Solder temp. | | 270±5°C | | |
| | Duration | | 3±0.5 sec. | | |
| Γest | Recovery | 6 to 24 hrs | S (Standard condition) N | loe 5 | |
| Methods and Remarks | | | | Class 2 | |
| | | 042,063 Type | | 07, 212 Type | 316, 325 Type |
| | Preconditioning | . ,,,, | | (at 150°C for 1 hr) No | |
| | Preheating | 150°C, 1 to 2 min. | 80 to 10 | 0°C, 2 to 5 min. | 80 to 100°C, 5 to 10 min. 150 to 200°C, 5 to 10 min. |
| | Solder temp. | | | 70±5°C | |
| | Duration | | | ±0.5 sec. | |
| | Recovery | | | ndard condition)Note 5 | i |

| 14. Temperatur | re Cycle (Thermal Shock) | | | | | | |
|--------------------------------|-----------------------------------|---|-------------------|--|--|---|--|
| | Temperature | Standard | | Appearance Capacitance change Q Insulation resistance Withstanding voltage | : No abnormality : Within ±2.5% or ±0.25 : Initial value : Initial value (between terminals) : N | - | |
| Specified Value | Compensating(Class1) | High Frequency | [,] Туре | Appearance Capacitance change Q Insulation resistance Withstanding voltage | : No abnormality : Within ±0.25pF : Initial value : Initial value (between terminals) : N | o abnormality | |
| | High Permittivity (Class2) Note 1 | | | Appearance Capacitance change Dissipation factor Insulation resistance Withstanding voltage Note: **LD Low distort | : No abnormality : Within ±7.5% (BJ, B7, : Initial value : Initial value (between terminals) : N ion high value multilayer c | o abnormality | |
| | | | C | Class 1 Class 2 | | | |
| | Preconditioning | None | | | Thermal trea | tment (at 150°C for 1 hr) Note 2 | |
| Test Methods and Remarks | 1 cycle | Step Temperature 1 Minimum operating to Normal temperature 3 Maximum operating to Normal temperature | | | nting temperature emperature ting temperature | Time (min.) 30 ± 3 $2 \text{ to } 3$ 30 ± 3 $2 \text{ to } 3$ | |
| | Number of cycles | | | | 5 times | | |
| | Recovery | 6 to 24 hr | S (Stan | dard condition)Note 5 | 24±2 hrs (5 | Standard condition)Note 5 | |

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 15. Humidity (| Steady State) | | | |
|------------------------|------------------------------------|---------------------|---|--|
| | Temperature Compensating(Class1 | Standard) | Capacitance change Q | : No abnormality : Within $\pm 5\%$ or $\pm 0.5 pF$, whichever is larger. : $C < 10 pF$: $Q \ge 200 + 10 C$ $10 \le C < 30 pF$: $Q \ge 275 + 2.5 C$ $C \ge 30 pF$: $Q \ge 350$ (C : Nominal capacitance) : $1000 \text{ M} \Omega \text{ min}$. |
| Specified Value | | High Frequency Type | Appearance Capacitance change Insulation resistance | : No abnormality : Within $\pm 0.5 \text{pF}$, : 1000 M Ω min. |
| | High Permittivity (Cla | ass2) Note 1 | Insulation resistance | : No abnormality : Within \pm 12.5% (BJ, B7, C6, C7, D7, LD($\stackrel{.}{\otimes}$)) : 5.0% max. (BJ, B7, C6, C7, D7, LD($\stackrel{.}{\otimes}$)) : 50 M $\Omega\mu$ F or 1000 M Ω whichever is smaller. on high value multilayer ceramic capacitor |
| | | | ass 1 | Class 2 |
| _ | | Standard | High Frequency Type | |
| Test | Preconditioning | | one co Lo°o | Thermal treatment (at 150°C for 1 hr) Note 2 |
| Methods and Remarks | Temperature | 40±2°C | 60±2°C | 40±2°C 90 to 95%RH |
| Remarks | Humidity Duration | | 95%R⊓ 4/−0 hrs | 90 to 95%RH 500+24/-0 hrs |
| | Recovery | | ard condition)Note 5 | 24±2 hrs (Standard condition) Note 5 |

| 16. Humidity Lo | pading | | | | |
|--------------------|-------------------------------------|---|---|---|--|
| Specified Value | Temperature Compensating(Class1) | Standard | $\begin{tabular}{lllllllllllllllllllllllllllllllllll$ | | |
| | | High Frequency Type | $\begin{tabular}{lllllllllllllllllllllllllllllllllll$ | | |
| | High Permittivity (Class2) Note 1 | | $\begin{tabular}{lllllllllllllllllllllllllllllllllll$ | | |
| | | C | Class 1 | Class 2 | |
| | | Standard | High Frequency Typ | pe All items | |
| | Preconditioning | None | | Voltage treatment (Rated voltage are applied for 1 hour at 40°C) Note 3 | |
| Test | Temperature | 40±2°C | 60±2°C | 40±2°C | |
| Methods and | Humidity | 90 t | :o 95%RH | 90 to 95%RH | |
| Remarks | Duration | 500+ | 24/-0 hrs | 500+24/-0 hrs | |
| | Applied voltage | Rate | d voltage | Rated voltage | |
| | Charge/discharge current | 50r | mA max. | 50mA max. | |
| | Recovery | 6 to 24 hrs (Standard condition) Note 5 | | 24±2 hrs(Standard condition) Note 5 | |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 17. High Tempe | erature Loading | | | | | |
|--------------------|-------------------------------------|---|--|---|---------------------|------------------------|
| Specified Value | Temperature Compensating(Class1) | $\begin{tabular}{lllllllllllllllllllllllllllllllllll$ | | 200+10C Q≧275+2.5C | | |
| | | High Frequency Type | Appearance Capacitance change Insulation resistance | | | |
| | High Permittivity(Class2) Note 1 | | Appearance Capacitance change Dissipation factor Insulation resistance Note: **LD Low dis* | : 5.0% max.(BJ, B7, C6, C7, D7, LD(※)) | | |
| | | Class 1 | | Class 2 | | |
| | | Standard H | High Frequency Type | BJ, LD() | C6 | B7, C7, D7 |
| | Preconditioning | None | | Voltage treatment (Twice the rated voltage shall be applied for 1 hour at 85°C, 105°C or 125°C) Note 3, 4 | | |
| Test | Temperature | Maximum operating temperature | | Maximum operating temperature | | |
| Methods and | Duration | 1000+48/-0 hrs | | 1000+48/-0 hrs | | |
| Remarks | Applied voltage | Rated voltage × 2 | | Rated voltage × 2 Note 4 | | |
| | Charge/discharge current | 50mA max. | | 50mA max. | | |
| | Recovery | 6 to 24hr (Standard condition) Note 5 | | 24±2 hrs(Standard condition)Note 5 | | |
| | | | Note | *LD Low distortion | n high value multil | ayer ceramic capacitor |

Note 1 The figures indicate typical specifications. Please refer to individual specifications in detail.

- Note 2 Thermal treatment : Initial value shall be measured after test sample is heat-treated at $150 \pm 0/-10^{\circ}$ C for an hour and kept at room temperature for 24 ± 2 hours.
- Note 3 Voltage treatment: Initial value shall be measured after test sample is voltage—treated for an hour at both the temperature and voltage specified in the test conditions, and kept at room temperature for 24±2hours.
- Note 4 150% of rated voltage is applicable to some items. Please refer to their specifications for further information.
- Note 5 Standard condition: Temperature: 5 to 35°C, Relative humidity: 45 to 85 % RH, Air pressure: 86 to 106kPa When there are questions concerning measurement results, in order to provide correlation data, the test shall be conducted under the following condition.

 Temperature: 20±2°C, Relative humidity: 60 to 70 % RH, Air pressure: 86 to 106kPa Unless otherwise specified, all the tests are conducted under the

"standard condition".

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Medium-High Voltage Multilayer Ceramic Capacitor

RELIABILITY DATA

| 1. Operating Tempe | rature Range | | | | |
|-----------------------------|---|--|--|--|--|
| | Temperature Compensating(High Frequency type) CG(COG) : -55 to +125°C | | | | |
| Specified Value | High permittivity X7R, X7S : -55 to +125°C X5 : -55 to +85°C B : -25 to +85°C | | | | |
| 2. Storage Tempera | ture Range | | | | |
| | Temperature Compensating(High Frequency type) CG(COG) : -55 to +125°C | | | | |
| Specified Value | High permittivity X7R, X7S : -55 to +125°C X5R : -55 to +85°C B : -25 to +85°C | | | | |
| | | | | | |
| 3. Rated Voltage | | | | | |
| Specified Value | 100VDC(HMK,HMJ), 250VDC(QMK,QMJ,QVS), 630VDC(SMK,SMJ) | | | | |
| | | | | | |
| 4. Withstanding Volt | age (Between terminals) | | | | |
| Specified Value | No breakdown or damage | | | | |
| Test Methods and Remarks | Applied voltage : Rated voltage × 2.5 (HMK,HMJ), Rated voltage × 2 (QMK,QMJ,QVS), Rated voltage × 1.2 (SMK,SMJ) Duration : 1 to 5sec. Carge/discharge current : 50mA max. | | | | |
| | | | | | |
| 5. Insulation Resist | | | | | |
| Specified Value | Temperature Compensating(High Frequency type) $10000M\Omega\text{min}$ High permittivity | | | | |
| | 100M Ω μF or 10G Ω whichever is smaller. | | | | |
| Test Methods and Remarks | Applied voltage : Rated voltage(HMK,HMJ, QMK,QMJ,QVS), 500V(SMK,SMJ) Duration : 60±5sec. Charge/discharge current : 50mA max. | | | | |

| 6. Capacitance (To | olerance) | | | |
|-----------------------------|---|---|--|--|
| Specified Value | Temperature Compensating(High Frequency type) $\pm 0.1 pF (C < 5pF) \pm 0.25pF (C < 10pF) \pm 0.5pF (5pF \le C < 10pF) \pm 2\%(C=10pF) \pm 5\%(C \ge 10pF)$ High permittivity $\pm 10\%$, $\pm 20\%$ | | | |
| Test Methods and Remarks | Temperature Compensation Measuring frequency Measuring voltage Bias application High permittivity Measuring frequency Measuring voltage Bias application | ng(High Frequency type) : 1MHz±10% : 0.5 to 5Vrms : None : 1kHz±10% : 1±0.2Vrms : None | | |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 7. Q or Dissipation | Factor | | | | | |
|---------------------|----------------------|---------------------------|--|--|--|--|
| | Temperature Compensa | ting(High Frequency type) | | | | |
| | C<30pF: Q≧800+20C | | | | | |
| | C≧30pF: Q≧1400 | C:Normal Capacitance(/pF) | | | | |
| Specified Value | | | | | | |
| | High permittivity | | | | | |
| | 3.5%max (HMK,HMJ) | | | | | |
| | 2.5%max (QMK,QMJ, SM | K,SMJ) | | | | |
| | Temperature Compensa | ting(High Frequency type) | | | | |
| | Measuring frequency | : 1MHz±10% | | | | |
| | Measuring voltage | : 0.5 to 5Vrms | | | | |
| Test Methods and | Bas application | : None | | | | |
| Remarks | High permittivity | | | | | |
| | Measuring frequency | : 1kHz±10% | | | | |
| | Measuring voltage | : 1±0.2Vrms | | | | |
| | Bas application | : None | | | | |

| 8. Temperature Cha | cteristic of Capacitance | | | | | |
|--------------------|--|--|--|--|--|--|
| | Temperature Compensating(High Frequency type) COG :±30ppm(25 to +125°C) | | | | | |
| Specified Value | High permittivity B : $\pm 10\%(-25 \text{ to } +85^{\circ}\text{C})$ X5R : $\pm 15\%(-55 \text{ to } +85^{\circ}\text{C})$ X7R : $\pm 15\%(-55 \text{ to } +125^{\circ}\text{C})$ X7S : $\pm 22\%(-55 \text{ to } +125^{\circ}\text{C})$ | | | | | |
| | emperature Compensating(High Frequency type) apacitance at 25° C and 85° C shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the bllowing equation. $\frac{(C_{65}-C_{25})}{C_{25}\times\Delta\Gamma}\times 10^{6}\times [\text{ppm/°C}]$ ligh permittivity apacitance value at each step shall be measured in thermal equilibrium, and the temperature characteristic shall be calculated from the bllowing equation. | | | | | |
| Test Methods and | Step B X5R, X7R, X7S | | | | | |
| Remarks | 1 Minimum operating tempeature | | | | | |
| | 2 20°C 25°C | | | | | |
| | 3 Maximum operating temperature | | | | | |
| | $\frac{(C-C_2)}{C_2} \times 100(\%)$ s: Capacitance value in Step 1 or Step 3 | | | | | |

| 9. Deflection | |
|-----------------------------|--|
| Specified Value | Temperature Compensating(High Frequency type) Appearance : No abnormality Capacitance change : ±5% or ±0.5pF, whichever is larger. |
| opecined value | High permittivity Appearance : No abnormality Capacitance change : Within±10% |
| Test Methods and Remarks | Warp : 1mm (Soft Termination type:3mm) Duration : 10sec. Test board : Glass epoxy-resin substrate Thicknss : 1.6mm Board Warp Warp (Unit: mm) |
| | Capacitance measurement shall be conducted with the board bent. |

C2 : Capacitance value in Step 2

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

10. Adhesive Strength of Terminal Electrodes Specified Value No terminal separation or its indication. Temperature Compensating(High Frequency type) Applied force : 2N Hooked jig Duration : 10±5sec. Board Test Methods and Remarks High permittivity Applied force : 5N Hooked jig Duration : 30±5sec. Board

| 11. Solderability | | | |
|-------------------|--------------------------------|-------------------------------|------------------|
| Specified Value | At least 95% of terminal elect | rode is covered by new solder | |
| | | Eutectic solder | Lead-free solder |
| Test Methods and | Solder type | H60A or H63A | Sn-3.0Ag-0.5Cu |
| Remarks | Solder temperature | 230±5°C | 245±3°C |
| | Duration | 4±1 sec. | |

| | Temperature Compensating(High Frequency type) | | | | | |
|------------------|---|--|--|--|--|--|
| | Appearance : No abnormality | | | | | |
| | Capacitance change | : C※≦10pF :±0.25pF C※>10pF :±2.5% | | | | |
| | Insulation resistance | : Initial value | | | | |
| | Withstanding voltage | (between terminals): No abnormality | | | | |
| Specified Value | High permittivity | | | | | |
| | Appearance | : No abnormality | | | | |
| | Capacitance change | : Within±15%(HMK,HMJ), ±10%(QMK,QMJ, SMK,SMJ) | | | | |
| | Dissipation factor | : Inital value | | | | |
| | Insulation resistance | : Initial value | | | | |
| | Withstanding voltage | (between terminals): No abnormality | | | | |
| | Preconditioning | : Thermal treatment(at 150°C for 1hr) Note1 (Only High permittivity) | | | | |
| Test Methods and | Solder temperature | : 270±5°C | | | | |
| Remarks | Duration | : 3±0.5sec. | | | | |
| rteiliains | Preheating conditions | : 80 to 100°C, 2 to 5 min. 150 to 200°C, 2 to 5min. | | | | |
| | Recovery | : 24 ± 2 hrs under the stadard condition Note 3 | | | | |

| 13. Temperature Cy | ycle (Thern | nal Shock) | | | | |
|--------------------|---|-------------------------------|--|---------------|--|--|
| | Temperature Compensating(High Frequency type) | | | | | |
| | Appearance | ce | : No abnormality | | | |
| | Capacitan | ce change | : C※≦10pF :±0.25% C※>10pF :±2.5% | | | |
| | Insulation | resistance | : Initial value | | | |
| | Withstand | ing voltage | (between terminals): No abnormality | | | |
| Specified Value | High permittivity | | | | | |
| | Appearance | | : No abnormality | | | |
| | Capacitance change | | : Within±15%(HMK,HMJ), ±7.5%(QMK,QMJ, SMK,SMJ) | | | |
| | Dissipation factor | | : Initial value | | | |
| | Insulation resistance | | : Initial value | | | |
| | Withstanding voltage | | (between terminals): No abnormality | | | |
| | Precondit | ioning : Therr | nal treatment (at 150°C for 1hr) Note1 | | | |
| | Conditions | s for 1 cycle | | | | |
| | Step | | temperature(°C) | Time (min.) | | |
| Test Methods and | 1 | Minimum operating temperature | | 30 ± 3 min. | | |
| Remarks | 2 | Normal temperature | | 2 to 3min. | | |
| | 3 | Maximum operating temperature | | 30±3min. | | |
| | 4 | Normal temperature | | 2 to 3min. | | |
| | Number of cycles : 5 times | | | | | |
| | Recovery : 24±2hrs under the standard condition Note3 | | | | | |

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 14. Humidity (Stea | ady state) | | | |
|--------------------|---|--|--|--|
| | Temperature Compensating(High Frequency type) | | | |
| | Appearance | : No abnormality | | |
| | Capacitance change | : C※≦10pF :±0.5pF C※>10pF :±5% ※Normal capacitance | | |
| | Insulation resistance | : 1000M Ωmin | | |
| Specified Value | High permittivity | | | |
| | Appearance | : No abnormality | | |
| | Capacitance change | : Within±15% | | |
| | Dissipation factor | : 7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ). | | |
| | Insulation resistance | : 25M $\Omega\mu\!\!\!\!/F$ or 1000M Ω whichever is smaller. | | |
| | Preconditioning | : Thermal treatment(at 150°C for 1hr) Note1 (Only High permittivity) | | |
| Test Methods and | Temperature | : 40±2℃ | | |
| Remarks | Humidity | : 90 to 95%RH | | |
| Remarks | Duration | :500 + 24/-0 hrs | | |
| | Recovery | : 24 ± 2 hrs under the standard condition Note 3 | | |

| 15. Humidity Loadii | ng | |
|---------------------|-----------------------------|---|
| | Temperature Compensating | (High Frequency type) |
| | Appearance | : No abnormality |
| | Capacitance change | : C $\frac{5}{2}$.0pF : ± 0.4 pF 2.0pF < C $\frac{5}{2}$ 10pF : ± 0.75 pF C $\frac{5}{2}$ 10pF : ± 7.5 % |
| | | : ※Normal capacitance |
| | Insulation resistance | : 500M Ωmin |
| Specified Value | | |
| | High permittivity | |
| | Appearance | : No abnormality |
| | Capacitance change | : Within±15% |
| | Dissipation factor | : 7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ). |
| | Insulation resistance | : 10M $\Omega\mu$ or 500M Ω whichever is smaller. |
| | According to JIS 5102 claus | se 9.9. |
| | Preconditioning | : Voltage treatment Note2 (Only High permittivity) |
| | Temperature | : 40±2°C |
| Test Methods and | Humidity | : 90 to 95%RH |
| Remarks | Applied voltage | : Rated voltage |
| | Charge/discharge current | : 50mA max. |
| | Duration | : 500 + 24/-0 hrs |
| | Recovery | : 24±2hrs under the standard condition Note3 |

| 16. High Temperatu | I | | | |
|--------------------|---|--|--|--|
| | Temperature Compensating(High Frequency type) | | | |
| | Appearance | : No abnormality | | |
| | Capacitance change | : C‰≦10pF :±0.3pF C‰>10pF :±3% | | |
| | Insulation resistance | :1000M Ωmin | | |
| Specified Value | High permittivity | | | |
| | Appearance | : No abnormality | | |
| | Capacitance change | : Within±15% | | |
| | Dissipation factor | : 7%max(HMK,HMJ), 5%max(QMK,QMJ, SMK,SMJ). | | |
| | Insulation resistance | : 50M $\Omega ot\!$ | | |
| | According to JIS 5102 claus | se 9.10. | | |
| | Preconditioning | : Voltage treatment Note2 (Only High permittivity) | | |
| Test Methods and | Temperature | : Maximum operating temperature | | |
| Remarks | Applied voltage | : Rated voltage × 2(HMK,HMJ,QVS) Rated voltage × 1.5(QMK,QMJ) Rated voltage × 1.2(SMK,SMJ) | | |
| Remarks | Charge/discharge current | : 50mA max. | | |
| | Duration | : 1000 + 24/-0 hrs | | |
| | Recovery | : 24±2hrs under the standard condition Note3 | | |

Note1 Thermal treatment : Initial value shall be measured after test sample is heat-treated at $150 \pm 0/-10^{\circ}\text{C}$ for an hour and kept at room temperature

for 24±2hours.

Note2 Voltage treatment : Initial value shall be measured after test sample is voltage-treated for an hour at both the temperature and voltage specified in

the test conditions, and kept at room temperature for 24 \pm 2hours.

Note3 Standard condition $\,:$ Temperature: 5 to 35°C, Relative humidity: 45 to 85 % RH, Air pressure: 86 to 106kPa

When there are questions concerning measurement results, in order to provide correlation data, the test shall be conducted

under the following condition.

Temperature: $20\pm2^{\circ}$ C, Relative humidity: 60 to 70 % RH, Air pressure: 86 to 106kPa Unless otherwise specified, all the tests are conducted under the "standard condition".

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Precautions on the use of Multilayer Ceramic Capacitors

■PRECAUTIONS

1. Circuit Design

- ◆ Verification of operating environment, electrical rating and performance
 - A malfunction of equipment in fields such as medical, aerospace, nuclear control, etc. may cause serious harm to human life or have severe social ramifications.

Therefore, any capacitors to be used in such equipment may require higher safety and reliability, and shall be clearly differentiated from them used in general purpose applications.

Precautions

- ◆Operating Voltage (Verification of Rated voltage)
 - 1. The operating voltage for capacitors must always be their rated voltage or less.
 - If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages shall be the rated voltage or less.
 - For a circuit where an AC or a pulse voltage may be used, the sum of their peak voltages shall also be the rated voltage or less.
 - 2. Even if an applied voltage is the rated voltage or less reliability of capacitors may be deteriorated in case that either a high frequency AC voltage or a pulse voltage having rapid rise time is used in a circuit.

2. PCB Design

Precautions

- ◆Pattern configurations (Design of Land-patterns)
- 1. When capacitors are mounted on PCBs, the amount of solder used (size of fillet) can directly affect the capacitor performance. Therefore, the following items must be carefully considered in the design of land patterns:
 - (1) Excessive solder applied can cause mechanical stresses which lead to chip breaking or cracking. Therefore, please consider appropriate land-patterns for proper amount of solder.
 - (2) When more than one component are jointly soldered onto the same land, each component's soldering point shall be separated by solder-resist.
- ◆Pattern configurations (Capacitor layout on PCBs)

After capacitors are mounted on boards, they can be subjected to mechanical stresses in subsequent manufacturing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering of the boards, etc.). For this reason, land pattern configurations and positions of capacitors shall be carefully considered to minimize stresses.

◆Pattern configurations (Design of Land-patterns)


The following diagrams and tables show some examples of recommended land patterns to prevent excessive solder amounts.


- (1) Recommended land dimensions for typical chip capacitors
- Multilayer Ceramic Capacitors : Recommended land dimensions (unit: mm)

Wave-soldering

| Ту | ре | 107 | 212 | 316 | 325 |
|------|----|------------|------------|------------|------------|
| Size | L | 1.6 | 2.0 | 3.2 | 3.2 |
| Size | W | 0.8 | 1.25 | 1.6 | 2.5 |
| A | 4 | 0.8 to 1.0 | 1.0 to 1.4 | 1.8 to 2.5 | 1.8 to 2.5 |
| Е | 3 | 0.5 to 0.8 | 0.8 to 1.5 | 0.8 to 1.7 | 0.8 to 1.7 |
| С | | 0.6 to 0.8 | 0.9 to 1.2 | 1.2 to 1.6 | 1.8 to 2.5 |

Land patterns for PCBs





Technical considerations


Reflow-soldering

| | Nellow Soldering | | | | | | | | |
|----|------------------|--------------|--------------|--------------|------------|------------|------------|------------|------------|
| | Туре | 042 | 063 | 105 | 107 | 212 | 316 | 325 | 432 |
| Si | L | 0.4 | 0.6 | 1.0 | 1.6 | 2.0 | 3.2 | 3.2 | 4.5 |
| SI | W | 0.2 | 0.3 | 0.5 | 0.8 | 1.25 | 1.6 | 2.5 | 3.2 |
| | Α | 0.15 to 0.25 | 0.20 to 0.30 | 0.45 to 0.55 | 0.8 to 1.0 | 0.8 to 1.2 | 1.8 to 2.5 | 1.8 to 2.5 | 2.5 to 3.5 |
| | В | 0.15 to 0.20 | 0.20 to 0.30 | 0.40 to 0.50 | 0.6 to 0.8 | 0.8 to 1.2 | 1.0 to 1.5 | 1.0 to 1.5 | 1.5 to 1.8 |
| | С | 0.15 to 0.30 | 0.25 to 0.40 | 0.45 to 0.55 | 0.6 to 0.8 | 0.9 to 1.6 | 1.2 to 2.0 | 1.8 to 3.2 | 2.3 to 3.5 |

Note: Recommended land size might be different according to the allowance of the size of the product.


●LWDC: Recommended land dimensions for reflow-soldering (unit: mm)

| Туре | | 105 | 107 | 212 |
|------|---|--------------|-------------|------------|
| Size | L | 0.52 | 0.8 | 1.25 |
| Size | W | 1.0 | 1.6 | 2.0 |
| ļ | ٨ | 0.18 to 0.22 | 0.25 to 0.3 | 0.5 to 0.7 |
| В | | 0.2 to 0.25 | 0.3 to 0.4 | 0.4 to 0.5 |
| С | | 0.9 to 1.1 | 1.5 to 1.7 | 1.9 to 2.1 |



[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty~top.com/).


(2) Examples of good and bad solder application



- ◆Pattern configurations (Capacitor layout on PCBs)
 - 1-1. The following is examples of good and bad capacitor layouts; capacitors shall be located to minimize any possible mechanical stresses from board warp or deflection.

| Items | Not recommended | Recommended |
|---------------------|-----------------|---|
| Deflection of board | | Place the product at a right angle to the direction of the anticipated mechanical stress. |

1-2. The amount of mechanical stresses given will vary depending on capacitor layout. Please refer to diagram below.



1-3. When PCB is split, the amount of mechanical stress on the capacitors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, please consider the PCB, split methods as well as chip location.

3. Mounting

- ◆Adjustment of mounting machine
 - 1. When capacitors are mounted on PCB, excessive impact load shall not be imposed on them.
 - 2. Maintenance and inspection of mounting machines shall be conducted periodically.


Precautions Selection of Adhesives

1. When chips are attached on PCBs with adhesives prior to soldering, it may cause capacitor characteristics degradation unless the following factors are appropriately checked: size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, please contact us for further information.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

◆Adjustment of mounting machine

- 1. When the bottom dead center of a pick-up nozzle is too low, excessive force is imposed on capacitors and causes damages. To avoid this, the following points shall be considerable.
 - (1) The bottom dead center of the pick-up nozzle shall be adjusted to the surface level of PCB without the board deflection.
 - (2) The pressure of nozzle shall be adjusted between 1 and 3 N static loads.
 - (3) To reduce the amount of deflection of the board caused by impact of the pick-up nozzle, supporting pins or back-up pins shall be used on the other side of the PCB. The following diagrams show some typical examples of good and bad pick-up nozzle placement:



Technical considerations

2. As the alignment pin is worn out, adjustment of the nozzle height can cause chipping or cracking of capacitors because of mechanical impact on the capacitors.

To avoid this, the monitoring of the width between the alignment pins in the stopped position, maintenance, check and replacement of the pin shall be conducted periodically.


◆Selection of Adhesives


Some adhesives may cause IR deterioration. The different shrinkage percentage of between the adhesive and the capacitors may result in stresses on the capacitors and lead to cracking. Moreover, too little or too much adhesive applied to the board may adversely affect components. Therefore, the following precautions shall be noted in the application of adhesives.

- (1) Required adhesive characteristics
 - a. The adhesive shall be strong enough to hold parts on the board during the mounting & solder process.
 - b. The adhesive shall have sufficient strength at high temperatures.
 - c. The adhesive shall have good coating and thickness consistency.
 - d. The adhesive shall be used during its prescribed shelf life.
 - e. The adhesive shall harden rapidly.
 - f. The adhesive shall have corrosion resistance.
 - g. The adhesive shall have excellent insulation characteristics.
 - h. The adhesive shall have no emission of toxic gasses and no effect on the human body.
- (2) The recommended amount of adhesives is as follows;

[Recommended condition]

| Figure | 212/316 case sizes as examples |
|--------|----------------------------------|
| а | 0.3mm min |
| b | 100 to 120 μm |
| С | Adhesives shall not contact land |





4. Soldering

Precautions

Technical

considerations

◆Selection of Flux

Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;

- (1) Flux used shall be less than or equal to 0.1 wt%(in CI equivalent) of halogenated content. Flux having a strong acidity content shall not be applied.
- (2) When shall capacitors are soldered on boards, the amount of flux applied shall be controlled at the optimum level.
- (3) When water-soluble flux is used, special care shall be taken to properly clean the boards.

◆ Soldering

Temperature, time, amount of solder, etc. shall be set in accordance with their recommended conditions.

Sn-Zn solder paste can adversely affect MLCC reliability.

Please contact us prior to usage of Sn-Zn solder.

◆Selection of Flux

1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate flux, or highly acidic flux is used, it may lead to corrosion of terminal electrodes or degradation of insulation resistance on the surfaces of the capacitors.

- 1-2. Flux is used to increase solderability in wave soldering. However if too much flux is applied, a large amount of flux gas may be emitted and may adversely affect the solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
- 1-3. Since the residue of water-soluble flux is easily dissolved in moisture in the air, the residues on the surfaces of capacitors in high humidity conditions may cause a degradation of insulation resistance and reliability of the capacitors. Therefore, the cleaning methods and the capability of the machines used shall also be considered carefully when water-soluble flux is used.


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

◆Soldering


- · Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling.
- · Therefore, the soldering must be conducted with great care so as to prevent malfunction of the components due to excessive thermal shock
- Preheating: Capacitors shall be preheated sufficiently, and the temperature difference between the capacitors and solder shall be within 100 to 130°C.
- · Cooling: The temperature difference between the capacitors and cleaning process shall not be greater than 100°C.

[Reflow soldering]

[Recommended conditions for eutectic soldering]




[Recommended condition for Pb-free soldering]




Caution

- \bigcirc The ideal condition is to have solder mass(fillet)controlled to 1/2 to 1/3 of the thickness of a capacitor.
- ②Because excessive dwell times can adversely affect solderability, soldering duration shall be kept as close to recommended times as possible.
- 3 Allowable number of reflow soldering: 2 times max.




[Wave soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]




Caution


- ①Wave soldering must not be applied to capacitors designated as for reflow soldering only.
- ②Allowable number of wave soldering: 1 times max.


[Hand soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]





Caution

- ①Use a 50W soldering iron with a maximum tip diameter of 1.0 mm.
- 2The soldering iron shall not directly touch capacitors.
- 3 Allowable number of hand soldering: 1 times max.

5. Cleaning Cleaning conditions 1. When PCBs are cleaned after capacitors mounting, please select the appropriate cleaning solution in accordance with the intended use Precautions of the cleaning. (e.g. to remove soldering flux or other materials from the production process.) 2. Cleaning condition shall be determined after it is verified by using actual cleaning machine that the cleaning process does not affect capacitor's characteristics. 1. The use of inappropriate cleaning solutions can cause foreign substances such as flux residue to adhere to capacitors or deteriorate their outer coating, resulting in a degradation of the capacitor's electrical properties (especially insulation resistance). 2. Inappropriate cleaning conditions (insufficient or excessive cleaning) may adversely affect the performance of the capacitors. In the case of ultrasonic cleaning, too much power output can cause excessive vibration of PCBs which may lead to the Technical cracking of capacitors or the soldered portion, or decrease the terminal electrodes' strength. Therefore, the following conditions shall considerations be carefully checked; Ultrasonic output: 20 W/Q or less Ultrasonic frequency: 40 kHz or less Ultrasonic washing period: 5 min. or less

6. Resin coating and mold

Precautions

- 1. With some type of resins, decomposition gas or chemical reaction vapor may remain inside the resin during the while left under normal storage conditions resulting in the deterioration of the capacitor's performance.
- 2. When a resin's hardening temperature is higher than capacitor's operating temperature, the stresses generated by the excessive heat may lead to damage or destruction of capacitors.

The use of such resins, molding materials etc. is not recommended.

7. Handling

♦Splitting of PCB

- 1. When PCBs are split after components mounting, care shall be taken so as not to give any stresses of deflection or twisting to the board.
- 2. Board separation shall not be done manually, but by using the appropriate devices.

Precautions

◆Mechanical considerations

Be careful not to subject capacitors to excessive mechanical shocks.

- (1) If ceramic capacitors are dropped onto a floor or a hard surface, they shall not be used.
- (2) Please be careful that the mounted components do not come in contact with or bump against other boards or components.

8. Storage conditions

◆Storage

- 1. To maintain the solderability of terminal electrodes and to keep packaging materials in good condition, care must be taken to control temperature and humidity in the storage area. Humidity should especially be kept as low as possible.
 - Recommended conditions

Precautions

Ambient temperature : Below 30°C
Humidity : Below 70% RH

The ambient temperature must be kept below 40° C. Even under ideal storage conditions, solderability of capacitor is deteriorated as time passes, so capacitors shall be used within 6 months from the time of delivery.

- •Ceramic chip capacitors shall be kept where no chlorine or sulfur exists in the air.
- 2. The capacitance values of high dielectric constant capacitors will gradually decrease with the passage of time, so care shall be taken to design circuits. Even if capacitance value decreases as time passes, it will get back to the initial value by a heat treatment at 150°C for 1hour.

Technical considerations

If capacitors are stored in a high temperature and humidity environment, it might rapidly cause poor solderability due to terminal oxidation and quality loss of taping/packaging materials. For this reason, capacitors shall be used within 6 months from the time of delivery. If exceeding the above period, please check solderability before using the capacitors.

**RCR-2335B(Safety Application Guide for fixed ceramic capacitors for use in electronic equipment) is published by JEITA.

Please check the guide regarding precautions for deflection test, soldering by spot heat, and so on.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

High Reliability Application Multilayer Ceramic Capacitors

■RELIABILITY DATA

| 1.0 | |
|-----------------------------|---|
| 1. Operating Tempe | |
| Specified Value | X7R(−55°C to +125°C) |
| Test Methods and Remarks | Continuous use is available in this range. (reference temperature : 25°C) |
| 01111 1 0 11 | |
| | temperature Range |
| Specified Value | X7R(−55°C to +125°C) |
| Test Methods and Remarks | Maximum ambient temperature at which capacitors can be continuously used with rated voltage applied. |
| 3. Rated Voltage | |
| Specified Value | Please refer to the page of the "PART NUMBERS". |
| Test Methods and Remarks | Continuous maximum applied voltage. If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages should be lower than the rated voltage of the capacitor. |
| 4. Shape and Dimer | sions |
| Specified Value | Please refer to the page of the "EXTERNAL DIMENSIONS". |
| | |
| 5. Heat Treatment | (Class II) |
| Test Methods and | Initial value shall be measured after test sample is heat—treated at $150+0/-10^{\circ}$ C for an hour and kept at room temperature for 24 \pm |
| Remarks | 2 hours. |
| | |
| 6. Voltage Treatmen | nt (Class II) |
| Test Methods and Remarks | Initial value shall be measured after test sample is voltage—treated for an hour at temperature and voltage which are specified as test |
| Remarks | conditions, and kept at room temperature for 24 ±2 hours. |
| 7 Dialoctric Withou | anding Valtage (hetween terminals) |
| | anding Voltage (between terminals) |
| Specified Value | No abnormality. |
| Test Methods and | Applied voltage : Rated voltage × 2.5 Duration : 1 to 5 seconds. |
| Remarks | Charging and discharging current shall be 50mA max. |
| | |
| 8. Insulation Resista | ance |
| Specified Value | Larger than whichever smaller of 500 M Ω^* μ F or 10 ⁴ M Ω |
| Test Methods and | Applied voltage : Rated voltage |
| Remarks | Duration : 60±5 seconds. Charging and discharging current shall be 50mA max. |
| | Charleing and disorderging out rolls shall be controlled. |
| 9. Capacitance and | Tolerance |
| Specified Value | Please refer to the page of the "PART NUMBERS". |
| 2,555104 74140 | Measurement frequency : 1kHz±10%(C≦10 μF) |
| Test Methods and | Measurement voltage : 1±0.2Vrms(C≦10 μF) |
| Remarks | 0.5±0.1V(6.3V rated voltage) |
| | Heat treatment specified in No.5 of the specification shall be conducted prior to measurement. |
| 10. Q or Dissipation | |
| Specified Value | Please refer to the page of the "PART NUMBERS". |
| Total Model | Measurement frequency : 1kHz±10%(C≤10 μF) |
| Test Methods and Remarks | Measurement voltage : 1 ± 0.2 Vrms($C \le 10 \mu F$) 0.5 ± 0.1 V(6.3V rated voltage) |
| | Heat treatment specified in No.5 of the specification shall be conducted prior to measurement. NO DC bias is applied. |
| | • |

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

11. Temperature Characteristic (without DC bias) Specified Value $X7R(-55^{\circ}C \text{ to } +125^{\circ}C): \pm 15\%$ Confirming to EIA RS-198-D (1991) Heat treatment specified in No.5 of the specification shall be conducted prior to measurement. Change of the maximum capacitance deviation in step 1 to 5. Temperature (°C) step Test Methods and +25 Remarks 2 Minimum operating temperature 3 +25 4 Maximum operating temperature 5 +25


12. Adhesive Force of Terminal Electrodes

Specified Value Appearance: Terminal electrodes shall be no exfoliation or a sign of exfoliation.

Solder lands refer to fig.1.

| | 1608 size | larger than 2012 size | |
|----------------|-----------------------------|-----------------------|--|
| Applying force | 5N | 10N | |
| Duration | 30±5 seconds. | | |
| Board | Glass epoxy-resin substrate | | |
| Thickness | 1.6mm | | |

Test Methods and Remarks



| | | Case | size | |
|-----------|------|------|------|------|
| Dimension | 1608 | 2012 | 3216 | 3225 |
| а | 1.0 | 1.2 | 2.2 | 2.2 |
| b | 3.0 | 4.0 | 5.0 | 5.0 |
| С | 1.2 | 1.65 | 2.0 | 2.9 |

| 13. Vibration | | | | |
|-----------------------------|--|---|--|--|
| Specified Value | Capacitance change : I Dissipation factor : I | : No abnormality : Initial value shall be satisfied. : Initial value shall be satisfied. : Initial value shall be satisfied. | | |
| Test Methods and Remarks | heat treated as specified in No.! Solder lands refer to figure 1. Direction of the vibration test Vibrationfrequency Total amplitude | is of the specification shall be conducted prior to test. Measurement shall be conducted after test sample is 5. : X, Y, Z each of 3 orientations for 2 hours respectively (total 6 hours) : 10 to 55 to 10Hz (1 minutes each) : 1.5 mm Il be made after test sample is kept at room temperature for 24 ±2 hours. | | |

| 14. Resistance to S | oldering Heat | | | |
|-----------------------------|---|--|--|--|
| Specified Value | Appearance Capacitance change Dissipation factor Insulation resistance Dielectric withstanding voltag | : No abnormality : ≦±7.5% : Initial value shall be satisfied. : Initial value shall be satisfied. e (between terminals): No abnormality | | |
| Test Methods and Remarks | Immerse test sample in an so Soldering temperature Duration Soaking position Preheating condition | o.5 of the specification shall be conducted prior to test. Ider solution (Sn-3Ag-0.5Cu). : 270°C±5°C : 3±0.5 seconds : Test sample is soaked until the termnal electrode is covered in solder solution. : 3216 size or smaller size:120 to 150°C for 1 minute, 3225 size:100 to 120°C for 1 minute, 170 to 200°C for 1 minute. | | |
| | Measurement after the test shall be made after test sample is kept at room temperature for 24 ±2 hours. | | | |

| 15. Solderability | | | | |
|-----------------------------|---|--|--|--|
| Specified Value | More than 95% of terminal electrode shall be covered with fresh solder. | | | |
| Test Methods and Remarks | · · | n No.5 of the specification shall be conducted prior to test. solder solution(Sn-3Ag-0.5Cu). : 245°C±5°C : 4±1 seconds : Test sample is immersed until the terminal electrode is covered in solder solution. | | |

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

16. Thermal shock Appearance

Appearance : No abnormality Capacitance change : $\leq \pm 7.5\%$

Dissipation factor : Initial value shall be satisfied.

Insulation resistance : Initial value shall be satisfied.

Dielectric withstanding voltage (between terminals) : No abnormality

Heat treatment specified in No.5 of the specification shall be conducted prior to test. Measurement shall be conducted after test sample is heat treated as specified in No.5.

condition of the one cycle (Air-Air)


| Step | Temperature (°C) | Time (min.) | Transfer time |
|------|---------------------------|-------------|-------------------|
| 1 | Minimum usage temperature | 15 | within 20 seconds |
| 2 | Maximum usage temperature | 15 | within 20 seconds |

Test Methods and Remarks

Specified Value

Test cycles: 100 times.

Measurement after the test shall be made after test sample is kept at room temperature for 24 ± 2 hours.



| | Case size | | | | |
|-----------|-----------|------|------|------|--|
| Dimension | 1608 | 2012 | 3216 | 3225 | |
| а | 0.6 | 0.8 | 2.0 | 2.0 | |
| b | 2.2 | 3.0 | 4.4 | 4.4 | |
| С | 0.9 | 1.3 | 1.7 | 2.6 | |

17. Humidity Loading

Test Methods and

Remarks

Test condition : 85°C/85%RH.

Duration : 1000 +48/-0 hours.

DC bias : Applied rated voltage.

Voltage treatment specified in No.6 of the specification shall be conducted prior to test.

Measurement after the test shall be made after test sample is kept at room temperature for 24 \pm 2 hours.

18. High Temperature Loading

Insulation resistance : Larger than whichever smaller of 25M Ω · μ F or 500M Ω

Voltage treatment specified in No.6 of the specification shall be conducted prior to test.

Test sample shall be put in thermostatic oven with maximum temperature.

Test Methods and Remarks

Applied voltage : Rated voltage x 2

Duration : 1000 +48/-0 hours.

Charging and discharging current shall be 50mA or less.

Measurement after the test shall be made after test sample is kept at room temperature for 24 ± 2 hours.

19. Resistance to Flexure of substrate

Fig.3


Insulation resistance : Initial value shall be satisfied.

Warp : 1mm

Testing board : Grass epoxy - resin substrate

Thickness : 1.6mm
Test board and solder lands : Refer to fig. 3.

Test Methods and Remarks



| | Case size | | | | |
|-----------|-----------|------|------|------|--|
| Dimension | 1608 | 2012 | 3216 | 3225 | |
| а | 0.6 | 0.8 | 2.0 | 2.0 | |
| b | 2.2 | 3.0 | 4.4 | 4.4 | |
| С | 0.9 | 1.3 | 1.7 | 2.6 | |

Board Warp | 45±2 | 45±2 | 1

Fig

Measurement shall be made with board in the bent position. (fig.4)

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

| 20. High Temperature Exposure | | | | |
|--|--|--|--|--|
| Specified Value Note1 | Appearance Capacitance change Dissipation factor Insulation resistance | : No abnormality : \leq \pm 12.5% : 5.0%max. : Larger than whichever smaller of 500M Ω - μ F or 10000M Ω | | |
| Test Methods and Remarks Heat treatment specified in No.5 of the specification shall be conducted prior to test. Test sample shall be put in thermostatic oven with maximum temperature. Duration: 1000 +48/-0 hours. Initial value shall be measured after test sample is heat—treated specified No.5. Measurement after the test shall be made after test sample is kept at room temperature for 24 ±2 hours. | | thermostatic oven with maximum temperature. nours. red after test sample is heat—treated specified No.5. | | |

| 21. Temperature Cy | cling | | | | |
|--------------------|--|---|------------------------------------|--|--|
| | Appearance | : No abnormality | | | |
| Specified Value | Capacitance cl | nange : ≦±7.5% | | | |
| Note1 | Dissipation fac | tor : Initial value shall be satisfi | : Initial value shall be satisfied | | |
| | Insulation resis | tance : Initial value shall be satisfi | : Initial value shall be satisfied | | |
| | Measurement s condition of th Step | shall be conducted after test sample is heat tre e one cycle Temperature(°C) Minimum usage temperature | Time (min.) 30±3 | | |
| Test Methods and | 2 | +25 | 2 to 3 | | |
| Remarks | 3 | Maximum usage temperature | 30±3 | | |
| | 4 | +25 | 2 to 3 | | |
| | Test cycles: 20 Solder lands re | | s kent at room temne | | |

| 22. Body strength | |
|-----------------------------|--|
| Specified Value | No mechanical damage |
| Test Methods and Remarks | Applying force : 10N Applying time : 10 seconds $R=0.5$ Pressurization L $L \ge W$ L |

Note 1 The figures indicate typical specifications. Please refer to individual specifications in detail.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Precautions on the use of High Reliability Application Multilayer Ceramic Capacitors

■PRECAUTIONS

1.Circuit Design

- ◆Verification of operating environment, electrical rating and performance
 - A malfunction in medical equipment, spacecraft, nuclear reactors, etc. may cause serious harm to human life or have severe social ramifications.

As such, any capacitors to be used in such equipment may require higher safety and/or reliability considerations and should be clearly differentiated from components used in general purpose applications.

Precautions

- ◆Operating Voltage (Verification of Rated voltage)
 - 1. The operating voltage for capacitors must always be lower than their rated values.
 - If an AC voltage is loaded on a DC voltage, the sum of the two peak voltages should be lower than the rated value of the capacitor chosen. For a circuit where both an AC and a pulse voltage may be present, the sum of their peak voltages should also be lower than the capacitor's rated voltage.
 - 2. Even if the applied voltage is lower than the rated value, the reliability of capacitors might be reduced if either a high frequency AC voltage or a pulse voltage having rapid rise time is present in the circuit.

2. PCB Design


Precautions

- ◆Pattern configurations (Design of Land-patterns)
 - 1. When capacitors are mounted on a PCB, the amount of solder used (size of fillet) can directly affect capacitor performance. Therefore, the following items must be carefully considered in the design of solder land patterns:
 - (1) The amount of solder applied can affect the ability of chips to withstand mechanical stresses which may lead to breaking or cracking. Therefore, when designing land-patterns it is necessary to consider the appropriate size and configuration of the solder pads which in turn determines the amount of solder necessary to form the fillets.
 - (2) When more than one part is jointly soldered onto the same land or pad, the pad must be designed so that each component's soldering point is separated by solder-resist.
- ◆Pattern configurations (Capacitor layout on panelized [breakaway] PC boards)
 - After capacitors have been mounted on the boards, chips can be subjected to mechanical stresses in subsequent manufacturing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering the reflow soldered boards etc.) For this reason, planning pattern configurations and the position of SMD capacitors should be carefully performed to minimize stress.
- ◆Pattern configurations (Design of Land-patterns)
 - 1. The following diagrams and tables show some examples of recommended patterns to prevent excessive solder amounts. (larger fillets which extend above the component end terminations) Examples of improper pattern designs are also shown.
 - (1) Recommended land dimensions for a typical chip capacitor land patterns for PCBs

Recommended land dimensions for reflow-soldering (unit: mm)

| Type | | 107 | 212 | 316 | 325 |
|------|---|---------|---------|---------|---------|
| C: | L | 1.6 | 2.0 | 3.2 | 3.2 |
| Size | W | 0.8 | 1.25 | 1.6 | 2.5 |
| - | 4 | 0.8~1.0 | 0.8~1.2 | 1.8~2.5 | 1.8~2.5 |
| Е | 3 | 0.6~0.8 | 0.8~1.2 | 1.0~1.5 | 1.0~1.5 |
| С | | 0.6~0.8 | 0.9~1.6 | 1.2~2.0 | 1.8~3.2 |
| | | | | | |

Land patterns for PCBs




Chip capacitor W

Technical considerations


Excess solder can affect the ability of chips to withstand mechanical stresses. Therefore, please take proper precautions when designing land-patterns.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


(2) Examples of good and bad solder application



- ◆Pattern configurations (Capacitor layout on panelized [breakaway] PC boards)
 - 1-1. The following is examples of good and bad capacitor layout; SMD capacitors should be located to minimize any possible mechanical stresses from board warp or deflection.



1-2. To layout the capacitors for the breakaway PC board, it should be noted that the amount of mechanical stresses given will vary depending on capacitor layout. The example below shows recommendations for better design.



1-3. When breaking PC boards along their perforations, the amount of mechanical stress on the capacitors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, any ideal SMD capacitor layout must also consider the PCB splitting procedure.

3.Soldering

Precautions

Technical

considerations

◆Selection of Flux

- Since flux may have a significant effect on the performance of capacitors, it is necessary to verify the following conditions prior to use;
 Flux used should be with less than or equal to 0.1 wt% (equivalent to chlorine) of halogenated content. Flux having strong acidity content should not be applied.
 - (2) When soldering capacitors on the board, the amount of flux applied should be controlled at the optimum level.
 - (3) When using water-soluble flux, special care should be taken to properly clean the boards.

◆ Soldering

Temperature, time, amount of solder, etc. are specified in accordance with the following recommended conditions.
 Sn-Zn solder paste can affect MLCC reliability performance.
 Please contact us prior to usage.

◆Selection of Flux

- 1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate the flux, or highly acidic flux is used, an excessive amount of residue after soldering may lead to corrosion of the terminal electrodes or degradation of insulation resistance on the surface of the capacitors.
- 1-2. Flux is used to increase solderability in flow soldering, but if too much is applied, a large amount of flux gas may be emitted and may detrimentally affect solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
- 1-3. Since the residue of water-soluble flux is easily dissolved by water content in the air, the residue on the surface of capacitors in high humidity conditions may cause a degradation of insulation resistance and therefore affect the reliability of the components. The cleaning methods and the capability of the machines used should also be considered carefully when selecting water-soluble flux.

◆Soldering

1-1. Preheating when soldering

Heating: Ceramic chip components should be preheated to within 100 to 130°C of the soldering.


Cooling: The temperature difference between the components and cleaning process should not be greater than 100°C.

Ceramic chip capacitors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling. Therefore, the soldering process must be conducted with great care so as to prevent malfunction of the components due to excessive thermal shock.


[Recommended conditions for soldering]

[Reflow soldering]

Temperature profile



[Recommended conditions for Pd Free soldering]




%Ceramic chip components should be preheated to within 100 to 130°C of the soldering.

*Assured to be reflow soldering for 2 times.

Caution

①The ideal condition is to have solder mass (fillet) controlled to 1/2 to 1/3 of the thickness of the capacitor, as shown below:



②Because excessive dwell times can detrimentally affect solderability, soldering duration should be kept as close to recommended times as possible.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).