



BERYL
绿宝石



PRODUCT CATALOG

© 2020.5

EDLCON[®] SUPERCAPACITOR

公司简介

Company Profile

绿宝石是一家集铝电解电容器、固态电容器和超级电容器研发、制造和销售为一体的国家火炬计划重点高新技术企业，创始于2004年，拥有“BERYL”、“G”、“EDLCON”三大品牌，拥有100多项核心技术专利。

公司通过了ISO9001、ISO14001、IATF16949以及知识产权管理体系认证。组建了“广东省高性能电容器工程技术研究中心”、“广东省级企业技术中心”。拥有日本、德国、美国技术合作团队，并与多家高校科研院所实现产学研合作。

绿宝石秉持“品质取信，服务取胜，变革创新，超越期望”的质量方针，同时奉行“遵守法规，拒用毒物，预防污染，节约资源”的环保方针，以“在客户的立场想，在专业的角度做，在共赢的层面定”的服务承诺，为客户提供优质产品和服务。

Beryl company is a key high-tech enterprise of the national Torch Plan integrating the R&D, manufacturing and sales of aluminum electrolytic capacitors, polymer capacitors and super capacitors. It was built in 2004, owns three renowned brands of “BERYL”, “G” and “EDLCON”, and has more than 100 core technology patents.

Beryl are certified to ISO 9001, ISO14001, IATF16949 and Intellectual Property Management System (IPMS). It has organized “Guangdong high performance capacitor Engineering Technology Research Center” and “Guangdong provincial enterprise technology center”. Beryl widely cooperates and communicates with experts at home and abroad in technology, by the way of building its foreign technical teams from Japan, German and American, and promoting the establishment of university-industry cooperation.

Beryl has been adhering to the quality policy of “Get confidence with quality, Get victory with service, Get leading with technology, Get exceeding on expectancy”, the environment policy of “Comply with regulations, Refuse to poisons, Prevent pollution, Save resources”, and the service commitment of “To stand on the position of the customer perspective, To manufacture in professional insight, To deal under win-win relationship”, to provide high quality products and services for customers.



国家火炬计划
重点高新技术企业



ISO9001质量管理
体系认证企业



TS16949质量
管理体系认证企业

目录 Contents

超级电容器简介	P2
Electric Double Layer Capacitor Introduction	
产品概要	P3~4
Product Outline	
产品编码	P5
Part Number System	
产品尺寸图示	P6~7
Product Dimentions	
BCS 标准系列	P8~9
BCS Standard Series	
BCC 高容量系列	P10~12
BCC High Capacitance Series	
BCE 低内阻系列	P13~14
BCE Low ESR Series	
BCV耐高压系列	P15~16
BCV High Voltage Series	
BCT耐高温系列	P17~18
BCT High Temperature Series	
BMW 微型模组系列	P19~21
BMW Small Module Series	
BMT耐高温模组系列	P22~23
BMT High Temperature Module Series	
BMB 定制模组系列	P24~25
BMB Customized Module Series	
技术信息	P26~27
Technical Information	
使用说明	P28~31
Instructions	

EDLC 超级电容器

Electric Double Layer Capacitor Introduction

RoHS
compliant

特性与优势 Features and Advantages


- 低内阻、高功率
- 免维护(500,000次循环充放电,10年使用寿命)
- 定制各类尺寸单体及模组
- 定制各类耐高温、耐高压、超低ESR、超低自放电、超长寿命的单体。
- 提供完整的系统解决方案
- Low ESR, high power
- Maintenance-free (500,000 cycles of charge and discharge, ten years of service life)
- Customized dimensions of products are available.
- Provide customized special specifications, such as high temperature, high voltage, ultra-low ESR, ultra-low self discharge and longer life.
- Offer integral system solution.

应用类型 Application Types

- 小功率短时间后备电源 Small power and short time backup supply
- 快速充放电 Fast charging and discharging
- 瞬间大功率支撑 Short-term peak power assistant
- 低温启动 Low temperature starting
- 工业储能及能量回收 Industrial energy storage and energy recovery
- 风光储能 Wind and Solar energy storage

应用领域 Application Areas

- 工业 Industry
- 消费电子产品 Consumer electronics
- 医疗 Medical treatment
- 交通运输 Traffic
- 军事 Military



产品概要

Product Outline

BCS 标准系列 BCS Standar Series

- 常规容量 Normal capacitance performance
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 额定电压 Rated voltage: 2.7V
- 尺寸 Size: $\Phi 8 \sim \Phi 35$
- 循环次数 Life cycles: $> 500,000$



BCC 高容量系列 BCC High Capacitance Series

- 高容量 High capacitance
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 额定电压 Rated voltage: 2.7V
- 尺寸 Size: $\Phi 8 \sim \Phi 60$
- 循环次数 Life cycles: $> 500,000$



BCE 低内阻系列 BCE Low ESR Series

- 低内阻 Low ESR
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 额定电压 Rated voltage: 2.7V
- 尺寸 Size: $\Phi 8 \sim \Phi 12.5$
- 循环次数 Life cycles: $> 500,000$



BCV 耐高压系列 BCV High Voltage Series

- 高电压 High voltage
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +65^{\circ}\text{C}$
- 额定电压 Rated voltage: 3.0V
- 尺寸 Size: $\Phi 8 \sim \Phi 35$
- 循环次数 Life cycles: $> 500,000$



产品概要

Product Outline

BCT 耐高温系列 BCT High Temperature Series

- 高温度 High temperature
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 额定电压 Rated voltage: 2.7V
- 尺寸 Size: $\Phi 8 \sim \Phi 18$
- 循环次数 Lifecycles: $>500,000$



BMW 微型模组系列 BMW Small Module Series

- 低漏电 Low leakage current
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 额定电压 Rated voltage: 5.5V, 6.0V, 7.5V
- 尺寸 Size: $\Phi 8 \sim \Phi 18$ 导针型产品2串/3串
2 or 3 capacitors of lead type in series



BMT 耐高温系列 BMT High Temperature Module Series

- 高温度 High temperature
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 额定电压 Rated voltage: 2.7V
- 尺寸 Size: $\Phi 8 \sim \Phi 18$
- 循环次数 Lifecycles: $>500,000$



BMB 定制模组系列 BMB Customized Module Series

- 性能、尺寸定制满足不同使用需求
Customized performance and size to satisfy different use
- 提供能源管理系统设计
Design for energy management system
- 单体分选配组以提高模组可靠性
Cell was sorted and matched to improve reliability of module
- 工作温度 Operating temperature: $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$



Part Number System

1	2	3
---	---	---

BCS

系列 Series
BCS
BCC
BCE
BCV
BCT
BMW
BMT

4 5 6
2R7

代码 Code	电压 Vol (V)
2R7	2.7
3R0	3.0
5R5	5.5
6R0	6.0
7R5	7.5

7
M

代码 Code	容量偏差 Tol (%)
S	-20 ~ +50
M	-20 ~ +20
R	0 ~ +30
V	-10 ~ +30
X	-20 ~ +100

8 9 10
506

代码 Code	容量 Cap (F)
334	0.33
474	0.47
105	1.0
255	2.5
335	3.3
106	10
506	50
107	100
367	360
128	1200
308	3000

11	12
YS	

代码 Code	焊脚类型 Type
YS	导针散装 Lead type bulk
TZ	两针盖板 2-solder pin Snap-in
TK	四针盖板 4-solder pin Snap-in
TL	两L片盖板 2-soldersheet Snap-in
CS	螺柱两端引出 Two ends with screw
CC	光柱两端引出 Two ends without screw
MA	导针两端引出 Lead at two end
MB	导针中间引出 Lead in middle
MC	导针一侧引出 Lead at one side

13	14
18	

代码 Code	直径/宽度 Dia/Width (mm)
08	8
10	10
1B	12.5
16	16
18	18
22	22
25	25
30	30
35	35
60	60

1516
40

代码 Code	高度 Len (mm)
12	12.0
16	16.0
30	30.0
40	40.0
60	60.0
66	66.0
85	85.0
1B	102.0
1E	138.0

1	2	3
---	---	---

BMB

系列
Series
BMB

4	5	6	7
---	---	---	---

0480

代码 Code	电压 Vol (V)
0055	5.5
0075	7.5
0162	16.2
0480	48.0
0850	85.0
1000	100.0

8
M

代码 Code	容量偏差 Tol (%)
S	-20 ~ +50
M	-20 ~ +20
R	0 ~ +30
V	-10 ~ +30
X	-20 ~ +100

9	10	11	12
---	----	----	----

1650

代码 Code	容量 Cap (F)
0R33	0.33
0R47	0.47
0015	1.5
0096	9.6
0220	22.0
1650	165.0
5000	500.0

1314
Z A

代码 Code	类型 Type
YA	PCB预留焊点 Without wire from PCB
LA	导线引出 Wire lead
BA	接线座引出 Connection box
SA	连接片引出 Connection sheet
ZA	接线柱引出 Terminal lead

15 16
A1

代码 Code	外壳类型 Outer shell
O1	无外壳 Without case
T1	热缩套管 PET heat shrink tube
S1	塑料外壳 Plastic shell with epoxy filling
F1	烤漆铁皮外壳 Paint iron case
G1	不锈钢外壳 Stainless steel case
A1	铝合金外壳 Aluminum case


17
C

代码 Code	均衡方式 Circuit balanced mode
A	无均衡 Without balance
B	被动均衡 Passive balance
C	主动均衡 Active balance

产品尺寸图示


Product Dimintions

• 导针型 Radial type




ϕD	8	10	12.5	16	18
P	3.5	5.0	5.0	7.5	7.5
ϕd	0.6	0.6	0.6	0.8	0.8

• 牛角型 Snap-in type




• 两针 TZ Type

ϕD	22	25	30	35
P	10	10	10	10
H	7.0	7.0	7.0	7.0



• 两L片 TL Type

ϕD	22	25	30	35
P	10	10	10	14
H	7.0	7.0	7.0	8.5




• 四针 TK Type


ϕD	35
P	22.5
H	7.0

• 5.5V-2串 / 2 cells in series connection


• MA Type



• MC Type




• MB Type



串联状况 connection mode	单体直径 Cell Dia.	D	W	脚距/P			ϕd
				MA	MB	MC	
两串 2 in series	$\Phi 8$	8	16	11.5	5.0	8.0	0.6
	$\Phi 10$	10	20	15.5	5.5	10.0	0.6
	$\Phi 12.5$	13	25	17.5	7.5	13.0	0.6
	$\Phi 16$	16	32	24.0	8.5	16.0	0.8
	$\Phi 18$	18	36	26.0	10.5	/	0.8


• 7.5V-3串 / 3 cells in series connection

• MA Type



串联状况 connection mode	单体直径 Cell Dia.	D	W	脚距/P			ϕd
				MA	MB	MC	
三串 3 in series	$\Phi 8$	8	24	20.5	13.5	/	0.6

• MB Type



BCS 标准型系列

BCS Standard Series

特点 Features

- 低自放电率、低漏电流 Low self-discharge and low leakage current
- 性能均衡、高可靠性 Consistent performance with high reliability
- 长寿命、免维护 Long life and free of maintenance

应用 Application

- 智能仪表 Smart meters
- 启动电源 Start power
- 后备电源 Back-up power

产品规格 Specifications



项目 Item	性能 Performance	
额定电压 Rated voltage	2.7 V	
浪涌电压 Surge voltage	2.85 V	
容量范围 Nominal cap. range	1.0 F ~ 500 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%; -10% ~ +30%	
工作温度 Operating temperature	-40℃ ~ +70℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +70℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 2,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +70℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 导针型 Radial type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}C$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCS2R7X105YS0812		1.0	8 × 12	160	240	0.47	1.09	0.006	4050	0.0010	1.13
BCS2R7S205YS0816		2.0	8 × 16	120	180	0.61	1.99	0.010	4459	0.0020	1.86
BCS2R7S335YS0820		3.3	8 × 20	100	150	0.74	2.98	0.012	4486	0.0033	2.57
BCS2R7S505YS0825		5.0	8 × 25	90	135	0.87	4.03	0.015	3857	0.0051	3.01
BCS2R7S505YS1016		5.0	10 × 16	90	135	0.80	4.03	0.020	3240	0.0051	2.53
BCS2R7S505YS1020		5.0	10 × 20	75	113	0.97	4.32	0.015	3535	0.0051	2.30
BCS2R7M705YS1025	2.7	7.0	10 × 25	60	90	1.20	5.80	0.020	3738	0.0071	2.73
BCS2R7M106YS1030		10	10 × 30	45	68	1.51	8.06	0.030	4114	0.0101	3.21
BCS2R7M106YS1B20		10	12.5 × 20	45	68	1.42	8.06	0.030	3757	0.0101	2.94
BCS2R7M126YS1B25		12	12.5 × 25	40	60	1.66	9.42	0.040	3995	0.0132	3.61
BCS2R7M156YS1B30		15	12.5 × 30	35	53	1.93	11.33	0.052	3921	0.0162	3.81
BCS2R7M206YS1B35		20	12.5 × 35	30	45	2.23	14.21	0.056	3535	0.0203	3.68
BCS2R7M256YS1625		25	16 × 25	25	38	2.41	17.42	0.068	3110	0.0253	3.38
BCS2R7M306YS1630		30	16 × 30	20	30	2.92	21.32	0.075	3513	0.0304	3.66
BCS2R7M406YS1835		40	18 × 35	18	27	3.52	25.96	0.088	2893	0.0405	3.62
BCS2R7M506YS1840		50	18 × 40	16	24	3.96	30.68	0.105	2848	0.0506	3.96
BCS2R7M606YS1840		60	18 × 40	15	23	4.09	34.47	0.150	2880	0.0608	4.28
BCS2R7M107YS1860		100	18 × 60	13	20	5.30	45.76	0.240	2136	0.1013	4.82

• 牛角型 Snap-in type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}C$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCS2R7V107TZ2245	2.7	100	22 × 45	8.0	11.2	6.84	63.68	0.240	3633	0.1013	4.71
BCS2R7V127TZ2250		120	22 × 50	7.5	10.5	7.40	71.68	0.300	3086	0.1215	4.50
BCS2R7V157TZ2550		150	25 × 50	7.0	9.8	8.22	81.98	0.400	2705	0.1519	4.60
BCS2R7V227TZ3050		220	30 × 50	6.0	8.4	9.83	104.28	0.520	2340	0.2228	5.01
BCS2R7V257TZ3055		250	30 × 55	5.5	7.7	10.71	115.38	0.580	2470	0.2531	5.50
BCS2R7V367TZ3560		360	35 × 60	4.0	5.4	14.49	165.08	0.850	2282	0.3645	5.13
BCS2R7V407TZ3566		400	35 × 66	3.5	4.7	16.15	186.85	1.000	2178	0.4050	4.77

BCC 高容量型系列

BCC High Capacitance Series

特点 Features

- 高容量 High capacitance
- 低自放电率 Low self-discharge
- 长寿命 Long life

应用 Application

- 电动玩具 Electronic toy
- 后备电源 Back-up power
- 公交巴士 Bus



产品规格 Specifications

项目 Item	性能 Performance	
额定电压 Rated voltage	2.7 V	
浪涌电压 Surge voltage	2.85 V	
容量范围 Nominal cap. range	1.0 F ~ 3000 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%; -10% ~ +30%	
工作温度 Operating temperature	-40℃ ~ +70℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +70℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 2,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +70℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 导针型 Radial type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCC2R7S205YS0812	2.7	2.0	8 × 12	160	240	0.47	1.82	0.010	4050	0.0020	2.25
BCC2R7S305YS0816		3.0	8 × 16	120	180	0.61	2.63	0.012	4459	0.0030	2.79
BCC2R7S405YS0820		4.0	8 × 20	100	150	0.74	3.38	0.015	4486	0.0041	3.12
BCC2R7M705YS0825		7.0	8 × 25	90	135	0.87	4.86	0.020	3600	0.0071	3.94
BCC2R7M705YS1020		7.0	10 × 20	75	113	0.97	5.29	0.020	3535	0.0071	3.22
BCC2R7M106YS1025		10	10 × 25	60	90	1.20	7.11	0.030	3738	0.0100	3.89
BCC2R7M156YS1B20		15	12.5 × 20	45	68	1.42	10.06	0.040	3550	0.0152	4.16
BCC2R7M186YS1B25		18	12.5 × 25	40	60	1.66	11.68	0.050	3787	0.0182	4.73
BCC2R7M206YS1B30		20	12.5 × 30	35	53	1.93	13.17	0.055	3920	0.0203	4.76
BCC2R7M256YS1B35		25	12.5 × 35	30	45	2.23	15.88	0.060	3534	0.0253	4.60
BCC2R7M406YS1B46		40	12.5 × 46	20	30	3.10	24.55	0.080	3738	0.0405	5.19
BCC2R7M306YS1625		30	16 × 25	25	38	2.41	19.06	0.072	3049	0.0304	3.97
BCC2R7M356YS1630		35	16 × 30	20	30	2.92	23.05	0.080	3513	0.0354	4.27
BCC2R7M606YS1835		60	18 × 35	18	27	3.52	30.92	0.110	2700	0.0608	5.06
BCC2R7M706YS1840		70	18 × 40	15	23	4.09	36.70	0.125	3038	0.0709	5.54
BCC2R7M127YS1860		120	18 × 60	13	20	5.30	48.50	0.280	2039	0.1215	5.52


• 牛角型 Snap-in type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCC2R7V127TZ2245	2.7	120	22 × 45	8.0	11.6	6.72	67.73	0.250	3351	0.1215	5.40
BCC2R7V147TZ2250		140	22 × 50	7.5	10.9	7.27	74.93	0.310	2872	0.1418	5.06
BCC2R7V187TZ2550		180	25 × 50	7.0	10.2	8.08	84.20	0.415	2535	0.1823	5.36
BCC2R7V207TZ2555		200	25 × 55	6.5	9.4	8.75	93.59	0.470	2443	0.2025	5.33
BCC2R7V257TZ3050		250	30 × 50	6.0	8.7	9.66	106.30	0.550	2260	0.2531	5.69
BCC2R7V307TZ3055		300	30 × 55	5.5	8.0	10.52	119.38	0.600	2385	0.3038	6.60
BCC2R7V367TZ3550		360	35 × 50	5.0	7.0	11.76	138.07	0.800	2403	0.3645	7.01
BCC2R7V407TZ3555		400	35 × 55	4.5	6.3	12.92	153.41	1.000	2200	0.4050	6.53
BCC2R7V477TZ3560		470	35 × 60	4.0	5.6	14.23	174.70	1.200	2170	0.4759	6.61
BCC2R7V507TZ3566		500	35 × 66	3.5	4.9	15.86	195.65	1.400	2076	0.5063	5.89
BCC2R7V607TZ3570		600	35 × 70	3.2	4.5	17.02	219.63	1.600	2170	0.6075	6.75


尺寸图示 Dimentions (mm)

• 两端引出型 Cylindrical type

• 螺柱 CS Type



• 光柱 CC Type



典型产品 Standard Products

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current (A) ($\Delta T = 15^\circ\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCC2R7V657CS6051	2.7	650	60 × 51	0.60	0.72	54.00	597.75	1.70	7594	0.6581	4.11
BCC2R7V128CS6074		1200	60 × 74	0.40	0.55	70.00	975.90	2.80	6117	1.2150	4.67
BCC2R7V158CS6085		1500	60 × 85	0.33	0.45	84.00	1208.96	3.00	6943	1.5188	5.42
BCC2R7V208CS601X		2000	60 × 102	0.25	0.35	110.00	1588.24	4.20	6943	2.0250	5.63
BCC2R7V308CS601W		3000	60 × 138	0.22	0.26	130.00	2275.28	5.20	6729	3.0375	6.08

BCE 低内阻型系列

BCE Low ESR Series

特点 Features

- 超低内阻 Extremely low ESR
- 低漏电、高可靠性 Low leakage current and high reliability
- 长寿命、免维护 Long life and free of maintenance

应用 Application

- 高端玩具 High-tech toy
- 启动电源 Start power
- 后备电源 Back-up power

产品规格 Specifications



项目 Item	性能 Performance	
额定电压 Rated voltage	2.7 V	
浪涌电压 Surge voltage	2.85 V	
容量范围 Nominal cap. range	1.0 F ~ 10 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%; -10% ~ +30%	
工作温度 Operating temperature	-40°C ~ +70°C	
循环寿命 Cycle life characteristics	在25°C下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25°C, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +70°C 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 2,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2°C (-40°C ≤ T ≤ +70°C) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2°C	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 导针型 Radial type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current (A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCE2R7X105YS0812	2.7	1	8 × 12	110	165	0.57	1.16	0.008	5891	0.0010	1.21
BCE2R7S205YS0816		2	8 × 16	90	135	0.71	2.13	0.013	5945	0.0020	1.86
BCE2R7S335YS0820		3.3	8 × 20	65	98	0.92	3.37	0.015	6902	0.0033	2.57
BCE2R7S505YS0825		5	8 × 25	55	83	1.11	4.78	0.020	6312	0.0051	3.01
BCE2R7S505YS1020		5	10 × 20	50	75	1.19	4.91	0.025	5302	0.0051	2.30
BCE2R7M705YS1025		7	10 × 25	30	45	1.70	7.19	0.030	7477	0.0071	2.73
BCE2R7M106YS1030		10	10 × 30	25	38	2.02	9.82	0.035	7406	0.0101	3.21
BCE2R7M106YS1B20		10	12.5 × 20	25	38	1.91	9.82	0.035	6762	0.0101	2.94



BCV 耐高压系列

BCV High Voltage Series

特点 Features

- 高耐压 High voltage
- 低漏电 Low Leakage current
- 长寿命 Long life

应用 Application

- 智能电表 Smart meter
- 电动工具 Electric tool
- 智能玩具 Intelligent toy

产品规格 Specifications



项目 Item	性能 Performance	
额定电压 Rated voltage	3.0 V	
浪涌电压 Surge voltage	3.15 V	
容量范围 Nominal cap. range	1.0 F ~ 400 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%; -10% ~ +30%	
工作温度 Operating temperature	-40℃ ~ +65℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +65℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 1,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的3倍; ≤ 3 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +70℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 导针型 Radial type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size Φ D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) (ΔT=15℃)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/mΩ)	ESR _{DC} IEC法 (mΩ)						
BCV3R0S105YS0812	3.0	1.0	8 × 12	160	240	0.47	1.21	0.007	4348	0.0013	1.21
BCV3R0S205YS0816		2.0	8 × 16	120	180	0.61	2.21	0.012	4787	0.0025	1.99
BCV3R0S335YS0820		3.3	8 × 20	100	150	0.74	3.31	0.014	4816	0.0041	2.76
BCV3R0S505YS0825		5.0	8 × 25	90	135	0.87	4.48	0.018	4141	0.0063	3.23
BCV3R0S505YS1020		5.0	10 × 20	75	113	0.97	4.80	0.018	3794	0.0063	2.47
BCV3R0M705YS1025		7.0	10 × 25	60	90	1.20	6.44	0.024	4013	0.0088	2.93
BCV3R0M106YS1025		10	10 × 25	55	83	1.25	8.22	0.030	4156	0.0125	3.97
BCV3R0M106YS1030		10	10 × 30	45	68	1.51	8.96	0.036	4417	0.0125	3.45
BCV3R0M106YS1B20		10	12.5 × 20	45	68	1.42	8.96	0.036	4033	0.0125	3.15
BCV3R0M126YS1B25		12	12.5 × 25	40	60	1.66	10.47	0.048	4288	0.0150	3.57
BCV3R0M156YS1B30		15	12.5 × 30	35	53	1.93	12.59	0.062	4209	0.0188	3.84
BCV3R0M256YS1625		25	16 × 25	25	38	2.41	19.35	0.082	3491	0.0313	3.79
BCV3R0M306YS1630		30	16 × 30	20	30	2.92	23.68	0.090	3930	0.0375	4.09
BCV3R0M506YS1840		50	18 × 40	16	24	3.96	34.09	0.126	3140	0.0625	4.36
BCV3R0M107YS1860		100	18 × 60	13	20	5.30	50.85	0.260	2523	0.1250	5.69

• 牛角型 Snap-in type

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size Φ D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) (ΔT=15℃)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/mΩ)	ESR _{DC} IEC法 (mΩ)						
BCV3R0V107TZ2245	3.0	100	22 × 45	8.0	11.2	6.84	70.75	0.276	4231	0.1250	5.48
BCV3R0V127TZ2250		120	22 × 50	7.5	10.5	7.40	79.65	0.345	3594	0.1500	5.24
BCV3R0V157TZ2550		150	25 × 50	7.0	9.8	8.22	91.09	0.460	3150	0.1875	5.36
BCV3R0V227TZ3050		220	30 × 50	6.0	8.4	9.83	115.87	0.598	2726	0.2750	5.83
BCV3R0V257TZ3055		250	30 × 55	5.5	7.7	10.71	128.21	0.667	2877	0.3125	6.41
BCV3R0V367TZ3560		360	35 × 60	4.0	5.4	14.49	183.42	0.978	2657	0.4500	5.98
BCV3R0V407TZ3566		400	35 × 66	3.5	4.7	16.15	207.61	1.150	2537	0.5000	5.55

BCT 耐高温系列

BCT High Temperature Series

特点 Features

- 高耐温 High Temperature
- 低阻抗 Low impedance
- 长寿命 Long life

应用 Application

- 智能仪表 Intelligent instrument
- 国防军工 National defence industry
- 汽车电子 Automotive electronics

产品规格 Specifications



项目 Item	性能 Performance	
额定电压 Rated voltage	2.7V	
浪涌电压 Surge voltage	2.85 V	
容量范围 Nominal cap. range	1.0 F ~ 100 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%; -10% ~ +30%	
工作温度 Operating temperature	-40℃ ~ +85℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +85℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 1,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的3倍; ≤ 3 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +85℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 导针型 Radial type


产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size $\Phi D \times L$ (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BCT2R7S105YS0812	2.7	1.0	8 × 12	160	240	0.47	1.09	0.007	3314	0.0010	0.92
BCT2R7S205YS0816		2.0	8 × 16	120	180	0.61	1.99	0.010	3591	0.0020	1.50
BCT2R7S335YS0820		3.3	8 × 20	100	150	0.74	2.98	0.012	3645	0.0033	2.09
BCT2R7S505YS0825		5.0	8 × 25	90	135	0.87	4.03	0.016	3115	0.0051	2.43
BCT2R7S505YS1020		5.0	10 × 20	75	113	0.97	4.32	0.016	2957	0.0051	1.92
BCT2R7M705YS1025		7.0	10 × 25	60	90	1.20	5.80	0.022	3135	0.0071	2.29
BCT2R7M106YS1025		10	10 × 25	55	83	1.25	7.40	0.030	3263	0.0101	3.12
BCT2R7M106YS1030		10	10 × 30	45	68	1.51	8.06	0.032	3482	0.0101	2.72
BCT2R7M106YS1B20		10	12.5 × 20	45	68	1.42	8.06	0.032	3186	0.0101	2.49
BCT2R7M126YS1B25		12	12.5 × 25	40	60	1.66	9.42	0.040	3393	0.0122	2.83
BCT2R7M156YS1B30		15	12.5 × 30	35	53	1.93	11.33	0.055	3341	0.0152	3.05
BCT2R7M256YS1625		25	16 × 25	25	38	2.41	17.42	0.078	2794	0.0253	3.03
BCT2R7M306YS1630		30	16 × 30	20	30	2.92	21.32	0.085	3149	0.0304	3.28
BCT2R7M506YS1840		50	18 × 40	16	24	3.96	30.68	0.120	2526	0.0506	3.51
BCT2R7M107YS1860		100	18 × 60	13	20	5.30	45.76	0.250	2035	0.1013	4.59

BMW 微型模组系列

BMW Small Module Series

特点 Features

- 低漏电, 长寿命 Low leakage current, long life
- 高能量、大功率 High power, high energy density
- 免维护 Maintenance-free
- 模组定制, 满足不同需求 Module customized to meet different requirement



应用 Application

- 智能仪表 Smart meters
- 智能家电 Intelligent home appliance
- 电动玩具 Electronic toy

产品规格 Specifications

项目 Item	性能 Performance	
额定电压 Rated voltage	5.5 V; 6.0 V; 7.5 V	
容量范围 Nominal cap. range	0.33 F ~ 50 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%	
工作温度 Operating temperature	5.5 V、7.5 V: -40℃ ~ +70℃; 6.0 V: -40℃ ~ +65℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: 5.5 V、7.5 V: +70℃; 6.0 V: +65℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 5.5 V、7.5 V: 2,000(+48)hrs; 6.0 V: 1,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value (5.5 V、7.5 V) ≤ 初始值的3倍; ≤ 3 times of initial value (6.0 V)
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +70℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

● 5.5V-2串 / 2 cells in series connection

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size W × D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/mΩ)	ESR _{DC} IEC法 (mΩ)						
BMW5R5S474MA0814	5.5	0.47	6 × 8 × 14	320	480	0.47	1.05	0.006	3601	0.0020	0.94
BMW5R5S105MA0814		1.0	16 × 8 × 14	320	480	0.47	1.86	0.006	3288	0.0042	1.83
BMW5R5S105MA0818		1.0	16 × 8 × 18	240	360	0.61	2.02	0.010	4201	0.0042	1.75
BMW5R5S155MA0822		1.5	16 × 8 × 22	200	300	0.74	2.84	0.012	4172	0.0063	2.17
BMW5R5S255MA0827		2.5	16 × 8 × 27	180	270	0.87	4.10	0.015	3447	0.0105	2.69
BMW5R5S255MA1018		2.5	20 × 10 × 18	180	270	0.80	4.10	0.015	3056	0.0105	2.39
BMW5R5S255MA1022		2.5	20 × 10 × 22	150	225	0.97	4.40	0.015	3361	0.0105	2.19
BMW5R5M355MA1022		3.5	20 × 10 × 22	150	225	0.97	5.38	0.020	3361	0.0147	3.06
BMW5R5M355MA1027		3.5	20 × 10 × 27	120	180	1.20	5.90	0.020	3667	0.0147	2.67
BMW5R5M505MA1027		5.0	20 × 10 × 27	120	180	1.20	7.24	0.030	3667	0.0210	3.82
BMW5R5M505MA1032		5.0	20 × 10 × 32	90	135	1.51	8.21	0.030	4074	0.0210	3.18
BMW5R5M505MA1B22		5.0	25 × 13 × 22	90	135	1.42	8.21	0.030	3634	0.0210	2.84
BMW5R5M755MA1B27		7.5	25 × 13 × 27	80	120	1.66	9.59	0.040	3929	0.0252	3.27
BMW5R5M755MA1B32		7.5	25 × 13 × 32	70	105	1.93	11.54	0.052	3841	0.0315	3.50
BMW5R5M106MA1B32		10	25 × 13 × 32	70	105	1.93	13.42	0.055	3841	0.0420	4.67
BMW5R5M106MA1B37		10	25 × 13 × 37	60	90	2.23	14.47	0.056	3507	0.0420	3.65
BMW5R5M1B6MA1627		12.5	32 × 16 × 27	50	75	2.41	17.74	0.068	3103	0.0525	3.37
BMW5R5M156MA1632		15	32 × 16 × 32	40	60	2.92	21.71	0.075	3517	0.0630	3.66
BMW5R5M206MA1837		20	36 × 18 × 37	36	54	3.52	26.44	0.088	2988	0.0840	3.73
BMW5R5M256MA1842		25	36 × 18 × 42	32	48	3.96	31.25	0.105	2875	0.1050	3.99
BMW5R5M306MA1842		30	36 × 18 × 42	30	45	4.09	35.11	0.145	2881	0.1260	4.50
BMW5R5M506MA1862		50	36 × 18 × 62	26	39	5.30	46.61	0.240	2165	0.2101	4.89

● 7.5V-3串 / 3 cells in series connection

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size W × D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/mΩ)	ESR _{DC} IEC法 (mΩ)						
BMW7R5S334MB0814	7.5	0.33	24 × 8 × 14	480	720	0.38	1.00	0.006	3125	0.0026	0.86
BMW7R5S604MB0818		0.6	24 × 8 × 18	360	540	0.50	1.70	0.010	3472	0.0047	1.30
BMW7R5S105MB0822		1.0	24 × 8 × 22	300	450	0.61	2.59	0.012	3488	0.0078	1.82

典型产品 Standard Products

• 6.0V-2串 / 2 cells in series connection

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size W × D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BMW6R0S474MA0814	6.0	0.47	16 × 8 × 14	320	480	0.47	1.15	0.007	4286	0.0024	1.12
BMW6R0S105MA0818		1.0	16 × 8 × 18	240	360	0.61	2.21	0.012	4762	0.0050	1.98
BMW6R0S155MA0822		1.5	16 × 8 × 22	200	300	0.74	3.10	0.014	4729	0.0075	2.46
BMW6R0S255MA0827		2.5	16 × 8 × 27	180	270	0.87	4.48	0.018	3907	0.0125	3.05
BMW6R0S255MA1022		2.5	20 × 10 × 22	150	225	0.97	4.80	0.018	3810	0.0125	2.48
BMW6R0M355MA1027		3.5	20 × 10 × 27	120	180	1.20	6.44	0.024	4156	0.0175	3.03
BMW6R0M505MA1027		5.0	20 × 10 × 27	120	180	1.20	7.89	0.036	4156	0.0250	4.33
BMW6R0M505MA1B22		5.0	25 × 13 × 22	90	135	1.42	8.96	0.036	4118	0.0250	3.22
BMW6R0M755MA1B27		7.5	25 × 13 × 27	80	120	1.66	11.84	0.048	4453	0.0375	4.64
BMW6R0M106MA1B32		10	25 × 13 × 32	70	105	1.93	14.63	0.066	4354	0.0500	5.29
BMW6R0M1B6MA1627		12.5	32 × 16 × 27	50	75	2.41	19.35	0.082	3516	0.0625	3.82
BMW6R0M156MA1632		15	32 × 16 × 32	40	60	2.92	23.68	0.090	3987	0.0750	4.15
BMW6R0M256MA1842		25	36 × 18 × 42	32	48	3.96	34.09	0.126	3259	0.1250	4.53
BMW6R0M506MA1862		50	36 × 18 × 62	26	39	5.30	50.85	0.288	2453	0.2500	5.54

BMT 耐高温模组系列


BMT High Temperature Module Series

特点 Features

- 耐高温 High Temperature
- 低阻抗 Low impedance
- 长寿命 Long life

应用 Application

- 智能仪表 Intelligent instrument
- 国防军工 National defence industry
- 汽车电子 Automotive electronics



产品规格 Specifications

项目 Item	性能 Performance	
额定电压 Rated voltage	5.5 V	
容量范围 Nominal cap. range	0.33 F ~ 50 F	
容量偏差 Capacitance tolerance	-20% ~ +50%; -20% ~ +20%	
工作温度 Operating temperature	-40℃ ~ +85℃	
循环寿命 Cycle life characteristics	在25℃下, 以恒定电流使电容器在额定电压和半额定电压间循环充放电(>500,000次)。 Capacitors charge-discharge between rated voltage and half rated voltage under constant current at +25℃, (>500,000 cycles)	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
高温负荷寿命 High temperature load time	温度 Temperature: +85℃ 电压 Voltage: 额定电压 Rated voltage 测试时长 Duration of testing: 1,000(+48)hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的3倍; ≤ 3 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
温度特性 Temperature characteristics	温度 Temperature: T ± 2℃ (-40℃ ≤ T ≤ +85℃) 测试时长 Duration of storage: 12hrs 无负载 Non-loaded	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
湿热特性 Humidity characteristic	电压 Voltage: 额定电压 Rated voltage 相对湿度 Relative humidity: 90%~95% 测试时长 Duration of testing: 240hrs 温度 Temperature: 40 ± 2℃	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change
抗振性 Vibration resistance	振幅 Amplitude: 1.5mm 频率 Frequency: 10~55Hz 方向 Direction: X,Y,Z(2hrs) 测试时长 Duration of testing: 6hrs	
	容量变化 Capacitance change	≤ 初始值的30%; ≤ 30% of initial value
	内阻变化 Internal resistance	≤ 初始值的2倍; ≤ 2 times of initial value
	外观变化 Appearance	无明显变化; No apparent change

典型产品 Standard Products

• 5.5V-2串 / 2 cells in series connection

产品编码 Part number	额定电压 Rated Voltage (V)	标称容量 Rated Cap. (F)	尺寸 Size W × D × L (mm)	最大等值阻抗 Max. ESR		最大工作电流 Maximum Continuous Current(A) ($\Delta T=15^{\circ}\text{C}$)	最大峰值电流 Maximum Peak Current (A)	最大漏电流 Maximum Leakage Current (72hrs/mA)	功率密度 Power Density (W/kg)	最大能量 Maximum Energy (W.h)	能量密度 Energy Density (Wh/kg)
				ESR _{AC} (1kHz/m Ω)	ESR _{DC} IEC法 (m Ω)						
BMT5R5S474MA0814	5.5	0.47	16 × 8 × 14	320	480	0.47	1.05	0.006	3601	0.0020	0.94
BMT5R5S105MA0818		1.0	16 × 8 × 18	240	360	0.61	2.02	0.010	4001	0.0042	1.67
BMT5R5S155MA0822		1.5	16 × 8 × 22	200	300	0.74	2.84	0.012	3974	0.0063	2.07
BMT5R5S255MA0827		2.5	16 × 8 × 27	180	270	0.87	4.10	0.015	3283	0.0105	2.56
BMT5R5S255MA1022		2.5	20 × 10 × 22	150	225	0.97	4.40	0.015	3201	0.0105	2.08
BMT5R5M355MA1027		3.5	20 × 10 × 27	120	180	1.20	5.90	0.020	3492	0.0147	2.55
BMT5R5M505MA1027		5.0	20 × 10 × 27	120	180	1.20	7.24	0.030	3492	0.0210	3.64
BMT5R5M505MA1B22		5.0	25 × 13 × 22	90	135	1.42	8.21	0.030	3461	0.0210	2.70
BMT5R5M755MA1B27		7.5	25 × 13 × 27	80	120	1.66	10.86	0.040	3741	0.0315	3.90
BMT5R5M106MA1B32		10	25 × 13 × 32	70	105	1.93	13.41	0.055	3658	0.0420	4.45
BMT5R5M1B6MA1627		12.5	32 × 16 × 27	50	75	2.41	17.74	0.068	2955	0.0525	3.21
BMT5R5M156MA1632		15	32 × 16 × 32	40	60	2.92	21.71	0.075	3350	0.0630	3.49
BMT5R5M256MA1842		25	36 × 18 × 42	32	48	3.96	31.25	0.105	2739	0.1050	3.80
BMT5R5M506MA1862		50	36 × 18 × 62	26	39	5.30	46.61	0.240	2062	0.2101	4.65

BMB 定制模组系列

BMB Customized Module Series

定制模组 Custom module

- 根据客户需求定制各种规格、尺寸模组产品，提供完整能源系统解决方案，满足客户不同储能、功率要求。
- Design different performance and size of module, provide integrate solution of power system, to satisfy different application in power output and energy storage.

模组设计案例 Designed module examples

产品型号 项目 Item	13.5V 44F	48V 22F	48V 165F
额定电压 Rated voltage	13.5V	48V	48V
额定容量 Rated capacity	44F	22F	165F
ESR _{DC}	≤45mΩ	≤65mΩ	≤6.0mΩ
最大峰值电流 Maximum peak current	100A	220A	1990A
外包装方式 Outer packing	塑料套管热缩 Heat-shrinkable plastic sleeve	塑料套管热缩 Heat-shrinkable plastic sleeve	金属外壳 Metal case
绝缘耐压特性 Voltage withstand characteristic	直流DC: 1KV, 交流AC: 2.5KV		
工作温度范围 Operating temp. range	-40~+70℃		
均衡方式 Balancing mode	主动 Active		主动+被动 Active & Passive
均衡开启电压 Balancing threshold voltage	2.65V	2.6~2.7V	2.65V
尺寸 Size	155 × 32 × 62mm	250 × 115 × 80mm	416 × 190 × 217mm
应用原理 Application principle	摩托车低温启动 Low temperature start-up for motorcycle	36V电动自行车辅助电源 36V auxiliary power supply for electric bicycle	风电变桨及其他储能系统 Wind turbine pitch and other energy storage systems



模组设计说明 Description of module design**● 单体分选 Cells separation**

- ◆ 超级电容单体按容量及内阻进行分档，并对漏电流和自放电进行分选，以提高超级电容单体配组的精准度，提高模组产品的可靠性及稳定性。
- ◆ Cells can be classified by capacitance, internal resistance, leakage current and self discharge to improve precision of the group matching, so as to improve the reliability and stability of the module.

● 电路设计 Circuit design

- ◆ 功能：根据客户需求专门设计
- ◆ 性能：根据客户应用负载特性优化设计
- ◆ 均衡：主动+被动均衡
- ◆ 检测：单体过充检测、过温检测、反充检测等
- ◆ 通讯：根据客户需求，可设计 SPI、RS232、RS485、CAN、12C、SMBUS、以太网及光纤通讯等多种通讯方式同
- ◆ PCB：用料扎实，牢固，内阻小、过电流高、散热好
- ◆ 附加功能：监测每并模组电压、计算模组剩余容量、甚至每只单体剩余容量及健康状况等
- ◆ Function: design by client's requirement.
- ◆ Property: design by client's applicated load characteristic
- ◆ Balance mode: active and passitive
- ◆ Detection: cell's over-charge test, over temperature test, counter charging test, etc.
- ◆ Communication mode: designed according to client's requirement, such as mode of SPI、RS232、RS485、CAN、12C、SMBUS ethernet or optical fiber communication
- ◆ PCB: sturdy, firm, low internal resistance, high overcurrent, good property of heat dissipation
- ◆ Additional function: monitoring voltage of every parallel module, calculate surplus capacitance of module, and even surplus capacitance and conditions of each cell


● 结构设计 Structure design

- ◆ 单体与模组互相配合
- ◆ 采用CAM三维设计
- ◆ 结构简单，方便易装
- ◆ 牢固结实，强度高，抗破坏性强
- ◆ 辅助配件精挑细选，保证在恶劣的环境中也能正常使用
- ◆ Cells and module work in coordination
- ◆ Design by CAM 3D
- ◆ Simple structure, easy for packing
- ◆ Firm, high strength, good property of damage resistance
- ◆ Carefully choose accessories to ensure normal use in hostile environment.

技术信息

Technical Information

IEC容量测试方法 IEC Capacity Test Method



容量计算公式:
Capacitance caculation fomula:

$$C = \frac{IX(t_2 - t_1)}{U_1 - U_2}$$

其中:

I : 放电电流 Discharge current

$$I = 4 \times C \times U_R (\text{mA})$$

U_1 : 初始电压 Initial voltage

$$U_1 = 0.8 \times U_R (\text{V})$$


U_2 : 测量结束电压 Test finish voltage

$$U_2 = 0.4 \times U_R (\text{V})$$

t_1 : 初始电压 U_1 对应的时间 Time corresponding to initial voltage (s);

t_2 : 测量结束电压 U_2 对应的时间 Time corresponding to test finish voltage (s);

IEC ESR_{DC} 测试方法 IEC ESR_{DC} Test Method



ESR_{DC}计算公式:
ESR_{DC} Caculation fomula:

$$\text{ESR}_{\text{DC}} = \frac{U_1 - U_2}{I}$$

其中:


I : 放电电流 Discharge current

$$I = 40 \times C \times U_R (\text{mA})$$

U_1 : 放电初始电压 Initial voltage at discharge beginning;

U_2 : 放电10ms后结束电压 Finish voltage after 10 msec' s discharge;

Δt : 放电时长 Time for discharge $\Delta t = (t_2 - t_1) = 10 \text{msec}$

六步法容量及ESR_{DC}测试方法 Capacity and ESR_{DC} Test Method by six steps

计算公式 Calculation formula:

两次循环放电容量 capacitance of the two cycle:

$$Cdch1 = I2 \times (t5 - t4) / (V3 - V4); \quad Cdch2 = I2 \times (t11 - t10) / (V9 - V10);$$

两次循环放电直流内阻 Discharge DC internal resistance:

$$ESRdch1 = (V5 - V4) / I2; \quad ESRdch2 = (V11 - V10) / I2;$$

放电容量 Discharge capacitance:

$$Cdch = (Cdch1 + Cdch2) / 2;$$

放电直流内阻 Discharge DCESR:

$$ESRdch = (ESRdch1 + ESRdch2) / 2;$$

其中: $I1 = I2 = 75\text{mA/F}$

测试步骤 Test steps:

step1: 搁置10s;

Rest (Open Circuit) 10 seconds;

step2: 以电流I1恒流充电至额定电压U_R;

Charge device to its rated voltage at constant current I1;

step3: 搁置5s;

Rest (Open Circuit) 5 seconds;

step4: 搁置10s, 记录t₄、V₃;

Rest 10 seconds. Record test time and voltage at end of test (t₄, V₃);

step5: 以电流I₂恒流放电至50%U_R, 记录I₂、V₄、t₅;

Discharge device to one-half its rated voltage at constant current I2.

Record test current, test time and voltage at end of the test (I₂, t₅, V₄);

step6: 搁置5s, 记录t₆、V₅;

Rest 5 seconds. Record test time and test voltage at end of the rest (t₆, V₅);

重复step1~step6, 并记录对应的电流、电压和时间, 最后以电流I₂恒流放电至0.1V以下。

Repeat Step 1 to step 6. Discharge device to low safe voltage (<0.1V) after the second cycle at current I2.

其他Others

- 最大工作电流: 15°C温升时的最大工作电流

Maximum operating current: the maximum current when temperature rised 15°C

$$I_{MAX} = \sqrt{15 \times S_{表} / ESR_{DC}}$$

- 最大峰值电流: 1秒钟放电至1/2U_R的最大放电电流

Maximum peak current: the maximum current which the capacitor discharges from U_R to 1/2U_R in 1 second.

$$I_{MAX} = 0.5U_R / (R_{DC} + 1/C)$$

- 漏电流: 25°C下恒压72小时后的泄漏电流

Leakage current: the current after 72 hours constant voltage load in 25°C

- 最大储存能量 Maximum storage energy :

$$E = 0.5CU_R^2$$

- 功率密度 Power density:

$$Pd = (0.12 \times U_R^2 / ESR_{DC}) / \text{mass}$$

- 能量密度 Energy density

$$Ed = (0.5CU_R^2) / (3600 \times \text{mass})$$

使用说明

Instruction

此文档将提供双电层电容器 (EDLC) 基本应用开发指南。若在开发使用过程中遇到问题且在此文件中找不到相关解决方案, 请直接与我们联系。

This document provides basic guidelines for application development using Electric Double Layer Capacitors (EDLC). If there is any questions during your development process that are not answered in the document, please contact us directly.

1、寿命 Lifetime

EDLC基本的寿命终止失效模式为容量下降、等效串联阻抗 (ESR) 增加, 通常以容量下降30%、阻抗增加200%之性能变化作为寿命终止之标准。EDLC只是在其使用期内性能不断衰减, 而非真正报废。当性能不再能保持在应用要求的水平时, 超级电容器将报废。

EDLC的寿命主要受工作电压和温度的影响。将电容器置于高温、高电压下会导致寿命缩短。如果持续过压, EDLC内将会产生气体, 导致漏液或防爆阀打开。高温下电容器ESR升高会导致电解液分解、EDLC永久劣化。

The basic end-of life failure mode for the EDLC is a decrease in capacitance and/or an increase in equivalent series resistance (ESR). Usually take the standard of capacitance decrease by 30% and/or ESR increase to 200% as the symbol of EDLC life end. Just the performance of EDLC will continue to decay during the application, but not to be scrapped. When its performance can not keep at the application level required, the super capacitor will be scrapped.

The EDLC's life mainly depends on working voltage and ambient temperature. If the capacitors are placed in high temperature or work at high voltage, their life time will be shortened. If the applied voltage is over rated voltage for long time, gas generation will occur inside the EDLC and may result in electrolyte leakage or rupture of safety vent. Increased ESR at higher temperature will lead to electrolyte decompose inside the EDLC and result in permanent degradation.

2、反向电压 Reverse voltage

EDLC的正、负极由相同材料组成。理论上EDLC没有真正的极性。出于制造和一致性目的, 每一个电容器有负极框或符号来标识极性。虽然EDLC被反向充电不会引发灾难性的故障, 但保持极性是推荐的做法。如果在一方向上长期充电后再进行反向充电, EDLC的寿命将会大大的缩短。

The positive and negative polarity of EDLC are similar in composition. So there's no real polarity for EDLC in theory. To keep consistency of manufacture and products, there's negative polarity sign on each capacitor. It is recommended to keep right polarity, though it will not cause disastrous failure when reverse charge. It will greatly shorten the life of EDLC when charge it in one polarity for long and then reverse charge.

3、温度表现 Temperature performance

绿宝石公司的EDLC标准工作温度范围为-40℃~+70℃。EDLC在高于额定温度下使用, 将导致容量快速下降, ESR上升, 电解液分解而产生大量气体, 最终导致产品漏液或防爆阀打开。温度越高、持续时间越长则性能劣化越严重。

一般来说, 环境温度每升高10℃, EDLC的寿命就会缩减一半; 在低于正常室温下使用时, EDLC的使用电压可以稍高于额定电压而不会造成内部劣化和寿命缩短。因此, 建议尽可能降低温度使用。在低温下电解液粘性提升, 离子的移动变得缓慢, ESR升高只是一种短暂现象; 在高温时ESR的升高, 电解液发生分解造成EDLC性能永久性劣化。环境温度加上内部温升应控制在额定上限温度之下。降低温度使用可提高产品工作电流或延长产品寿命。

BERYL EDLC normal working temperature is $-40^{\circ}\text{C}\sim+70^{\circ}\text{C}$. If the EDLC is applied in higher temperature than rated temperature, it will cause capacitance decrease quickly, ESR increase and decomposition of electrolyte, which will produce a large volume of gas, then lead to electrolyte leakage or rupture of safety vent. The higher the temperature and the longer the time, the performance of EDLC will be worse.

Generally, the ambient temperature raise by every 10°C , the life time of EDLC will shorten by half. At temperature lower than normal room temperature, it is possible to apply voltages slightly higher than the rated voltage without significant effects of degradation in performance and reduction in life time. Therefore, it is recommended to use EDLC in low temperature. At low temperature, increased ESR is only a temporary phenomenon due to the increased viscosity of the electrolyte and slower movement of the ions. At high temperature, ESR increasing will result in permanent degradation and electrolyte decomposition inside the EDLC. The total temperature, ambient temperature add internal temperature rise, should be controlled under the rated maximum temperature. Larger working current and longer life time can be obtained when introduce cooler environment.

4、充电方法 Charge method

EDLC主要是通过静电电荷在活性碳电极表面进行物理性吸附/脱附，瞬间存储能量，充放电过程不发生化学反应，因此可采用大倍率快速充放电。EDLC可采用多种方法进行充电，包括恒定电流、恒定电压、恒定功率或与能量储存器（例如电池）进行并联充电。如果EDLC与电池并联，加一个低阻值串联电阻将会提升电池的寿命。

EDLC stores energy by the physical mechanism of electric charge absorption/desorption at the surface of active carbon electrode. There is not chemical reaction during charge-discharge process, so it can be charged or discharged fast with high current. EDLC can be charged using various methods including constant current, constant power, constant voltage or by paralleling to an energy source (i.e. battery). If an EDLC is configured in parallel with a battery, adding a low value resistor in series will increase the life of the battery.

5、串联 Series connection

对于大多数应用而言，单个EDLC的电压过低（2.7V或3.0V），需通过串联电容器达到更高电压的使用要求。由于每个EDLC在电容和阻抗上有轻微的差别，应采取电路均衡以防止某单体过充而造成模组性能劣化。

The voltage of single EDLC is too low (2.7V or 3.0V) for most applications. So EDLC connection in series is used to obtain higher voltage for those application. Since there is slight difference between each EDLC in capacitance and resistance, circuit balance should be considered in the module to prevent single cell exceeds the rated voltage during charge, which would cause performance degradation of the module.

6、焊接 Welding

焊接过热会导致EDLC电性能退化、漏液或内压上升。EDLC焊接应遵循以下具体指引：

不能把EDLC浸入已熔解的焊锡中，只能在其导针或焊脚上粘上焊锡。

- 确保EDLC外部套管不与PCB或其它组件直接接触，焊锡温度过高会导致套管收缩或破裂。
- 避免EDLC在裸露的电路板上工作，以防止发生短路。

• 手工焊接：

避免EDLC外部套管与烙铁接触，否则套管会熔化或破裂；焊嘴温度建议低于 350°C ，焊接持续时间少于4秒钟；应尽可能减少烙铁与EDLC焊脚直接接触的时间，以免过热导致EDLC性能不良。

• 波峰焊：

给PCB预热不应超过60秒钟，预热温度不高于 100°C ，浸锡应使锡层厚度达到0.8mm或更厚。

下表波峰焊接信息仅适用于导针型产品：

Wave soldering information listed in following table is used only for leads type EDLC:

焊锡温度 Solder Bath Temperature (°C)	建议焊锡时间 Recommended solder duration (second)	最大焊接时间 Maximum Solder duration (second)
220	7	9
240	7	9
250	5	7
260	3	5

- 回流焊：

除非规定有明确的额定耐回流焊接温度，否则EDLC不能使用回流焊接，而应使用红外线或传送加热方式进行焊接。

Excessive heat may result in deterioration of the electrical properties of the EDLC and electrolyte leakage or internal pressure increasing. Follow the specific soldering instructions listed as below:

- ◆ Do not dip EDLC body into melted solder. Only the lead or welded leg of the EDLC can immerse solder.
- ◆ Ensure there is no direct contact between the sleeve of the EDLC and the PCB or any other component.

Excessive heat may cause sleeve to shrink or crack.

- ◆ Avoid installing the EDLC on the exposed circuit board to prevent electrical shorts
- Hand welding：

Do not contact the sleeve of EDLC with soldering iron, otherwise the sleeve will melt or rupture. The recommended temperature of the soldering rod tip is less than 350°C and the solder duration should be less than 4 seconds. Minimize the time that the soldering iron is in direct contact with the terminals of the EDLC, as excessive heat of the terminal of EDLC may lead to deterioration of EDLC.

- Wave soldering：

Use a preheating time not more than 60 seconds for PCB, and preheating temperature should be limited to less than 100°C. Let the thickness of immersion tin layer to be 0.8mm or thicker.

- Reflow soldering：

Do not use reflow soldering unless there are specific rated soldering temperature. Use infrared or convection heating method on the EDLC instead.

7、纹波电流 Ripple Current

EDLC相比于铝电解电容器具有更高的内阻，在纹波电流中容易受内部热量的影响而使ESR升高，寿命缩短。为了避免过热造成电解液分解、ESR增加及寿命缩短，建议在最大纹波电流下工作时EDLC表面温度增加不超过3°C。

EDLC has a higher resistance than aluminum electrolytic capacitor, so it is more susceptible to internal heat generation when exposed to ripple current. The maximum ripple current recommended should not increase the surface temperature of the EDLC by more than 3° C, to avoid heat generation which leads to electrolyte decomposition, increased ESR and reduced life time.

8、贮存 Storage

不要在以下环境中长期储存EDLC：

- 高温/高湿环境。
- 阳光直射，粉尘环境。
- 直接与水、盐水、油或其它化学品接触。
- 直接与腐蚀性材料、酸、碱金属或有毒气体接触。
- 冲击或振动环境。

Do not store the EDLC in the following environments:

- High temperature / high humidity environments.
- Direct sunlight, dust environment.
- Direct contact with the water, salt, oil or other chemicals.
- Direct contact with corrosive materials, acids, alkalies or toxic gases.
- Shock or vibration environments.

9、运输 Transportation

EDLC的国际运输受到US DOT (运输部) /IATA的规定；正确的国际运输产品编码是UN3499 Capacitor: electric double layer (with an energy storage capacity greater than 0.3Wh) (双电层电容，储电量大于0.3Wh)

EDLC are regulated by the US DOT / IATA transportation regulations. Proper shipping name for EDLC is UN3499 CAPACITOR, electric double layer (with an energy storage capacity greater than 0.3Wh).

10、紧急事故应用程序 Emergency procedures

如果发现EDLC过热或是闻到气味，应立即断开与EDLC连接的电源和负载，让其降温，然后进行正确处理，不可让脸或手接触过热的EDLC；如果EDLC发生漏液或防爆阀打开，请与我司联系索取材料物质安全资料表（MSDS）。

如果暴露于电解液：

- 皮肤接触：用肥皂水和清水彻底冲洗皮肤。
- 眼睛接触：用流动清水或生理盐水冲洗，就医。
- 吸取：立即用水漱口，就医。

If you detect the EDLC overheating or if you smell unique odor, immediately disconnect any power or load to the EDLC. Allow the EDLC to cool down, then dispose it properly. Do not expose your face or hands to an overheating EDLC. Contact the factory for a Material Safety Data Sheet if the EDLC leaks or vents.

If exposed to electrolyte:

- Skin contact: Use soap and water thoroughly wash skin.
- Eye contact: Flush with flowing water or saline, and immediately ask for medical treatment.
- Ingestion: Immediately wash with water and ask for medical treatment.

11、一般性安全考虑 General safety consideration

EDLC在使用或测试完后，需将其电压放电至0.1V以下，以避免短路产生安全隐患。

如果过度充电、反向充电、焚烧或高于150℃加热，EDLC有可能发生防爆阀爆裂。不要压挤、损伤、穿刺或拆解EDLC，滥用可能导致铝壳发热造成高温烫伤或烧伤。

不要随意丢弃EDLC，应根据当地法律法规处置。

Make sure the EDLC is discharged to below 0.1V at the end of use or test to avoid potential safety hazard caused by short circuit.

EDLC may vent or rupture if overcharged, reverse charged, incinerated or heated above 150° C. Do not crush, mutilate, nail penetrate or disassemble the EDLC. Abuse of EDLC may result in high temperature on aluminum shell which may cause burn hazard.

Do not carelessly dispose EDLC in trash, but dispose according to local regulations.

Qualifications and certificates





肇庆绿宝石电子科技股份有限公司

Zhao Qing Beryl Electronic Technology Co., Ltd.

中国广东省肇庆市端州区端州八路

NO.8 Duanzhou Road, Duanzhou District, Zhaoqing City, Guangdong Province, P.R. China

邮政编码 Postcode : 526020

邮箱 Email : master@zq-beryl.com

总机 TEL : +86-758-2862871

传真 FAX : +86-758-2862870

广东伊缔康新能源科技有限公司

Guangdong EDLCON New Energy Technology Co., Ltd.

中国广东省肇庆市肇庆高新区创新创业科学园B1幢

Building B1, Innovation and Entrepreneurship Science Park, Zhaoqing High-tech Zone,
Zhaoqing City, Guangdong Province, P.R. China



[http : //www.zq-beryl.com](http://www.zq-beryl.com)