

1EDI EiceDRIVER™ Compact

1EDI20N12AF

Single Channel MOSFET and GaN HEMT Gate Driver IC

1EDI20N12AF

Data Sheet

Rev. 2.0, 2015-06-01

Industrial Power Control

Edition 2015-06-01

Published by Infineon Technologies AG 81726 Munich, Germany © 2015 Infineon Technologies AG All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



Revision Histo	ory	
Page or Item	Subjects (major changes since previous revision)	
Rev. 2.0, 2015	-06-01	
p17	dynamic parameter update	
Rev. 1.03, 201	4-10-14	
all pages	parameter completion	
Rev. 1.02, 201	4-02-14	
p 8	application diagram	

Trademarks of Infineon Technologies AG

AURIXTM, BlueMoonTM, C166TM, CanPAKTM, CIPOSTM, CIPURSETM, COMNEONTM, EconoPACKTM, CoolMOSTM, CoolSETTM, CORECONTROLTM, CROSSAVETM, DAVETM, EasyPIMTM, EconoBRIDGETM, EconoDUALTM, EconoPIMTM, EiceDRIVERTM, eupecTM, FCOSTM, HITFETTM, HybridPACKTM, I2RFTM, ISOFACETM, IsoPACKTM, MIPAQTM, ModSTACKTM, my-dTM, NovalithICTM, OmniTuneTM, OptiMOSTM, ORIGATM, PRIMARIONTM, PrimePACKTM, PrimeSTACKTM, PRO-SILTM, PROFETTM, RASICTM, ReverSaveTM, SatRICTM, SIEGETTM, SINDRIONTM, SIPMOSTM, SMARTITM, SmartLEWISTM, SOLID FLASHTM, TEMPFETTM, thinQ!TM, TRENCHSTOPTM, TriCoreTM, X-GOLDTM, X-PMUTM, XMMTM, XPOSYSTM.

Other Trademarks

Advance Design System™ (ADS) of Agilent Technologies, AMBA™, ARM™, MULTI-ICE™, KEIL™, PRIMECELL™, REALVIEW™, THUMB™, µVision™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. Mifare™ of NXP. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO., MICROWAVE OFFICE™ (MWO) of Applied Wave Research Inc., OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Satellite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2010-10-26

Data Sheet 3 Rev. 2.0, 2015-06-01



Table of Contents

	Table of Contents
	List of Figures
	List of Tables
I	Overview
2	Block Diagram
3.1 3.2	Pin Configuration and Functionality 10 Pin Configuration 10 Pin Functionality 10
14.1 14.2 14.3 14.3.1 14.3.2 14.3.3 14.4 14.5	Functional Description 12 Introduction 12 Supply 12 Protection Features 13 Undervoltage Lockout (UVLO) 13 Active Shut-Down 13 Short Circuit Clamping 13 Non-Inverting and Inverting Inputs 13 Driver Outputs 13
5.1 5.2 5.3 5.3.1 5.3.2 5.3.3 5.3.4 5.3.5 5.3.6	Electrical Parameters 14 Absolute Maximum Ratings 14 Operating Parameters 15 Electrical Characteristics 15 Voltage Supply 15 Logic Input 16 Gate Driver 16 Short Circuit Clamping 17 Dynamic Characteristics 17 Active Shut Down 18
6	Timing Diagramms
7	Package Outlines
3 3.1 3.2	Application Notes 2° Reference Layout for Thermal Data 2° Printed Circuit Board Guidelines 2°





List of Figures

igure 1	Typical Application	. 8
igure 2	Block Diagram 1EDI20N12AF	. 9
igure 3	PG-DSO-8-51 (top view)	10
igure 4	Application Example Bipolar Supply	12
igure 5	Application Example Unipolar Supply	12
igure 6	Propagation Delay, Rise and Fall Time	19
igure 7	Typical Switching Behavior	19
igure 8	UVLO Behavior	19
igure 9	PG-DSO-8-51 (Plastic (Green) Dual Small Outline Package)	20
igure 10	Reference Layout for Thermal Data (Copper thickness 35 µm)	21

Data Sheet 5 Rev. 2.0, 2015-06-01





List of Tables

Table 1	Pin Configuration
Table 2	Absolute Maximum Ratings
Table 3	Operating Parameters
Table 4	Voltage Supply
Table 5	Logic Input
Table 6	Gate Driver
Table 7	Short Circuit Clamping
Table 8	Dynamic Characteristics
Table 9	Active Shut Down

Data Sheet 6 Rev. 2.0, 2015-06-01



1EDI EiceDRIVER™ Compact Single Channel MOSFET and GaN HEMT Gate Driver IC

1EDI20N12AF

1 Overview

Main Features

- Single channel isolated Gate Driver
- Input to output isolation voltage up to 1200 V
- For high voltage power FETs
- 4 A typical peak current at rail-to-rail outputs
- Separate source and sink outputs

Product Highlights

- Galvanically isolated Coreless Transformer Driver
- Low input to output capacitive coupling
- Suitable for operation at high ambient temperature
- · Wide input voltage operating range
- ideally suited for driving cascoded or normally-off Gallium Nitride HEMTs

Typical Application

- · AC and Brushless DC Motor Drives
- High Voltage PFC, DC/DC-Converter and DC/AC-Inverter
- Induction Heating Resonant Application
- UPS-Systems
- Welding
- · Solar MPPT boost converter

Description

The 1EDI20N12AF is a galvanically isolated single channel FET driver in a PG-DSO-8-51 package that provides output currents of at least 2 A at separated output pins.

The input logic pins operate on a wide input voltage range from 3 V to 15 V using CMOS threshold levels to support even 3.3 V microcontroller.

Data transfer across the isolation barrier is realized by the Coreless Transformer Technology.

The undervoltage lockout (UVLO) functions for both input and output chip and an active shutdown feature are included to always guarantee safe operation.

Product Name	Gate Drive Current (min)	Package		
1EDI20N12AF	±2.0 A MOSFET level optimized	PG-DSO-8-51		







Overview




Figure 1 Typical Application

Data Sheet 8 Rev. 2.0, 2015-06-01



Block Diagram

2 Block Diagram




Figure 2 Block Diagram 1EDI20N12AF

Data Sheet 9 Rev. 2.0, 2015-06-01



Pin Configuration and Functionality

3 Pin Configuration and Functionality

3.1 Pin Configuration

Table 1 Pin Configuration

Pin No.	Name	Function
1	VCC1	Positive Logic Supply
2	IN+	Non-Inverting Driver Input (active high)
3	IN-	Inverting Driver Input (active low)
4	GND1	Logic Ground
5	VCC2	Positive Power Supply Output Side
6	OUT+	Driver Source Output
7	OUT-	Driver Sink Output
8	GND2	Power Ground




Figure 3 PG-DSO-8-51 (top view)

3.2 Pin Functionality

VCC1

Logic input supply voltage with wide operating range (3.3 V o 15 V).

IN+ Non Inverting Driver Input

IN+ non-inverted control signal for driver output if IN- is set to low. (Output sourcing active at IN+ = high and IN- = low)

Due to internal filtering a minimum pulse width is defined to ensure robustness against noise at IN+. An internal pull-down-resistor favors off-state.

Data Sheet 10 Rev. 2.0, 2015-06-01



1EDI EiceDRIVER™ Compact 1EDI20N12AF

Pin Configuration and Functionality

IN- Inverting Driver Input

IN- inverted control signal for driver output if IN+ is set to high. (Output sourcing active at IN- = low and IN+ = high) Due to internal filtering a minimum pulse width is defined to ensure robustness against noise at IN-. An internal pull-up-resistor favors off-state.

GND1

Ground connection of input circuit.

VCC2

Positive power supply pin of output driving circuit. A proper blocking capacitor has to be placed close to this supply pin.

OUT+ Driver Source Output

Driver output pin sourcing current to turn on external switch transistor. During on-state the driving output is switched to VCC2. Switching of this output is controlled by IN+ and IN-, resp.. This output will also be turned off at an UVLO event.

During turn off the OUT+ terminal is able to sink approx. 100 mA.

OUT- Driver Sink Output)

Driver output pin sinking current to turn off external switch transistor. During off-state the driving output is switched to GND2. Switching of this output is controlled by IN+ and IN-, resp.. In case of UVLO an active shut down keeps the output low.

GND2 Reference Ground

Reference ground of the output driving circuit.

In case of a bipolar supply (positive and negative voltage with respect to switch source potential) this pin is connected to the negative supply voltage.

Data Sheet 11 Rev. 2.0, 2015-06-01



Functional Description

4 Functional Description

4.1 Introduction

The 1EDI EiceDRIVER™ Compact is a general purpose gate driver. Basic control and protection features support fast and easy design of highly reliable systems.

The galvanic isolation between input logic and driver output is achieved by utilizing on-chip Coreless Transformer Technology. The wide input range supports the direct connection of various signal sources like DSPs and microcontrollers.

The separated rail-to-rail driver outputs simplify gate resistor selection, save an external high current bypass diode and improve dV/dt control.




Figure 4 Application Example Bipolar Supply

4.2 Supply

The driver can operate over a wide supply voltage range, either unipolar or bipolar.

With bipolar supply the driver is typically operated with a positive voltage of 12 V at VCC2 and a negative voltage of -8V at GND2 relative to the source potential as seen in **Figure 4**. Negative supply can help to prevent a dynamic turn on.

For unipolar supply configuration the driver is typically supplied with a positive voltage of 12 V at VCC2. In this case, careful evaluation for turn off gate resistor selection is recommended to avoid dynamic turn on (see Figure 5).




Figure 5 Application Example Unipolar Supply

Data Sheet 12 Rev. 2.0, 2015-06-01



1EDI EiceDRIVER™ Compact 1EDI20N12AF

Functional Description

4.3 Protection Features

4.3.1 Undervoltage Lockout (UVLO)

To ensure correct switching the device is equipped with an undervoltage lockout for input and output independently. Operation starts only after both VCC levels have increased beyond the respective V_{UVLOH} levels (see also **Figure 8**).

If the power supply voltage V_{VCC1} of the input chip drops below V_{UVLOL1} a turn-off signal is sent to the output chip before power-down. The switch is turned off and the signals at IN+ and IN- are ignored until V_{VCC1} reaches the power-up voltage V_{UVLOH1} again.

If the power supply voltage V_{VCC2} of the output chip goes down below V_{UVLOL2} the switch is again turned off and signals from the input chip are ignored until V_{VCC2} reaches the power-up voltage V_{UVLOH2} again.

Note: V_{VCC2} is always referred to GND2; the output UVLO function thus depends on the total supply voltage.

4.3.2 Active Shut-Down

The Active Shut-Down feature ensures a safe off-state if the output chip is not connected to the power supply, The gate is clamped at OUT- to GND2.

4.3.3 Short Circuit Clamping

During short circuit the gate voltage tends to rise because of the feedback via the Miller capacitance. An additional protection circuit connected to OUT+ limits this voltage to a value slightly higher than the supply voltage. A maximum current of 500 mA may be fed back to the supply through this path for 10 μ s. If higher currents are expected or tighter clamping is desired external Schottky diodes may be added.

4.4 Non-Inverting and Inverting Inputs

There are two possible input modes to control the switch. In the non-inverting mode IN+ controls the driver output while IN- is set to low. In the inverting mode IN- controls the driver output while IN+ is set to high, see **Figure 7**. A minimum input pulse width is required to filter occasional glitches.

4.5 Driver Outputs

The output driver section uses MOSFETs to provide a rail-to-rail output. This feature permits that tight control of gate voltage during on-state and short circuit can be maintained as long as the driver's supply is stable. Due to the low internal voltage drop, switching behaviour is predominantly governed by the gate resistor. Furthermore, it reduces the power to be dissipated in the driver.

Data Sheet 13 Rev. 2.0, 2015-06-01



Electrical Parameters

5 Electrical Parameters

5.1 Absolute Maximum Ratings

Note: Absolute maximum ratings are defined as absolute limits, i.e. exceeding them may lead to destruction of the integrated circuit.

Table 2 Absolute Maximum Ratings

Parameter	Symbol	Va	lues	Unit	Note /	
		Min.	Max.		Test Condition	
Power supply output side	$V_{\sf VCC2}$	-0.3	40	V	1)	
Gate driver output	V_{OUT}	V_{GND2} -0.3	V _{VCC2} +0.3	V	_	
Positive power supply input side	$V_{\sf VCC1}$	-0.3	18.0	V	_	
Logic input voltages (IN+,IN-)	$V_{LogicIN}$	-0.3	18.0	V	_	
Input to output isolation voltage	V_{ISO}	-1200	1200	V		
Junction temperature	T_{J}	-40	150	°C	_	
Storage temperature	T_{S}	-55	150	°C	_	
Power dissipation (Input side)	$P_{D,IN}$	_	25	mW	$^{2)}$ @ T_{A} = 25°C	
Power dissipation (Output side)	$P_{D,OUT}$	_	400	mW	$^{2)}$ @ T_{A} = 25°C	
Thermal resistance (Input side)	$R_{THJA,IN}$	_	145	K/W	²⁾ @T _A = 85°C	
Thermal resistance (Output side)	$R_{THJA,OUT}$	_	165	K/W	²⁾ @T _A = 85°C	
ESD capability	$V_{\mathrm{ESD,HBM}}$	_	2	kV	Human Body Model ³⁾	

¹⁾ With respect to GND2.

Data Sheet 14 Rev. 2.0, 2015-06-01

²⁾ See **Figure 10** for reference layouts for these thermal data. Thermal performance may change significantly with layout and heat dissipation of components in close proximity.

³⁾ According to EIA/JESD22-A114-C (discharging a 100 pF capacitor through a 1.5 k Ω series resistor).



Electrical Parameters

5.2 Operating Parameters

Note: Within the operating range the IC operates as described in the functional description. Unless otherwise noted all parameters refer to GND1.

Table 3 Operating Parameters

Parameter	Symbol		Values		Note /
		Min.	Max.		Test Condition
Power supply output side	$V_{\sf VCC2}$	10	35	V	1)
Power supply input side	V_{VCC1}	3.1	17	V	_
Logic input voltages (IN+,IN-)	$V_{LogicIN}$	-0.3	17	V	_
Switching frequency	$f_{\sf sw}$	_	4.0	MHz	2) 3)
Ambient temperature	T_{A}	-40	125	°C	_
Thermal coefficient, junction-top	$\Psi_{th,jt}$	_	4.8	K/W	³⁾ @T _A = 85°C
Common mode transient immunity (CMTI)	$ \mathrm{d}V_{\mathrm{ISO}}/\mathrm{dt} $	-	100	kV/μs	³⁾ @ 1000 V

¹⁾ With respect to GND2.

5.3 Electrical Characteristics

Note: The electrical characteristics include the spread of values in supply voltages, load and junction temperatures given below. Typical values represent the median values at T_A = 25°C. Unless otherwise noted all voltages are given with respect to their respective GND (GND1 for pins 1 to 3, GND2 for pins 5 to 7).

5.3.1 Voltage Supply

Table 4 Voltage Supply

Parameter	Symbol	Values			Unit	Note /
		Min.	Тур.	Max.		Test Condition
UVLO threshold input	$V_{\rm UVLOH1}$	_	2.85	3.1	V	_
chip	V_{UVLOL1}	2.55	2.75	_	V	_
	V _{HYS1}	90	100	-	mV	_
UVLO threshold output	$V_{\sf UVLOH2}$	_	9.1	10.0	V	_
chip (MOSFET Supply)	$V_{\sf UVLOL2}$	8.0	8.5	_	V	_
	V_{HYS2}	550	600	-	mV	_

Data Sheet 15 Rev. 2.0, 2015-06-01

²⁾ do not exceed max. power dissipation

³⁾ Parameter is not subject to production test - verified by design/characterization

1EDI EiceDRIVER™ Compact 1EDI20N12AF

Electrical Parameters

Table 4 Voltage Supply (cont'd)

Parameter	Symbol		Values			Note /
		Min.	Тур.	Max.		Test Condition
Quiescent current input chip	I_{Q1}	-	0.65	1.0	mA	V_{VCC1} = 5 V IN+ = High, IN- = Low =>OUT = High
Quiescent current output chip	I_{Q2}	_	1.2	2.0	mA	$V_{\rm VCC2}$ = 15 V IN+ = High, IN- = Low =>OUT = High

5.3.2 Logic Input

Note: Unless stated otherwise VCC1 = 5.0V

Table 5 Logic Input

Parameter	Symbol	Values			Unit	Note /
		Min.	Тур.	Max.		Test Condition
IN+,IN- low input voltage	V_{IN+L}, V_{IN-L}	_	_	30	%	of VCC1
IN+,IN- high input voltage	V_{IN+H}, V_{IN-H}	70	_	_	%	of VCC1
IN+,IN- low input voltage	V_{IN+L}, V_{IN-L}	_	_	1.5	V	_
IN+,IN- high input voltage	V_{IN+H}, V_{IN-H}	3.5	_	_	V	_
IN- input current	I_{IN-}	_	70	200	μΑ	$V_{\text{IN-}}$ = GND1
IN+ input current	I_{IN+}	_	70	200	μΑ	$V_{\text{IN+}} = \text{VCC1}$

5.3.3 Gate Driver

Table 6 Gate Driver

Parameter	Symbol	Values			Unit	Note /
		Min.	Тур.	Max.		Test Condition
High level output peak	$I_{OUT+,PEAK}$			_	Α	1)
current (source)	3311,1 E/11					IN+ = High,
1EDI20N12AF		2.0	4.0			IN- = Low,
						$V_{\rm VCC2}$ = 15 V
Low level output peak	$I_{OUT\text{-},PEAK}$			_	Α	1)
current (sink)	OO. ,I LAIR					IN+ = Low,
1EDI20N12AF		2.0	3.5			IN- = Low,
						V _{VCC2} = 15 V

¹⁾ voltage across the device $V_{(VCC2-OUT+)}$ or $V_{(OUT-GND2)} < V_{VCC2}$.

Data Sheet 16 Rev. 2.0, 2015-06-01



Electrical Parameters

5.3.4 Short Circuit Clamping

Table 7 Short Circuit Clamping

Parameter	Symbol	Values			Unit	Note /
		Min.	Тур.	Max.		Test Condition
Clamping voltage (OUT+) $(V_{\rm OUT}$ - $V_{\rm VCC2})$	V_{CLPout}	-	0.9	1.3	V	IN+ = High, IN- = Low, OUT = High I_{OUT} = 500 mA pulse test, t_{CLPmax} = 10 µs)

5.3.5 Dynamic Characteristics

Dynamic characteristics are measured with $V_{\rm VCC1}$ = 5 V and $V_{\rm VCC2}$ = 15 V.

Table 8 Dynamic Characteristics

Parameter	Symbol	Values			Unit	Note /
		Min.	Тур.	Max.		Test Condition
Input IN to output propagation delay ON	T_{PDON}	90	115	137	ns	$C_{\rm LOAD}$ = 100 pF $V_{\rm IN+}$ = 50%, $V_{\rm OUT}$ =50% @ 25°C
Input IN to output propa- gation delay OFF	T_{PDOFF}	100	120	143	ns	
Input IN to output propagation delay distortion $(T_{\text{PDOFF}} - T_{\text{PDON}})$	T_{PDISTO}	-15	5	25	ns	
Input pulse suppression IN+, IN-	$T_{\text{MININ+}},$ $T_{\text{MININ-}}$	30	40	-	ns	_
IN input to output propagation delay ON variation due to temp	T_{PDONt}	_	-	10	ns	$^{1)}C_{\text{LOAD}}$ = 100 pF $V_{\text{IN+}}$ = 50%, V_{OUT} =50%
IN input to output propagation delay OFF variation due to temp	T_{PDOFFt}	-	_	10	ns	$^{1)}C_{\text{LOAD}}$ = 100 pF $V_{\text{IN+}}$ = 50%, V_{OUT} =50%
IN input to output propagation delay distortion variation due to temp ($T_{\rm PDOFF}$ - $T_{\rm PDON}$)	$T_{ m PDISTOt}$	-	-	4	ns	$^{1)}C_{\rm LOAD}$ = 100 pF $V_{\rm IN+}$ = 50%, $V_{\rm OUT}$ =50%
Rise time	T_{RISE}	5	10	20	ns	$C_{\rm LOAD}$ = 1 nF $V_{\rm L}$ 20%, $V_{\rm H}$ 80%
Fall time	T_{FALL}	4	9	19	ns	C_{LOAD} = 1 nF V_{L} 20%, V_{H} 80%

¹⁾ The parameter is not subject to production test - verified by design/characterization



1EDI EiceDRIVER™ Compact 1EDI20N12AF

Electrical Parameters

5.3.6 Active Shut Down

Table 9 Active Shut Down

Parameter	Symbol	Values			Unit	Note /	
		Min.	Тур.	Max.		Test Condition	
Active shut down voltage	V _{ACTSD} ¹⁾	_	2.2	2.5	V	$I_{\rm OUT-}/I_{\rm OUT-,PEAK} = 0.1,$ $V_{\rm CC2} \ {\rm open}$	

¹⁾ Referred to GND2

Data Sheet 18 Rev. 2.0, 2015-06-01



Timing Diagramms

6 Timing Diagramms




Figure 6 Propagation Delay, Rise and Fall Time




Figure 7 Typical Switching Behavior




Figure 8 UVLO Behavior

Data Sheet 19 Rev. 2.0, 2015-06-01



Package Outlines

7 Package Outlines




Figure 9 PG-DSO-8-51 (Plastic (Green) Dual Small Outline Package)

Data Sheet 20 Rev. 2.0, 2015-06-01



Application Notes

8 Application Notes

8.1 Reference Layout for Thermal Data

The PCB layout shown in **Figure 10** represents the reference layout used for the thermal characterisation. Pin 4 (GND1) and pin 8 (GND2) require each a ground plane of 100 mm² for achieving maximum power dissipation. The 1EDI20N12AF is conceived to dissipate most of the heat generated through these pins.

The thermal coefficient junction-top ($\Psi_{th,jt}$) can be used to calculate the junction temperature at a given top case temperature and driver power dissipation:

$$T_i = \Psi_{th,it} \cdot P_D + T_{top}$$




Figure 10 Reference Layout for Thermal Data (Copper thickness 35 μm)

8.2 Printed Circuit Board Guidelines

The following factors should be taken into account for an optimum PCB layout.

- Sufficient spacing should be kept between high voltage isolated side and low voltage side circuits.
- The same minimum distance between two adjacent high-side isolated parts of the PCB should be maintained to increase the effective isolation and to reduce parasitic coupling.
- In order to ensure low supply ripple and clean switching signals, bypass capacitor trace lengths should be kept as short as possible.

Data Sheet 21 Rev. 2.0, 2015-06-01

w w w .in fineon.com