Memory FRAM

4 M Bit (512 K × 8)

MB85R4001A

■ DESCRIPTIONS

The MB85R4001A is an FRAM (Ferroelectric Random Access Memory) chip consisting of 524,288 words \times 8 bits of nonvolatile memory cells fabricated using ferroelectric process and silicon gate CMOS process technologies.

The MB85R4001A is able to retain data without using a back-up battery, as is needed for SRAM.

The memory cells used in the MB85R4001A can be used for 10¹⁰ read/write operations, which is a significant improvement over the number of read and write operations supported by Flash memory and E²PROM.

The MB85R4001A uses a pseudo-SRAM interface that is compatible with conventional asynchronous SRAM.

■ FEATURES

• Bit configuration : 524,288 words × 8 bits

• Read/write endurance : 10¹⁰ times / byte

• Data retention : 10 years (+ 55 °C), 55 years (+ 35 °C)

Operating power supply voltage : 3.0 V to 3.6 V

Low power operation : Operating power supply current 15 mA (Typ)

Standby current 50 µA (Typ)

Operation ambient temperature range : −40 °C to +85 °C


Package : 48-pin plastic TSOP (FPT-48P-M48)

RoHS compliant



MB85R4001A


■ PIN ASSIGNMENTS



■ PIN DESCRIPTIONS

Pin Number	Pin Name	Functional Description
1, 2, 4, 5, 8, 9, 17 to 26, 28, 29, 45	A0 to A18	Address Input pins
33 to 35, 38 to 42	I/O1 to I/O8	Data Input/Output pins
44	CE1	Chip Enable 1 Input pin
7	CE2	Chip Enable 2 Input pin
6	WE	Write Enable Input pin
48	ŌĒ	Output Enable Input pin
10, 16, 37	VDD	Supply Voltage pins Connect all three pins to the power supply.
13, 27, 46	VSS	Ground pins Connect all three pins to ground.
3, 11, 12, 14, 15, 36, 43, 47	NC	No Connect pins Leave these pins open, or connect to VDD or VSS.
30 to 32	DNU	Do Not Use pins Make sure to connect these pins to ground.

■ BLOCK DIAGRAM



■ FUNCTIONAL TRUTH TABLE

Operation Mode	CE1	CE2	WE	OE	I/O ₁ to I/O ₈	Supply Current
	Н	Х	Х	Х		
Standby Precharge	Х	L	X	X	Hi-Z	Standby (IsB)
	Х	Х	Н	Н		(102)
Read	7_	Н	Н	L		
Nead	L	工	11	٦	Data Output	
Read (Pseudo-SRAM, OE control*1)	L	Н	Н	7_		Operation
Write	Ł	Н	L	Н		(IDD)
VVIIIC	L	<u>_</u>	_	11	Data Input	
Write (Pseudo-SRAM, WE control*2)	L	Н	Z	Н		

Note: L = V_{IL}, H = V_{IH}, X can be either V_{IL}, V_{IH}, \searrow or \surd , Hi-Z = High Impedance

*1 : $\overline{\text{OE}}$ control of the Pseudo-SRAM means the valid address at the falling edge of $\overline{\text{OE}}$ to read.

*2: WE control of the Pseudo-SRAM means the valid address and data at the falling edge of WE to write.

■ ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Rat	Rating		
Farameter	Symbol	Min	Max	Unit	
Power Supply Voltage*	V _{DD}	- 0.5	+ 4.0	V	
Input Pin Voltage*	Vin	- 0.5	$V_{DD} + 0.5 \ (\le 4.0)$	V	
Output Pin Voltage*	Vоит	- 0.5	$V_{DD} + 0.5 \ (\le 4.0)$	V	
Operation Ambient Temperature	TA	- 40	+ 85	°C	
Storage Temperature	Тѕтс	– 55	+ 125	°C	

^{*:} All voltages are referenced to VSS (ground 0 V).

WARNING: Semiconductor devices can be permanently damaged by application of stress (voltage, current, temperature, etc.) in excess of absolute maximum ratings. Do not exceed these ratings.

■ RECOMMENDED OPERATING CONDITIONS

Parameter	Cumbal		Value	Unit	
Parameter	Symbol	Min	Тур	Max	Unit
Power Supply Voltage*	V _{DD}	3.0	3.3	3.6	V
High Level Input Voltage*	ViH	$V_{DD} \times 0.8$	_	$V_{DD} + 0.5 (\le 4.0)$	V
Low Level Input Voltage*	Vıl	- 0.5	_	+ 0.6	V
Operation Ambient Temperature	TA	- 40	_	+ 85	°C

^{*:} All voltages are referenced to VSS (ground 0 V).

WARNING: The recommended operating conditions are required in order to ensure the normal operation of the semiconductor device. All of the device's electrical characteristics are warranted when the device is operated within these ranges.

> Always use semiconductor devices within their recommended operating condition ranges. Operation outside these ranges may adversely affect reliability and could result in device failure.

> No warranty is made with respect to uses, operating conditions, or combinations not represented on the data sheet. Users considering application outside the listed conditions are advised to contact their representatives beforehand.

■ ELECTRICAL CHARACTERISTICS

1. DC Characteristics

(within recommended operating conditions)

Parameter	Symbol	Condition		Value		Unit
raiailletei	Syllibol	Condition	Min Typ Max		Max	
Input Leakage Current*1	lu	$V_{IN} = 0 V to V_{DD}$		_	10	μΑ
Output Leakage Current	I LO	$V_{OUT} = 0 \text{ V to } V_{DD},$ $\overline{CE}1 = V_{IH} \text{ or } \overline{OE} = V_{IH}$			10	μΑ
Operating Power Supply Current*2	loo	$\overline{\text{CE}}$ 1 = 0.2 V, CE2 = V _{DD} -0.2 V, I _{out} = 0 mA		15	20	mA
Standby Current*3	Isa	$\overline{CE}1 \ge V_{DD}-0.2 \text{ V}$ $CE2 \le 0.2 \text{ V}$ $\overline{OE} \ge V_{DD}-0.2 \text{ V}, \overline{WE} \ge V_{DD}-0.2 \text{ V}$	_	50	150	μΑ
High Level Output Voltage	Vон	Iон = −1.0 mA	V _{DD} × 0.8	_	_	V
Low Level Output Voltage	Vol	IoL = 2.0 mA	_	_	0.4	V

^{*1:} This also applies to DNU pins.

^{*2 :} During the measurement of IDD, the Address and Data In were taken to only change once per active cycle. Iout: output current

^{*2 :} All pins other than setting pins shall be input at the CMOS level voltages such as $H \ge V_{DD} - 0.2 \text{ V}$, $L \le 0.2 \text{ V}$.

MB85R4001A

2. AC Characteristics

• AC Test Conditions

Power Supply Voltage : 3.0 V to 3.6 V Operation Ambient Temperature : -40 °C to +85 °C Input Voltage Amplitude : 0.3 V to 2.7 V

Input Rising Time : 5 ns Input Falling Time : 5 ns

Input Falling Time
Input Evaluation Level : 2.0 V /
Output Evaluation Level : 2.0 V /
Capacitance : 50 pF : 2.0 V / 0.8 V : 2.0 V / 0.8 V

(1) Read Cycle

Parameter	Symbol	Va	lue	Unit
r ai ailletei	Symbol	Min	Max	Onit
Read Cycle Time	t RC	150	_	ns
CE1 Active Time	t CA1	120	_	ns
CE2 Active Time	t _{CA2}	120	_	ns
OE Active Time	t RP	120	_	ns
Precharge Time	t PC	20	_	ns
Address Setup Time	tas	0	_	ns
Address Hold Time	t ah	50	_	ns
OE Setup Time	t ES	0	_	ns
Output Hold Time	tон	0	_	ns
Output Set Time	t LZ	30	_	ns
CE1 Access Time	t _{CE1}	_	120	ns
CE2 Access Time	t _{CE2}	_	120	ns
OE Access Time	t oe	_	120	ns
Output Floating Time	tонz	_	20	ns

(2) Write Cycle


Parameter	Symbol	Va	Value		
Parameter	Symbol	Min	Max	Unit	
Write Cycle Time	twc	150	_	ns	
CE1 Active Time	t CA1	120	_	ns	
CE2 Active Time	t _{CA2}	120	_	ns	
Precharge Time	tpc	20	_	ns	
Address Setup Time	tas	0	_	ns	
Address Hold Time	tан	50	_	ns	
Write Pulse Width	twp	120	_	ns	
Data Setup Time	tos	0	_	ns	
Data Hold Time	tон	50	_	ns	
Write Setup Time	tws	0	_	ns	

3. Pin Capacitance


Parameter	Symbol	Condition		Value		Unit
Faranietei	Зуппоп	Condition	Min	Тур	Max	Oilit
Input Capacitance	Cin	V V V 0V	_	_	10	pF
Output Capacitance	Соит	$V_{DD} = V_{IN} = V_{OUT} = 0 V,$ $f = 1 MHz, T_A = +25 °C$	_	_	10	pF
DNU Pin Input Capacitance	CDNU		_	_	10	pF

■ TIMING DIAGRAMS


1. Read Cycle Timing (CE1 Control)




2. Read Cycle Timing (CE2 Control)




3. Read Cycle Timing (OE Control)




4. Write Cycle Timing (CE1 Control)




5. Write Cycle Timing (CE2 Control)



6. Write Cycle Timing (WE Control)



■ POWER ON/OFF SEQUENCE



Parameter	Symbol	Value			
Farameter	Symbol	Min	Тур	Max	Unit
CE1 level hold time for Power OFF	t PD	85			ns
CE1 level hold time for Power ON	t PU	85			ns
Power supply rising time	t R	0.05		200	ms

If the device does not operate within the specified conditions of read cycle, write cycle or power on/off sequence, memory data can not be guaranteed.

In case the power is turned on or off, use the power supply reset IC and fix the CE2 to low level, to prevent unexpected writing. Use either of $\overline{\text{CE}}1$ or CE2, or both to disable control of the device.

■ FRAM CHARACTERISTICS

Item	Min	Max	Unit	Parameter
Read/Write Endurance*1	10 ¹⁰		Times/byte	Operation Ambient Temperature T _A = +85 °C
Data Retention*2	10	_	Years	Operation Ambient Temperature T _A = +55 °C
Data Retention -	55		Teals	Operation Ambient Temperature T _A = +35 °C

^{*1:} Total number of reading and writing defines the minimum value of endurance, as an FRAM memory operates with destructive readout mechanism.

■ NOTES ON USE


Data written before performing IR reflow is not guaranteed after IR reflow.

^{*2 :} Minimun values define retention time of the first reading/writing data right after shipment, and these values are calculated by qualification results.

■ ESD AND LATCH-UP


Test	DUT	Value
ESD HBM (Human Body Model) JESD22-A114 compliant		≥ 2000 V
ESD MM (Machine Model) JESD22-A115 compliant		≥ 200 V
ESD CDM (Charged Device Model) JESD22-C101 compliant		_
Latch-Up (I-test) JESD78 compliant	MB85R4001ANC-GE1	_
Latch-Up (V _{supply} overvoltage test) JESD78 compliant		_
Latch-Up (Current Method) Proprietary method		≥ 300 mA
Latch-Up (C-V Method) Proprietary method		_

• Current method of Latch-Up Resistance Test



Note: The voltage V_{IN} is increased gradually and the current I_{IN} of 300 mA at maximum shall flow. Confirm the latch up does not occur under $I_{IN} = \pm 300$ mA.

• C-V method of Latch-Up Resistance Test




Note: Charge voltage alternately switching 1 and 2 approximately 2 sec interval. This switching process is considered as one cycle.

Repeat this process 5 times. However, if the latch-up condition occurs before completing 5 times, this test must be stopped immediately.

■ REFLOW CONDITIONS AND FLOOR LIFE

Item	Condition				
Method	IR (infrared	reflow), Convection			
Times		2			
	Before unpacking	Please use within 2 years after production.			
	From unpacking to 2nd reflow	Within 8 days			
Floor life	In case over period of floor life	Baking with 125 °C+/-3 °C for 24hrs+2hrs/-0hrs is required. Then please use within 8 days. (Please remember baking is up to 2 times)			
Floor life condition	Between 5 °C and 30 °C and also below 70%RH required. (It is preferred lower humidity in the required temp range.)				

Reflow Profile



(a) Average ramp-up rate

(b) Preheat & Soak

(c) Average ramp-up rate (d) Peak temperature

(d') Liquidous temperature

: 1 °C/s to 4 °C/s : 170 °C to 190 °C, 60 s to 180 s

: 1 °C/s to 4 °C/s

: Temperature 260 °C Max; 255 °C within 10 s : Up to 230 °C within 40 s or

Up to 225 °C within 60 s or

Up to 220 °C within 80 s

: Natural cooling or forced cooling (e) Cooling

Note: Temperature on the top of the package body is measured.

■ RESTRICTED SUBSTANCES

This product complies with the regulations below (Based on current knowledge as of November 2011).

- EU RoHS Directive (2002/95/EC)
- China RoHS (Administration on the Control of Pollution Caused by Electronic Information Products (电子信息产品污染控制管理办法))
- Vietnam RoHS (30/2011/TT-BCT)

Restricted substances in each regulation are as follows.

Substances	Threshold	Contain status*
Lead and its compounds	1,000 ppm	О
Mercury and its compounds	1,000 ppm	0
Cadmium and its compounds	100 ppm	О
Hexavalent chromium compound	1,000 ppm	О
Polybrominated biphenyls (PBB)	1,000 ppm	0
Polybrominated diphenyl ethers (PBDE)	1,000 ppm	0


^{*:} The mark of "O" shows below a threshold value.


MB85R4001A

■ ORDERING INFORMATION


Part Number	Package	Shipping form	Minimum shipping quantity
MB85R4001ANC-GE1	48-pin plastic TSOP (FPT-48P-M48)	Tray	1

■ PACKAGE DIMENSIONS






■ MARKING




■ SHIPPING FORM

1. Tray

1.1 Tray Dimensions






- *1: For a product of witch part number is suffixed with "E1", a " G 🔊 " marks is display to the moisture barrier bag and the inner boxes.
- *2: The size of the outer box may be changed depending on the quantity of inner boxes.
- *3: The space in the outer box will be filled with empty inner boxes, or cushions, etc.
- *4: Please refer to an attached sheet about the indication label.
- *5: The packing materials except tray may differ slightly from the color and dimensions depend on country of manufacture.


Note: The packing specifications may not be applied when the product is delivered via a distributer.

1.3 Product label indicators


Label I: Label on Inner box/Moisture Barrier Bag/ (It sticks it on the reel for the emboss taping)
[C-3 Label (50mm x 100mm) Supplemental Label (20mm x 100mm)]



Label II-A: Label on Outer box [D Label] (100mm x 100mm)



Label II-B: Outer boxes product indicate




Note: Depending on shipment state, "Label II-A" and "Label II-B" on the external boxes might not be printed.

MB85R4001A

1.4 Dimensions for Containers


(1) Dimensions for inner box



L	W	Н
165	360	75

(Dimensions in mm)

(2) Dimensions for outer box



L	W	Н
355	385	195

(Dimensions in mm)

■ MAJOR CHANGES IN THIS EDITION

A change on a page is indicated by a vertical line drawn on the left side of that page.

Page	Section	Change Results
1	■ FEATURES	Revised the Data retention 10 years (+ 55 °C) →10 years (+ 55 °C), 55 years (+ 35 °C)
4	■ ABSOLUTE MAXIMUM RANGES	Revised the Storage Temperature $-40~^{\circ}\text{C} \rightarrow -55~^{\circ}\text{C}$
11	■ POWER ON/OFF SEQUENCE	Deleted the following description: "Because turning the power-on from an intermediate level cause malfunction, when the power is turned on, VDD is required to be started from 0V (see the figure below)." Moved the following description under the table: "If the device does not operate within the specified conditions of read cycle, write cycle or power on/off sequence, memory data can not be guaranteed. In case the power is turned on or off, use the power supply reset IC and fix the CE2 to low level, to prevent unexpected writing. Use either of CE1 or CE2, or both to disable control of the device."
	■ FRAM CHARACTERISTICS	Revised the table and Note

FUJITSU SEMICONDUCTOR LIMITED

Nomura Fudosan Shin-yokohama Bldg. 10-23, Shin-yokohama 2-Chome, Kohoku-ku Yokohama Kanagawa 222-0033, Japan

Tel: +81-45-415-5858 http://jp.fujitsu.com/fsl/en/

For further information please contact:

North and South America

FUJITSU SEMICONDUCTOR AMERICA, INC. 1250 E. Arques Avenue, M/S 333 Sunnyvale, CA 94085-5401, U.S.A. Tel: +1-408-737-5600 Fax: +1-408-737-5999 http://us.fujitsu.com/micro/

Europe

FUJITSU SEMICONDUCTOR EUROPE GmbH Pittlerstrasse 47, 63225 Langen, Germany Tel: +49-6103-690-0 Fax: +49-6103-690-122 http://emea.fujitsu.com/semiconductor/

Korea

FUJITSU SEMICONDUCTOR KOREA LTD. 902 Kosmo Tower Building, 1002 Daechi-Dong, Gangnam-Gu, Seoul 135-280, Republic of Korea Tel: +82-2-3484-7100 Fax: +82-2-3484-7111 http://kr.fujitsu.com/fsk/

Asia Pacific

FUJITSU SEMICONDUCTOR ASIA PTE. LTD. 151 Lorong Chuan, #05-08 New Tech Park 556741 Singapore Tel: +65-6281-0770 Fax: +65-6281-0220 http://sg.fujitsu.com/semiconductor/

FUJITSU SEMICONDUCTOR SHANGHAI CO., LTD. 30F, Kerry Parkside, 1155 Fang Dian Road, Pudong District, Shanghai 201204, China
Tel: +86-21-6146-3688 Fax: +86-21-6146-3660
http://cn.fujitsu.com/fss/

FUJITSU SEMICONDUCTOR PACIFIC ASIA LTD. 2/F, Green 18 Building, Hong Kong Science Park, Shatin, N.T., Hong Kong
Tel: +852-2736-3232 Fax: +852-2314-4207

http://cn.fujitsu.com/fsp/

Specifications are subject to change without notice. For further information please contact each office.

All Rights Reserved.

The contents of this document are subject to change without notice.

Customers are advised to consult with sales representatives before ordering.

The information, such as descriptions of function and application circuit examples, in this document are presented solely for the purpose of reference to show examples of operations and uses of FUJITSU SEMICONDUCTOR device; FUJITSU SEMICONDUCTOR does not warrant proper operation of the device with respect to use based on such information. When you develop equipment incorporating the device based on such information, you must assume any responsibility arising out of such use of the information.

FUJITSU SEMICONDUCTOR assumes no liability for any damages whatsoever arising out of the use of the information.

Any information in this document, including descriptions of function and schematic diagrams, shall not be construed as license of the use or exercise of any intellectual property right, such as patent right or copyright, or any other right of FUJITSU SEMICONDUCTOR or any third party or does FUJITSU SEMICONDUCTOR warrant non-infringement of any third-party's intellectual property right or other right by using such information. FUJITSU SEMICONDUCTOR assumes no liability for any infringement of the intellectual property rights or other rights of third parties which would result from the use of information contained herein.

The products described in this document are designed, developed and manufactured as contemplated for general use, including without limitation, ordinary industrial use, general office use, personal use, and household use, but are not designed, developed and manufactured as contemplated (1) for use accompanying fatal risks or dangers that, unless extremely high safety is secured, could have a serious effect to the public, and could lead directly to death, personal injury, severe physical damage or other loss (i.e., nuclear reaction control in nuclear facility, aircraft flight control, air traffic control, mass transport control, medical life support system, missile launch control in weapon system), or (2) for use requiring extremely high reliability (i.e., submersible repeater and artificial satellite).

Please note that FUJITSU SEMICONDUCTOR will not be liable against you and/or any third party for any claims or damages arising in connection with above-mentioned uses of the products.

Any semiconductor devices have an inherent chance of failure. You must protect against injury, damage or loss from such failures by incorporating safety design measures into your facility and equipment such as redundancy, fire protection, and prevention of overcurrent levels and other abnormal operating conditions.

Exportation/release of any products described in this document may require necessary procedures in accordance with the regulations of the Foreign Exchange and Foreign Trade Control Law of Japan and/or US export control laws.

The company names and brand names herein are the trademarks or registered trademarks of their respective owners.

Edited: Sales Promotion Department