



SAMXON BRAND ALUMINUM ELECTROLYTIC CAPACITORS

# PRODUCT SPECIFICATION

## 規格書

**CUSTOMER :**

(客戶) : 志盛翔

**DATE :**

(日期) 2020-9-10

**CATEGORY (品名) :** ALUMINUM ELECTROLYTIC CAPACITORS

**DESCRIPTION (型号) :** GT 35V100μF(φ6.3x11)

GT 63V47μF(φ8x12)

GT 63V100μF(φ8x16)

**VERSION (版本) :** 01

**Customer P/N :**

**SUPPLIER :**

SUPPLIER	
PREPARED (拟定)	CHECKED (审核)
李雪妮	刘渭清

CUSTOMER	
APPROVAL (批准)	SIGNATURE (签名)



<b>MAN YUE ELECTRONICS COMPANY LIMITED</b>	<i>ELECTROLYTIC CAPACITOR SPECIFICATION GT SERIES</i>	<b>SAMXON</b>
--	---	---------------

SPECIFICATION GT SERIES					ALTERNATION HISTORY RECORDS		
Rev.	Date	Mark	Page	Contents	Purpose	Drafter	Approver

Name	Specification Sheet – GT		
Version	01		Page 1
STANDARD MANUAL			

**Table 1 Product Dimensions and Characteristics**

Safety vent for  $\geq \Phi 6.3$



**Unit: mm**

$\alpha$	$L < 20 : \alpha = 1.5; L \geq 20 : \alpha = 2.0$
$\beta$	$\Phi D < 20 : \beta = 0.5; \Phi D \geq 20 : \beta = 1.0$

\* If it is flat rubber, there is no bulge from the flat rubber surface.

Table 1

No.	SAMXON Part No.	WV (Vdc)	Cap. ( $\mu$ F)	Cap. tolerance	Temp. range ( $^{\circ}$ C)	$\tan \delta$ (120Hz, 20 $^{\circ}$ C)	Leakage Current ( $\mu$ A, 2min)	Max Ripple Current at 105 $^{\circ}$ C 100kHz (mA rms)	Impedance at 20 $^{\circ}$ C 100kHz ( $\Omega$ max)	Load lifetime (Hrs)	Dimension (mm)			Sleeve
											D × L	F	$\phi d$	
1	EGT107M1VE11RR**P	35	100	-20%~+20%	-40~105	0.12	35	340	0.220	5000	6.3X11	2.5	0.5	PET
2	EGT476M1JF12RR**P	63	47	-20%~+20%	-40~105	0.09	30	232	0.504	7000	8X12	3.5	0.5	PET
3	EGT107M1JF16RR**P	63	100	-20%~+20%	-40~105	0.09	63	300	0.360	7000	8X16	3.5	0.5	PET

Issued-date: 2013-6-11

Specification Sheet – GT

Version

01

Page 2

**C O N T E N T S**

	<b>Sheet</b>
1. Application	4
2. Part Number System	4
3. Construction	5
4. Characteristics	6~13
4.1 Rated voltage & Surge voltage	
4.2 Capacitance (Tolerance)	
4.3 Leakage current	
4.4 $\tan \delta$	
4.5 Impedance	
4.6 Terminal strength	
4.7 Temperature characteristic	
4.8 Load life test	
4.9 Shelf life test	
4.10 Surge test	
4.11 Vibration	
4.12 Solderability test	
4.13 Resistance to solder heat	
4.14 Change of temperature	
4.15 Damp heat test	
4.16 Vent test	
4.17 Maximum permissible (ripple current)	
5. Forming Dimension	14
6. Taping Dimension	15~17
7. List of "Environment-related Substances to be Controlled ("Controlled Substances")"	18
Attachment: Application Guidelines	19~24

Name		Specification Sheet – GT	
Version	01		Page 3
STANDARD MANUAL			

## 1. Application

This specification applies to polar Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC60384.


## 2. Part Number System

1 2 3	4 5 6	7	8 9	10 11 12	13 14	15 16	17
EGS	1 0 5	M	1 H	D 1 1	T C	S A	P
SERIES	CAPACITANCE	TOL.	VOLTAGE	CASE SIZE	TYPE	SAMXON PRODUCT LINE	SLEEVE MATERIAL
ESM	0.1	104	2	0D	Radial bulk	RR	
EKF	0.22	224	2.5	0E	Ammo Taping		
ESS	0.33	334	4	0G	2.0mm Pitch	TT	
EKS	0.47	474	6.3	0J	2.5mm Pitch	TU	
EGS	1	105	8	0K	3.5mm Pitch	TV	
EKM	2.2	225	10	1A	5.0mm Pitch	TC	
EKG	3.3	335	12.5	1B			
EOM	4.7	475	16	1C			
EZM	10	106	20	1D			
EZS	22	226	25	1E			
EGF	33	336	30	1I			
ESF	47	476	32	13			
EGT	100	107	35	1V			
EGK	220	227	40	1G			
EGE	330	337	42	1M			
EGD	470	477	50	1H			
EGC	2200	228	57	1L			
ERS	22000	229	63	1J			
ERF	33000	339	71	1S			
ERL	47000	479	75	1T			
ERR	100000	10T	80	1K			
ERT	150000	15T	85	1R			
ERE	220000	22T	90	19			
ERD	330000	33T	100	2A			
ERH	470000	47T	120	20			
EHD	1000000	10M	125	2B			
ERA	1500000	15M	150	2Z			
ERB	2200000	22M	160	2C			
ERC	3300000	33M	180	2P			
EFA			200	2D			
ENP			215	22			
ENH			220	2N			
ERW			230	23			
ERY			250	2E			
ELP			275	2T			
EAP			300	2I			
EQP			310	2R			
EDP			315	2F			
ETP			330	2U			
EHP			350	2V			
EUP			360	2X			
EKP			375	2Q			
EEP			385	2Y			
EFP			400	2G			
ESP			420	2M			
EVP			450	2W			
EGP			500	2H			
EWR			550	25			
EWU			600	26			
EWT			630	2J			
EWX							
EFW							
EWS							
EWH							
EWL							
EWB							
VSS							
VNS							
VKS							
VKM							
VRL							
VNH							
VZS							
VRF							

Name	Specification Sheet – GT		
Version	01		Page 4
STANDARD MANUAL			

### 3. Construction

Single ended type to be produced to fix the terminals to anode and cathode foil, and wind together with paper, and then wound element to be impregnated with electrolyte will be enclosed in an aluminum case. Finally sealed up tightly with end seal rubber, then finished by putting on the vinyl sleeve.



No	Component	Material
1	Lead Line	Tinned CP wire (Pb Free)
2	Terminal	Aluminum wire
3	Rubber seal	Rubber
4	Al-Foil (+)	Formed aluminum foil
5	Al-Foil (-)	Etched aluminum foil or formed aluminum foil
6	Case	Aluminum case
7	Sleeve	PVC/PET
8	Separator	Electrolyte paper

Name	Specification Sheet – GT		
Version	01		Page 5
STANDARD MANUAL			

#### 4. Characteristics

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C  
Relative humidity : 45% to 85%  
Air Pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : 20°C ± 2°C  
Relative humidity : 60% to 70%  
Air Pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage  
See table 1 temperature range.

As to the detailed information, please refer to table 2

Name	Specification Sheet – GT		
Version	01		Page 6
STANDARD MANUAL			

Table 2

ITEM		PERFORMANCE																									
4.1	Rated voltage (WV)	<table border="1"> <tr> <td>WV (V.DC)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td></tr> <tr> <td>SV (V.DC)</td><td>8</td><td>13</td><td>20</td><td>32</td><td>44</td><td>63</td><td>79</td><td>125</td></tr> </table>								WV (V.DC)	6.3	10	16	25	35	50	63	100	SV (V.DC)	8	13	20	32	44	63	79	125
WV (V.DC)	6.3	10	16	25	35	50	63	100																			
SV (V.DC)	8	13	20	32	44	63	79	125																			
Surge voltage (SV)																											
4.2	Nominal capacitance (Tolerance)	<p><b>&lt;Condition&gt;</b>            Measuring frequency : 120Hz±12Hz            Measuring voltage : Not more than 0.5Vrms            Measuring temperature : 20±2°C  <b>&lt;Criteria&gt;</b>            Shall be within the specified capacitance tolerance.</p>																									
4.3	Leakage current	<p><b>&lt;Condition&gt;</b>            Connecting the capacitor with a protective resistor (1kΩ ± 10Ω) in series for 2 minutes, and then, measure Leakage Current.  <b>&lt;Criteria&gt;</b>            Refer to table 1</p>																									
4.4	Tan δ	<p><b>&lt;Condition&gt;</b>            See 4.2, Norm capacitance, for measuring frequency, voltage and temperature.  <b>&lt;Criteria&gt;</b>            Refer to table 1</p>																									
4.5	Impedance	<p><b>&lt;Condition&gt;</b>            Measuring frequency:100kHz; Measuring temperature:20±2°C            Measuring point: 2mm max from the surface of a sealing rubber on the lead wire.  <b>&lt;Criteria&gt;</b>            Refer to table 1</p>																									


Name	Specification Sheet – GT		
Version	01		Page 7
STANDARD MANUAL			

4.6	Terminal strength	<b>&lt;Condition&gt;</b> Tensile strength of terminals Fixed the capacitor, applied force to the terminal in lead out direction for $10 \pm 1$ seconds. Bending strength of terminals. Fixed the capacitor, applied force to bent the terminal (1~4 mm from the rubber) for $90^\circ$ within 2~3 seconds, and then bent it for $90^\circ$ to its original position within 2~3 seconds. <table border="1"><thead><tr><th>Diameter of lead wire</th><th>Tensile force N (kgf)</th><th>Bending force N (kgf)</th></tr></thead><tbody><tr><td>0.5mm and less</td><td>5 (0.51)</td><td>2.5 (0.25)</td></tr><tr><td>Over 0.5mm to 0.8mm</td><td>10 (1.0)</td><td>5 (0.51)</td></tr></tbody></table> <b>&lt;Criteria&gt;</b> No noticeable changes shall be found, no breakage or looseness at the terminal.	Diameter of lead wire	Tensile force N (kgf)	Bending force N (kgf)	0.5mm and less	5 (0.51)	2.5 (0.25)	Over 0.5mm to 0.8mm	10 (1.0)	5 (0.51)							
Diameter of lead wire	Tensile force N (kgf)	Bending force N (kgf)																
0.5mm and less	5 (0.51)	2.5 (0.25)																
Over 0.5mm to 0.8mm	10 (1.0)	5 (0.51)																
<b>&lt;Condition&gt;</b> <table border="1"><thead><tr><th>STEP</th><th>Testing temperature(<math>^\circ</math>C)</th><th>Time</th></tr></thead><tbody><tr><td>1</td><td><math>20 \pm 2</math></td><td>Time to reach thermal equilibrium</td></tr><tr><td>2</td><td><math>-40 \text{ (-25)} \pm 3</math></td><td>Time to reach thermal equilibrium</td></tr><tr><td>3</td><td><math>20 \pm 2</math></td><td>Time to reach thermal equilibrium</td></tr><tr><td>4</td><td><math>105 \pm 2</math></td><td>Time to reach thermal equilibrium</td></tr><tr><td>5</td><td><math>20 \pm 2</math></td><td>Time to reach thermal equilibrium</td></tr></tbody></table> <b>&lt;Criteria&gt;</b> a. $\tan \delta$ shall be within the limit of Item 4.4 The leakage current measured shall not more than 8 times of its specified value. b. In step 5, $\tan \delta$ shall be within the limit of Item 4.4 The leakage current shall not more than the specified value.	STEP	Testing temperature( $^\circ$ C)	Time	1	$20 \pm 2$	Time to reach thermal equilibrium	2	$-40 \text{ (-25)} \pm 3$	Time to reach thermal equilibrium	3	$20 \pm 2$	Time to reach thermal equilibrium	4	$105 \pm 2$	Time to reach thermal equilibrium	5	$20 \pm 2$	Time to reach thermal equilibrium
STEP	Testing temperature( $^\circ$ C)	Time																
1	$20 \pm 2$	Time to reach thermal equilibrium																
2	$-40 \text{ (-25)} \pm 3$	Time to reach thermal equilibrium																
3	$20 \pm 2$	Time to reach thermal equilibrium																
4	$105 \pm 2$	Time to reach thermal equilibrium																
5	$20 \pm 2$	Time to reach thermal equilibrium																

Name	Specification Sheet – GT		
Version	01		Page 8
STANDARD MANUAL			

4.7		b. At-40°C (-25°C), impedance (Z) ratio shall not exceed the value of the following table.																									
		<table border="1"> <thead> <tr> <th>Working Voltage (V)</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th><th>63</th><th>100</th></tr> </thead> <tbody> <tr> <td>Z-25°C/Z+20°C</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td></tr> <tr> <td>Z-40°C/Z+20°C</td><td>8</td><td>6</td><td>4</td><td>3</td><td>3</td><td>3</td><td>3</td><td>3</td></tr> </tbody> </table> <p>Capacitance, Tan δ, and impedance shall be measured at 120Hz.</p>	Working Voltage (V)	6.3	10	16	25	35	50	63	100	Z-25°C/Z+20°C	4	3	2	2	2	2	2	2	Z-40°C/Z+20°C	8	6	4	3	3	3
Working Voltage (V)	6.3	10	16	25	35	50	63	100																			
Z-25°C/Z+20°C	4	3	2	2	2	2	2	2																			
Z-40°C/Z+20°C	8	6	4	3	3	3	3	3																			
4.8	Load life test	<p><b>&lt;Condition&gt;</b> According to IEC60384-4No.4.13 methods, The capacitor is stored at a temperature of 105 ± 2 °C with DC bias voltage plus the rated ripple current for Table 1. (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table:</p> <p><b>&lt;Criteria&gt;</b> The characteristic shall meet the following requirements.</p> <table border="1"> <tbody> <tr> <td>Leakage current</td><td>Value in 4.3 shall be satisfied</td></tr> <tr> <td>Capacitance Change</td><td>Within ± 25% of initial value.</td></tr> <tr> <td>Tan δ</td><td>Not more than 200% of the specified value.</td></tr> <tr> <td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr> </tbody> </table>	Leakage current	Value in 4.3 shall be satisfied	Capacitance Change	Within ± 25% of initial value.	Tan δ	Not more than 200% of the specified value.	Appearance	There shall be no leakage of electrolyte.																	
Leakage current	Value in 4.3 shall be satisfied																										
Capacitance Change	Within ± 25% of initial value.																										
Tan δ	Not more than 200% of the specified value.																										
Appearance	There shall be no leakage of electrolyte.																										
<p><b>&lt;Condition&gt;</b> The capacitors are then stored with no voltage applied at a temperature of 105 ± 2 °C for 1000+48/0 hours. Following this period the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for 4~8 hours. Next they shall be connected to a series limiting resistor(1k ± 100 Ω) with D.C. rated voltage applied for 30min. After which the capacitors shall be discharged, and then, tested the characteristics.</p> <p><b>&lt;Criteria&gt;</b> The characteristic shall meet the following requirements.</p> <table border="1"> <tbody> <tr> <td>Leakage current</td><td>Value in 4.3 shall be satisfied</td></tr> <tr> <td>Capacitance Change</td><td>Within ± 25% of initial value.</td></tr> <tr> <td>Tan δ</td><td>Not more than 200% of the specified value.</td></tr> <tr> <td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr> </tbody> </table> <p>Remark: If the capacitors are stored more than 1 year, the leakage current may increase. Please apply voltage through about 1 kΩ resistor, if necessary.</p>	Leakage current	Value in 4.3 shall be satisfied	Capacitance Change	Within ± 25% of initial value.	Tan δ	Not more than 200% of the specified value.	Appearance	There shall be no leakage of electrolyte.																			
Leakage current	Value in 4.3 shall be satisfied																										
Capacitance Change	Within ± 25% of initial value.																										
Tan δ	Not more than 200% of the specified value.																										
Appearance	There shall be no leakage of electrolyte.																										

Name	Specification Sheet – GT		
Version	01		Page 9
STANDARD MANUAL			

4.10	Surge test	<p><b>&lt;Condition&gt;</b></p> <p>Applied a surge voltage to the capacitor connected with a <math>(100 \pm 50)/C_R</math> (<math>k\Omega</math>) resistor.</p> <p>The capacitor shall be submitted to 1000 cycles, each consisting of charge of <math>30 \pm 5</math>s, followed discharge of 5 min 30s.</p> <p>The test temperature shall be <math>15 \sim 35^\circ\text{C}</math>.</p> <p><math>C_R</math> : Nominal Capacitance (<math>\mu\text{F}</math>)</p> <p><b>&lt;Criteria&gt;</b></p> <table border="1"><tr><td>Leakage current</td><td>Not more than the specified value.</td></tr><tr><td>Capacitance Change</td><td>Within <math>\pm 15\%</math> of initial value.</td></tr><tr><td><math>\tan \delta</math></td><td>Not more than the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table>	Leakage current	Not more than the specified value.	Capacitance Change	Within $\pm 15\%$ of initial value.	$\tan \delta$	Not more than the specified value.	Appearance	There shall be no leakage of electrolyte.
Leakage current	Not more than the specified value.									
Capacitance Change	Within $\pm 15\%$ of initial value.									
$\tan \delta$	Not more than the specified value.									
Appearance	There shall be no leakage of electrolyte.									
<p>Attention:</p> <p>This test simulates over voltage at abnormal situation only. It is not applicable to such over voltage as often applied.</p>										
4.11	Vibration test	<p><b>&lt;Condition&gt;</b></p> <p>The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions.</p> <p>Vibration frequency range : <math>10\text{Hz} \sim 55\text{Hz}</math></p> <p>Peak to peak amplitude : <math>1.5\text{mm}</math></p> <p>Sweep rate : <math>10\text{Hz} \sim 55\text{Hz} \sim 10\text{Hz}</math> in about 1 minute</p> <p>Mounting method:</p> <p>The capacitor with diameter greater than <math>12.5\text{mm}</math> or longer than <math>25\text{mm}</math> must be fixed in place with a bracket.</p> 								

Name	Specification Sheet – GT		
Version	01		Page 10
STANDARD MANUAL			

<p><b>&lt;Criteria&gt;</b> After the test, the following items shall be tested:</p> <table border="1"> <tr> <td>Inner construction</td><td>No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.</td></tr> <tr> <td>Appearance</td><td>No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.</td></tr> </table>			Inner construction	No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.	Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.				
Inner construction	No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.									
Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.									
4.12	Solderability test	<p><b>&lt;Condition&gt;</b> The capacitor shall be tested under the following conditions:</p> <p>Soldering temperature : <math>245 \pm 3^\circ\text{C}</math>  Dipping depth : 2mm  Dipping speed : <math>25 \pm 2.5 \text{mm/s}</math>  Dipping time : <math>3 \pm 0.5\text{s}</math></p> <p><b>&lt;Criteria&gt;</b></p> <table border="1"> <tr> <td>Coating quality</td> <td>A minimum of 95% of the surface being immersed</td> </tr> </table>	Coating quality	A minimum of 95% of the surface being immersed						
Coating quality	A minimum of 95% of the surface being immersed									
4.13	Resistance to solder heat test	<p><b>&lt;Condition&gt;</b> Terminals of the capacitor shall be immersed into solder bath at <math>260 \pm 5^\circ\text{C}</math> for <math>10 \pm 1</math> seconds or <math>400 \pm 10^\circ\text{C}</math> for <math>3 \pm 1</math> seconds to 1.5~2.0mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement.</p> <p><b>&lt;Criteria&gt;</b></p> <table border="1"> <tr> <td>Leakage current</td> <td>Not more than the specified value.</td> </tr> <tr> <td>Capacitance Change</td> <td>Within <math>\pm 10\%</math> of initial value.</td> </tr> <tr> <td>Tan <math>\delta</math></td> <td>Not more than the specified value.</td> </tr> <tr> <td>Appearance</td> <td>There shall be no leakage of electrolyte.</td> </tr> </table>	Leakage current	Not more than the specified value.	Capacitance Change	Within $\pm 10\%$ of initial value.	Tan $\delta$	Not more than the specified value.	Appearance	There shall be no leakage of electrolyte.
Leakage current	Not more than the specified value.									
Capacitance Change	Within $\pm 10\%$ of initial value.									
Tan $\delta$	Not more than the specified value.									
Appearance	There shall be no leakage of electrolyte.									

Name	Specification Sheet – GT		
Version	01		Page 11
STANDARD MANUAL			

4.14

Change of  
temperature  
test**<Condition>**

Temperature Cycle:

According to IEC60384-4No.4.7 methods, capacitor shall be placed in an oven, the condition according as below:

Temperature	Time
(1)+20°C	≤3 Minutes
(2)Rated low temperature (-40°C) (-25°C)	30±2 Minutes
(3)Rated high temperature (+105°C)	30±2 Minutes
(1) to (3)=1 cycle, total 5 cycle	

**<Criteria>**

The characteristic shall meet the following requirement.

Leakage current	Not more than the specified value.
Tan δ	Not more than the specified value.
Appearance	There shall be no leakage of electrolyte.

4.15

Damp  
heat  
test**<Condition>**

Humidity Test:

According to IEC60384-4No.4.12methods, capacitor shall be exposed for 500 ± 8 hours in an atmosphere of 90~95%R H. at 40±2°C, the characteristic change shall meet the following requirement.

**<Criteria>**

Leakage current	Not more than the specified value.
Capacitance Change	Within ±20% of initial value.
Tan δ	Not more than 120% of the specified value.
Appearance	There shall be no leakage of electrolyte.

Name

Specification Sheet – GT

Version

01

Page | 12

4.16	Vent test	<p><b>&lt;Condition&gt;</b> The following test only apply to those products with vent products at diameter <math>\geq \varnothing 6.3</math> with vent.</p> <p>D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied.</p> <p>&lt;Table 3&gt;</p> <table border="1" data-bbox="536 669 985 743"> <thead> <tr> <th>Diameter (mm)</th><th>DC Current (A)</th></tr> </thead> <tbody> <tr> <td>22.4 or less</td><td>1</td></tr> </tbody> </table> <p><b>&lt;Criteria&gt;</b> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</p>	Diameter (mm)	DC Current (A)	22.4 or less	1																																
Diameter (mm)	DC Current (A)																																					
22.4 or less	1																																					
4.17	Maximum permissible (ripple current, temperature coefficient)	<p><b>&lt;Condition&gt;</b> The maximum permissible ripple current is the maximum A.C current at 100kHz and can be applied at maximum operating temperature Table-1 The combined value of D.C voltage and the peak A.C voltage shall not exceed the rated voltage and shall not reverse voltage.</p> <p>Frequency Multipliers:</p> <table border="1" data-bbox="525 1237 1350 1507"> <thead> <tr> <th rowspan="2">Cap. ( <math>\mu</math> F)</th> <th rowspan="2">Coefficient</th> <th colspan="5">Freq. (Hz)</th> </tr> <tr> <th>50</th> <th>120</th> <th>300</th> <th>1k</th> <th>100k</th> </tr> </thead> <tbody> <tr> <td>15~33</td> <td>0.45</td> <td>0.55</td> <td>0.70</td> <td>0.90</td> <td>1.00</td> </tr> <tr> <td>39~330</td> <td>0.60</td> <td>0.70</td> <td>0.85</td> <td>0.95</td> <td>1.00</td> </tr> <tr> <td>390~1000</td> <td>0.65</td> <td>0.75</td> <td>0.90</td> <td>0.98</td> <td>1.00</td> </tr> <tr> <td>1200~18000</td> <td>0.75</td> <td>0.80</td> <td>0.95</td> <td>1.00</td> <td>1.00</td> </tr> </tbody> </table>	Cap. ( $\mu$ F)	Coefficient	Freq. (Hz)					50	120	300	1k	100k	15~33	0.45	0.55	0.70	0.90	1.00	39~330	0.60	0.70	0.85	0.95	1.00	390~1000	0.65	0.75	0.90	0.98	1.00	1200~18000	0.75	0.80	0.95	1.00	1.00
Cap. ( $\mu$ F)	Coefficient	Freq. (Hz)																																				
		50	120	300	1k	100k																																
15~33	0.45	0.55	0.70	0.90	1.00																																	
39~330	0.60	0.70	0.85	0.95	1.00																																	
390~1000	0.65	0.75	0.90	0.98	1.00																																	
1200~18000	0.75	0.80	0.95	1.00	1.00																																	


Name	Specification Sheet – GT		
Version	01		Page 13
STANDARD MANUAL			

**5. Forming Dimension**


**Unit: mm**

Shape Code	Φ D	Φ 5	Φ 6.3	Φ 8	Φ 10	Φ 12.5	Φ 16	Φ 18
CB	F	2.0	2.5	3.5	5.0	5.0	7.5	7.5
	H	3.5	3.5	3.5	3.5	3.5	3.5	3.5
	d	0.5	0.5	0.5	0.6	0.6	0.8	0.8
HE	F	5.0	5.0	5.0	-----	-----	-----	-----
	H	5.0	5.0	5.0	-----	-----	-----	-----
	d	0.5	0.5	0.5	-----	-----	-----	-----
FD	F	5.0	5.0	5.0	-----	-----	-----	-----
	H1	4.5	4.5	4.5	-----	-----	-----	-----
	H2	2.0	2.0	2.0	-----	-----	-----	-----
	d	0.5	0.5	0.5	-----	-----	-----	-----
KD	F	-----	-----	-----	5.0	5.0	7.5	7.5
	H1	-----	-----	-----	4.5	4.5	4.5	4.5
	H2	-----	-----	-----	2.0	2.0	2.0	2.0
	d	-----	-----	-----	0.6	0.6	0.8	0.8


CB Type




HE Type



FD Type



KD Type



Name


Specification Sheet – GT

Version


01

Page 14

**6. Taping Specification**




Name	Specification Sheet – GT		
Version	01		Page 15
STANDARD MANUAL			



$\phi = 5 \sim 8$   
 $F = 5.0$   
 TC Type Taping  
 $\phi = 8$   
 $F = 5.0$

TE Type Taping



$\phi = 16/18$   
 $F = 7.5$   
 TQ Type Taping

Name	Specification Sheet – GT		
Version	01		Page 16
STANDARD MANUAL			

**MAN YUE ELECTRONICS  
COMPANY LIMITED**

*ELECTROLYTIC  
CAPACITOR  
SPECIFICATION  
GT SERIES*

**SAMXON**

Remark: Maximum Taping Dimension: 18mm Diameter

Unit: mm

Item	Code	TU		TV	TC				TE	TQ
Diameter	D	5	6.3	8	5 / 6.3	8	10	12.5	8	16/18
Height	A	9~15	9~15	10~20	9~15	10~20	9~30	15~35	10~20	15~40
Lead Diameter	$d \pm 0.05$	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.5	0.8
Component Spacing	$P \pm 1.0$	12.7	12.7	12.7	12.7	12.7	12.7	15	12.7	30
Pitch of sprocket holes	$P_0 \pm 0.2$	12.7	12.7	12.7	12.7	12.7	12.7	15	12.7	15
Distance between centers of terminal	$P_1 \pm 0.5$	5.1	5.1	4.6	3.85	3.85	3.85	5.0	3.85	3.75
Feed hole center to component center	$P_2 \pm 1.0$	6.35						7.5	6.35	7.5
Distance between centers of component leads	$F_{-0.2}^{+0.8}$	2.5	2.5	3.5	5.0	5.0	5.0	5.0	5.0	7.5
Carrier tape width	$W_{-0.5}^{+1}$	18	18	18	18	18	18	18	18	18
Hold down tape width	$W_0$	7min						15min	7min	15min
Distance between the center of upper edge of carrier tape and sprocket hole	$W_1 \pm 0.5$	9	9	9	9	9	9	9	9	9
Distance between the upper edges of the carrier tape and the hold down tape	$W_2$	3max								
Distance between the abscissa and the bottom of the components body	$H_{-0.5}^{+0.75}$	18.5	18.5	18.5	18.5	20.0	18.5	18.5	18.5	18.5
Distance between the abscissa and the reference plane of the components with crimped leads	$H_0 \pm 0.5$	----	----	----	16	16	----	----	16	----
Cut off position of defectives	L	11 max								
Max. lateral deviation of the component body vertical to the tape plane	$\Delta h$	2 max								
Max. deviation of the component body in the tape plane	$\Delta P$	1.3 max								

Name	Specification Sheet – GT		
Version	01		Page   17
STANDARD MANUAL			

**7. List of “Environment-related Substances to be Controlled (‘Controlled Substances’)”**

The latest version of <Substances Prohibited as per Sony-SS-00259>

Substances	
Heavy metals	Cadmium and cadmium compounds
	Lead and lead compounds
	Mercury and mercury compounds
	Hexavalent chromium compounds
Chlorinated organic compounds	Polychlorinated biphenyls (PCB)
	Polychlorinated naphthalenes (PCN)
	Polychlorinated terphenyls (PCT)
	Short-chain chlorinated paraffins(SCCP)
	Other chlorinated organic compounds
Brominated organic compounds	Polybrominated biphenyls (PBB)
	Polybrominated diphenylethers(PBDE) (including decabromodiphenyl ether[DecaBDE])
	Other brominated organic compounds
Tributyltin compounds(TBT)	
Triphenyltin compounds(TPT)	
Asbestos	
Specific azo compounds	
Formaldehyde	
Polyvinyl chloride (PVC) and PVC blevds	
Beryllium oxide	
Beryllium copper	
Specific phthalates (DEHP,DBP,BBP,DINP,DIDP,DNOP,DNHP)	
Hydrofluorocarbon (HFC), Perfluorocarbon (PFC)	
Perfluorooctane sulfonates (PFOS)	
Specific Benzotriazole	

Name	Specification Sheet – GT		
Version	01		Page 18
STANDARD MANUAL			

<b>MAN YUE ELECTRONICS COMPANY LIMITED</b>	<i>ELECTROLYTIC CAPACITOR SPECIFICATION GT SERIES</i>	<b>SAMXON</b>
--	---	---------------

## Attachment: Application Guidelines

### 1. Circuit Design

#### 1.1 Operating Temperature and Frequency

Electrolytic capacitor electrical parameters are normally specified at 20°C temperature and 120Hz frequency. These parameters vary with changes in temperature and frequency. Circuit designers should take these changes into consideration.

##### (1) Effects of operating temperature on electrical parameters

- a) At higher temperatures, leakage current and capacitance increase while equivalent series resistance (ESR) decreases.
- b) At lower temperatures, leakage current and capacitance decrease while equivalent series resistance (ESR) increases.

##### (2) Effects of frequency on electrical parameters

- a) At higher frequencies capacitance and impedance decrease while  $\tan \delta$  increases.
- b) At lower frequencies, ripple current generated heat will rise due to an increase in equivalent series resistance (ESR).

#### 1.2 Operating Temperature and Life Expectancy

See the file: Life calculation of aluminum electrolytic capacitor

#### 1.3 Common Application Conditions to Avoid

The following misapplication load conditions will cause rapid deterioration to capacitor electrical parameters. In addition, rapid heating and gas generation within the capacitor can occur causing the pressure relief vent to operate and resultant leakage of electrolyte. Under Leaking electrolyte is combustible and electrically conductive.

Name	Specification Sheet – GT		
Version	01		Page 19
STANDARD MANUAL			

**(1) Reverse Voltage**

DC capacitors have polarity. Verify correct polarity before insertion. For circuits with changing or uncertain polarity, use DC bipolar capacitors. DC bipolar capacitors are not suitable for use in AC circuits.

**(2) Charge / Discharge Applications**

Standard capacitors are not suitable for use in repeating charge / discharge applications. For charge / discharge applications consult us and advise actual conditions.

**(3) Over voltage**

Do not apply voltages exceeding the maximum specified rated voltage. Voltages up to the surge voltage rating are acceptable for short periods of time. Ensure that the sum of the DC voltage and the superimposed AC ripple voltage does not exceed the rated voltage.

**(4) Ripple Current**

Do not apply ripple currents exceeding the maximum specified value. For high ripple current applications, use a capacitor designed for high ripple currents or contact us with your requirements.

Ensure that allowable ripple currents superimposed on low DC bias voltages do not cause reverse voltage conditions.

**1.4 Using Two or More Capacitors in Series or Parallel**

**(1) Capacitors Connected in Parallel**

The circuit resistance can closely approximate the series resistance of the capacitor causing an imbalance of ripple current loads within the capacitors. Careful design of wiring methods can minimize the possibility of excessive ripple currents applied to a capacitor.

**(2) Capacitors Connected in Series**

Normal DC leakage current differences among capacitors can cause voltage imbalances. The use of voltage divider shunt resistors with consideration to leakage current can prevent capacitor voltage imbalances.

**1.5 Capacitor Mounting Considerations**

**(1) Double Sided Circuit Boards**

Avoid wiring pattern runs, which pass between the mounted capacitor and the circuit board.

When dipping into a solder bath, excess solder may collect under the capacitor by capillary action and short circuit the anode and cathode terminals.

**(2) Circuit Board Hole Positioning**

The vinyl sleeve of the capacitor can be damaged if solder passes through a lead hole for subsequently processed parts. Special care when locating hole positions in proximity to capacitors is recommended.

**(3) Circuit Board Hole Spacing**

The circuit board holes spacing should match the capacitor lead wire spacing within the specified tolerances.

Incorrect spacing can cause excessive lead wire stress during the insertion process. This may result in premature capacitor failure due to short or open circuit, increased leakage current, or electrolyte leakage.

Name		Specification Sheet – GT	
Version	01		Page 20
STANDARD MANUAL			

**(4) Clearance for Case Mounted Pressure Relief vents**

Capacitors with case mounted pressure relief vents require sufficient clearance to allow for proper vent operation. The minimum clearances are dependent on capacitor diameters as proper vent operation. The minimum clearances are dependent on capacitor diameters as follows.

Φ 6.3~Φ 16mm:2mm minimum, Φ 18~Φ 35mm:3mm minimum, Φ 40mm or greater:5mm minimum.

**(5) Clearance for Seal Mounted Pressure Relief Vents**

A hole in the circuit board directly under the seal vent location is required to allow proper release of pressure.

**(6) Wiring Near the Pressure Relief Vent**

Avoid locating high voltage or high current wiring or circuit board paths above the pressure relief vent. Flammable, high temperature gas exceeding 100°C may be released which could dissolve the wire insulation and ignite.

**(7) Circuit Board patterns Under the Capacitor**

Avoid circuit board runs under the capacitor as electrolyte leakage could cause an electrical short.

**(8) Screw Terminal Capacitor Mounting**

Do not orient the capacitor with the screw terminal side of the capacitor facing downwards.

Tighten the terminal and mounting bracket screws within the torque range specified in the specification.

**1.6 Electrical Isolation of the Capacitor**

Completely isolate the capacitor as follows.

- (1) Between the cathode and the case (except for axially leaded B types) and between the anode terminal and other circuit paths
- (3) Between the extra mounting terminals (on T types) and the anode terminal, cathode terminal, and other circuit paths.

**1.7 The Product endurance should take the sample as the standard.****1.8 If conduct the load or shelf life test, must be collect date code within 6 months products sampling.****1.9 Capacitor Sleeve**

The vinyl sleeve or laminate coating is intended for marking and identification purposes and is not meant to electrically insulate the capacitor.

The sleeve may split or crack if immersed into solvents such as toluene or xylene, and then exposed to high temperatures.

**CAUTION!**

Always consider safety when designing equipment and circuits. Plan for worst case failure modes such as short circuits and open circuits which could occur during use.

- (1) Provide protection circuits and protection devices to allow safe failure modes.
- (2) Design redundant or secondary circuits where possible to assure continued operation in case of main circuit failure.

Name	Specification Sheet – GT		
Version	01		Page 21
STANDARD MANUAL			

## **2. Capacitor Handling Techniques**

### **2.1 Considerations Before Using**

- (1) Capacitors have a finite life. Do not reuse or recycle capacitors from used equipment.
- (2) Transient recovery voltage may be generated in the capacitor due to dielectric absorption. If required, this voltage can be discharged with a resistor with a value of about  $1k\Omega$ .
- (3) Capacitors stored for long periods of time may exhibit an increase in leakage current. This can be corrected by gradually applying rated voltage in series with a resistor of approximately  $1k\Omega$ .
- (4) If capacitors are dropped, they can be damaged mechanically or electrically. Avoid using dropped capacitors.
- (5) Dented or crushed capacitors should not be used. The seal integrity can be compromised and loss of electrolyte / shortened life can result.

### **2.2 Capacitor Insertion**

- \* (1) Verify the correct capacitance and rated voltage of the capacitor.
- \* (2) Verify the correct polarity of the capacitor before inserting.
- \* (3) Verify the correct hole spacing before insertion (land pattern size on chip type) to avoid stress on the terminals.
- (4) Ensure that the auto insertion equipment lead clinching operation does not stress the capacitor leads where they enter the seal of the capacitor.

For chip type capacitors, excessive mounting pressure can cause high leakage current, short circuit, or disconnection.

### **2.3 Manual Soldering**

- (1) Observe temperature and time soldering specifications or do not exceed temperatures of  $400\text{ }^{\circ}\text{C}$  for 3 seconds or less.
- (2) If lead wires must be formed to meet terminal board hole spacing, avoid stress on the lead wire where it enters the capacitor seal.
- (3) If a soldered capacitor must be removed and reinserted, avoid excessive stress to the capacitor leads.
- (4) Avoid touching the tip of the soldering iron to the capacitor, to prevent melting of the vinyl sleeve.

### **2.4 Flow Soldering**

- (1) Do not immerse the capacitor body into the solder bath as excessive internal pressure could result.
- (2) Observe proper soldering conditions (temperature, time, etc.) Do not exceed the specified limits.
- (3) Do not allow other parts or components to touch the capacitor during soldering.

### **2.5 Other Soldering Considerations**

Rapid temperature rises during the preheat operation and resin bonding operation can cause cracking of the capacitor vinyl sleeve.

For heat curing, do not exceed  $150\text{ }^{\circ}\text{C}$  for a maximum time of 2 minutes.

Name	Specification Sheet – GT		
Version	01		Page 22
STANDARD MANUAL			

**2.6 Capacitor Handling after Solder**

- (1). Avoid movement of the capacitor after soldering to prevent excessive stress on the lead wires where they enter the seal.
- (2). Do not use capacitor as a handle when moving the circuit board assembly.
- (3). Avoid striking the capacitor after assembly to prevent failure due to excessive shock.

**2.7 Circuit Board Cleaning**

- \* (1) Circuit boards can be immersed or ultrasonically cleaned using suitable cleaning solvents for up 5 minutes and up to 60°C maximum temperatures. The boards should be thoroughly rinsed and dried.  
The use of ozone depleting cleaning agents is not recommended in the interest of protecting the environment.
- \* (2) Avoid using the following solvent groups unless specifically allowed for in the specification;
  - Halogenated cleaning solvents: except for solvent resistant capacitor types, halogenated solvents can permeate the seal and cause internal capacitor corrosion and failure. For solvent resistant capacitors, carefully follow the temperature and time requirements of the specification. 1-1-1 trichloroethane should never be used on any aluminum electrolytic capacitor.
  - Alkali solvents : could attack and dissolve the aluminum case.
  - Petroleum based solvents: deterioration of the rubber seal could result.
  - Xylene : deterioration of the rubber seal could result.
  - Acetone : removal of the ink markings on the vinyl sleeve could result.
- \* (3) A thorough drying after cleaning is required to remove residual cleaning solvents which may be trapped between the capacitor and the circuit board. Avoid drying temperatures, which exceed the maximum rated temperature of the capacitor.
- \* (4) Monitor the contamination levels of the cleaning solvents during use by electrical conductivity, pH, specific gravity, or water content. Chlorine levels can rise with contamination and adversely affect the performance of the capacitor.

Please consult us for additional information about acceptable cleaning solvents or cleaning methods.

**2.8 Mounting Adhesives and Coating Agents**

When using mounting adhesives or coating agents to control humidity, avoid using materials containing halogenated solvents. Also, avoid the use of chloroprene based polymers.

After applying adhesives or coatings, dry thoroughly to prevent residual solvents from being trapped between the capacitor and the circuit board.

**3. Precautions for using capacitors****3.1 Environmental Conditions**

Capacitors should not be stored or used in the following environments.

- \* (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.
- \* (2) Direct contact with water, salt water, or oil.
- \* (3) High humidity conditions where water could condense on the capacitor.

Name		Specification Sheet – GT	
Version	01		Page 23
STANDARD MANUAL			

- \* (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, or ammonia.
- \* (5) Exposure to ozone, radiation, or ultraviolet rays.
- \* (6) Vibration and shock conditions exceeding specified requirements.

### 3.2 Electrical Precautions

- (1) Avoid touching the terminals of the capacitor as possible electric shock could result. The exposed aluminum case is not insulated and could also cause electric shock if touched.
- (2) Avoid short circuit the area between the capacitor terminals with conductive materials including liquids such as acids or alkaline solutions.

### 4. Emergency Procedures

- (1) If the pressure relief vent of the capacitor operates, immediately turn off the equipment and disconnect from the power source. This will minimize additional damage caused by the vaporizing electrolyte.
- (2) Avoid contact with the escaping electrolyte gas which can exceed 100°C temperatures.
  - If electrolyte or gas enters the eye, immediately flush the eyes with large amounts of water.
  - If electrolyte or gas is ingested by mouth, gargle with water.
  - If electrolyte contacts the skin, wash with soap and water.

### 5. Long Term Storage

Leakage current of a capacitor increases with long storage times. The aluminum oxide film deteriorates as a function of temperature and time. If used without reconditioning, an abnormally high current will be required to restore the oxide film. This current surge could cause the circuit or the capacitor to fail.

After one year, a capacitor should be reconditioned by applying rated voltage in series with a 1000 Ω current limiting resistor for a time period of 30 minutes.

If the expired date of products date code is over eighteen months, the products should be returned to confirmation.

#### 5.1 Environmental Conditions

The capacitor shall not be used in the following conditions:

- (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.
- (2) Direct contact with water, salt water, or oil.
- (3) High humidity conditions where water could condense on the capacitor.
- (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, or ammonia.
- (5) Exposure to ozone, radiation, or ultraviolet rays.
- (6) Vibration and shock conditions exceeding specified requirements.

### 6. Capacitor Disposal

When disposing of capacitors, use one of the following methods.

- \* Incinerate after crushing the capacitor or puncturing the can wall (to prevent explosion due to internal pressure rise). Capacitors should be incinerated at high temperatures to prevent the release of toxic gases such as chlorine from the polyvinyl chloride sleeve, etc.
- \* Dispose of as solid waste.

NOTE: Local laws may have specific disposal requirements, which must be followed.

Name		Specification Sheet – GT	
Version	01		Page 24
STANDARD MANUAL			